

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332142-935

Luminaire Tested: **S123DIW-S560D1320U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332142-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6544.4 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.1
10°-20°	204.0	3.1
20°-30°	301.4	4.6
30°-40°	352.0	5.4
40°-50°	353.9	5.4
50°-60°	310.9	4.8
60°-70°	231.6	3.5
70°-80°	132.0	2.0
80°-90°	42.0	0.6
90°-100°	54.2	0.8
100°-110°	258.2	3.9
110°-120°	620.2	9.5
120°-130°	789.8	12.1
130°-140°	843.9	12.9
140°-150°	789.1	12.1
150°-160°	636.5	9.7
160°-170°	410.8	6.3
170°-180°	141.6	2.2
0°-30°	577.6	8.8
0°-40°	929.7	14.2
0°-60°	1594.5	24.4
0°-90°	2000.1	30.6
90°-120°	932.6	14.3
90°-150°	3355.4	51.3
90°-180°	4544.0	69.4
0°-180°	6544.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	12	27	31	33	5
95°	68	25	34	42	42	83
105°	330	336	242	58	49	350
115°	619	626	636	646	651	611
125°	872	881	886	888	890	779
135°	1086	1093	1097	1100	1097	836
145°	1253	1261	1263	1265	1265	784
155°	1380	1378	1379	1384	1378	636
165°	1456	1453	1451	1459	1452	411
175°	1490	1485	1486	1493	1485	142
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	14.1	14.2	14.4	14.5	14.8	15.3	15.8	16.4	17.0	17.0
90°	1.1	3.5	6.0	8.5	10.9	13.8	17.0	20.1	23.3	26.6	27.6
92.5°	20.6	19.9	19.2	18.5	17.8	18.7	21.1	23.5	25.9	28.3	29.9
95°	67.5	57.4	47.4	37.3	27.2	23.5	26.2	28.9	31.6	34.4	36.1
97.5°	135.7	131.2	126.7	122.2	117.6	106.5	88.8	71.1	53.4	35.6	37.6
100°	187.1	192.0	196.9	201.8	206.8	190.0	151.7	113.3	74.9	36.5	38.5
102.5°	245.6	249.1	252.6	256.1	259.8	240.6	198.6	156.7	114.8	72.8	66.7
105°	329.9	332.6	335.4	338.0	340.7	331.1	308.8	286.7	264.6	242.5	198.9
107.5°	419.0	421.1	423.3	425.4	427.6	430.4	433.9	437.4	440.9	444.4	412.4
110°	478.3	480.3	482.2	484.1	486.1	488.4	491.2	493.9	496.6	499.3	491.2



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.9	536.7	538.5	540.3	542.0	544.2	547.0	549.7	552.4	555.1	555.3
115°	618.9	620.4	621.8	623.3	624.7	626.6	628.8	631.0	633.3	635.5	637.9
117.5°	700.2	702.0	703.8	705.6	707.4	708.9	710.0	711.2	712.3	713.4	715.4
120°	750.6	752.9	755.0	757.2	759.5	761.0	761.6	762.4	763.2	763.9	765.9
122.5°	802.0	803.8	805.6	807.4	809.3	810.6	811.6	812.5	813.5	814.4	815.8
125°	872.4	874.3	876.3	878.3	880.3	881.8	882.7	883.7	884.7	885.7	886.1
127.5°	940.6	942.5	944.5	946.5	948.5	950.0	951.2	952.4	953.6	954.8	955.5
130°	983.1	985.1	987.1	989.0	991.0	992.5	993.4	994.5	995.4	996.3	997.4
132.5°	1023.8	1025.8	1027.8	1029.8	1031.7	1033.1	1033.9	1034.7	1035.4	1036.2	1037.2
135°	1086.1	1087.5	1089.0	1090.5	1092.0	1093.2	1094.2	1095.2	1096.1	1097.2	1097.9
137.5°	1139.2	1141.1	1143.0	1144.8	1146.7	1147.9	1148.4	1149.0	1149.5	1150.0	1151.2
140°	1174.7	1176.1	1177.6	1179.1	1180.5	1181.6	1182.4	1183.1	1183.9	1184.6	1185.6
142.5°	1207.4	1208.8	1210.4	1211.9	1213.3	1214.4	1215.1	1215.9	1216.6	1217.4	1218.1
145°	1253.3	1255.0	1256.7	1258.4	1260.2	1261.2	1261.7	1262.2	1262.7	1263.2	1263.7
147.5°	1296.4	1297.5	1298.6	1299.8	1301.0	1301.7	1302.3	1302.7	1303.2	1303.7	1304.2
150°	1323.0	1323.7	1324.5	1325.2	1325.9	1326.5	1327.1	1327.5	1328.0	1328.5	1329.0
152.5°	1346.9	1347.2	1347.6	1347.9	1348.2	1348.6	1348.9	1349.2	1349.4	1349.8	1350.7
155°	1380.5	1380.1	1379.6	1379.1	1378.5	1378.5	1378.7	1379.0	1379.2	1379.4	1380.7
157.5°	1406.7	1406.6	1406.6	1406.5	1406.4	1406.4	1406.1	1405.8	1405.6	1405.3	1406.8
160°	1422.6	1422.4	1422.1	1421.9	1421.6	1421.4	1421.2	1420.9	1420.6	1420.4	1421.9
162.5°	1437.7	1437.0	1436.4	1435.7	1435.1	1434.7	1434.4	1434.2	1433.9	1433.7	1435.4
165°	1455.9	1455.1	1454.3	1453.6	1452.9	1452.4	1452.2	1451.9	1451.6	1451.4	1453.4
167.5°	1470.0	1469.0	1468.0	1467.1	1466.0	1465.6	1465.6	1465.6	1465.6	1465.6	1467.6
170°	1478.0	1477.0	1476.0	1475.1	1474.0	1473.5	1473.5	1473.5	1473.5	1473.5	1475.5
172.5°	1483.3	1482.1	1480.9	1479.7	1478.6	1478.1	1478.3	1478.5	1478.7	1478.9	1480.8
175°	1490.1	1488.9	1487.7	1486.4	1485.2	1484.7	1485.0	1485.2	1485.5	1485.7	1487.5
177.5°	1491.9	1490.9	1490.0	1489.0	1488.0	1487.6	1487.8	1488.0	1488.2	1488.4	1490.0
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	17.0	17.1	17.2	17.3	17.4	17.6	17.7	17.7
90°	28.5	29.5	30.5	31.3	31.8	32.2	32.7	33.2
92.5°	31.5	33.1	34.6	35.6	35.9	36.2	36.4	36.8
95°	37.8	39.5	41.2	42.1	42.1	42.1	42.1	42.1
97.5°	39.6	41.6	43.5	44.6	44.9	45.1	45.4	45.6
100°	40.5	42.4	44.4	45.5	45.7	46.0	46.2	46.5
102.5°	60.6	54.5	48.5	45.6	46.1	46.5	46.9	47.4
105°	155.3	111.8	68.3	46.8	47.3	47.7	48.2	48.7
107.5°	380.6	348.6	316.7	284.3	251.5	218.6	185.8	153.0
110°	483.0	474.9	466.8	445.1	410.0	374.8	339.7	304.4



TEST NUMBER: P332142-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	555.4	555.5	555.7	552.1	544.6	537.2	529.8	522.4
115°	640.4	642.8	645.3	647.0	648.0	649.0	650.0	651.0
117.5°	717.4	719.3	721.3	722.4	722.6	722.7	723.0	723.2
120°	767.8	769.8	771.8	772.7	772.7	772.7	772.7	772.7
122.5°	817.2	818.6	819.9	820.7	820.9	821.0	821.3	821.5
125°	886.7	887.2	887.6	888.1	888.6	889.2	889.6	890.1
127.5°	956.3	957.1	957.9	958.0	957.6	957.1	956.6	956.1
130°	998.3	999.4	1000.3	1000.6	1000.1	999.6	999.1	998.6
132.5°	1038.2	1039.2	1040.2	1040.3	1039.7	1039.0	1038.3	1037.6
135°	1098.6	1099.3	1100.1	1100.1	1099.3	1098.6	1097.9	1097.2
137.5°	1152.4	1153.6	1154.8	1155.1	1154.6	1154.2	1153.7	1153.1
140°	1186.5	1187.6	1188.5	1188.8	1188.3	1187.7	1187.3	1186.8
142.5°	1218.9	1219.7	1220.6	1220.6	1219.9	1219.2	1218.5	1217.8
145°	1264.2	1264.6	1265.2	1265.4	1265.4	1265.4	1265.4	1265.4
147.5°	1304.7	1305.2	1305.7	1305.4	1304.2	1303.1	1302.0	1300.8
150°	1329.5	1330.0	1330.5	1330.3	1329.6	1328.9	1328.2	1327.4
152.5°	1351.5	1352.5	1353.3	1353.2	1352.0	1350.9	1349.8	1348.7
155°	1381.9	1383.1	1384.4	1384.2	1382.8	1381.3	1379.8	1378.4
157.5°	1408.3	1409.8	1411.3	1411.0	1409.1	1407.2	1405.2	1403.3
160°	1423.3	1424.9	1426.3	1426.2	1424.4	1422.7	1421.0	1419.3
162.5°	1437.0	1438.7	1440.4	1440.5	1438.9	1437.4	1435.9	1434.3
165°	1455.3	1457.3	1459.3	1459.4	1457.7	1456.0	1454.2	1452.5
167.5°	1469.6	1471.4	1473.4	1473.4	1471.4	1469.6	1467.6	1465.6
170°	1477.5	1479.5	1481.4	1481.4	1479.5	1477.5	1475.5	1473.5
172.5°	1482.8	1484.8	1486.8	1486.6	1484.5	1482.3	1480.1	1478.0
175°	1489.2	1490.9	1492.6	1492.5	1490.6	1488.6	1486.6	1484.6
177.5°	1491.5	1493.1	1494.7	1494.5	1492.5	1490.6	1488.6	1486.6
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1

(END OF REPORT)