

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332144-935

Luminaire Tested: **S123DIW-S560D1535U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332144-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D1535U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7342.6 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15				
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	11				
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10				
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	15	13	12	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	10	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.0	0.9
10°-20°	215.0	2.9
20°-30°	360.8	4.9
30°-40°	408.6	5.6
40°-50°	366.4	5.0
50°-60°	295.7	4.0
60°-70°	206.0	2.8
70°-80°	108.3	1.5
80°-90°	31.3	0.4
90°-100°	63.0	0.9
100°-110°	300.2	4.1
110°-120°	721.1	9.8
120°-130°	918.3	12.5
130°-140°	981.1	13.4
140°-150°	917.5	12.5
150°-160°	740.1	10.1
160°-170°	477.6	6.5
170°-180°	164.6	2.2
0°-30°	642.9	8.8
0°-40°	1051.4	14.3
0°-60°	1713.5	23.3
0°-90°	2059.1	28.0
90°-120°	1084.3	14.8
90°-150°	3901.2	53.1
90°-180°	5283.0	72.0
0°-180°	7342.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	27
90°	39	1	39	1	39	19
95°	49	78	49	78	49	41
105°	57	384	57	384	57	129
115°	757	720	757	720	757	699
125°	1035	1014	1035	1014	1035	924
135°	1276	1263	1276	1263	1276	984
145°	1471	1457	1471	1457	1471	918
155°	1603	1605	1603	1605	1603	739
165°	1689	1693	1689	1693	1689	477
175°	1726	1732	1726	1732	1726	164
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	15.7	15.0	15.2	15.3	14.9	15.0	15.1	15.1	15.2	15.2	14.6
90°	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1	32.0	30.9	27.2
92.5°	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6	34.8	33.0	30.1
95°	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.8
97.5°	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1	43.7	41.4	38.1
100°	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0	44.8	42.4	39.1
102.5°	55.1	54.6	54.1	53.6	53.0	51.7	49.3	47.0	44.8	42.4	39.1
105°	56.7	56.1	55.5	54.9	54.3	53.0	51.7	49.3	47.0	44.8	42.4
107.5°	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4	479.6	516.7	552.6
110°	354.0	394.9	435.8	476.6	517.5	552.8	592.2	631.6	671.1	710.5	750.4



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8	645.6	645.4	642.2
115°	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6	741.7	738.8	736.2
117.5°	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1	831.7	829.5	828.1
120°	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8	890.4	888.1	887.3
122.5°	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0	948.5	946.8	945.7
125°	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9	1030.4	1029.8	1028.6
127.5°	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9	1110.9	1110.1	1108.7
130°	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7	1159.6	1158.5	1157.4
132.5°	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1	1205.9	1204.8	1203.9
135°	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6	1274.5
137.5°	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9	1338.5	1337.1	1336.5
140°	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6	1378.5	1377.3	1376.4
142.5°	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2	1416.3	1415.4	1414.5
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8	1469.2	1468.7	1468.1
147.5°	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9	1516.4	1515.8	1515.2
150°	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8	1545.2	1544.6	1544.0
152.5°	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4	1570.4	1569.3	1569.0
155°	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7	1605.2	1603.8	1603.5
157.5°	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4	1635.6	1633.9	1634.3
160°	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9	1653.2	1651.5	1651.7
162.5°	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8	1668.9	1666.9	1667.2
165°	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0	1689.8	1687.5	1687.8
167.5°	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0	1704.0
170°	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2	1713.2
172.5°	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0	1721.7	1719.4	1719.2
175°	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4	1729.4	1727.4	1727.1
177.5°	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1	1732.3	1730.5	1730.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	14.5	13.9	12.4	10.8	9.6	8.3	7.7	6.6	6.6	7.2	7.5
90°	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3	4.1	7.0	9.9
92.5°	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9	23.2	22.3	21.5
95°	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5	66.8	55.1	43.3
97.5°	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8	152.6	147.3	142.0
100°	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6	223.3	228.9	234.7
102.5°	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5	289.6	293.8	297.8
105°	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6	386.8	389.9	393.0
107.5°	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1	489.6	492.1	494.6
110°	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0	558.4	560.6	562.9





TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0	624.1	626.1	628.2
115°	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5	721.3	723.0	724.7
117.5°	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0	816.1	818.2	820.4
120°	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7	875.3	877.9	880.5
122.5°	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5	934.5	936.7	938.7
125°	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3	1016.6	1018.9	1021.1
127.5°	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6	1095.9	1098.2	1100.4
130°	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0	1145.3	1147.6	1149.9
132.5°	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4	1192.7	1195.0	1197.2
135°	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7	1264.5	1266.2	1267.9
137.5°	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5	1326.7	1328.9	1331.0
140°	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7	1367.4	1369.2	1370.9
142.5°	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8	1405.5	1407.2	1408.9
145°	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1	1459.1	1461.1	1463.1
147.5°	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3	1508.6	1509.9	1511.2
150°	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2	1539.0	1539.9	1540.8
152.5°	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0	1566.4	1566.8	1567.2
155°	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1	1604.6	1604.0	1603.4
157.5°	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5	1635.5	1635.4	1635.3
160°	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1	1653.7	1653.5	1653.2
162.5°	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5	1670.8	1670.1	1669.3
165°	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6	1691.8	1690.9	1690.1
167.5°	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1	1708.0	1706.8	1705.7
170°	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4	1717.3	1716.1	1714.9
172.5°	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6	1723.2	1721.8	1720.5
175°	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5	1731.1	1729.7	1728.3
177.5°	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6	1733.5	1732.3	1731.2
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	7.8	8.8	9.2	10.2	10.7	11.7	12.0	11.6	11.9	12.9	12.1
90°	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1	34.4	35.5	36.3
92.5°	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6	38.5	40.3	41.3
95°	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9	45.9	47.9	48.9
97.5°	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1	48.3	50.6	51.9
100°	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0	49.3	51.7	53.0
102.5°	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5	63.5	56.3	53.0
105°	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6	130.0	79.4	54.3
107.5°	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4	405.3	368.2	330.5
110°	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6	552.2	542.8	517.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8	645.9	646.1	641.9
115°	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6	747.4	750.3	752.3
117.5°	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1	836.3	838.6	839.9
120°	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8	895.0	897.3	898.5
122.5°	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0	951.7	953.3	954.2
125°	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9	1031.5	1032.0	1032.6
127.5°	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9	1112.8	1113.7	1113.9
130°	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7	1161.9	1163.0	1163.3
132.5°	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1	1208.2	1209.4	1209.5
135°	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0
137.5°	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9	1341.3	1342.6	1343.0
140°	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6	1380.7	1381.8	1382.2
142.5°	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2	1418.2	1419.0	1419.1
145°	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8	1470.4	1470.9	1471.3
147.5°	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9	1517.5	1518.1	1517.7
150°	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8	1546.4	1546.9	1546.8
152.5°	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4	1572.4	1573.5	1573.3
155°	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7	1608.1	1609.6	1609.4
157.5°	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4	1639.1	1640.8	1640.5
160°	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9	1656.6	1658.3	1658.2
162.5°	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8	1672.8	1674.6	1674.7
165°	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0	1694.4	1696.7	1696.8
167.5°	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1
170°	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4
172.5°	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0	1726.3	1728.5	1728.5
175°	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4	1733.4	1735.4	1735.3
177.5°	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1	1735.9	1737.8	1737.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	12.1	12.2	12.1	12.0	12.1	12.2	12.1	12.1	12.9	11.9	11.6
90°	36.9	37.5	38.1	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1
92.5°	41.7	42.0	42.4	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9
97.5°	52.2	52.4	52.8	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1
100°	53.2	53.5	53.8	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0
102.5°	53.6	54.1	54.6	55.1	54.6	54.1	53.6	53.0	56.3	63.5	70.5
105°	54.9	55.5	56.1	56.7	56.1	55.5	54.9	54.3	79.4	130.0	180.6
107.5°	292.4	254.2	216.0	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4
110°	476.6	435.8	394.9	354.0	394.9	435.8	476.6	517.5	542.8	552.2	561.6



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	633.2	624.6	616.0	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8
115°	753.5	754.6	755.7	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6
117.5°	840.1	840.3	840.6	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1
120°	898.5	898.5	898.5	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8
122.5°	954.4	954.6	954.8	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0
125°	1033.2	1033.7	1034.3	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9
127.5°	1113.4	1112.8	1112.2	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9
130°	1162.8	1162.2	1161.6	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7
132.5°	1208.8	1208.0	1207.1	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1
135°	1278.2	1277.3	1276.4	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3
137.5°	1342.5	1341.9	1341.3	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9
140°	1381.6	1381.0	1380.4	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6
142.5°	1418.3	1417.5	1416.7	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8
147.5°	1516.4	1515.1	1513.7	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9
150°	1545.9	1545.1	1544.2	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8
152.5°	1572.0	1570.6	1569.3	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4
155°	1607.7	1605.9	1604.2	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7
157.5°	1638.3	1636.1	1633.8	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4
160°	1656.1	1654.2	1652.2	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9
162.5°	1673.0	1671.2	1669.5	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8
165°	1694.8	1692.8	1690.7	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0
167.5°	1710.8	1708.6	1706.2	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6
170°	1720.1	1717.8	1715.5	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8
172.5°	1726.0	1723.5	1720.9	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0
175°	1732.9	1730.7	1728.4	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4
177.5°	1735.3	1733.0	1730.7	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	12.0	11.7	10.7	10.2	9.2	8.8	7.8	7.5	7.2	6.6	6.6
90°	32.0	30.9	27.2	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3
92.5°	34.8	33.0	30.1	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9
95°	41.9	39.9	36.8	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5
97.5°	43.7	41.4	62.1	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8
100°	44.8	42.4	87.1	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6
102.5°	77.6	84.7	133.5	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5
105°	231.3	281.9	307.6	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6
107.5°	479.6	516.7	512.6	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1
110°	571.1	580.5	577.4	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.6	645.4	642.2	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0
115°	741.7	738.8	736.2	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5
117.5°	831.7	829.5	828.1	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0
120°	890.4	888.1	887.3	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7
122.5°	948.5	946.8	945.7	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5
125°	1030.4	1029.8	1028.6	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3
127.5°	1110.9	1110.1	1108.7	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6
130°	1159.6	1158.5	1157.4	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0
132.5°	1205.9	1204.8	1203.9	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4
135°	1276.4	1275.6	1274.5	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7
137.5°	1338.5	1337.1	1336.5	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5
140°	1378.5	1377.3	1376.4	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7
142.5°	1416.3	1415.4	1414.5	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8
145°	1469.2	1468.7	1468.1	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1
147.5°	1516.4	1515.8	1515.2	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3
150°	1545.2	1544.6	1544.0	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2
152.5°	1570.4	1569.3	1569.0	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0
155°	1605.2	1603.8	1603.5	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1
157.5°	1635.6	1633.9	1634.3	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5
160°	1653.2	1651.5	1651.7	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1
162.5°	1668.9	1666.9	1667.2	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5
165°	1689.8	1687.5	1687.8	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6
167.5°	1706.2	1704.0	1704.0	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1
170°	1715.5	1713.2	1713.2	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4
172.5°	1721.7	1719.4	1719.2	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6
175°	1729.4	1727.4	1727.1	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5
177.5°	1732.3	1730.5	1730.3	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.7	8.3	9.6	10.8	12.4	13.9	14.5	14.6	15.2	15.2	15.1
90°	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1
92.5°	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6
95°	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9
97.5°	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1
100°	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0
102.5°	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5
105°	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6
107.5°	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4
110°	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6





TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8
115°	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6
117.5°	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1
120°	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8
122.5°	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0
125°	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9
127.5°	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9
130°	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7
132.5°	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1
135°	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3
137.5°	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9
140°	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6
142.5°	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2
145°	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8
147.5°	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9
150°	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8
152.5°	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4
155°	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7
157.5°	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4
160°	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9
162.5°	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8
165°	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0
167.5°	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6
170°	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8
172.5°	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0
175°	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4
177.5°	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	15.1	15.0	14.9	15.3	15.2	15.0	15.7
90°	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332144-935

CATALOG NUMBER: S123DIW-S560D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)