

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332161-935

Luminaire Tested: **S123DIW-S775D755U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332161-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D755U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4984.7 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11286	11286	11286
5°	11339	11182	11261
10°	11262	11086	11154
15°	11131	10961	10981
20°	10977	10781	10791
25°	10772	10568	10546
30°	10544	10331	10253
35°	10307	10081	9950
40°	10058	9805	9653
45°	9785	9552	9319
50°	9512	9239	8982
55°	9154	8916	8646
60°	8792	8540	8269
65°	8474	8130	7875
70°	8003	7660	7320
75°	7311	7049	6750
80°	6595	6316	6261
85°	5780	5570	5348



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.0
10°-20°	278.9	5.6
20°-30°	411.9	8.3
30°-40°	481.2	9.7
40°-50°	483.8	9.7
50°-60°	425.0	8.5
60°-70°	316.6	6.4
70°-80°	180.4	3.6
80°-90°	54.2	1.1
90°-100°	53.0	1.1
100°-110°	158.6	3.2
110°-120°	269.8	5.4
120°-130°	354.9	7.1
130°-140°	398.9	8.0
140°-150°	392.1	7.9
150°-160°	330.1	6.6
160°-170°	219.7	4.4
170°-180°	76.9	1.5
0°-30°	789.6	15.8
0°-40°	1270.8	25.5
0°-60°	2179.5	43.7
0°-90°	2730.7	54.8
90°-120°	481.4	9.7
90°-150°	1627.3	32.6
90°-180°	2254.0	45.2
0°-180°	4984.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1049	1045	1035	1043	1042	99
15°	999	995	984	990	985	281
25°	907	901	890	890	888	418
35°	784	779	767	762	757	490
45°	643	639	628	617	612	496
55°	488	486	475	466	461	437
65°	333	328	319	312	309	328
75°	176	172	170	165	162	188
85°	47	45	45	43	43	51
90°	1	7	15	18	19	5
95°	38	42	47	50	50	42
105°	144	145	151	151	152	154
115°	272	273	272	273	272	269
125°	398	399	398	396	393	354
135°	516	519	519	516	515	397
145°	626	627	629	628	626	391
155°	716	716	717	719	715	330
165°	780	778	778	782	778	220
175°	812	809	809	812	808	77
180°	814	814	814	814	814	



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1052.1	1051.5	1050.9	1050.2	1049.6	1048.4	1046.5	1044.8	1043.0	1041.3	1042.8
5°	1049.4	1048.4	1047.4	1046.4	1045.3	1043.8	1041.6	1039.4	1037.2	1034.9	1037.0
7.5°	1039.1	1038.1	1037.1	1036.1	1035.1	1033.5	1031.1	1028.9	1026.6	1024.3	1026.1
10°	1030.4	1029.4	1028.5	1027.4	1026.5	1024.7	1022.0	1019.4	1016.8	1014.3	1016.1
12.5°	1018.9	1018.0	1017.3	1016.4	1015.5	1013.9	1011.5	1009.0	1006.6	1004.1	1005.5
15°	998.9	998.1	997.3	996.5	995.7	994.0	991.4	988.8	986.2	983.6	985.2
17.5°	975.6	974.6	973.5	972.5	971.5	969.7	967.1	964.4	961.8	959.2	960.4
20°	958.3	957.1	956.0	954.8	953.6	951.6	949.0	946.4	943.8	941.2	942.0
22.5°	938.8	937.6	936.4	935.2	934.0	932.1	929.5	927.0	924.4	921.7	922.4
25°	907.0	905.8	904.6	903.4	902.2	900.3	897.6	895.0	892.4	889.8	890.0
27.5°	872.9	871.7	870.6	869.4	868.2	866.3	863.4	860.7	857.8	855.0	855.1
30°	848.3	847.3	846.4	845.3	844.3	842.4	839.6	836.8	834.1	831.2	831.2
32.5°	823.8	822.5	821.1	819.8	818.6	816.8	814.6	812.4	810.3	808.1	807.0
35°	784.4	783.2	782.0	780.8	779.5	777.7	775.0	772.4	769.8	767.2	766.0
37.5°	743.9	742.4	740.9	739.3	737.9	735.8	733.1	730.5	727.8	725.2	723.8
40°	715.8	714.6	713.4	712.2	711.0	709.0	706.2	703.4	700.6	697.8	696.2
42.5°	687.7	686.3	684.9	683.6	682.3	680.2	677.3	674.5	671.8	668.9	667.4
45°	642.8	642.0	641.2	640.4	639.6	637.9	635.2	632.7	630.1	627.5	625.1
47.5°	598.2	597.1	595.9	594.8	593.6	591.8	589.4	586.9	584.4	582.0	579.6
50°	568.0	567.0	565.9	565.0	564.0	562.1	559.6	557.0	554.3	551.7	549.6
52.5°	536.2	535.5	534.9	534.2	533.5	531.8	529.0	526.2	523.5	520.7	518.8
55°	487.8	487.5	487.3	487.2	486.9	485.5	482.9	480.4	477.7	475.1	472.9
57.5°	441.6	440.9	440.2	439.5	438.9	437.5	435.4	433.3	431.2	429.1	427.1
60°	408.4	408.2	408.0	407.8	407.6	406.3	403.9	401.5	399.1	396.7	394.9
62.5°	378.8	378.3	377.8	377.3	376.8	375.3	372.9	370.5	368.1	365.7	363.9
65°	332.7	331.7	330.6	329.7	328.6	327.2	325.1	323.1	321.2	319.2	317.5
67.5°	283.8	282.9	282.1	281.1	280.3	279.1	277.6	276.0	274.5	273.0	271.6
70°	254.3	253.0	251.8	250.6	249.4	248.2	247.0	245.8	244.6	243.4	242.0
72.5°	223.3	222.3	221.4	220.6	219.7	218.6	217.2	215.9	214.5	213.1	211.9
75°	175.8	175.0	174.2	173.4	172.6	171.9	171.3	170.7	170.0	169.5	168.5
77.5°	133.8	133.4	132.9	132.5	132.0	131.5	130.7	130.0	129.3	128.5	127.9
80°	106.4	105.8	105.2	104.6	104.0	103.5	103.1	102.7	102.3	101.9	101.7
82.5°	79.7	79.6	79.5	79.3	79.2	79.1	79.0	79.0	78.9	78.8	78.4
85°	46.8	46.5	46.1	45.7	45.3	45.1	45.1	45.1	45.1	45.1	44.7
87.5°	18.9	18.7	18.5	18.3	18.1	18.1	18.3	18.5	18.7	18.9	18.9
90°	0.6	2.1	3.4	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.5	16.4	17.4	18.3	19.3	20.3	21.4	22.5	23.5	24.5	25.0
95°	37.7	38.7	39.7	40.7	41.7	42.7	43.9	45.0	46.1	47.3	47.9
97.5°	67.0	67.7	68.4	69.2	69.9	70.7	71.5	72.3	73.2	74.0	74.6
100°	86.9	87.7	88.6	89.5	90.3	91.1	91.8	92.6	93.2	93.9	94.4
102.5°	109.9	110.5	111.0	111.4	111.9	112.7	113.7	114.6	115.5	116.4	116.8
105°	143.8	144.0	144.4	144.6	144.9	145.7	147.0	148.3	149.6	150.8	150.8
107.5°	183.1	183.3	183.5	183.7	183.8	184.2	184.7	185.2	185.7	186.2	186.7
110°	207.7	208.0	208.3	208.5	208.8	209.1	209.4	209.7	210.0	210.3	210.9



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	233.2	233.4	233.6	233.8	233.9	234.0	234.1	234.2	234.2	234.3	235.0
115°	271.6	272.0	272.4	272.9	273.3	273.4	273.1	272.9	272.5	272.2	272.4
117.5°	310.2	310.5	310.7	311.1	311.3	311.3	310.9	310.6	310.2	309.8	309.8
120°	334.2	335.1	336.0	336.8	337.7	337.7	337.0	336.3	335.6	334.8	334.8
122.5°	359.3	359.9	360.5	361.2	361.8	361.9	361.5	361.2	360.8	360.4	360.1
125°	397.5	398.0	398.4	398.8	399.2	399.2	399.0	398.7	398.4	398.1	397.6
127.5°	432.7	433.7	434.6	435.5	436.4	436.7	436.4	436.1	435.8	435.5	434.6
130°	456.3	457.4	458.6	459.7	460.8	461.2	460.8	460.4	459.9	459.5	458.9
132.5°	479.8	481.0	482.1	483.2	484.4	484.7	484.5	484.1	483.8	483.5	482.8
135°	515.7	516.6	517.5	518.3	519.1	519.5	519.4	519.2	519.1	518.9	518.3
137.5°	549.0	549.7	550.4	551.1	551.8	552.3	552.7	553.1	553.5	553.8	553.2
140°	572.0	572.7	573.4	574.1	574.8	575.2	575.4	575.5	575.7	575.8	575.7
142.5°	593.0	593.7	594.3	595.0	595.7	596.2	596.5	596.8	597.0	597.3	597.1
145°	625.7	625.9	626.2	626.5	626.8	627.2	627.6	628.0	628.4	628.9	628.7
147.5°	654.3	654.8	655.3	655.8	656.3	656.8	657.2	657.5	658.0	658.4	658.4
150°	674.2	674.5	674.8	675.1	675.4	675.6	675.9	676.2	676.5	676.7	676.7
152.5°	690.6	691.0	691.4	691.8	692.2	692.4	692.6	692.8	692.9	693.1	693.4
155°	716.4	716.4	716.4	716.4	716.4	716.4	716.6	716.8	716.9	717.0	717.6
157.5°	738.4	738.2	738.0	737.9	737.7	737.7	737.8	737.9	738.0	738.1	738.7
160°	752.2	751.9	751.7	751.3	751.1	750.9	750.9	750.9	750.9	750.9	751.7
162.5°	764.5	764.1	763.6	763.3	762.8	762.8	762.8	762.9	763.1	763.2	763.9
165°	780.3	779.9	779.5	779.0	778.6	778.3	778.3	778.3	778.3	778.3	779.2
167.5°	793.0	792.4	791.9	791.3	790.7	790.5	790.6	790.7	790.8	790.9	791.8
170°	800.1	799.5	799.0	798.4	797.8	797.5	797.5	797.5	797.5	797.5	798.6
172.5°	805.7	805.2	804.6	804.0	803.5	803.1	803.1	803.1	803.1	803.1	804.1
175°	811.6	811.1	810.5	809.9	809.3	809.1	809.1	809.1	809.1	809.1	809.9
177.5°	814.1	813.6	813.1	812.7	812.3	812.0	812.0	812.0	812.0	812.0	812.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1044.5	1046.1	1047.7	1048.4	1048.3	1048.1	1047.9	1047.8
5°	1039.0	1040.9	1043.0	1043.8	1043.4	1043.0	1042.6	1042.2
7.5°	1027.9	1029.8	1031.6	1032.3	1032.1	1031.8	1031.6	1031.4
10°	1017.9	1019.6	1021.4	1022.2	1021.7	1021.3	1021.0	1020.5
12.5°	1006.8	1008.1	1009.4	1010.0	1009.7	1009.4	1009.3	1009.0
15°	986.8	988.3	990.0	990.2	988.9	987.7	986.6	985.4
17.5°	961.5	962.6	963.7	964.1	963.6	963.2	962.8	962.3
20°	942.8	943.6	944.4	944.5	943.9	943.3	942.7	942.1
22.5°	923.0	923.7	924.3	924.2	923.5	922.7	922.0	921.2
25°	890.2	890.4	890.6	890.4	889.8	889.2	888.6	888.0
27.5°	855.3	855.5	855.7	855.3	854.6	853.9	853.1	852.3
30°	831.2	831.2	831.2	830.5	829.1	827.7	826.3	824.9
32.5°	805.9	804.8	803.7	802.7	801.9	801.2	800.4	799.7
35°	764.8	763.6	762.4	761.3	760.3	759.3	758.3	757.2
37.5°	722.3	720.8	719.5	718.4	717.7	717.1	716.4	715.8
40°	694.6	693.0	691.4	690.2	689.4	688.5	687.8	687.0
42.5°	665.7	664.1	662.5	661.3	660.6	659.7	658.9	658.1
45°	622.7	620.3	617.9	616.1	615.2	614.2	613.1	612.2
47.5°	577.3	575.0	572.6	570.9	570.1	569.2	568.3	567.4
50°	547.3	545.1	542.9	541.2	540.0	538.8	537.6	536.4
52.5°	516.9	515.1	513.2	511.7	510.5	509.3	508.1	506.9
55°	470.7	468.5	466.3	464.7	463.6	462.7	461.7	460.7
57.5°	425.2	423.3	421.3	419.7	418.5	417.4	416.2	415.1
60°	393.0	391.2	389.4	388.1	387.0	386.1	385.0	384.1
62.5°	362.1	360.2	358.4	357.2	356.5	355.9	355.2	354.5
65°	315.9	314.4	312.7	311.6	311.0	310.4	309.8	309.2
67.5°	270.2	268.8	267.3	266.2	265.4	264.6	263.7	262.9
70°	240.6	239.2	237.8	236.6	235.6	234.6	233.6	232.6
72.5°	210.6	209.4	208.2	207.2	206.7	206.2	205.7	205.2
75°	167.5	166.5	165.5	164.7	164.1	163.5	162.9	162.3
77.5°	127.2	126.5	125.8	125.5	125.5	125.5	125.5	125.5
80°	101.5	101.3	101.1	101.0	101.0	101.0	101.0	101.0
82.5°	78.1	77.7	77.3	77.1	77.0	76.8	76.6	76.5
85°	44.3	43.9	43.5	43.3	43.3	43.3	43.3	43.3
87.5°	18.9	18.8	18.8	18.8	18.8	18.9	18.9	18.9
90°	16.4	17.0	17.7	18.0	18.3	18.6	18.9	19.2
92.5°	25.5	25.9	26.3	26.5	26.3	26.2	26.0	25.8
95°	48.4	49.0	49.6	49.9	49.9	49.9	49.9	49.9
97.5°	75.3	75.9	76.6	76.9	76.9	76.8	76.7	76.7
100°	94.8	95.2	95.7	96.0	96.3	96.6	96.9	97.1
102.5°	117.3	117.7	118.1	118.3	118.3	118.2	118.1	118.1
105°	150.8	150.8	150.8	150.9	151.3	151.5	151.8	152.1
107.5°	187.1	187.6	188.0	188.2	188.0	187.9	187.7	187.5
110°	211.4	212.0	212.5	212.7	212.4	212.1	211.8	211.5



TEST NUMBER: P332161-935

CATALOG NUMBER: S123DIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.7	236.3	237.0	237.3	237.3	237.2	237.1	237.1
115°	272.5	272.7	272.9	272.9	272.7	272.5	272.4	272.2
117.5°	309.8	309.7	309.7	309.5	309.1	308.7	308.3	307.9
120°	334.6	334.4	334.3	334.1	333.8	333.6	333.2	332.9
122.5°	359.7	359.3	359.0	358.6	358.2	357.7	357.4	357.0
125°	397.0	396.4	395.9	395.3	394.8	394.2	393.6	393.0
127.5°	433.9	433.1	432.3	431.5	430.9	430.2	429.6	429.0
130°	458.4	457.8	457.2	456.4	455.5	454.4	453.5	452.5
132.5°	482.2	481.5	480.8	480.1	479.3	478.5	477.8	477.0
135°	517.8	517.2	516.7	516.3	515.9	515.7	515.4	515.1
137.5°	552.6	552.0	551.5	550.9	550.4	549.7	549.2	548.7
140°	575.5	575.4	575.2	574.6	573.7	572.7	571.7	570.7
142.5°	597.0	596.8	596.7	596.2	595.5	594.7	593.9	593.1
145°	628.5	628.4	628.3	627.9	627.3	626.8	626.2	625.7
147.5°	658.4	658.4	658.4	658.0	657.1	656.3	655.4	654.5
150°	676.7	676.7	676.7	676.3	675.5	674.7	673.8	673.0
152.5°	693.6	693.8	694.1	693.8	693.0	692.3	691.6	690.9
155°	718.2	718.8	719.3	719.1	718.1	717.1	716.1	715.1
157.5°	739.3	739.9	740.5	740.4	739.6	738.8	738.0	737.2
160°	752.3	753.0	753.7	753.8	753.3	752.7	752.1	751.6
162.5°	764.6	765.3	766.0	765.9	765.0	764.1	763.2	762.2
165°	780.1	780.9	781.8	781.7	780.8	779.7	778.8	777.7
167.5°	792.6	793.6	794.4	794.4	793.6	792.6	791.8	790.9
170°	799.5	800.6	801.5	801.5	800.6	799.5	798.6	797.5
172.5°	804.9	805.8	806.7	806.7	805.6	804.7	803.7	802.7
175°	810.8	811.6	812.4	812.4	811.4	810.4	809.4	808.4
177.5°	813.4	814.1	814.8	814.7	813.9	813.0	812.3	811.5
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6

(END OF REPORT)