

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332458-935

Luminaire Tested: **S123RDIW-S1000D1030U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332458-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1030U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6960.9 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	42
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	44	43	41	36
3	82	73	66	61	76	68	62	57	58	53	50	49	45	42	40	38	36	32
4	76	65	58	52	69	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	58	50	45	64	54	47	42	47	41	37	39	35	32	33	30	27	24
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22
7	59	48	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14733	14733	14733	14733
5°	17562	14795	13029	14795
10°	21928	14711	11770	14711
15°	25740	14561	10735	14561
20°	28726	14336	9852	14336
25°	28268	14099	9311	14099
30°	20319	13881	8754	13881
35°	13566	13596	8393	13596
40°	9996	13256	8019	13256
45°	8385	12657	7652	12657
50°	7398	11871	7142	11871
55°	6488	10975	6444	10975
60°	5778	10116	5903	10116
65°	5074	9192	5491	9192
70°	3984	8371	5017	8371
75°	3510	7311	4579	7311
80°	3050	6211	4506	6211
85°	2458	5002	4780	5002



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.9
10°-20°	420.5	6.0
20°-30°	660.6	9.5
30°-40°	689.3	9.9
40°-50°	589.9	8.5
50°-60°	449.6	6.5
60°-70°	288.2	4.1
70°-80°	138.6	2.0
80°-90°	39.9	0.6
90°-100°	42.3	0.6
100°-110°	201.7	2.9
110°-120°	484.5	7.0
120°-130°	616.9	8.9
130°-140°	659.2	9.5
140°-150°	616.4	8.9
150°-160°	497.2	7.1
160°-170°	320.9	4.6
170°-180°	110.6	1.6
0°-30°	1215.8	17.5
0°-40°	1905.0	27.4
0°-60°	2944.5	42.3
0°-90°	3411.2	49.0
90°-120°	728.5	10.5
90°-150°	2621.0	37.7
90°-180°	3550.0	51.0
0°-180°	6960.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1625	1369	1206	1369	1625	168
15°	2310	1307	963	1307	2310	655
25°	2380	1187	784	1187	2380	1023
35°	1032	1035	639	1035	1032	677
45°	551	832	503	832	551	433
55°	346	585	343	585	346	313
65°	199	361	216	361	199	196
75°	84	176	110	176	84	90
85°	20	40	39	40	20	24
90°	26	1	26	1	26	12
95°	33	53	33	53	33	27
105°	38	258	38	258	38	87
115°	508	484	508	484	508	470
125°	695	682	695	682	695	621
135°	857	848	857	848	857	661
145°	988	979	988	979	988	617
155°	1077	1078	1077	1078	1077	496
165°	1135	1137	1135	1137	1135	320
175°	1160	1164	1160	1164	1160	110
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1457.8	1459.7	1453.6	1452.7	1445.6	1443.7	1443.7	1433.9	1427.8	1419.9	1415.1
5°	1625.4	1634.8	1630.0	1619.5	1602.0	1597.8	1586.7	1569.2	1549.2	1524.6	1512.9
7.5°	1834.7	1847.4	1842.5	1826.3	1807.8	1792.9	1761.6	1732.4	1691.5	1655.6	1625.0
10°	2006.2	1992.8	1982.2	1966.4	1949.4	1921.8	1889.0	1843.9	1791.8	1750.8	1705.1
12.5°	2134.7	2132.4	2119.1	2102.8	2078.8	2052.6	2012.3	1957.4	1896.8	1837.5	1785.2
15°	2309.8	2313.2	2304.5	2287.5	2253.5	2207.3	2146.3	2123.5	2036.7	1972.3	1907.8
17.5°	2430.9	2430.3	2429.1	2405.5	2370.8	2337.9	2281.4	2221.3	2142.8	2051.9	1965.1
20°	2507.8	2502.0	2503.1	2476.8	2451.0	2412.9	2357.8	2270.5	2206.1	2101.2	2011.6
22.5°	2505.9	2504.7	2509.2	2500.2	2481.5	2452.3	2408.9	2335.2	2252.9	2147.1	2046.3
25°	2380.1	2375.4	2403.0	2410.5	2440.4	2445.7	2432.8	2392.4	2314.5	2205.5	2080.7
27.5°	1991.9	1989.3	2040.5	2104.5	2185.6	2248.6	2309.5	2339.0	2314.5	2236.4	2111.3
30°	1634.8	1689.9	1715.6	1808.2	1911.3	2034.4	2142.2	2244.7	2269.9	2235.9	2133.4
32.5°	1357.3	1405.3	1426.8	1506.3	1602.4	1746.5	1908.3	2053.5	2156.0	2182.0	2120.3
35°	1032.4	1033.0	1082.2	1117.4	1206.4	1354.7	1511.7	1706.2	1899.6	2046.1	2061.3
37.5°	823.8	826.7	856.5	891.6	958.4	1036.7	1175.0	1336.8	1560.1	1785.0	1916.8
40°	711.4	716.6	738.9	773.4	821.5	880.6	988.5	1140.8	1327.1	1577.4	1781.8
42.5°	639.1	647.7	659.2	685.8	715.6	770.9	858.2	975.9	1145.3	1381.9	1617.8
45°	550.8	555.4	564.3	576.5	603.5	642.2	700.8	779.9	920.5	1110.9	1347.0
47.5°	485.9	483.4	492.7	502.7	520.6	546.9	586.2	650.7	751.1	903.9	1104.1
50°	441.8	441.2	447.6	455.3	472.3	491.6	523.8	572.5	652.1	778.7	962.1
52.5°	400.5	402.8	407.3	416.8	429.1	444.7	473.6	508.7	577.1	686.4	839.3
55°	345.7	347.5	353.9	359.2	368.0	383.7	401.9	431.3	478.1	554.3	680.3
57.5°	299.3	298.5	304.7	306.0	315.9	328.8	342.9	365.7	399.6	456.2	541.1
60°	268.4	266.6	271.9	276.0	281.3	291.8	303.5	325.8	352.8	394.3	467.0
62.5°	240.2	239.4	243.3	247.4	251.8	261.3	271.2	288.3	309.6	344.7	402.3
65°	199.2	201.0	202.8	204.5	206.8	212.7	222.1	233.8	248.4	273.0	314.6
67.5°	156.5	158.3	158.9	162.6	167.6	171.3	176.9	187.4	197.6	218.3	242.0
70°	126.6	126.0	126.6	128.3	134.7	141.2	148.9	156.4	162.9	177.5	197.4
72.5°	108.7	107.7	109.3	109.6	112.7	114.5	119.3	126.5	134.7	144.7	159.0
75°	84.4	84.4	84.4	84.4	86.7	87.9	89.6	91.4	94.4	99.0	109.6
77.5°	62.3	62.4	63.3	63.9	64.3	65.0	66.1	67.8	68.9	71.4	75.9
80°	49.2	49.8	49.2	49.8	49.8	51.0	51.6	53.3	53.9	56.8	58.6
82.5°	37.0	36.7	37.0	37.6	37.6	38.8	38.9	40.2	40.3	41.8	43.6
85°	19.9	18.8	19.9	19.4	20.5	19.4	19.9	21.1	21.1	21.7	24.0
87.5°	9.9	10.8	9.7	10.1	10.1	10.4	10.2	10.1	10.8	10.2	10.2
90°	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3	21.5	20.8	18.3
92.5°	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6	23.3	22.1	20.2
95°	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5	28.2	26.8	24.7
97.5°	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9	29.4	27.8	41.7
100°	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6	30.0	28.5	58.5
102.5°	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4	52.2	56.9	89.6
105°	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4	155.4	189.4	206.7
107.5°	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2	322.2	347.2	344.4
110°	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4	383.7	390.0	387.9



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9	433.7	433.6	431.5
115°	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2	498.3	496.4	494.6
117.5°	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3	558.8	557.2	556.4
120°	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8	598.2	596.7	596.2
122.5°	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3	637.2	636.1	635.4
125°	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6	692.2	691.8	691.0
127.5°	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0	746.4	745.8	744.9
130°	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9	779.1	778.3	777.6
132.5°	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0	810.2	809.4	808.8
135°	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0	856.3
137.5°	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2	899.2	898.4	897.9
140°	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9	926.1	925.3	924.7
142.5°	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2	951.6	950.9	950.4
145°	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5	987.1	986.7	986.4
147.5°	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2	1018.7	1018.4	1018.0
150°	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5	1038.1	1037.8	1037.3
152.5°	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8	1055.1	1054.4	1054.1
155°	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4	1078.5	1077.5	1077.4
157.5°	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1	1098.9	1097.8	1097.9
160°	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8	1110.7	1109.6	1109.7
162.5°	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5	1121.2	1119.9	1120.1
165°	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8	1135.3	1133.8	1133.9
167.5°	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8	1144.8
170°	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1	1151.1
172.5°	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3	1156.8	1155.2	1155.0
175°	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2	1161.9	1160.5	1160.4
177.5°	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1	1163.9	1162.6	1162.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1413.2	1411.9	1405.3	1397.8	1387.9	1381.4	1376.2	1373.5	1365.0	1354.7	1347.6
5°	1500.6	1483.0	1464.3	1441.4	1420.3	1398.6	1385.2	1369.3	1350.0	1328.4	1313.1
7.5°	1594.1	1559.6	1522.5	1484.2	1446.3	1412.4	1382.3	1356.7	1325.9	1294.8	1273.0
10°	1665.9	1615.4	1563.3	1509.9	1461.3	1415.7	1380.4	1345.9	1309.0	1273.2	1246.3
12.5°	1731.0	1664.7	1604.6	1539.0	1476.8	1422.2	1371.6	1330.9	1286.5	1248.4	1217.7
15°	1813.4	1745.5	1672.8	1573.2	1490.6	1421.5	1359.9	1306.7	1252.8	1205.8	1176.0
17.5°	1890.6	1788.3	1690.7	1607.6	1500.2	1413.8	1338.8	1275.0	1215.8	1166.1	1129.4
20°	1922.4	1823.4	1717.4	1611.4	1505.9	1409.2	1321.9	1251.5	1190.1	1133.8	1099.8
22.5°	1941.6	1829.5	1717.9	1603.9	1491.8	1391.4	1305.0	1227.7	1161.0	1107.5	1065.6
25°	1964.0	1830.5	1707.4	1594.9	1480.7	1371.7	1269.1	1187.1	1115.1	1058.2	1013.7
27.5°	1978.8	1821.7	1676.3	1551.2	1435.3	1326.8	1232.8	1145.8	1072.7	1012.6	964.8
30°	1981.7	1814.6	1652.3	1517.0	1399.2	1299.6	1200.0	1116.8	1039.5	975.6	931.1
32.5°	1985.4	1797.3	1620.0	1476.2	1355.6	1257.0	1166.7	1087.3	1008.1	945.1	899.7
35°	1970.0	1787.7	1570.9	1405.7	1285.0	1189.5	1108.0	1034.7	956.8	895.9	849.6
37.5°	1903.3	1749.6	1520.0	1326.2	1200.0	1111.6	1045.2	981.4	909.8	844.1	800.5
40°	1836.3	1712.1	1480.7	1277.9	1146.1	1055.2	995.5	943.4	874.3	812.7	765.9
42.5°	1736.5	1661.0	1443.2	1227.3	1085.1	997.6	947.2	898.4	837.7	775.2	731.2
45°	1553.3	1563.3	1366.4	1146.7	1000.7	912.9	865.4	831.5	777.6	726.0	680.9
47.5°	1323.6	1416.8	1276.3	1060.8	911.8	829.3	787.8	758.2	721.9	671.2	630.1
50°	1173.6	1306.7	1204.1	1003.2	856.1	774.0	733.0	708.9	677.3	637.5	598.2
52.5°	1035.4	1178.2	1116.9	938.9	795.6	720.6	680.5	660.7	635.6	598.1	562.6
55°	844.3	989.0	975.0	842.0	704.9	637.5	607.0	584.8	567.7	539.7	511.5
57.5°	682.9	820.2	827.4	734.2	625.0	558.4	532.2	515.4	504.3	483.0	457.0
60°	581.3	707.2	731.8	661.5	567.7	509.2	483.4	469.9	461.2	444.1	424.2
62.5°	496.9	604.1	632.0	581.3	512.9	458.1	437.9	424.9	419.0	404.3	386.8
65°	380.3	469.3	496.3	468.1	432.4	388.5	372.0	360.9	355.7	347.5	334.6
67.5°	285.9	350.9	380.4	360.6	347.7	319.9	309.5	303.5	298.9	293.2	282.4
70°	229.7	277.8	308.2	302.9	292.4	277.8	270.1	266.0	261.3	256.7	247.3
72.5°	184.7	217.7	246.3	249.0	240.4	237.5	230.7	229.0	226.2	220.6	215.4
75°	122.4	145.3	165.2	172.9	176.3	179.3	176.3	175.8	175.2	170.5	167.6
77.5°	80.2	92.6	105.1	118.1	123.6	127.6	128.5	130.7	129.2	126.7	125.3
80°	61.6	64.5	73.3	84.4	93.2	96.7	99.0	100.2	99.6	99.0	96.7
82.5°	44.7	47.1	51.2	59.1	66.5	72.3	73.7	73.4	74.7	75.1	73.3
85°	24.0	24.6	25.7	26.9	31.1	37.5	39.3	40.5	41.6	41.6	38.1
87.5°	10.7	9.6	10.2	9.6	10.7	10.8	13.2	15.2	16.0	14.6	14.9
90°	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9	2.8	4.7	6.6
92.5°	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1	15.6	15.0	14.5
95°	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8	44.9	37.0	29.1
97.5°	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0	102.5	98.9	95.4
100°	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1	150.0	153.9	157.6
102.5°	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8	194.6	197.3	200.1
105°	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7	259.8	261.9	264.1
107.5°	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3	328.9	330.6	332.3
110°	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6	375.1	376.7	378.2



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8	419.2	420.6	422.1
115°	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5	484.6	485.7	486.9
117.5°	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9	548.3	549.7	551.1
120°	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3	588.1	589.8	591.5
122.5°	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5	627.8	629.3	630.7
125°	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5	683.0	684.5	686.0
127.5°	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7	736.2	737.8	739.3
130°	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9	769.5	771.0	772.6
132.5°	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8	801.3	802.8	804.3
135°	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3	849.5	850.7	851.8
137.5°	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8	891.3	892.8	894.2
140°	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6	918.7	919.9	921.0
142.5°	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1	944.3	945.5	946.6
145°	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0	980.2	981.6	983.0
147.5°	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7	1013.6	1014.4	1015.3
150°	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5	1034.0	1034.6	1035.2
152.5°	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1	1052.4	1052.7	1052.9
155°	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4	1078.0	1077.6	1077.3
157.5°	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8	1098.8	1098.7	1098.7
160°	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3	1111.0	1110.9	1110.7
162.5°	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0	1122.5	1122.1	1121.5
165°	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2	1136.6	1136.1	1135.5
167.5°	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2	1147.5	1146.8	1146.0
170°	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5	1153.7	1153.0	1152.2
172.5°	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6	1157.7	1156.8	1155.9
175°	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0	1163.0	1162.1	1161.1
177.5°	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4	1164.6	1163.9	1163.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1345.3	1339.2	1335.0	1325.6	1319.6	1312.9	1306.4	1310.6	1310.2	1309.7	1309.7
5°	1300.2	1286.7	1274.5	1258.6	1248.6	1236.3	1226.9	1225.8	1228.1	1220.0	1215.2
7.5°	1255.4	1237.0	1219.6	1202.1	1183.6	1168.8	1159.6	1155.2	1149.3	1144.2	1138.9
10°	1224.0	1202.4	1185.3	1163.6	1143.8	1126.2	1115.1	1107.4	1103.3	1099.2	1091.6
12.5°	1191.7	1170.4	1148.8	1124.3	1105.4	1084.9	1076.6	1068.1	1060.2	1055.6	1045.2
15°	1144.4	1116.8	1094.0	1068.2	1047.1	1027.2	1015.5	998.4	996.1	990.2	979.7
17.5°	1096.9	1067.0	1035.4	1016.4	992.6	971.8	954.0	948.3	931.5	925.2	916.0
20°	1059.4	1031.8	1007.8	982.7	948.0	928.7	914.6	907.1	893.5	885.4	879.5
22.5°	1027.0	999.0	971.3	941.8	913.3	891.7	881.4	869.5	862.1	850.7	844.3
25°	980.9	950.4	917.0	885.4	864.9	848.4	832.1	821.5	811.0	805.6	793.9
27.5°	927.2	895.4	864.1	840.1	814.9	798.7	783.9	774.5	761.8	752.9	746.5
30°	897.7	860.1	833.2	811.5	779.3	764.1	752.9	741.2	731.8	722.5	716.0
32.5°	863.4	829.2	803.7	776.9	752.1	735.5	721.1	710.8	702.7	693.9	687.4
35°	809.8	781.1	754.7	727.7	709.6	692.6	675.6	666.8	659.2	651.0	645.1
37.5°	761.2	734.4	709.4	683.8	661.2	647.5	633.8	627.1	616.7	611.2	605.3
40°	731.2	704.9	678.0	653.3	629.9	619.3	607.0	597.1	587.7	583.6	577.1
42.5°	698.4	672.1	649.4	622.8	603.6	589.4	578.0	567.1	560.1	554.1	550.4
45°	649.8	626.4	604.1	577.7	559.6	547.3	534.3	524.4	518.0	513.8	507.4
47.5°	602.6	579.1	556.6	533.6	516.0	501.9	489.0	482.1	473.6	468.6	464.2
50°	568.3	547.3	523.2	502.1	484.6	470.5	459.9	451.2	443.6	437.1	434.2
52.5°	536.9	514.4	493.7	474.1	455.5	439.5	430.0	420.7	415.0	407.6	404.2
55°	485.2	463.5	445.9	426.5	408.4	394.9	383.2	375.0	369.1	360.9	356.3
57.5°	436.5	417.1	396.1	379.4	360.6	349.2	339.5	328.4	321.2	314.8	310.2
60°	403.7	381.4	363.3	347.5	331.1	316.4	307.6	298.9	291.2	284.7	280.7
62.5°	369.5	350.1	332.8	315.6	300.6	287.8	277.6	270.3	263.6	259.4	255.4
65°	317.0	301.8	284.2	270.1	256.1	246.7	238.5	232.0	227.3	224.4	220.9
67.5°	268.7	253.9	238.6	224.8	215.4	208.3	202.9	197.3	195.0	191.2	188.9
70°	237.3	222.1	208.6	198.0	188.6	183.4	179.9	175.8	173.4	168.8	166.4
72.5°	203.1	192.1	182.4	173.7	166.2	161.4	156.9	151.9	148.1	142.9	140.6
75°	160.0	150.0	142.4	136.6	131.8	125.4	118.9	113.7	111.9	110.1	109.6
77.5°	118.5	112.2	106.7	101.7	95.8	91.2	89.8	88.6	88.3	87.3	87.3
80°	93.2	87.3	83.2	77.3	73.8	73.8	73.8	72.7	73.3	73.3	73.3
82.5°	69.2	63.9	61.6	59.5	58.8	59.3	59.3	59.5	59.2	60.1	59.7
85°	35.7	36.3	37.5	36.9	37.5	37.5	38.7	38.1	38.7	37.5	38.7
87.5°	14.8	16.7	17.7	18.6	19.6	19.6	20.2	20.4	21.0	21.2	21.3
90°	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3	23.1	23.8	24.4
92.5°	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6	25.8	27.0	27.8
95°	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5	30.8	32.2	32.9
97.5°	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9	32.5	34.0	34.9
100°	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6	33.1	34.7	35.6
102.5°	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4	42.6	37.8	35.6
105°	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4	87.3	53.3	36.5
107.5°	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2	272.3	247.4	222.1
110°	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4	371.0	364.6	347.8



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9	433.9	434.0	431.2
115°	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2	502.1	504.1	505.4
117.5°	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3	561.9	563.4	564.3
120°	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8	601.3	602.9	603.6
122.5°	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3	639.4	640.4	641.1
125°	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6	693.0	693.4	693.8
127.5°	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0	747.6	748.3	748.4
130°	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9	780.6	781.4	781.6
132.5°	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0	811.8	812.5	812.6
135°	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2	858.8	859.3	859.3
137.5°	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2	901.1	902.1	902.3
140°	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9	927.6	928.4	928.6
142.5°	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2	952.8	953.4	953.4
145°	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5	987.9	988.3	988.4
147.5°	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2	1019.5	1019.9	1019.7
150°	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5	1038.9	1039.3	1039.2
152.5°	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8	1056.4	1057.1	1057.0
155°	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4	1080.4	1081.4	1081.2
157.5°	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1	1101.2	1102.3	1102.2
160°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8	1113.0	1114.1	1114.0
162.5°	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5	1123.9	1125.2	1125.2
165°	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8	1138.3	1139.9	1140.0
167.5°	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0
170°	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2
172.5°	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3	1159.8	1161.3	1161.2
175°	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2	1164.6	1166.0	1165.9
177.5°	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1	1166.3	1167.5	1167.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1304.1	1303.6	1304.1	1302.2	1304.1	1303.6	1304.1	1309.7	1309.7	1310.2	1310.6
5°	1213.5	1212.9	1211.2	1205.8	1211.2	1212.9	1213.5	1215.2	1220.0	1228.1	1225.8
7.5°	1134.4	1133.6	1128.4	1128.5	1128.4	1133.6	1134.4	1138.9	1144.2	1149.3	1155.2
10°	1087.5	1088.0	1081.1	1076.9	1081.1	1088.0	1087.5	1091.6	1099.2	1103.3	1107.4
12.5°	1042.1	1039.3	1033.7	1029.2	1033.7	1039.3	1042.1	1045.2	1055.6	1060.2	1068.1
15°	982.1	976.2	962.1	963.3	962.1	976.2	982.1	979.7	990.2	996.1	998.4
17.5°	911.4	907.1	906.8	898.6	906.8	907.1	911.4	916.0	925.2	931.5	948.3
20°	870.1	867.2	868.3	860.1	868.3	867.2	870.1	879.5	885.4	893.5	907.1
22.5°	837.8	834.8	829.9	827.3	829.9	834.8	837.8	844.3	850.7	862.1	869.5
25°	790.4	785.7	781.1	784.0	781.1	785.7	790.4	793.9	805.6	811.0	821.5
27.5°	743.1	739.6	734.9	734.3	734.9	739.6	743.1	746.5	752.9	761.8	774.5
30°	713.1	709.6	707.2	704.3	707.2	709.6	713.1	716.0	722.5	731.8	741.2
32.5°	682.6	681.9	677.7	677.1	677.7	681.9	682.6	687.4	693.9	702.7	710.8
35°	642.7	639.3	638.1	638.7	638.1	639.3	642.7	645.1	651.0	659.2	666.8
37.5°	604.9	600.2	598.1	596.0	598.1	600.2	604.9	605.3	611.2	616.7	627.1
40°	577.7	573.1	571.9	570.7	571.9	573.1	577.7	577.1	583.6	587.7	597.1
42.5°	547.3	545.4	544.7	542.6	544.7	545.4	547.3	550.4	554.1	560.1	567.1
45°	505.7	505.1	501.5	502.7	501.5	505.1	505.7	507.4	513.8	518.0	524.4
47.5°	461.8	459.3	456.8	458.4	456.8	459.3	461.8	464.2	468.6	473.6	482.1
50°	431.9	430.7	425.4	426.5	425.4	430.7	431.9	434.2	437.1	443.6	451.2
52.5°	401.8	397.4	395.4	394.7	395.4	397.4	401.8	404.2	407.6	415.0	420.7
55°	352.1	346.9	344.6	343.4	344.6	346.9	352.1	356.3	360.9	369.1	375.0
57.5°	303.4	302.0	300.1	301.4	300.1	302.0	303.4	310.2	314.8	321.2	328.4
60°	274.8	274.8	274.8	274.2	274.8	274.8	274.8	280.7	284.7	291.2	298.9
62.5°	252.8	251.3	250.9	251.8	250.9	251.3	252.8	255.4	259.4	263.6	270.3
65°	219.1	218.5	216.2	215.6	216.2	218.5	219.1	220.9	224.4	227.3	232.0
67.5°	187.4	185.3	184.6	183.7	184.6	185.3	187.4	188.9	191.2	195.0	197.3
70°	163.5	162.3	158.8	159.4	158.8	162.3	163.5	166.4	168.8	173.4	175.8
72.5°	137.7	136.6	135.8	135.0	135.8	136.6	137.7	140.6	142.9	148.1	151.9
75°	109.0	108.4	107.8	110.1	107.8	108.4	109.0	109.6	110.1	111.9	113.7
77.5°	87.3	87.3	87.6	86.7	87.6	87.3	87.3	87.3	87.3	88.3	88.6
80°	73.3	73.3	72.7	72.7	72.7	73.3	73.3	73.3	73.3	73.3	72.7
82.5°	58.7	59.2	59.5	58.6	59.5	59.2	58.7	59.7	60.1	59.2	59.5
85°	38.7	38.1	39.3	38.7	39.3	38.1	38.7	38.7	37.5	38.7	38.1
87.5°	22.3	21.4	21.5	22.0	21.5	21.4	22.3	21.3	21.2	21.0	20.4
90°	24.8	25.1	25.6	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3
92.5°	28.0	28.2	28.5	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6
95°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5
97.5°	35.0	35.2	35.5	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9
100°	35.7	35.9	36.2	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6
102.5°	36.0	36.3	36.7	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4
105°	36.9	37.3	37.6	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4
107.5°	196.4	170.8	145.2	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2
110°	320.3	292.7	265.3	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	425.4	419.7	413.8	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9
115°	506.2	507.0	507.7	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2
117.5°	564.4	564.6	564.7	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3
120°	603.6	603.6	603.6	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8
122.5°	641.2	641.4	641.5	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3
125°	694.1	694.5	694.9	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6
127.5°	748.0	747.6	747.3	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0
130°	781.2	780.8	780.4	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9
132.5°	812.1	811.6	811.1	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0
135°	858.8	858.2	857.6	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2
137.5°	901.9	901.6	901.1	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2
140°	928.2	927.8	927.5	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9
142.5°	952.9	952.4	951.8	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2
145°	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5
147.5°	1018.8	1017.9	1017.0	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2
150°	1038.6	1038.0	1037.5	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5
152.5°	1056.1	1055.2	1054.4	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8
155°	1080.1	1079.0	1077.8	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4
157.5°	1100.7	1099.2	1097.7	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1
160°	1112.7	1111.4	1110.0	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8
162.5°	1124.0	1122.8	1121.6	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5
165°	1138.7	1137.3	1135.9	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8
167.5°	1149.4	1147.9	1146.3	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9
170°	1155.6	1154.1	1152.5	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1
172.5°	1159.6	1157.9	1156.2	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3
175°	1164.3	1162.8	1161.2	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2
177.5°	1165.9	1164.3	1162.8	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1306.4	1312.9	1319.6	1325.6	1335.0	1339.2	1345.3	1347.6	1354.7	1365.0	1373.5
5°	1226.9	1236.3	1248.6	1258.6	1274.5	1286.7	1300.2	1313.1	1328.4	1350.0	1369.3
7.5°	1159.6	1168.8	1183.6	1202.1	1219.6	1237.0	1255.4	1273.0	1294.8	1325.9	1356.7
10°	1115.1	1126.2	1143.8	1163.6	1185.3	1202.4	1224.0	1246.3	1273.2	1309.0	1345.9
12.5°	1076.6	1084.9	1105.4	1124.3	1148.8	1170.4	1191.7	1217.7	1248.4	1286.5	1330.9
15°	1015.5	1027.2	1047.1	1068.2	1094.0	1116.8	1144.4	1176.0	1205.8	1252.8	1306.7
17.5°	954.0	971.8	992.6	1016.4	1035.4	1067.0	1096.9	1129.4	1166.1	1215.8	1275.0
20°	914.6	928.7	948.0	982.7	1007.8	1031.8	1059.4	1099.8	1133.8	1190.1	1251.5
22.5°	881.4	891.7	913.3	941.8	971.3	999.0	1027.0	1065.6	1107.5	1161.0	1227.7
25°	832.1	848.4	864.9	885.4	917.0	950.4	980.9	1013.7	1058.2	1115.1	1187.1
27.5°	783.9	798.7	814.9	840.1	864.1	895.4	927.2	964.8	1012.6	1072.7	1145.8
30°	752.9	764.1	779.3	811.5	833.2	860.1	897.7	931.1	975.6	1039.5	1116.8
32.5°	721.1	735.5	752.1	776.9	803.7	829.2	863.4	899.7	945.1	1008.1	1087.3
35°	675.6	692.6	709.6	727.7	754.7	781.1	809.8	849.6	895.9	956.8	1034.7
37.5°	633.8	647.5	661.2	683.8	709.4	734.4	761.2	800.5	844.1	909.8	981.4
40°	607.0	619.3	629.9	653.3	678.0	704.9	731.2	765.9	812.7	874.3	943.4
42.5°	578.0	589.4	603.6	622.8	649.4	672.1	698.4	731.2	775.2	837.7	898.4
45°	534.3	547.3	559.6	577.7	604.1	626.4	649.8	680.9	726.0	777.6	831.5
47.5°	489.0	501.9	516.0	533.6	556.6	579.1	602.6	630.1	671.2	721.9	758.2
50°	459.9	470.5	484.6	502.1	523.2	547.3	568.3	598.2	637.5	677.3	708.9
52.5°	430.0	439.5	455.5	474.1	493.7	514.4	536.9	562.6	598.1	635.6	660.7
55°	383.2	394.9	408.4	426.5	445.9	463.5	485.2	511.5	539.7	567.7	584.8
57.5°	339.5	349.2	360.6	379.4	396.1	417.1	436.5	457.0	483.0	504.3	515.4
60°	307.6	316.4	331.1	347.5	363.3	381.4	403.7	424.2	444.1	461.2	469.9
62.5°	277.6	287.8	300.6	315.6	332.8	350.1	369.5	386.8	404.3	419.0	424.9
65°	238.5	246.7	256.1	270.1	284.2	301.8	317.0	334.6	347.5	355.7	360.9
67.5°	202.9	208.3	215.4	224.8	238.6	253.9	268.7	282.4	293.2	298.9	303.5
70°	179.9	183.4	188.6	198.0	208.6	222.1	237.3	247.3	256.7	261.3	266.0
72.5°	156.9	161.4	166.2	173.7	182.4	192.1	203.1	215.4	220.6	226.2	229.0
75°	118.9	125.4	131.8	136.6	142.4	150.0	160.0	167.6	170.5	175.2	175.8
77.5°	89.8	91.2	95.8	101.7	106.7	112.2	118.5	125.3	126.7	129.2	130.7
80°	73.8	73.8	73.8	77.3	83.2	87.3	93.2	96.7	99.0	99.6	100.2
82.5°	59.3	59.3	58.8	59.5	61.6	63.9	69.2	73.3	75.1	74.7	73.4
85°	38.7	37.5	37.5	36.9	37.5	36.3	35.7	38.1	41.6	41.6	40.5
87.5°	20.2	19.6	19.6	18.6	17.7	16.7	14.8	14.9	14.6	16.0	15.2
90°	21.5	20.8	18.3	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9
92.5°	23.3	22.1	20.2	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1
95°	28.2	26.8	24.7	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8
97.5°	29.4	27.8	41.7	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0
100°	30.0	28.5	58.5	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1
102.5°	52.2	56.9	89.6	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8
105°	155.4	189.4	206.7	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7
107.5°	322.2	347.2	344.4	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3
110°	383.7	390.0	387.9	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	433.7	433.6	431.5	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8
115°	498.3	496.4	494.6	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5
117.5°	558.8	557.2	556.4	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9
120°	598.2	596.7	596.2	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3
122.5°	637.2	636.1	635.4	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5
125°	692.2	691.8	691.0	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5
127.5°	746.4	745.8	744.9	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7
130°	779.1	778.3	777.6	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9
132.5°	810.2	809.4	808.8	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8
135°	857.6	857.0	856.3	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3
137.5°	899.2	898.4	897.9	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8
140°	926.1	925.3	924.7	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6
142.5°	951.6	950.9	950.4	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1
145°	987.1	986.7	986.4	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0
147.5°	1018.7	1018.4	1018.0	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7
150°	1038.1	1037.8	1037.3	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5
152.5°	1055.1	1054.4	1054.1	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1
155°	1078.5	1077.5	1077.4	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4
157.5°	1098.9	1097.8	1097.9	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8
160°	1110.7	1109.6	1109.7	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3
162.5°	1121.2	1119.9	1120.1	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0
165°	1135.3	1133.8	1133.9	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2
167.5°	1146.3	1144.8	1144.8	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2
170°	1152.5	1151.1	1151.1	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5
172.5°	1156.8	1155.2	1155.0	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6
175°	1161.9	1160.5	1160.4	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0
177.5°	1163.9	1162.6	1162.4	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1376.2	1381.4	1387.9	1397.8	1405.3	1411.9	1413.2	1415.1	1419.9	1427.8	1433.9
5°	1385.2	1398.6	1420.3	1441.4	1464.3	1483.0	1500.6	1512.9	1524.6	1549.2	1569.2
7.5°	1382.3	1412.4	1446.3	1484.2	1522.5	1559.6	1594.1	1625.0	1655.6	1691.5	1732.4
10°	1380.4	1415.7	1461.3	1509.9	1563.3	1615.4	1665.9	1705.1	1750.8	1791.8	1843.9
12.5°	1371.6	1422.2	1476.8	1539.0	1604.6	1664.7	1731.0	1785.2	1837.5	1896.8	1957.4
15°	1359.9	1421.5	1490.6	1573.2	1672.8	1745.5	1813.4	1907.8	1972.3	2036.7	2123.5
17.5°	1338.8	1413.8	1500.2	1607.6	1690.7	1788.3	1890.6	1965.1	2051.9	2142.8	2221.3
20°	1321.9	1409.2	1505.9	1611.4	1717.4	1823.4	1922.4	2011.6	2101.2	2206.1	2270.5
22.5°	1305.0	1391.4	1491.8	1603.9	1717.9	1829.5	1941.6	2046.3	2147.1	2252.9	2335.2
25°	1269.1	1371.7	1480.7	1594.9	1707.4	1830.5	1964.0	2080.7	2205.5	2314.5	2392.4
27.5°	1232.8	1326.8	1435.3	1551.2	1676.3	1821.7	1978.8	2111.3	2236.4	2314.5	2339.0
30°	1200.0	1299.6	1399.2	1517.0	1652.3	1814.6	1981.7	2133.4	2235.9	2269.9	2244.7
32.5°	1166.7	1257.0	1355.6	1476.2	1620.0	1797.3	1985.4	2120.3	2182.0	2156.0	2053.5
35°	1108.0	1189.5	1285.0	1405.7	1570.9	1787.7	1970.0	2061.3	2046.1	1899.6	1706.2
37.5°	1045.2	1111.6	1200.0	1326.2	1520.0	1749.6	1903.3	1916.8	1785.0	1560.1	1336.8
40°	995.5	1055.2	1146.1	1277.9	1480.7	1712.1	1836.3	1781.8	1577.4	1327.1	1140.8
42.5°	947.2	997.6	1085.1	1227.3	1443.2	1661.0	1736.5	1617.8	1381.9	1145.3	975.9
45°	865.4	912.9	1000.7	1146.7	1366.4	1563.3	1553.3	1347.0	1110.9	920.5	779.9
47.5°	787.8	829.3	911.8	1060.8	1276.3	1416.8	1323.6	1104.1	903.9	751.1	650.7
50°	733.0	774.0	856.1	1003.2	1204.1	1306.7	1173.6	962.1	778.7	652.1	572.5
52.5°	680.5	720.6	795.6	938.9	1116.9	1178.2	1035.4	839.3	686.4	577.1	508.7
55°	607.0	637.5	704.9	842.0	975.0	989.0	844.3	680.3	554.3	478.1	431.3
57.5°	532.2	558.4	625.0	734.2	827.4	820.2	682.9	541.1	456.2	399.6	365.7
60°	483.4	509.2	567.7	661.5	731.8	707.2	581.3	467.0	394.3	352.8	325.8
62.5°	437.9	458.1	512.9	581.3	632.0	604.1	496.9	402.3	344.7	309.6	288.3
65°	372.0	388.5	432.4	468.1	496.3	469.3	380.3	314.6	273.0	248.4	233.8
67.5°	309.5	319.9	347.7	360.6	380.4	350.9	285.9	242.0	218.3	197.6	187.4
70°	270.1	277.8	292.4	302.9	308.2	277.8	229.7	197.4	177.5	162.9	156.4
72.5°	230.7	237.5	240.4	249.0	246.3	217.7	184.7	159.0	144.7	134.7	126.5
75°	176.3	179.3	176.3	172.9	165.2	145.3	122.4	109.6	99.0	94.4	91.4
77.5°	128.5	127.6	123.6	118.1	105.1	92.6	80.2	75.9	71.4	68.9	67.8
80°	99.0	96.7	93.2	84.4	73.3	64.5	61.6	58.6	56.8	53.9	53.3
82.5°	73.7	72.3	66.5	59.1	51.2	47.1	44.7	43.6	41.8	40.3	40.2
85°	39.3	37.5	31.1	26.9	25.7	24.6	24.0	24.0	21.7	21.1	21.1
87.5°	13.2	10.8	10.7	9.6	10.2	9.6	10.7	10.2	10.2	10.8	10.1
90°	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3
92.5°	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6
95°	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5
97.5°	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9
100°	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6
102.5°	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4
105°	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4
107.5°	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2
110°	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9
115°	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2
117.5°	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3
120°	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8
122.5°	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3
125°	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6
127.5°	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0
130°	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9
132.5°	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0
135°	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2
137.5°	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2
140°	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9
142.5°	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2
145°	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5
147.5°	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2
150°	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5
152.5°	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8
155°	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4
157.5°	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1
160°	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8
162.5°	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5
165°	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8
167.5°	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9
170°	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1
172.5°	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3
175°	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2
177.5°	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1443.7	1443.7	1445.6	1452.7	1453.6	1459.7	1457.8
5°	1586.7	1597.8	1602.0	1619.5	1630.0	1634.8	1625.4
7.5°	1761.6	1792.9	1807.8	1826.3	1842.5	1847.4	1834.7
10°	1889.0	1921.8	1949.4	1966.4	1982.2	1992.8	2006.2
12.5°	2012.3	2052.6	2078.8	2102.8	2119.1	2132.4	2134.7
15°	2146.3	2207.3	2253.5	2287.5	2304.5	2313.2	2309.8
17.5°	2281.4	2337.9	2370.8	2405.5	2429.1	2430.3	2430.9
20°	2357.8	2412.9	2451.0	2476.8	2503.1	2502.0	2507.8
22.5°	2408.9	2452.3	2481.5	2500.2	2509.2	2504.7	2505.9
25°	2432.8	2445.7	2440.4	2410.5	2403.0	2375.4	2380.1
27.5°	2309.5	2248.6	2185.6	2104.5	2040.5	1989.3	1991.9
30°	2142.2	2034.4	1911.3	1808.2	1715.6	1689.9	1634.8
32.5°	1908.3	1746.5	1602.4	1506.3	1426.8	1405.3	1357.3
35°	1511.7	1354.7	1206.4	1117.4	1082.2	1033.0	1032.4
37.5°	1175.0	1036.7	958.4	891.6	856.5	826.7	823.8
40°	988.5	880.6	821.5	773.4	738.9	716.6	711.4
42.5°	858.2	770.9	715.6	685.8	659.2	647.7	639.1
45°	700.8	642.2	603.5	576.5	564.3	555.4	550.8
47.5°	586.2	546.9	520.6	502.7	492.7	483.4	485.9
50°	523.8	491.6	472.3	455.3	447.6	441.2	441.8
52.5°	473.6	444.7	429.1	416.8	407.3	402.8	400.5
55°	401.9	383.7	368.0	359.2	353.9	347.5	345.7
57.5°	342.9	328.8	315.9	306.0	304.7	298.5	299.3
60°	303.5	291.8	281.3	276.0	271.9	266.6	268.4
62.5°	271.2	261.3	251.8	247.4	243.3	239.4	240.2
65°	222.1	212.7	206.8	204.5	202.8	201.0	199.2
67.5°	176.9	171.3	167.6	162.6	158.9	158.3	156.5
70°	148.9	141.2	134.7	128.3	126.6	126.0	126.6
72.5°	119.3	114.5	112.7	109.6	109.3	107.7	108.7
75°	89.6	87.9	86.7	84.4	84.4	84.4	84.4
77.5°	66.1	65.0	64.3	63.9	63.3	62.4	62.3
80°	51.6	51.0	49.8	49.8	49.2	49.8	49.2
82.5°	38.9	38.8	37.6	37.6	37.0	36.7	37.0
85°	19.9	19.4	20.5	19.4	19.9	18.8	19.9
87.5°	10.2	10.4	10.1	10.1	9.7	10.8	9.9
90°	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	371.0	364.6	347.8	320.3	292.7	265.3	237.8



TEST NUMBER: P332458-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)