

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332466-935

Luminaire Tested: **S123RDIW-S1000D1535U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332466-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1535U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8696.3 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																				
1	96	92	88	85	87	84	81	78	68	66	64	54	53	52	42	41	40	34																				
2	88	81	75	70	80	74	69	65	60	57	54	48	46	44	37	36	34	29																				
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25																				
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22																				
5	68	57	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17																				
7	58	46	38	33	52	42	36	31	35	30	26	29	25	22	23	20	18	15																				
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14																				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13																				
10	47	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14733	14733	14733	14733
5°	17562	14795	13029	14795
10°	21928	14711	11770	14711
15°	25740	14561	10735	14561
20°	28726	14336	9852	14336
25°	28268	14099	9311	14099
30°	20319	13881	8754	13881
35°	13566	13596	8393	13596
40°	9996	13256	8019	13256
45°	8385	12657	7652	12657
50°	7398	11871	7142	11871
55°	6488	10975	6444	10975
60°	5778	10116	5903	10116
65°	5074	9192	5491	9192
70°	3984	8371	5017	8371
75°	3510	7311	4579	7311
80°	3050	6211	4506	6211
85°	2458	5002	4780	5002



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.6	1.5
10°-20°	420.5	4.8
20°-30°	660.6	7.6
30°-40°	689.3	7.9
40°-50°	589.9	6.8
50°-60°	449.6	5.2
60°-70°	288.2	3.3
70°-80°	138.6	1.6
80°-90°	41.5	0.5
90°-100°	63.0	0.7
100°-110°	300.2	3.5
110°-120°	721.1	8.3
120°-130°	918.3	10.6
130°-140°	981.1	11.3
140°-150°	917.5	10.6
150°-160°	740.1	8.5
160°-170°	477.6	5.5
170°-180°	164.6	1.9
0°-30°	1215.8	14.0
0°-40°	1905.0	21.9
0°-60°	2944.5	33.9
0°-90°	3412.8	39.2
90°-120°	1084.3	12.5
90°-150°	3901.2	44.9
90°-180°	5283.0	60.8
0°-180°	8696.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1625	1369	1206	1369	1625	168
15°	2310	1307	963	1307	2310	655
25°	2380	1187	784	1187	2380	1023
35°	1032	1035	639	1035	1032	677
45°	551	832	503	832	551	433
55°	346	585	343	585	346	313
65°	199	361	216	361	199	196
75°	84	176	110	176	84	90
85°	20	40	39	40	20	24
90°	39	1	39	1	39	18
95°	49	78	49	78	49	41
105°	57	384	57	384	57	129
115°	757	720	757	720	757	699
125°	1035	1014	1035	1014	1035	924
135°	1276	1263	1276	1263	1276	984
145°	1471	1457	1471	1457	1471	918
155°	1603	1605	1603	1605	1603	739
165°	1689	1693	1689	1693	1689	477
175°	1726	1732	1726	1732	1726	164
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1457.8	1459.7	1453.6	1452.7	1445.6	1443.7	1443.7	1433.9	1427.8	1419.9	1415.1
5°	1625.4	1634.8	1630.0	1619.5	1602.0	1597.8	1586.7	1569.2	1549.2	1524.6	1512.9
7.5°	1834.7	1847.4	1842.5	1826.3	1807.8	1792.9	1761.6	1732.4	1691.5	1655.6	1625.0
10°	2006.2	1992.8	1982.2	1966.4	1949.4	1921.8	1889.0	1843.9	1791.8	1750.8	1705.1
12.5°	2134.7	2132.4	2119.1	2102.8	2078.8	2052.6	2012.3	1957.4	1896.8	1837.5	1785.2
15°	2309.8	2313.2	2304.5	2287.5	2253.5	2207.3	2146.3	2123.5	2036.7	1972.3	1907.8
17.5°	2430.9	2430.3	2429.1	2405.5	2370.8	2337.9	2281.4	2221.3	2142.8	2051.9	1965.1
20°	2507.8	2502.0	2503.1	2476.8	2451.0	2412.9	2357.8	2270.5	2206.1	2101.2	2011.6
22.5°	2505.9	2504.7	2509.2	2500.2	2481.5	2452.3	2408.9	2335.2	2252.9	2147.1	2046.3
25°	2380.1	2375.4	2403.0	2410.5	2440.4	2445.7	2432.8	2392.4	2314.5	2205.5	2080.7
27.5°	1991.9	1989.3	2040.5	2104.5	2185.6	2248.6	2309.5	2339.0	2314.5	2236.4	2111.3
30°	1634.8	1689.9	1715.6	1808.2	1911.3	2034.4	2142.2	2244.7	2269.9	2235.9	2133.4
32.5°	1357.3	1405.3	1426.8	1506.3	1602.4	1746.5	1908.3	2053.5	2156.0	2182.0	2120.3
35°	1032.4	1033.0	1082.2	1117.4	1206.4	1354.7	1511.7	1706.2	1899.6	2046.1	2061.3
37.5°	823.8	826.7	856.5	891.6	958.4	1036.7	1175.0	1336.8	1560.1	1785.0	1916.8
40°	711.4	716.6	738.9	773.4	821.5	880.6	988.5	1140.8	1327.1	1577.4	1781.8
42.5°	639.1	647.7	659.2	685.8	715.6	770.9	858.2	975.9	1145.3	1381.9	1617.8
45°	550.8	555.4	564.3	576.5	603.5	642.2	700.8	779.9	920.5	1110.9	1347.0
47.5°	485.9	483.4	492.7	502.7	520.6	546.9	586.2	650.7	751.1	903.9	1104.1
50°	441.8	441.2	447.6	455.3	472.3	491.6	523.8	572.5	652.1	778.7	962.1
52.5°	400.5	402.8	407.3	416.8	429.1	444.7	473.6	508.7	577.1	686.4	839.3
55°	345.7	347.5	353.9	359.2	368.0	383.7	401.9	431.3	478.1	554.3	680.3
57.5°	299.3	298.5	304.7	306.0	315.9	328.8	342.9	365.7	399.6	456.2	541.1
60°	268.4	266.6	271.9	276.0	281.3	291.8	303.5	325.8	352.8	394.3	467.0
62.5°	240.2	239.4	243.3	247.4	251.8	261.3	271.2	288.3	309.6	344.7	402.3
65°	199.2	201.0	202.8	204.5	206.8	212.7	222.1	233.8	248.4	273.0	314.6
67.5°	156.5	158.3	158.9	162.6	167.6	171.3	176.9	187.4	197.6	218.3	242.0
70°	126.6	126.0	126.6	128.3	134.7	141.2	148.9	156.4	162.9	177.5	197.4
72.5°	108.7	107.7	109.3	109.6	112.7	114.5	119.3	126.5	134.7	144.7	159.0
75°	84.4	84.4	84.4	84.4	86.7	87.9	89.6	91.4	94.4	99.0	109.6
77.5°	62.3	62.4	63.3	63.9	64.3	65.0	66.1	67.8	68.9	71.4	75.9
80°	49.2	49.8	49.2	49.8	49.8	51.0	51.6	53.3	53.9	56.8	58.6
82.5°	37.0	36.7	37.0	37.6	37.6	38.8	38.9	40.2	40.3	41.8	43.6
85°	19.9	18.8	19.9	19.4	20.5	19.4	19.9	21.1	21.1	21.7	24.0
87.5°	12.4	13.3	12.1	12.6	12.4	12.7	12.5	12.2	13.0	12.3	12.0
90°	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1	32.0	30.9	27.2
92.5°	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6	34.8	33.0	30.1
95°	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.8
97.5°	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1	43.7	41.4	38.1
100°	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0	44.8	42.4	39.1
102.5°	55.1	54.6	54.1	53.6	53.0	56.3	63.5	70.5	77.6	84.7	100.5
105°	56.7	56.1	55.5	54.9	54.3	79.4	130.0	180.6	231.3	281.9	347.6
107.5°	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4	479.6	516.7	552.6
110°	354.0	394.9	435.8	476.6	517.5	542.8	552.2	561.6	571.1	580.5	577.4



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8	645.6	645.4	642.2
115°	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6	741.7	738.8	736.2
117.5°	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1	831.7	829.5	828.1
120°	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8	890.4	888.1	887.3
122.5°	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0	948.5	946.8	945.7
125°	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9	1030.4	1029.8	1028.6
127.5°	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9	1110.9	1110.1	1108.7
130°	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7	1159.6	1158.5	1157.4
132.5°	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1	1205.9	1204.8	1203.9
135°	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6	1274.5
137.5°	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9	1338.5	1337.1	1336.5
140°	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6	1378.5	1377.3	1376.4
142.5°	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2	1416.3	1415.4	1414.5
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8	1469.2	1468.7	1468.1
147.5°	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9	1516.4	1515.8	1515.2
150°	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8	1545.2	1544.6	1544.0
152.5°	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4	1570.4	1569.3	1569.0
155°	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7	1605.2	1603.8	1603.5
157.5°	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4	1635.6	1633.9	1634.3
160°	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9	1653.2	1651.5	1651.7
162.5°	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8	1668.9	1666.9	1667.2
165°	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0	1689.8	1687.5	1687.8
167.5°	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0	1704.0
170°	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2	1713.2
172.5°	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0	1721.7	1719.4	1719.2
175°	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4	1729.4	1727.4	1727.1
177.5°	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1	1732.3	1730.5	1730.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1413.2	1411.9	1405.3	1397.8	1387.9	1381.4	1376.2	1373.5	1365.0	1354.7	1347.6
5°	1500.6	1483.0	1464.3	1441.4	1420.3	1398.6	1385.2	1369.3	1350.0	1328.4	1313.1
7.5°	1594.1	1559.6	1522.5	1484.2	1446.3	1412.4	1382.3	1356.7	1325.9	1294.8	1273.0
10°	1665.9	1615.4	1563.3	1509.9	1461.3	1415.7	1380.4	1345.9	1309.0	1273.2	1246.3
12.5°	1731.0	1664.7	1604.6	1539.0	1476.8	1422.2	1371.6	1330.9	1286.5	1248.4	1217.7
15°	1813.4	1745.5	1672.8	1573.2	1490.6	1421.5	1359.9	1306.7	1252.8	1205.8	1176.0
17.5°	1890.6	1788.3	1690.7	1607.6	1500.2	1413.8	1338.8	1275.0	1215.8	1166.1	1129.4
20°	1922.4	1823.4	1717.4	1611.4	1505.9	1409.2	1321.9	1251.5	1190.1	1133.8	1099.8
22.5°	1941.6	1829.5	1717.9	1603.9	1491.8	1391.4	1305.0	1227.7	1161.0	1107.5	1065.6
25°	1964.0	1830.5	1707.4	1594.9	1480.7	1371.7	1269.1	1187.1	1115.1	1058.2	1013.7
27.5°	1978.8	1821.7	1676.3	1551.2	1435.3	1326.8	1232.8	1145.8	1072.7	1012.6	964.8
30°	1981.7	1814.6	1652.3	1517.0	1399.2	1299.6	1200.0	1116.8	1039.5	975.6	931.1
32.5°	1985.4	1797.3	1620.0	1476.2	1355.6	1257.0	1166.7	1087.3	1008.1	945.1	899.7
35°	1970.0	1787.7	1570.9	1405.7	1285.0	1189.5	1108.0	1034.7	956.8	895.9	849.6
37.5°	1903.3	1749.6	1520.0	1326.2	1200.0	1111.6	1045.2	981.4	909.8	844.1	800.5
40°	1836.3	1712.1	1480.7	1277.9	1146.1	1055.2	995.5	943.4	874.3	812.7	765.9
42.5°	1736.5	1661.0	1443.2	1227.3	1085.1	997.6	947.2	898.4	837.7	775.2	731.2
45°	1553.3	1563.3	1366.4	1146.7	1000.7	912.9	865.4	831.5	777.6	726.0	680.9
47.5°	1323.6	1416.8	1276.3	1060.8	911.8	829.3	787.8	758.2	721.9	671.2	630.1
50°	1173.6	1306.7	1204.1	1003.2	856.1	774.0	733.0	708.9	677.3	637.5	598.2
52.5°	1035.4	1178.2	1116.9	938.9	795.6	720.6	680.5	660.7	635.6	598.1	562.6
55°	844.3	989.0	975.0	842.0	704.9	637.5	607.0	584.8	567.7	539.7	511.5
57.5°	682.9	820.2	827.4	734.2	625.0	558.4	532.2	515.4	504.3	483.0	457.0
60°	581.3	707.2	731.8	661.5	567.7	509.2	483.4	469.9	461.2	444.1	424.2
62.5°	496.9	604.1	632.0	581.3	512.9	458.1	437.9	424.9	419.0	404.3	386.8
65°	380.3	469.3	496.3	468.1	432.4	388.5	372.0	360.9	355.7	347.5	334.6
67.5°	285.9	350.9	380.4	360.6	347.7	319.9	309.5	303.5	298.9	293.2	282.4
70°	229.7	277.8	308.2	302.9	292.4	277.8	270.1	266.0	261.3	256.7	247.3
72.5°	184.7	217.7	246.3	249.0	240.4	237.5	230.7	229.0	226.2	220.6	215.4
75°	122.4	145.3	165.2	172.9	176.3	179.3	176.3	175.8	175.2	170.5	167.6
77.5°	80.2	92.6	105.1	118.1	123.6	127.6	128.5	130.7	129.2	126.7	125.3
80°	61.6	64.5	73.3	84.4	93.2	96.7	99.0	100.2	99.6	99.0	96.7
82.5°	44.7	47.1	51.2	59.1	66.5	72.3	73.7	73.4	74.7	75.1	73.3
85°	24.0	24.6	25.7	26.9	31.1	37.5	39.3	40.5	41.6	41.6	38.1
87.5°	12.2	11.0	11.2	10.5	11.4	11.3	13.5	15.2	16.3	15.0	15.6
90°	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3	4.1	7.0	9.9
92.5°	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9	23.2	22.3	21.5
95°	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5	66.8	55.1	43.3
97.5°	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8	152.6	147.3	142.0
100°	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6	223.3	228.9	234.7
102.5°	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5	289.6	293.8	297.8
105°	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6	386.8	389.9	393.0
107.5°	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1	489.6	492.1	494.6
110°	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0	558.4	560.6	562.9





TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0	624.1	626.1	628.2
115°	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5	721.3	723.0	724.7
117.5°	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0	816.1	818.2	820.4
120°	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7	875.3	877.9	880.5
122.5°	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5	934.5	936.7	938.7
125°	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3	1016.6	1018.9	1021.1
127.5°	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6	1095.9	1098.2	1100.4
130°	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0	1145.3	1147.6	1149.9
132.5°	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4	1192.7	1195.0	1197.2
135°	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7	1264.5	1266.2	1267.9
137.5°	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5	1326.7	1328.9	1331.0
140°	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7	1367.4	1369.2	1370.9
142.5°	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8	1405.5	1407.2	1408.9
145°	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1	1459.1	1461.1	1463.1
147.5°	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3	1508.6	1509.9	1511.2
150°	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2	1539.0	1539.9	1540.8
152.5°	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0	1566.4	1566.8	1567.2
155°	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1	1604.6	1604.0	1603.4
157.5°	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5	1635.5	1635.4	1635.3
160°	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1	1653.7	1653.5	1653.2
162.5°	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5	1670.8	1670.1	1669.3
165°	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6	1691.8	1690.9	1690.1
167.5°	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1	1708.0	1706.8	1705.7
170°	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4	1717.3	1716.1	1714.9
172.5°	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6	1723.2	1721.8	1720.5
175°	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5	1731.1	1729.7	1728.3
177.5°	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6	1733.5	1732.3	1731.2
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1345.3	1339.2	1335.0	1325.6	1319.6	1312.9	1306.4	1310.6	1310.2	1309.7	1309.7
5°	1300.2	1286.7	1274.5	1258.6	1248.6	1236.3	1226.9	1225.8	1228.1	1220.0	1215.2
7.5°	1255.4	1237.0	1219.6	1202.1	1183.6	1168.8	1159.6	1155.2	1149.3	1144.2	1138.9
10°	1224.0	1202.4	1185.3	1163.6	1143.8	1126.2	1115.1	1107.4	1103.3	1099.2	1091.6
12.5°	1191.7	1170.4	1148.8	1124.3	1105.4	1084.9	1076.6	1068.1	1060.2	1055.6	1045.2
15°	1144.4	1116.8	1094.0	1068.2	1047.1	1027.2	1015.5	998.4	996.1	990.2	979.7
17.5°	1096.9	1067.0	1035.4	1016.4	992.6	971.8	954.0	948.3	931.5	925.2	916.0
20°	1059.4	1031.8	1007.8	982.7	948.0	928.7	914.6	907.1	893.5	885.4	879.5
22.5°	1027.0	999.0	971.3	941.8	913.3	891.7	881.4	869.5	862.1	850.7	844.3
25°	980.9	950.4	917.0	885.4	864.9	848.4	832.1	821.5	811.0	805.6	793.9
27.5°	927.2	895.4	864.1	840.1	814.9	798.7	783.9	774.5	761.8	752.9	746.5
30°	897.7	860.1	833.2	811.5	779.3	764.1	752.9	741.2	731.8	722.5	716.0
32.5°	863.4	829.2	803.7	776.9	752.1	735.5	721.1	710.8	702.7	693.9	687.4
35°	809.8	781.1	754.7	727.7	709.6	692.6	675.6	666.8	659.2	651.0	645.1
37.5°	761.2	734.4	709.4	683.8	661.2	647.5	633.8	627.1	616.7	611.2	605.3
40°	731.2	704.9	678.0	653.3	629.9	619.3	607.0	597.1	587.7	583.6	577.1
42.5°	698.4	672.1	649.4	622.8	603.6	589.4	578.0	567.1	560.1	554.1	550.4
45°	649.8	626.4	604.1	577.7	559.6	547.3	534.3	524.4	518.0	513.8	507.4
47.5°	602.6	579.1	556.6	533.6	516.0	501.9	489.0	482.1	473.6	468.6	464.2
50°	568.3	547.3	523.2	502.1	484.6	470.5	459.9	451.2	443.6	437.1	434.2
52.5°	536.9	514.4	493.7	474.1	455.5	439.5	430.0	420.7	415.0	407.6	404.2
55°	485.2	463.5	445.9	426.5	408.4	394.9	383.2	375.0	369.1	360.9	356.3
57.5°	436.5	417.1	396.1	379.4	360.6	349.2	339.5	328.4	321.2	314.8	310.2
60°	403.7	381.4	363.3	347.5	331.1	316.4	307.6	298.9	291.2	284.7	280.7
62.5°	369.5	350.1	332.8	315.6	300.6	287.8	277.6	270.3	263.6	259.4	255.4
65°	317.0	301.8	284.2	270.1	256.1	246.7	238.5	232.0	227.3	224.4	220.9
67.5°	268.7	253.9	238.6	224.8	215.4	208.3	202.9	197.3	195.0	191.2	188.9
70°	237.3	222.1	208.6	198.0	188.6	183.4	179.9	175.8	173.4	168.8	166.4
72.5°	203.1	192.1	182.4	173.7	166.2	161.4	156.9	151.9	148.1	142.9	140.6
75°	160.0	150.0	142.4	136.6	131.8	125.4	118.9	113.7	111.9	110.1	109.6
77.5°	118.5	112.2	106.7	101.7	95.8	91.2	89.8	88.6	88.3	87.3	87.3
80°	93.2	87.3	83.2	77.3	73.8	73.8	73.8	72.7	73.3	73.3	73.3
82.5°	69.2	63.9	61.6	59.5	58.8	59.3	59.3	59.5	59.2	60.1	59.7
85°	35.7	36.3	37.5	36.9	37.5	37.5	38.7	38.1	38.7	37.5	38.7
87.5°	15.7	17.7	18.9	20.1	21.4	21.6	22.4	22.6	23.2	23.5	23.7
90°	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1	34.4	35.5	36.3
92.5°	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6	38.5	40.3	41.3
95°	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9	45.9	47.9	48.9
97.5°	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1	48.3	50.6	51.9
100°	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0	49.3	51.7	53.0
102.5°	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5	63.5	56.3	53.0
105°	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6	130.0	79.4	54.3
107.5°	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4	405.3	368.2	330.5
110°	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6	552.2	542.8	517.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8	645.9	646.1	641.9
115°	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6	747.4	750.3	752.3
117.5°	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1	836.3	838.6	839.9
120°	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8	895.0	897.3	898.5
122.5°	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0	951.7	953.3	954.2
125°	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9	1031.5	1032.0	1032.6
127.5°	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9	1112.8	1113.7	1113.9
130°	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7	1161.9	1163.0	1163.3
132.5°	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1	1208.2	1209.4	1209.5
135°	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0
137.5°	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9	1341.3	1342.6	1343.0
140°	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6	1380.7	1381.8	1382.2
142.5°	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2	1418.2	1419.0	1419.1
145°	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8	1470.4	1470.9	1471.3
147.5°	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9	1517.5	1518.1	1517.7
150°	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8	1546.4	1546.9	1546.8
152.5°	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4	1572.4	1573.5	1573.3
155°	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7	1608.1	1609.6	1609.4
157.5°	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4	1639.1	1640.8	1640.5
160°	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9	1656.6	1658.3	1658.2
162.5°	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8	1672.8	1674.6	1674.7
165°	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0	1694.4	1696.7	1696.8
167.5°	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1
170°	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4
172.5°	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0	1726.3	1728.5	1728.5
175°	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4	1733.4	1735.4	1735.3
177.5°	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1	1735.9	1737.8	1737.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1304.1	1303.6	1304.1	1302.2	1304.1	1303.6	1304.1	1309.7	1309.7	1310.2	1310.6
5°	1213.5	1212.9	1211.2	1205.8	1211.2	1212.9	1213.5	1215.2	1220.0	1228.1	1225.8
7.5°	1134.4	1133.6	1128.4	1128.5	1128.4	1133.6	1134.4	1138.9	1144.2	1149.3	1155.2
10°	1087.5	1088.0	1081.1	1076.9	1081.1	1088.0	1087.5	1091.6	1099.2	1103.3	1107.4
12.5°	1042.1	1039.3	1033.7	1029.2	1033.7	1039.3	1042.1	1045.2	1055.6	1060.2	1068.1
15°	982.1	976.2	962.1	963.3	962.1	976.2	982.1	979.7	990.2	996.1	998.4
17.5°	911.4	907.1	906.8	898.6	906.8	907.1	911.4	916.0	925.2	931.5	948.3
20°	870.1	867.2	868.3	860.1	868.3	867.2	870.1	879.5	885.4	893.5	907.1
22.5°	837.8	834.8	829.9	827.3	829.9	834.8	837.8	844.3	850.7	862.1	869.5
25°	790.4	785.7	781.1	784.0	781.1	785.7	790.4	793.9	805.6	811.0	821.5
27.5°	743.1	739.6	734.9	734.3	734.9	739.6	743.1	746.5	752.9	761.8	774.5
30°	713.1	709.6	707.2	704.3	707.2	709.6	713.1	716.0	722.5	731.8	741.2
32.5°	682.6	681.9	677.7	677.1	677.7	681.9	682.6	687.4	693.9	702.7	710.8
35°	642.7	639.3	638.1	638.7	638.1	639.3	642.7	645.1	651.0	659.2	666.8
37.5°	604.9	600.2	598.1	596.0	598.1	600.2	604.9	605.3	611.2	616.7	627.1
40°	577.7	573.1	571.9	570.7	571.9	573.1	577.7	577.1	583.6	587.7	597.1
42.5°	547.3	545.4	544.7	542.6	544.7	545.4	547.3	550.4	554.1	560.1	567.1
45°	505.7	505.1	501.5	502.7	501.5	505.1	505.7	507.4	513.8	518.0	524.4
47.5°	461.8	459.3	456.8	458.4	456.8	459.3	461.8	464.2	468.6	473.6	482.1
50°	431.9	430.7	425.4	426.5	425.4	430.7	431.9	434.2	437.1	443.6	451.2
52.5°	401.8	397.4	395.4	394.7	395.4	397.4	401.8	404.2	407.6	415.0	420.7
55°	352.1	346.9	344.6	343.4	344.6	346.9	352.1	356.3	360.9	369.1	375.0
57.5°	303.4	302.0	300.1	301.4	300.1	302.0	303.4	310.2	314.8	321.2	328.4
60°	274.8	274.8	274.8	274.2	274.8	274.8	274.8	280.7	284.7	291.2	298.9
62.5°	252.8	251.3	250.9	251.8	250.9	251.3	252.8	255.4	259.4	263.6	270.3
65°	219.1	218.5	216.2	215.6	216.2	218.5	219.1	220.9	224.4	227.3	232.0
67.5°	187.4	185.3	184.6	183.7	184.6	185.3	187.4	188.9	191.2	195.0	197.3
70°	163.5	162.3	158.8	159.4	158.8	162.3	163.5	166.4	168.8	173.4	175.8
72.5°	137.7	136.6	135.8	135.0	135.8	136.6	137.7	140.6	142.9	148.1	151.9
75°	109.0	108.4	107.8	110.1	107.8	108.4	109.0	109.6	110.1	111.9	113.7
77.5°	87.3	87.3	87.6	86.7	87.6	87.3	87.3	87.3	87.3	88.3	88.6
80°	73.3	73.3	72.7	72.7	72.7	73.3	73.3	73.3	73.3	73.3	72.7
82.5°	58.7	59.2	59.5	58.6	59.5	59.2	58.7	59.7	60.1	59.2	59.5
85°	38.7	38.1	39.3	38.7	39.3	38.1	38.7	38.7	37.5	38.7	38.1
87.5°	24.7	23.9	24.0	24.6	24.0	23.9	24.7	23.7	23.5	23.2	22.6
90°	36.9	37.5	38.1	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1
92.5°	41.7	42.0	42.4	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9
97.5°	52.2	52.4	52.8	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1
100°	53.2	53.5	53.8	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0
102.5°	53.6	54.1	54.6	55.1	54.6	54.1	53.6	53.0	56.3	63.5	70.5
105°	54.9	55.5	56.1	56.7	56.1	55.5	54.9	54.3	79.4	130.0	180.6
107.5°	292.4	254.2	216.0	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4
110°	476.6	435.8	394.9	354.0	394.9	435.8	476.6	517.5	542.8	552.2	561.6



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	633.2	624.6	616.0	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8
115°	753.5	754.6	755.7	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6
117.5°	840.1	840.3	840.6	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1
120°	898.5	898.5	898.5	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8
122.5°	954.4	954.6	954.8	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0
125°	1033.2	1033.7	1034.3	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9
127.5°	1113.4	1112.8	1112.2	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9
130°	1162.8	1162.2	1161.6	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7
132.5°	1208.8	1208.0	1207.1	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1
135°	1278.2	1277.3	1276.4	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3
137.5°	1342.5	1341.9	1341.3	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9
140°	1381.6	1381.0	1380.4	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6
142.5°	1418.3	1417.5	1416.7	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8
147.5°	1516.4	1515.1	1513.7	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9
150°	1545.9	1545.1	1544.2	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8
152.5°	1572.0	1570.6	1569.3	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4
155°	1607.7	1605.9	1604.2	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7
157.5°	1638.3	1636.1	1633.8	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4
160°	1656.1	1654.2	1652.2	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9
162.5°	1673.0	1671.2	1669.5	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8
165°	1694.8	1692.8	1690.7	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0
167.5°	1710.8	1708.6	1706.2	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6
170°	1720.1	1717.8	1715.5	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8
172.5°	1726.0	1723.5	1720.9	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0
175°	1732.9	1730.7	1728.4	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4
177.5°	1735.3	1733.0	1730.7	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1306.4	1312.9	1319.6	1325.6	1335.0	1339.2	1345.3	1347.6	1354.7	1365.0	1373.5
5°	1226.9	1236.3	1248.6	1258.6	1274.5	1286.7	1300.2	1313.1	1328.4	1350.0	1369.3
7.5°	1159.6	1168.8	1183.6	1202.1	1219.6	1237.0	1255.4	1273.0	1294.8	1325.9	1356.7
10°	1115.1	1126.2	1143.8	1163.6	1185.3	1202.4	1224.0	1246.3	1273.2	1309.0	1345.9
12.5°	1076.6	1084.9	1105.4	1124.3	1148.8	1170.4	1191.7	1217.7	1248.4	1286.5	1330.9
15°	1015.5	1027.2	1047.1	1068.2	1094.0	1116.8	1144.4	1176.0	1205.8	1252.8	1306.7
17.5°	954.0	971.8	992.6	1016.4	1035.4	1067.0	1096.9	1129.4	1166.1	1215.8	1275.0
20°	914.6	928.7	948.0	982.7	1007.8	1031.8	1059.4	1099.8	1133.8	1190.1	1251.5
22.5°	881.4	891.7	913.3	941.8	971.3	999.0	1027.0	1065.6	1107.5	1161.0	1227.7
25°	832.1	848.4	864.9	885.4	917.0	950.4	980.9	1013.7	1058.2	1115.1	1187.1
27.5°	783.9	798.7	814.9	840.1	864.1	895.4	927.2	964.8	1012.6	1072.7	1145.8
30°	752.9	764.1	779.3	811.5	833.2	860.1	897.7	931.1	975.6	1039.5	1116.8
32.5°	721.1	735.5	752.1	776.9	803.7	829.2	863.4	899.7	945.1	1008.1	1087.3
35°	675.6	692.6	709.6	727.7	754.7	781.1	809.8	849.6	895.9	956.8	1034.7
37.5°	633.8	647.5	661.2	683.8	709.4	734.4	761.2	800.5	844.1	909.8	981.4
40°	607.0	619.3	629.9	653.3	678.0	704.9	731.2	765.9	812.7	874.3	943.4
42.5°	578.0	589.4	603.6	622.8	649.4	672.1	698.4	731.2	775.2	837.7	898.4
45°	534.3	547.3	559.6	577.7	604.1	626.4	649.8	680.9	726.0	777.6	831.5
47.5°	489.0	501.9	516.0	533.6	556.6	579.1	602.6	630.1	671.2	721.9	758.2
50°	459.9	470.5	484.6	502.1	523.2	547.3	568.3	598.2	637.5	677.3	708.9
52.5°	430.0	439.5	455.5	474.1	493.7	514.4	536.9	562.6	598.1	635.6	660.7
55°	383.2	394.9	408.4	426.5	445.9	463.5	485.2	511.5	539.7	567.7	584.8
57.5°	339.5	349.2	360.6	379.4	396.1	417.1	436.5	457.0	483.0	504.3	515.4
60°	307.6	316.4	331.1	347.5	363.3	381.4	403.7	424.2	444.1	461.2	469.9
62.5°	277.6	287.8	300.6	315.6	332.8	350.1	369.5	386.8	404.3	419.0	424.9
65°	238.5	246.7	256.1	270.1	284.2	301.8	317.0	334.6	347.5	355.7	360.9
67.5°	202.9	208.3	215.4	224.8	238.6	253.9	268.7	282.4	293.2	298.9	303.5
70°	179.9	183.4	188.6	198.0	208.6	222.1	237.3	247.3	256.7	261.3	266.0
72.5°	156.9	161.4	166.2	173.7	182.4	192.1	203.1	215.4	220.6	226.2	229.0
75°	118.9	125.4	131.8	136.6	142.4	150.0	160.0	167.6	170.5	175.2	175.8
77.5°	89.8	91.2	95.8	101.7	106.7	112.2	118.5	125.3	126.7	129.2	130.7
80°	73.8	73.8	73.8	77.3	83.2	87.3	93.2	96.7	99.0	99.6	100.2
82.5°	59.3	59.3	58.8	59.5	61.6	63.9	69.2	73.3	75.1	74.7	73.4
85°	38.7	37.5	37.5	36.9	37.5	36.3	35.7	38.1	41.6	41.6	40.5
87.5°	22.4	21.6	21.4	20.1	18.9	17.7	15.7	15.6	15.0	16.3	15.2
90°	32.0	30.9	27.2	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3
92.5°	34.8	33.0	30.1	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9
95°	41.9	39.9	36.8	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5
97.5°	43.7	41.4	62.1	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8
100°	44.8	42.4	87.1	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6
102.5°	77.6	84.7	133.5	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5
105°	231.3	281.9	307.6	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6
107.5°	479.6	516.7	512.6	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1
110°	571.1	580.5	577.4	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.6	645.4	642.2	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0
115°	741.7	738.8	736.2	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5
117.5°	831.7	829.5	828.1	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0
120°	890.4	888.1	887.3	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7
122.5°	948.5	946.8	945.7	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5
125°	1030.4	1029.8	1028.6	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3
127.5°	1110.9	1110.1	1108.7	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6
130°	1159.6	1158.5	1157.4	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0
132.5°	1205.9	1204.8	1203.9	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4
135°	1276.4	1275.6	1274.5	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7
137.5°	1338.5	1337.1	1336.5	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5
140°	1378.5	1377.3	1376.4	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7
142.5°	1416.3	1415.4	1414.5	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8
145°	1469.2	1468.7	1468.1	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1
147.5°	1516.4	1515.8	1515.2	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3
150°	1545.2	1544.6	1544.0	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2
152.5°	1570.4	1569.3	1569.0	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0
155°	1605.2	1603.8	1603.5	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1
157.5°	1635.6	1633.9	1634.3	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5
160°	1653.2	1651.5	1651.7	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1
162.5°	1668.9	1666.9	1667.2	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5
165°	1689.8	1687.5	1687.8	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6
167.5°	1706.2	1704.0	1704.0	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1
170°	1715.5	1713.2	1713.2	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4
172.5°	1721.7	1719.4	1719.2	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6
175°	1729.4	1727.4	1727.1	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5
177.5°	1732.3	1730.5	1730.3	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1376.2	1381.4	1387.9	1397.8	1405.3	1411.9	1413.2	1415.1	1419.9	1427.8	1433.9
5°	1385.2	1398.6	1420.3	1441.4	1464.3	1483.0	1500.6	1512.9	1524.6	1549.2	1569.2
7.5°	1382.3	1412.4	1446.3	1484.2	1522.5	1559.6	1594.1	1625.0	1655.6	1691.5	1732.4
10°	1380.4	1415.7	1461.3	1509.9	1563.3	1615.4	1665.9	1705.1	1750.8	1791.8	1843.9
12.5°	1371.6	1422.2	1476.8	1539.0	1604.6	1664.7	1731.0	1785.2	1837.5	1896.8	1957.4
15°	1359.9	1421.5	1490.6	1573.2	1672.8	1745.5	1813.4	1907.8	1972.3	2036.7	2123.5
17.5°	1338.8	1413.8	1500.2	1607.6	1690.7	1788.3	1890.6	1965.1	2051.9	2142.8	2221.3
20°	1321.9	1409.2	1505.9	1611.4	1717.4	1823.4	1922.4	2011.6	2101.2	2206.1	2270.5
22.5°	1305.0	1391.4	1491.8	1603.9	1717.9	1829.5	1941.6	2046.3	2147.1	2252.9	2335.2
25°	1269.1	1371.7	1480.7	1594.9	1707.4	1830.5	1964.0	2080.7	2205.5	2314.5	2392.4
27.5°	1232.8	1326.8	1435.3	1551.2	1676.3	1821.7	1978.8	2111.3	2236.4	2314.5	2339.0
30°	1200.0	1299.6	1399.2	1517.0	1652.3	1814.6	1981.7	2133.4	2235.9	2269.9	2244.7
32.5°	1166.7	1257.0	1355.6	1476.2	1620.0	1797.3	1985.4	2120.3	2182.0	2156.0	2053.5
35°	1108.0	1189.5	1285.0	1405.7	1570.9	1787.7	1970.0	2061.3	2046.1	1899.6	1706.2
37.5°	1045.2	1111.6	1200.0	1326.2	1520.0	1749.6	1903.3	1916.8	1785.0	1560.1	1336.8
40°	995.5	1055.2	1146.1	1277.9	1480.7	1712.1	1836.3	1781.8	1577.4	1327.1	1140.8
42.5°	947.2	997.6	1085.1	1227.3	1443.2	1661.0	1736.5	1617.8	1381.9	1145.3	975.9
45°	865.4	912.9	1000.7	1146.7	1366.4	1563.3	1553.3	1347.0	1110.9	920.5	779.9
47.5°	787.8	829.3	911.8	1060.8	1276.3	1416.8	1323.6	1104.1	903.9	751.1	650.7
50°	733.0	774.0	856.1	1003.2	1204.1	1306.7	1173.6	962.1	778.7	652.1	572.5
52.5°	680.5	720.6	795.6	938.9	1116.9	1178.2	1035.4	839.3	686.4	577.1	508.7
55°	607.0	637.5	704.9	842.0	975.0	989.0	844.3	680.3	554.3	478.1	431.3
57.5°	532.2	558.4	625.0	734.2	827.4	820.2	682.9	541.1	456.2	399.6	365.7
60°	483.4	509.2	567.7	661.5	731.8	707.2	581.3	467.0	394.3	352.8	325.8
62.5°	437.9	458.1	512.9	581.3	632.0	604.1	496.9	402.3	344.7	309.6	288.3
65°	372.0	388.5	432.4	468.1	496.3	469.3	380.3	314.6	273.0	248.4	233.8
67.5°	309.5	319.9	347.7	360.6	380.4	350.9	285.9	242.0	218.3	197.6	187.4
70°	270.1	277.8	292.4	302.9	308.2	277.8	229.7	197.4	177.5	162.9	156.4
72.5°	230.7	237.5	240.4	249.0	246.3	217.7	184.7	159.0	144.7	134.7	126.5
75°	176.3	179.3	176.3	172.9	165.2	145.3	122.4	109.6	99.0	94.4	91.4
77.5°	128.5	127.6	123.6	118.1	105.1	92.6	80.2	75.9	71.4	68.9	67.8
80°	99.0	96.7	93.2	84.4	73.3	64.5	61.6	58.6	56.8	53.9	53.3
82.5°	73.7	72.3	66.5	59.1	51.2	47.1	44.7	43.6	41.8	40.3	40.2
85°	39.3	37.5	31.1	26.9	25.7	24.6	24.0	24.0	21.7	21.1	21.1
87.5°	13.5	11.3	11.4	10.5	11.2	11.0	12.2	12.0	12.3	13.0	12.2
90°	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1
92.5°	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6
95°	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9
97.5°	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1
100°	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0
102.5°	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5
105°	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6
107.5°	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4
110°	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6





TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8
115°	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6
117.5°	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1
120°	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8
122.5°	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0
125°	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9
127.5°	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9
130°	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7
132.5°	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1
135°	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3
137.5°	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9
140°	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6
142.5°	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2
145°	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8
147.5°	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9
150°	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8
152.5°	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4
155°	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7
157.5°	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4
160°	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9
162.5°	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8
165°	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0
167.5°	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6
170°	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8
172.5°	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0
175°	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4
177.5°	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1443.7	1443.7	1445.6	1452.7	1453.6	1459.7	1457.8
5°	1586.7	1597.8	1602.0	1619.5	1630.0	1634.8	1625.4
7.5°	1761.6	1792.9	1807.8	1826.3	1842.5	1847.4	1834.7
10°	1889.0	1921.8	1949.4	1966.4	1982.2	1992.8	2006.2
12.5°	2012.3	2052.6	2078.8	2102.8	2119.1	2132.4	2134.7
15°	2146.3	2207.3	2253.5	2287.5	2304.5	2313.2	2309.8
17.5°	2281.4	2337.9	2370.8	2405.5	2429.1	2430.3	2430.9
20°	2357.8	2412.9	2451.0	2476.8	2503.1	2502.0	2507.8
22.5°	2408.9	2452.3	2481.5	2500.2	2509.2	2504.7	2505.9
25°	2432.8	2445.7	2440.4	2410.5	2403.0	2375.4	2380.1
27.5°	2309.5	2248.6	2185.6	2104.5	2040.5	1989.3	1991.9
30°	2142.2	2034.4	1911.3	1808.2	1715.6	1689.9	1634.8
32.5°	1908.3	1746.5	1602.4	1506.3	1426.8	1405.3	1357.3
35°	1511.7	1354.7	1206.4	1117.4	1082.2	1033.0	1032.4
37.5°	1175.0	1036.7	958.4	891.6	856.5	826.7	823.8
40°	988.5	880.6	821.5	773.4	738.9	716.6	711.4
42.5°	858.2	770.9	715.6	685.8	659.2	647.7	639.1
45°	700.8	642.2	603.5	576.5	564.3	555.4	550.8
47.5°	586.2	546.9	520.6	502.7	492.7	483.4	485.9
50°	523.8	491.6	472.3	455.3	447.6	441.2	441.8
52.5°	473.6	444.7	429.1	416.8	407.3	402.8	400.5
55°	401.9	383.7	368.0	359.2	353.9	347.5	345.7
57.5°	342.9	328.8	315.9	306.0	304.7	298.5	299.3
60°	303.5	291.8	281.3	276.0	271.9	266.6	268.4
62.5°	271.2	261.3	251.8	247.4	243.3	239.4	240.2
65°	222.1	212.7	206.8	204.5	202.8	201.0	199.2
67.5°	176.9	171.3	167.6	162.6	158.9	158.3	156.5
70°	148.9	141.2	134.7	128.3	126.6	126.0	126.6
72.5°	119.3	114.5	112.7	109.6	109.3	107.7	108.7
75°	89.6	87.9	86.7	84.4	84.4	84.4	84.4
77.5°	66.1	65.0	64.3	63.9	63.3	62.4	62.3
80°	51.6	51.0	49.8	49.8	49.2	49.8	49.2
82.5°	38.9	38.8	37.6	37.6	37.0	36.7	37.0
85°	19.9	19.4	20.5	19.4	19.9	18.8	19.9
87.5°	12.5	12.7	12.4	12.6	12.1	13.3	12.4
90°	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332466-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)