

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332468-935

Luminaire Tested: **S123RDIW-S1000D1535U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332468-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8552.5 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	40	39	33
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22	18
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	14	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	1.6
10°-20°	377.5	4.4
20°-30°	543.6	6.4
30°-40°	612.3	7.2
40°-50°	585.8	6.8
50°-60°	479.7	5.6
60°-70°	323.7	3.8
70°-80°	162.8	1.9
80°-90°	47.9	0.6
90°-100°	63.0	0.7
100°-110°	300.2	3.5
110°-120°	721.1	8.4
120°-130°	918.3	10.7
130°-140°	981.1	11.5
140°-150°	917.5	10.7
150°-160°	740.1	8.7
160°-170°	477.6	5.6
170°-180°	164.6	1.9
0°-30°	1056.8	12.4
0°-40°	1669.1	19.5
0°-60°	2734.6	32.0
0°-90°	3269.0	38.2
90°-120°	1084.3	12.7
90°-150°	3901.2	45.6
90°-180°	5283.0	61.8
0°-180°	8552.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	14	31	36	39	7
95°	78	29	40	48	49	97
105°	384	390	282	67	57	407
115°	720	728	739	751	757	710
125°	1014	1024	1030	1032	1035	905
135°	1263	1270	1276	1279	1276	972
145°	1457	1466	1469	1471	1471	912
155°	1605	1603	1604	1610	1603	739
165°	1693	1689	1688	1697	1689	478
175°	1732	1726	1727	1735	1726	165
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.7	21.0	19.3	17.6	15.8	15.4	16.1	16.9	17.7	18.3	18.4
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0
92.5°	23.9	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8
95°	78.5	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9
97.5°	157.8	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7
100°	217.6	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8
102.5°	285.5	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6
105°	383.6	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3
107.5°	487.1	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6
110°	556.0	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.0	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6
115°	719.5	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7
117.5°	814.0	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7
120°	872.7	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4
122.5°	932.5	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5
125°	1014.3	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4
127.5°	1093.6	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9
130°	1143.0	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6
132.5°	1190.4	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9
135°	1262.7	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4
137.5°	1324.5	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5
140°	1365.7	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5
142.5°	1403.8	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3
145°	1457.1	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2
147.5°	1507.3	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4
150°	1538.2	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2
152.5°	1566.0	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4
155°	1605.1	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2
157.5°	1635.5	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6
160°	1654.1	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2
162.5°	1671.5	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9
165°	1692.6	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8
167.5°	1709.1	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2
170°	1718.4	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5
172.5°	1724.6	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7
175°	1732.5	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4
177.5°	1734.6	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	18.4	18.4	18.4	18.4	18.3	18.3	18.2	18.0
90°	33.1	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	36.6	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.1	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	47.0	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	70.5	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	180.6	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	442.4	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	561.6	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332468-935

CATALOG NUMBER: S123RDIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.8	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	744.6	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	834.1	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	892.8	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	950.0	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1030.9	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1111.9	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1160.7	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1207.1	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1339.9	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1379.6	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1417.2	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1469.8	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1516.9	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1545.8	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1571.4	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1606.7	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1637.4	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1654.9	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1670.8	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1692.0	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1724.0	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1731.4	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1734.1	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)