

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332452-935

Luminaire Tested: **S123RDIW-S1000D460U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332452-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4853.4 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	46	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	2.8
10°-20°	377.5	7.8
20°-30°	543.6	11.2
30°-40°	612.3	12.6
40°-50°	585.8	12.1
50°-60°	479.7	9.9
60°-70°	323.7	6.7
70°-80°	162.8	3.4
80°-90°	44.5	0.9
90°-100°	18.9	0.4
100°-110°	90.2	1.9
110°-120°	216.7	4.5
120°-130°	276.0	5.7
130°-140°	294.8	6.1
140°-150°	275.7	5.7
150°-160°	222.4	4.6
160°-170°	143.5	3.0
170°-180°	49.5	1.0
0°-30°	1056.8	21.8
0°-40°	1669.1	34.4
0°-60°	2734.6	56.3
0°-90°	3265.6	67.3
90°-120°	325.9	6.7
90°-150°	1172.4	24.2
90°-180°	1588.0	32.7
0°-180°	4853.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	0	4	9	11	12	4
95°	24	9	12	15	15	29
105°	115	117	85	20	17	122
115°	216	219	222	226	228	213
125°	305	308	309	310	311	272
135°	379	382	383	384	383	292
145°	438	440	441	442	442	274
155°	482	482	482	484	482	222
165°	509	508	507	510	508	144
175°	521	519	519	522	519	50
180°	521	521	521	521	521	



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.5	18.3	16.2	14.1	13.2	13.3	13.6	13.9	14.0	13.9
90°	0.3	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6
92.5°	7.2	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4
95°	23.6	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6
97.5°	47.4	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2
100°	65.3	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4
102.5°	85.8	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3
105°	115.3	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5
107.5°	146.4	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1
110°	167.1	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.9	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0
115°	216.2	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9
117.5°	244.6	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9
120°	262.3	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6
122.5°	280.3	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0
125°	304.8	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6
127.5°	328.6	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9
130°	343.5	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4
132.5°	357.7	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4
135°	379.4	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6
137.5°	398.0	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3
140°	410.4	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2
142.5°	421.9	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6
145°	437.9	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5
147.5°	453.0	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7
150°	462.3	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3
152.5°	470.6	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9
155°	482.3	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4
157.5°	491.5	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5
160°	497.1	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8
162.5°	502.3	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5
165°	508.7	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8
167.5°	513.7	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8
170°	516.4	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6
172.5°	518.2	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4
175°	520.6	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7
177.5°	521.2	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	13.8	13.6	13.5	13.3	13.2	13.0	12.8	12.7
90°	10.0	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.0	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.2	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	13.9	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.1	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	21.2	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	54.2	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	132.9	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	168.8	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332452-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	194.1	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	223.8	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	250.6	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	268.3	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	285.5	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	309.8	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.2	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	348.8	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	362.7	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	402.7	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.6	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	425.9	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.7	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	455.9	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.5	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.3	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	482.8	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.1	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.3	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.1	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	508.5	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.1	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.3	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.2	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)