

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332456-935

Luminaire Tested: **S123RDIW-S1000D755U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332456-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D755U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5867.2 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	84	78	72	84	78	73	68	67	63	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	57	60	55	51	51	48	45	43	41	38	35
4	76	66	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.7	2.3
10°-20°	377.5	6.4
20°-30°	543.6	9.3
30°-40°	612.3	10.4
40°-50°	585.8	10.0
50°-60°	479.7	8.2
60°-70°	323.7	5.5
70°-80°	162.8	2.8
80°-90°	45.5	0.8
90°-100°	31.0	0.5
100°-110°	147.8	2.5
110°-120°	355.0	6.0
120°-130°	452.0	7.7
130°-140°	482.9	8.2
140°-150°	451.6	7.7
150°-160°	364.3	6.2
160°-170°	235.1	4.0
170°-180°	81.0	1.4
0°-30°	1056.8	18.0
0°-40°	1669.1	28.4
0°-60°	2734.6	46.6
0°-90°	3266.5	55.7
90°-120°	533.7	9.1
90°-150°	1920.2	32.7
90°-180°	2601.0	44.3
0°-180°	5867.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	7	15	18	19	5
95°	39	14	20	24	24	48
105°	189	192	139	33	28	200
115°	354	358	364	370	373	349
125°	499	504	507	508	509	446
135°	622	625	628	630	628	478
145°	717	722	723	724	724	449
155°	790	789	790	792	789	364
165°	833	831	831	835	831	235
175°	853	850	850	854	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.6	18.6	16.6	14.6	13.8	14.1	14.5	14.9	15.2	15.2
90°	0.6	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8
92.5°	11.8	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1
95°	38.7	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7
97.5°	77.7	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5
100°	107.1	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0
102.5°	140.5	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2
105°	188.8	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8
107.5°	239.7	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0
110°	273.7	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1



TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.2	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8
115°	354.1	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1
117.5°	400.7	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4
120°	429.6	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3
122.5°	459.0	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8
125°	499.3	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1
127.5°	538.3	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8
130°	562.6	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8
132.5°	585.9	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6
135°	621.6	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3
137.5°	651.9	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8
140°	672.2	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5
142.5°	691.0	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2
145°	717.2	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2
147.5°	741.9	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4
150°	757.2	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6
152.5°	770.8	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9
155°	790.1	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1
157.5°	805.0	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1
160°	814.2	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7
162.5°	822.8	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5
165°	833.2	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7
167.5°	841.3	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8
170°	845.8	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4
172.5°	848.9	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5
175°	852.8	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3
177.5°	853.8	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	15.1	15.0	14.8	14.7	14.6	14.4	14.3	14.1
90°	16.4	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.0	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	21.6	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	22.6	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	23.2	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	34.7	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	88.9	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	217.7	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	276.5	271.8	267.2	254.8	234.6	214.5	194.3	174.3





TEST NUMBER: P332456-935

CATALOG NUMBER: S123RDIW-S1000D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	317.9	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	366.5	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	410.5	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	439.5	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	467.6	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.4	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.3	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.4	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.2	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	659.5	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.1	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	697.6	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.5	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.7	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	760.9	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	773.4	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	790.8	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.0	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	814.6	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	822.4	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	832.8	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	848.6	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	852.2	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	853.6	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)