

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332484-935

Luminaire Tested: **S123RDIW-S1165D1320U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332484-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8318.3 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28				
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	1.9
10°-20°	436.0	5.2
20°-30°	627.8	7.5
30°-40°	707.2	8.5
40°-50°	676.5	8.1
50°-60°	554.0	6.7
60°-70°	373.8	4.5
70°-80°	188.1	2.3
80°-90°	53.9	0.6
90°-100°	54.2	0.7
100°-110°	258.2	3.1
110°-120°	620.2	7.5
120°-130°	789.8	9.5
130°-140°	843.9	10.1
140°-150°	789.1	9.5
150°-160°	636.5	7.7
160°-170°	410.8	4.9
170°-180°	141.6	1.7
0°-30°	1220.5	14.7
0°-40°	1927.7	23.2
0°-60°	3158.3	38.0
0°-90°	3774.0	45.4
90°-120°	932.6	11.2
90°-150°	3355.4	40.3
90°-180°	4544.0	54.6
0°-180°	8318.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	1	12	27	31	33	7
95°	68	25	34	42	42	83
105°	330	336	242	58	49	350
115°	619	626	636	646	651	611
125°	872	881	886	888	890	779
135°	1086	1093	1097	1100	1097	836
145°	1253	1261	1263	1265	1265	784
155°	1380	1378	1379	1384	1378	636
165°	1456	1453	1451	1459	1452	411
175°	1490	1485	1486	1493	1485	142
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.2	24.0	21.9	19.7	17.6	16.8	17.5	18.1	18.8	19.4	19.4
90°	1.1	3.5	6.0	8.5	10.9	13.8	17.0	20.1	23.3	26.6	27.6
92.5°	20.6	19.9	19.2	18.5	17.8	18.7	21.1	23.5	25.9	28.3	29.9
95°	67.5	57.4	47.4	37.3	27.2	23.5	26.2	28.9	31.6	34.4	36.1
97.5°	135.7	131.2	126.7	122.2	117.6	106.5	88.8	71.1	53.4	35.6	37.6
100°	187.1	192.0	196.9	201.8	206.8	190.0	151.7	113.3	74.9	36.5	38.5
102.5°	245.6	249.1	252.6	256.1	259.8	240.6	198.6	156.7	114.8	72.8	66.7
105°	329.9	332.6	335.4	338.0	340.7	331.1	308.8	286.7	264.6	242.5	198.9
107.5°	419.0	421.1	423.3	425.4	427.6	430.4	433.9	437.4	440.9	444.4	412.4
110°	478.3	480.3	482.2	484.1	486.1	488.4	491.2	493.9	496.6	499.3	491.2



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.9	536.7	538.5	540.3	542.0	544.2	547.0	549.7	552.4	555.1	555.3
115°	618.9	620.4	621.8	623.3	624.7	626.6	628.8	631.0	633.3	635.5	637.9
117.5°	700.2	702.0	703.8	705.6	707.4	708.9	710.0	711.2	712.3	713.4	715.4
120°	750.6	752.9	755.0	757.2	759.5	761.0	761.6	762.4	763.2	763.9	765.9
122.5°	802.0	803.8	805.6	807.4	809.3	810.6	811.6	812.5	813.5	814.4	815.8
125°	872.4	874.3	876.3	878.3	880.3	881.8	882.7	883.7	884.7	885.7	886.1
127.5°	940.6	942.5	944.5	946.5	948.5	950.0	951.2	952.4	953.6	954.8	955.5
130°	983.1	985.1	987.1	989.0	991.0	992.5	993.4	994.5	995.4	996.3	997.4
132.5°	1023.8	1025.8	1027.8	1029.8	1031.7	1033.1	1033.9	1034.7	1035.4	1036.2	1037.2
135°	1086.1	1087.5	1089.0	1090.5	1092.0	1093.2	1094.2	1095.2	1096.1	1097.2	1097.9
137.5°	1139.2	1141.1	1143.0	1144.8	1146.7	1147.9	1148.4	1149.0	1149.5	1150.0	1151.2
140°	1174.7	1176.1	1177.6	1179.1	1180.5	1181.6	1182.4	1183.1	1183.9	1184.6	1185.6
142.5°	1207.4	1208.8	1210.4	1211.9	1213.3	1214.4	1215.1	1215.9	1216.6	1217.4	1218.1
145°	1253.3	1255.0	1256.7	1258.4	1260.2	1261.2	1261.7	1262.2	1262.7	1263.2	1263.7
147.5°	1296.4	1297.5	1298.6	1299.8	1301.0	1301.7	1302.3	1302.7	1303.2	1303.7	1304.2
150°	1323.0	1323.7	1324.5	1325.2	1325.9	1326.5	1327.1	1327.5	1328.0	1328.5	1329.0
152.5°	1346.9	1347.2	1347.6	1347.9	1348.2	1348.6	1348.9	1349.2	1349.4	1349.8	1350.7
155°	1380.5	1380.1	1379.6	1379.1	1378.5	1378.5	1378.7	1379.0	1379.2	1379.4	1380.7
157.5°	1406.7	1406.6	1406.6	1406.5	1406.4	1406.4	1406.1	1405.8	1405.6	1405.3	1406.8
160°	1422.6	1422.4	1422.1	1421.9	1421.6	1421.4	1421.2	1420.9	1420.6	1420.4	1421.9
162.5°	1437.7	1437.0	1436.4	1435.7	1435.1	1434.7	1434.4	1434.2	1433.9	1433.7	1435.4
165°	1455.9	1455.1	1454.3	1453.6	1452.9	1452.4	1452.2	1451.9	1451.6	1451.4	1453.4
167.5°	1470.0	1469.0	1468.0	1467.1	1466.0	1465.6	1465.6	1465.6	1465.6	1465.6	1467.6
170°	1478.0	1477.0	1476.0	1475.1	1474.0	1473.5	1473.5	1473.5	1473.5	1473.5	1475.5
172.5°	1483.3	1482.1	1480.9	1479.7	1478.6	1478.1	1478.3	1478.5	1478.7	1478.9	1480.8
175°	1490.1	1488.9	1487.7	1486.4	1485.2	1484.7	1485.0	1485.2	1485.5	1485.7	1487.5
177.5°	1491.9	1490.9	1490.0	1489.0	1488.0	1487.6	1487.8	1488.0	1488.2	1488.4	1490.0
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	19.3	19.3	19.2	19.1	18.9	18.9	18.7	18.5
90°	28.5	29.5	30.5	31.3	31.8	32.2	32.7	33.2
92.5°	31.5	33.1	34.6	35.6	35.9	36.2	36.4	36.8
95°	37.8	39.5	41.2	42.1	42.1	42.1	42.1	42.1
97.5°	39.6	41.6	43.5	44.6	44.9	45.1	45.4	45.6
100°	40.5	42.4	44.4	45.5	45.7	46.0	46.2	46.5
102.5°	60.6	54.5	48.5	45.6	46.1	46.5	46.9	47.4
105°	155.3	111.8	68.3	46.8	47.3	47.7	48.2	48.7
107.5°	380.6	348.6	316.7	284.3	251.5	218.6	185.8	153.0
110°	483.0	474.9	466.8	445.1	410.0	374.8	339.7	304.4



TEST NUMBER: P332484-935

CATALOG NUMBER: S123RDIW-S1165D1320U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	555.4	555.5	555.7	552.1	544.6	537.2	529.8	522.4
115°	640.4	642.8	645.3	647.0	648.0	649.0	650.0	651.0
117.5°	717.4	719.3	721.3	722.4	722.6	722.7	723.0	723.2
120°	767.8	769.8	771.8	772.7	772.7	772.7	772.7	772.7
122.5°	817.2	818.6	819.9	820.7	820.9	821.0	821.3	821.5
125°	886.7	887.2	887.6	888.1	888.6	889.2	889.6	890.1
127.5°	956.3	957.1	957.9	958.0	957.6	957.1	956.6	956.1
130°	998.3	999.4	1000.3	1000.6	1000.1	999.6	999.1	998.6
132.5°	1038.2	1039.2	1040.2	1040.3	1039.7	1039.0	1038.3	1037.6
135°	1098.6	1099.3	1100.1	1100.1	1099.3	1098.6	1097.9	1097.2
137.5°	1152.4	1153.6	1154.8	1155.1	1154.6	1154.2	1153.7	1153.1
140°	1186.5	1187.6	1188.5	1188.8	1188.3	1187.7	1187.3	1186.8
142.5°	1218.9	1219.7	1220.6	1220.6	1219.9	1219.2	1218.5	1217.8
145°	1264.2	1264.6	1265.2	1265.4	1265.4	1265.4	1265.4	1265.4
147.5°	1304.7	1305.2	1305.7	1305.4	1304.2	1303.1	1302.0	1300.8
150°	1329.5	1330.0	1330.5	1330.3	1329.6	1328.9	1328.2	1327.4
152.5°	1351.5	1352.5	1353.3	1353.2	1352.0	1350.9	1349.8	1348.7
155°	1381.9	1383.1	1384.4	1384.2	1382.8	1381.3	1379.8	1378.4
157.5°	1408.3	1409.8	1411.3	1411.0	1409.1	1407.2	1405.2	1403.3
160°	1423.3	1424.9	1426.3	1426.2	1424.4	1422.7	1421.0	1419.3
162.5°	1437.0	1438.7	1440.4	1440.5	1438.9	1437.4	1435.9	1434.3
165°	1455.3	1457.3	1459.3	1459.4	1457.7	1456.0	1454.2	1452.5
167.5°	1469.6	1471.4	1473.4	1473.4	1471.4	1469.6	1467.6	1465.6
170°	1477.5	1479.5	1481.4	1481.4	1479.5	1477.5	1475.5	1473.5
172.5°	1482.8	1484.8	1486.8	1486.6	1484.5	1482.3	1480.1	1478.0
175°	1489.2	1490.9	1492.6	1492.5	1490.6	1488.6	1486.6	1484.6
177.5°	1491.5	1493.1	1494.7	1494.5	1492.5	1490.6	1488.6	1486.6
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1

(END OF REPORT)