

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332472-935

Luminaire Tested: **S123RDIW-S1165D460U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332472-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D460U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5359.1 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.9
10°-20°	436.0	8.1
20°-30°	627.8	11.7
30°-40°	707.2	13.2
40°-50°	676.5	12.6
50°-60°	554.0	10.3
60°-70°	373.8	7.0
70°-80°	188.1	3.5
80°-90°	51.2	1.0
90°-100°	18.9	0.4
100°-110°	90.2	1.7
110°-120°	216.7	4.0
120°-130°	276.0	5.1
130°-140°	294.8	5.5
140°-150°	275.7	5.1
150°-160°	222.4	4.1
160°-170°	143.5	2.7
170°-180°	49.5	0.9
0°-30°	1220.5	22.8
0°-40°	1927.7	36.0
0°-60°	3158.3	58.9
0°-90°	3771.3	70.4
90°-120°	325.9	6.1
90°-150°	1172.4	21.9
90°-180°	1588.0	29.6
0°-180°	5359.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	0	4	9	11	12	5
95°	24	9	12	15	15	29
105°	115	117	85	20	17	122
115°	216	219	222	226	228	213
125°	305	308	309	310	311	272
135°	379	382	383	384	383	292
145°	438	440	441	442	442	274
155°	482	482	482	484	482	222
165°	509	508	507	510	508	144
175°	521	519	519	522	519	50
180°	521	521	521	521	521	



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.1	23.6	21.1	18.6	16.2	15.1	15.2	15.5	15.7	15.9	15.8
90°	0.3	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6
92.5°	7.2	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4
95°	23.6	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6
97.5°	47.4	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2
100°	65.3	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4
102.5°	85.8	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3
105°	115.3	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5
107.5°	146.4	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1
110°	167.1	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.9	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0
115°	216.2	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9
117.5°	244.6	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9
120°	262.3	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6
122.5°	280.3	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0
125°	304.8	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6
127.5°	328.6	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9
130°	343.5	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4
132.5°	357.7	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4
135°	379.4	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6
137.5°	398.0	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3
140°	410.4	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2
142.5°	421.9	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6
145°	437.9	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5
147.5°	453.0	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7
150°	462.3	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3
152.5°	470.6	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9
155°	482.3	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4
157.5°	491.5	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5
160°	497.1	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8
162.5°	502.3	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5
165°	508.7	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8
167.5°	513.7	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8
170°	516.4	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6
172.5°	518.2	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4
175°	520.6	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7
177.5°	521.2	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	15.6	15.4	15.2	15.1	14.8	14.6	14.5	14.2
90°	10.0	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.0	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.2	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	13.9	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.1	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	21.2	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	54.2	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	132.9	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	168.8	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332472-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	194.1	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	223.8	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	250.6	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	268.3	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	285.5	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	309.8	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.2	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	348.8	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	362.7	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	402.7	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.6	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	425.9	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.7	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	455.9	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.5	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.3	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	482.8	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.1	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.3	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.1	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	508.5	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.1	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.3	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.2	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)