

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332400-935

Luminaire Tested: **S123RDIW-S340D1030U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332400-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1030U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4670.4 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69		50	50	50		32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57		44	43	42		29	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47		39	37	35		25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40		34	32	30		23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34		31	28	25		20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29		27	24	22		18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25		25	22	19		17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22		22	19	17		15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20		20	17	15		14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17		19	16	13		13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16		17	14	12		12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	1.0
10°-20°	129.2	2.8
20°-30°	186.1	4.0
30°-40°	209.6	4.5
40°-50°	200.5	4.3
50°-60°	164.2	3.5
60°-70°	110.8	2.4
70°-80°	55.7	1.2
80°-90°	18.0	0.4
90°-100°	42.3	0.9
100°-110°	201.7	4.3
110°-120°	484.5	10.4
120°-130°	616.9	13.2
130°-140°	659.2	14.1
140°-150°	616.4	13.2
150°-160°	497.2	10.6
160°-170°	320.9	6.9
170°-180°	110.6	2.4
0°-30°	361.8	7.7
0°-40°	571.4	12.2
0°-60°	936.2	20.0
0°-90°	1120.7	24.0
90°-120°	728.5	15.6
90°-150°	2621.0	56.1
90°-180°	3550.0	76.0
0°-180°	4670.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	10	21	24	26	4
95°	53	20	27	33	33	65
105°	258	262	189	45	38	273
115°	484	489	496	505	508	477
125°	682	688	692	694	695	608
135°	848	853	857	859	857	653
145°	979	985	987	988	988	613
155°	1078	1077	1078	1081	1077	497
165°	1137	1135	1134	1140	1135	321
175°	1164	1160	1160	1166	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.5	7.1	6.7	6.3	6.3	6.8	7.3	7.8	8.4	8.4
90°	0.9	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5
92.5°	16.1	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3
95°	52.8	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2
97.5°	106.0	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4
100°	146.1	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0
102.5°	191.8	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2
105°	257.7	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4
107.5°	327.3	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2
110°	373.6	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7



TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.8	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7
115°	483.5	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3
117.5°	546.9	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8
120°	586.3	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2
122.5°	626.5	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2
125°	681.5	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2
127.5°	734.7	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4
130°	767.9	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1
132.5°	799.8	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2
135°	848.3	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6
137.5°	889.8	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2
140°	917.6	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1
142.5°	943.1	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6
145°	979.0	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1
147.5°	1012.7	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7
150°	1033.5	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1
152.5°	1052.1	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1
155°	1078.4	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5
157.5°	1098.8	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9
160°	1111.3	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7
162.5°	1123.0	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2
165°	1137.2	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3
167.5°	1148.2	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3
170°	1154.5	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5
172.5°	1158.6	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8
175°	1164.0	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9
177.5°	1165.4	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	8.5	8.6	8.6	8.7	8.7	8.7	8.7	8.7
90°	22.3	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	24.6	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	29.5	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	30.9	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	31.6	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	47.4	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	121.4	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	297.2	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	377.4	371.0	364.6	347.8	320.3	292.7	265.3	237.8





TEST NUMBER: P332400-935

CATALOG NUMBER: S123RDIW-S340D1030U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	433.9	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	500.2	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	560.3	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	599.8	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	638.3	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	692.6	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.0	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	779.9	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.0	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	900.2	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	926.9	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.2	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.5	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.2	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.5	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1055.8	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1079.4	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1100.1	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1111.8	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1122.5	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1136.8	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1158.3	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1163.2	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1165.1	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)