

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332396-935

Luminaire Tested: **S123RDIW-S340D755U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332396-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3720.5 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	82	84	80	77	74	63	61	60	48	47	45	34	33	32	26
2	85	78	72	68	76	70	66	61	56	52	50	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.2
10°-20°	129.2	3.5
20°-30°	186.1	5.0
30°-40°	209.6	5.6
40°-50°	200.5	5.4
50°-60°	164.2	4.4
60°-70°	110.8	3.0
70°-80°	55.7	1.5
80°-90°	17.1	0.5
90°-100°	31.0	0.8
100°-110°	147.8	4.0
110°-120°	355.0	9.5
120°-130°	452.0	12.1
130°-140°	482.9	13.0
140°-150°	451.6	12.1
150°-160°	364.3	9.8
160°-170°	235.1	6.3
170°-180°	81.0	2.2
0°-30°	361.8	9.7
0°-40°	571.4	15.4
0°-60°	936.2	25.2
0°-90°	1119.9	30.1
90°-120°	533.7	14.3
90°-150°	1920.2	51.6
90°-180°	2601.0	69.9
0°-180°	3720.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	7	15	18	19	3
95°	39	14	20	24	24	48
105°	189	192	139	33	28	200
115°	354	358	364	370	373	349
125°	499	504	507	508	509	446
135°	622	625	628	630	628	478
145°	717	722	723	724	724	449
155°	790	789	790	792	789	364
165°	833	831	831	835	831	235
175°	853	850	850	854	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.3	6.8	6.3	5.9	5.8	6.1	6.5	6.9	7.2	7.2
90°	0.6	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8
92.5°	11.8	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1
95°	38.7	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7
97.5°	77.7	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5
100°	107.1	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0
102.5°	140.5	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2
105°	188.8	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8
107.5°	239.7	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0
110°	273.7	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.2	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8
115°	354.1	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1
117.5°	400.7	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4
120°	429.6	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3
122.5°	459.0	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8
125°	499.3	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1
127.5°	538.3	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8
130°	562.6	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8
132.5°	585.9	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6
135°	621.6	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3
137.5°	651.9	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8
140°	672.2	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5
142.5°	691.0	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2
145°	717.2	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2
147.5°	741.9	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4
150°	757.2	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6
152.5°	770.8	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9
155°	790.1	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1
157.5°	805.0	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1
160°	814.2	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7
162.5°	822.8	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5
165°	833.2	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7
167.5°	841.3	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8
170°	845.8	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4
172.5°	848.9	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5
175°	852.8	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3
177.5°	853.8	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	7.3	7.3	7.4	7.4	7.4	7.4	7.3	7.3
90°	16.4	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.0	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	21.6	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	22.6	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	23.2	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	34.7	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	88.9	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	217.7	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	276.5	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332396-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	317.9	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	366.5	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	410.5	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	439.5	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	467.6	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.4	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.3	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.4	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.2	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	659.5	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.1	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	697.6	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.5	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.7	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	760.9	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	773.4	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	790.8	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.0	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	814.6	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	822.4	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	832.8	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	848.6	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	852.2	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	853.6	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)