

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332425-935

Luminaire Tested: **S123RDIW-S560D1320U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332425-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1320U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5780.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	38	36	33	28	26	25	20
4	72	61	54	48	64	55	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	28	24	25	22	19	19	16	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	1.3
10°-20°	212.5	3.7
20°-30°	305.9	5.3
30°-40°	344.6	6.0
40°-50°	329.7	5.7
50°-60°	270.0	4.7
60°-70°	182.2	3.2
70°-80°	91.6	1.6
80°-90°	28.4	0.5
90°-100°	92.6	1.6
100°-110°	277.2	4.8
110°-120°	471.4	8.2
120°-130°	620.1	10.7
130°-140°	697.0	12.1
140°-150°	685.1	11.9
150°-160°	576.8	10.0
160°-170°	383.9	6.6
170°-180°	134.4	2.3
0°-30°	594.8	10.3
0°-40°	939.4	16.3
0°-60°	1539.1	26.6
0°-90°	1841.3	31.9
90°-120°	841.3	14.6
90°-150°	2843.5	49.2
90°-180°	3939.0	68.1
0°-180°	5780.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	1	12	27	31	34	6
95°	66	74	83	87	87	74
105°	251	254	264	264	266	269
115°	475	478	476	477	476	469
125°	695	698	696	691	687	619
135°	901	907	907	902	900	694
145°	1093	1096	1099	1098	1093	683
155°	1252	1252	1253	1257	1250	576
165°	1364	1360	1360	1366	1359	384
175°	1418	1414	1414	1420	1413	135
180°	1422	1422	1422	1422	1422	



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.9	12.1	11.3	10.5	9.7	9.6	10.2	10.9	11.5	12.2	12.3
90°	1.1	3.6	6.1	8.5	11.0	13.9	17.1	20.3	23.6	26.8	27.8
92.5°	27.0	28.7	30.4	32.1	33.8	35.6	37.4	39.2	41.1	42.9	43.7
95°	65.9	67.6	69.4	71.1	72.8	74.7	76.7	78.7	80.7	82.7	83.6
97.5°	117.0	118.3	119.6	120.9	122.2	123.6	125.0	126.4	127.9	129.3	130.4
100°	151.9	153.3	154.8	156.4	157.8	159.2	160.4	161.7	162.9	164.2	164.9
102.5°	192.1	193.0	193.9	194.8	195.6	196.9	198.5	200.2	201.8	203.5	204.2
105°	251.2	251.8	252.3	252.7	253.2	254.6	256.8	259.1	261.3	263.6	263.6
107.5°	320.0	320.4	320.6	321.0	321.2	321.8	322.7	323.6	324.5	325.4	326.2
110°	362.9	363.4	363.9	364.4	364.9	365.4	365.9	366.4	366.9	367.4	368.4



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.6	407.9	408.2	408.5	408.8	409.0	409.1	409.1	409.3	409.4	410.6
115°	474.6	475.4	476.0	476.8	477.6	477.7	477.2	476.7	476.2	475.7	476.0
117.5°	542.1	542.5	543.0	543.5	544.1	544.0	543.3	542.7	542.0	541.4	541.3
120°	584.0	585.5	587.0	588.5	590.0	590.1	588.8	587.6	586.4	585.1	584.9
122.5°	627.8	628.9	630.0	631.1	632.1	632.4	631.7	631.1	630.4	629.8	629.1
125°	694.6	695.3	696.0	696.8	697.6	697.7	697.2	696.7	696.2	695.7	694.7
127.5°	756.2	757.9	759.4	761.0	762.6	763.1	762.6	762.0	761.5	761.0	759.5
130°	797.3	799.3	801.3	803.3	805.3	805.9	805.1	804.4	803.7	802.9	801.9
132.5°	838.4	840.4	842.4	844.4	846.4	847.1	846.5	846.0	845.4	844.9	843.7
135°	901.2	902.7	904.1	905.6	907.1	907.8	907.5	907.2	907.0	906.7	905.8
137.5°	959.2	960.4	961.7	962.9	964.2	965.2	965.8	966.5	967.1	967.8	966.6
140°	999.4	1000.7	1001.9	1003.2	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9
142.5°	1036.0	1037.3	1038.5	1039.8	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4
145°	1093.2	1093.7	1094.2	1094.8	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5
147.5°	1143.2	1144.2	1145.0	1146.0	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4
150°	1178.1	1178.6	1179.1	1179.6	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6
152.5°	1206.7	1207.4	1208.1	1208.8	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6
155°	1251.8	1251.8	1251.8	1251.8	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0
157.5°	1290.2	1290.0	1289.6	1289.3	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8
160°	1314.3	1313.9	1313.4	1312.9	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4
162.5°	1335.8	1335.1	1334.4	1333.7	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8
165°	1363.5	1362.7	1362.0	1361.2	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6
167.5°	1385.6	1384.6	1383.6	1382.6	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5
170°	1398.1	1397.1	1396.1	1395.2	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3
172.5°	1407.9	1407.0	1405.9	1405.0	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0
175°	1418.2	1417.2	1416.3	1415.2	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2
177.5°	1422.5	1421.7	1420.8	1420.0	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	12.4	12.5	12.6	12.6	12.6	12.6	12.5	12.5
90°	28.8	29.8	30.7	31.5	32.0	32.5	33.0	33.5
92.5°	44.4	45.3	46.1	46.3	46.0	45.7	45.4	45.1
95°	84.6	85.6	86.6	87.1	87.1	87.1	87.1	87.1
97.5°	131.6	132.8	133.9	134.4	134.3	134.2	134.1	134.0
100°	165.7	166.3	167.1	167.7	168.2	168.8	169.3	169.7
102.5°	204.9	205.7	206.5	206.7	206.6	206.6	206.5	206.4
105°	263.6	263.6	263.6	263.8	264.3	264.8	265.3	265.8
107.5°	327.0	327.8	328.6	328.8	328.6	328.2	328.0	327.6
110°	369.4	370.4	371.3	371.6	371.1	370.7	370.1	369.6



TEST NUMBER: P332425-935

CATALOG NUMBER: S123RDIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	411.7	412.9	414.1	414.7	414.6	414.5	414.4	414.3
115°	476.2	476.5	476.7	476.7	476.5	476.2	476.0	475.7
117.5°	541.3	541.2	541.1	540.8	540.1	539.4	538.7	538.0
120°	584.6	584.4	584.2	583.8	583.3	582.8	582.3	581.8
122.5°	628.5	627.8	627.2	626.5	625.9	625.2	624.5	623.8
125°	693.7	692.8	691.7	690.8	689.7	688.7	687.8	686.7
127.5°	758.1	756.7	755.4	754.1	752.9	751.8	750.7	749.5
130°	800.9	800.0	798.9	797.5	795.8	794.1	792.4	790.7
132.5°	842.5	841.3	840.2	838.9	837.5	836.2	834.8	833.5
135°	904.7	903.8	902.8	902.1	901.6	901.0	900.5	900.1
137.5°	965.6	964.6	963.5	962.6	961.7	960.7	959.8	958.8
140°	1005.6	1005.4	1005.1	1004.2	1002.5	1000.7	998.9	997.2
142.5°	1043.2	1042.9	1042.7	1041.9	1040.5	1039.2	1037.8	1036.6
145°	1098.3	1098.1	1097.9	1097.3	1096.2	1095.2	1094.2	1093.2
147.5°	1150.4	1150.4	1150.4	1149.7	1148.2	1146.7	1145.2	1143.8
150°	1182.6	1182.6	1182.6	1181.8	1180.3	1178.9	1177.3	1175.9
152.5°	1211.9	1212.4	1212.7	1212.3	1211.0	1209.7	1208.4	1207.1
155°	1254.9	1255.9	1256.9	1256.5	1254.8	1253.1	1251.3	1249.6
157.5°	1291.8	1292.9	1294.0	1293.7	1292.4	1291.0	1289.6	1288.2
160°	1314.6	1315.9	1317.1	1317.2	1316.2	1315.3	1314.2	1313.2
162.5°	1336.0	1337.3	1338.5	1338.3	1336.8	1335.2	1333.6	1332.0
165°	1363.1	1364.6	1366.1	1366.0	1364.3	1362.5	1360.7	1359.0
167.5°	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0
170°	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6
172.5°	1406.5	1408.1	1409.6	1409.5	1407.8	1406.0	1404.3	1402.6
175°	1416.7	1418.2	1419.7	1419.5	1417.8	1416.1	1414.4	1412.6
177.5°	1421.3	1422.5	1423.7	1423.6	1422.1	1420.7	1419.4	1418.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6

(END OF REPORT)