

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332448-935

Luminaire Tested: **S123RDIW-S775D1535U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332448-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1535U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7799.5 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	85	81	78	75	65	62	61	49	48	47	35	35	34	28
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	1.3
10°-20°	290.4	3.7
20°-30°	418.2	5.4
30°-40°	471.1	6.0
40°-50°	450.7	5.8
50°-60°	369.0	4.7
60°-70°	249.0	3.2
70°-80°	125.3	1.6
80°-90°	38.0	0.5
90°-100°	63.0	0.8
100°-110°	300.2	3.8
110°-120°	721.1	9.2
120°-130°	918.3	11.8
130°-140°	981.1	12.6
140°-150°	917.5	11.8
150°-160°	740.1	9.5
160°-170°	477.6	6.1
170°-180°	164.6	2.1
0°-30°	813.0	10.4
0°-40°	1284.1	16.5
0°-60°	2103.8	27.0
0°-90°	2516.0	32.3
90°-120°	1084.3	13.9
90°-150°	3901.2	50.0
90°-180°	5283.0	67.7
0°-180°	7799.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	14	31	36	39	6
95°	78	29	40	48	49	97
105°	384	390	282	67	57	407
115°	720	728	739	751	757	710
125°	1014	1024	1030	1032	1035	905
135°	1263	1270	1276	1279	1276	972
145°	1457	1466	1469	1471	1471	912
155°	1605	1603	1604	1610	1603	739
165°	1693	1689	1688	1697	1689	478
175°	1732	1726	1727	1735	1726	165
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.6	16.4	15.2	14.0	12.8	12.6	13.3	14.0	14.8	15.6	15.6
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0
92.5°	23.9	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8
95°	78.5	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9
97.5°	157.8	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7
100°	217.6	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8
102.5°	285.5	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6
105°	383.6	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3
107.5°	487.1	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6
110°	556.0	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.0	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6
115°	719.5	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7
117.5°	814.0	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7
120°	872.7	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4
122.5°	932.5	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5
125°	1014.3	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4
127.5°	1093.6	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9
130°	1143.0	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6
132.5°	1190.4	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9
135°	1262.7	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4
137.5°	1324.5	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5
140°	1365.7	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5
142.5°	1403.8	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3
145°	1457.1	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2
147.5°	1507.3	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4
150°	1538.2	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2
152.5°	1566.0	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4
155°	1605.1	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2
157.5°	1635.5	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6
160°	1654.1	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2
162.5°	1671.5	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9
165°	1692.6	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8
167.5°	1709.1	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2
170°	1718.4	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5
172.5°	1724.6	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7
175°	1732.5	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4
177.5°	1734.6	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	15.7	15.8	15.8	15.8	15.8	15.8	15.7	15.7
90°	33.1	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	36.6	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.1	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	47.0	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	70.5	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	180.6	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	442.4	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	561.6	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332448-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.8	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	744.6	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	834.1	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	892.8	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	950.0	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1030.9	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1111.9	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1160.7	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1207.1	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1339.9	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1379.6	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1417.2	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1469.8	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1516.9	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1545.8	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1571.4	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1606.7	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1637.4	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1654.9	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1670.8	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1692.0	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1724.0	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1731.4	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1734.1	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)