

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332828-927

Luminaire Tested: **S124DIW-S1020D1340U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332828-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1340U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7197.2 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83		68	68	68		55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68		60	58	57		49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56		53	50	47		43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47		47	43	40		38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40		41	38	34		34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35		37	33	30		30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30		34	29	26		28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27		31	26	23		25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24		28	24	21		23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21		26	21	18		21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19		24	20	17		20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	1.8
10°-20°	362.7	5.0
20°-30°	533.8	7.4
30°-40°	620.6	8.6
40°-50°	620.6	8.6
50°-60°	542.9	7.5
60°-70°	403.2	5.6
70°-80°	229.1	3.2
80°-90°	70.1	1.0
90°-100°	87.6	1.2
100°-110°	259.5	3.6
110°-120°	440.5	6.1
120°-130°	580.9	8.1
130°-140°	652.4	9.1
140°-150°	641.1	8.9
150°-160°	539.2	7.5
160°-170°	358.7	5.0
170°-180°	125.6	1.7
0°-30°	1025.2	14.2
0°-40°	1645.9	22.9
0°-60°	2809.4	39.0
0°-90°	3511.7	48.8
90°-120°	787.7	10.9
90°-150°	2662.0	37.0
90°-180°	3686.0	51.2
0°-180°	7197.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	3	14	23	28	31	7
95°	62	71	78	81	81	69
105°	239	241	244	248	251	254
115°	448	448	446	445	444	442
125°	652	652	651	649	647	581
135°	841	847	848	845	842	651
145°	1022	1026	1027	1026	1023	639
155°	1171	1171	1170	1174	1170	539
165°	1275	1272	1270	1275	1272	359
175°	1326	1321	1320	1327	1320	126
180°	1328	1328	1328	1328	1328	



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.4	23.7	24.0	24.3	24.6	24.9	25.0	25.2	25.3	25.6	25.8
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	22.0	24.9	27.7	30.6	33.5	35.6	36.8	38.1	39.4	40.7	41.5
95°	61.6	63.7	65.8	67.8	69.9	71.7	73.3	74.9	76.4	78.1	78.7
97.5°	107.7	109.3	111.0	112.6	114.2	116.0	117.9	119.8	121.6	123.5	124.3
100°	143.9	144.7	145.7	146.6	147.5	148.9	151.0	153.0	155.1	157.2	157.6
102.5°	181.6	182.0	182.4	182.8	183.1	184.2	186.1	188.0	189.8	191.7	192.3
105°	239.4	239.6	239.9	240.0	240.3	240.8	241.8	242.7	243.6	244.5	245.2
107.5°	300.0	300.2	300.6	300.8	301.1	301.3	301.4	301.6	301.7	301.8	302.5
110°	341.1	341.5	342.0	342.5	342.9	343.0	342.8	342.5	342.4	342.1	341.7



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.8	383.9	384.0	384.1	384.2	384.0	383.7	383.2	382.8	382.4	382.3
115°	447.9	447.9	447.9	447.9	447.9	447.7	447.3	446.8	446.3	445.8	445.7
117.5°	508.3	508.5	508.7	508.9	509.1	509.0	508.7	508.3	508.0	507.7	506.9
120°	548.6	549.5	550.4	551.4	552.2	552.4	551.7	551.0	550.3	549.6	548.5
122.5°	590.5	590.9	591.3	591.6	592.0	592.0	591.7	591.4	591.0	590.7	589.9
125°	652.4	652.4	652.4	652.4	652.4	652.3	652.0	651.8	651.6	651.3	650.9
127.5°	708.4	709.2	709.9	710.5	711.2	711.4	711.0	710.7	710.3	709.9	709.5
130°	747.9	748.6	749.3	750.0	750.7	751.0	751.0	751.0	751.0	751.0	750.5
132.5°	788.2	788.7	789.2	789.7	790.2	790.4	790.2	790.0	789.8	789.6	789.2
135°	841.4	842.8	844.1	845.5	846.9	847.6	847.6	847.6	847.6	847.6	847.2
137.5°	899.4	900.0	900.6	901.3	901.9	902.5	902.8	903.2	903.5	903.9	903.2
140°	938.0	938.4	938.9	939.4	939.8	940.0	940.0	940.0	940.0	940.0	939.8
142.5°	973.4	973.8	974.2	974.7	975.2	975.3	975.1	974.9	974.8	974.5	974.5
145°	1022.2	1023.2	1024.1	1025.0	1025.9	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1
147.5°	1070.7	1071.8	1072.9	1074.0	1075.1	1075.5	1075.4	1075.2	1075.0	1074.8	1074.7
150°	1100.3	1101.2	1102.2	1103.0	1104.0	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4
152.5°	1128.2	1128.8	1129.3	1129.9	1130.4	1130.8	1131.0	1131.2	1131.4	1131.6	1132.1
155°	1171.2	1171.2	1171.2	1171.2	1171.2	1171.1	1170.8	1170.6	1170.4	1170.2	1171.1
157.5°	1207.4	1207.0	1206.6	1206.1	1205.7	1205.5	1205.5	1205.4	1205.4	1205.3	1206.0
160°	1228.8	1228.5	1228.3	1228.0	1227.8	1227.6	1227.3	1227.2	1226.9	1226.7	1227.3
162.5°	1248.5	1247.8	1247.3	1246.7	1246.1	1245.7	1245.5	1245.2	1245.0	1244.8	1246.0
165°	1274.9	1274.3	1273.6	1272.9	1272.2	1271.7	1271.2	1270.7	1270.3	1269.8	1271.2
167.5°	1295.3	1294.3	1293.4	1292.4	1291.5	1291.0	1291.1	1291.1	1291.2	1291.2	1292.6
170°	1306.8	1305.7	1304.6	1303.4	1302.3	1301.8	1302.0	1302.3	1302.5	1302.7	1304.1
172.5°	1315.0	1314.1	1313.1	1312.2	1311.2	1310.7	1310.8	1310.8	1310.9	1310.9	1312.5
175°	1326.4	1325.2	1324.1	1322.9	1321.8	1321.0	1320.9	1320.6	1320.4	1320.2	1321.8
177.5°	1330.0	1329.1	1328.2	1327.3	1326.4	1326.0	1326.0	1326.0	1326.0	1326.0	1327.2
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	26.1	26.4	26.6	26.9	26.9	27.0	27.1	27.2
90°	25.3	26.7	28.0	29.0	29.5	29.9	30.3	30.8
92.5°	42.3	43.2	44.0	44.5	44.8	45.1	45.3	45.6
95°	79.5	80.2	80.8	81.2	81.2	81.2	81.2	81.2
97.5°	125.2	126.0	126.7	127.2	127.2	127.2	127.2	127.2
100°	158.1	158.6	159.0	159.2	159.2	159.2	159.2	159.2
102.5°	193.0	193.6	194.2	194.6	194.9	195.0	195.2	195.4
105°	245.9	246.6	247.2	248.0	248.6	249.3	250.0	250.6
107.5°	303.1	303.7	304.4	304.7	304.7	304.6	304.6	304.5
110°	341.2	340.7	340.3	340.4	341.1	341.7	342.5	343.2



TEST NUMBER: P332828-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.2	382.1	382.0	382.1	382.1	382.3	382.5	382.6
115°	445.4	445.2	445.0	444.7	444.5	444.3	444.0	443.9
117.5°	506.2	505.4	504.6	504.0	503.5	503.1	502.6	502.2
120°	547.4	546.2	545.1	544.7	545.2	545.7	546.1	546.5
122.5°	589.1	588.4	587.6	586.8	586.0	585.2	584.4	583.5
125°	650.5	650.0	649.5	649.0	648.6	648.2	647.7	647.2
127.5°	709.0	708.5	708.1	707.7	707.3	706.9	706.5	706.2
130°	750.1	749.6	749.2	748.5	747.6	746.6	745.8	744.8
132.5°	788.7	788.3	787.8	787.4	787.0	786.6	786.3	785.9
135°	846.7	846.2	845.7	845.2	844.5	843.8	843.1	842.4
137.5°	902.7	902.1	901.5	901.3	901.4	901.6	901.7	901.8
140°	939.6	939.4	939.1	938.9	938.7	938.4	938.2	938.0
142.5°	974.5	974.5	974.4	974.3	974.3	974.2	974.2	974.1
145°	1026.9	1026.7	1026.4	1026.0	1025.3	1024.6	1024.0	1023.3
147.5°	1074.4	1074.3	1074.1	1073.9	1073.6	1073.4	1073.2	1073.0
150°	1104.4	1104.4	1104.4	1104.3	1104.1	1103.8	1103.6	1103.4
152.5°	1132.7	1133.2	1133.8	1133.7	1133.1	1132.5	1131.9	1131.3
155°	1172.0	1172.9	1173.9	1173.9	1172.9	1172.0	1171.1	1170.2
157.5°	1206.7	1207.4	1208.1	1208.0	1207.2	1206.4	1205.7	1204.9
160°	1228.0	1228.8	1229.4	1229.2	1228.0	1226.9	1225.7	1224.6
162.5°	1247.2	1248.5	1249.7	1249.7	1248.6	1247.4	1246.3	1245.2
165°	1272.6	1273.9	1275.3	1275.6	1274.6	1273.7	1272.8	1271.8
167.5°	1294.0	1295.3	1296.6	1296.6	1295.2	1293.8	1292.4	1291.0
170°	1305.4	1306.8	1308.2	1308.1	1306.5	1304.9	1303.3	1301.7
172.5°	1314.0	1315.6	1317.2	1317.1	1315.5	1313.9	1312.3	1310.7
175°	1323.3	1324.9	1326.6	1326.6	1324.9	1323.3	1321.8	1320.2
177.5°	1328.5	1329.8	1331.0	1330.9	1329.5	1328.0	1326.6	1325.1
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4

(END OF REPORT)