

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332433-935

Luminaire Tested: **S123RDIW-S775D460U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332433-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D460U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3888.8 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	45	41	37	40	36	33	31
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	33	29	26	24
8	57	45	37	32	54	43	35	30	38	32	28	34	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.4	2.7
10°-20°	290.4	7.5
20°-30°	418.2	10.8
30°-40°	471.1	12.1
40°-50°	450.7	11.6
50°-60°	369.0	9.5
60°-70°	249.0	6.4
70°-80°	125.3	3.2
80°-90°	34.6	0.9
90°-100°	32.4	0.8
100°-110°	96.8	2.5
110°-120°	164.7	4.2
120°-130°	216.7	5.6
130°-140°	243.5	6.3
140°-150°	239.4	6.2
150°-160°	201.5	5.2
160°-170°	134.2	3.4
170°-180°	47.0	1.2
0°-30°	813.0	20.9
0°-40°	1284.1	33.0
0°-60°	2103.8	54.1
0°-90°	2512.6	64.6
90°-120°	293.9	7.6
90°-150°	993.5	25.5
90°-180°	1376.0	35.4
0°-180°	3888.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	0	4	9	11	12	4
95°	23	26	29	30	30	26
105°	88	89	92	92	93	94
115°	166	167	166	167	166	164
125°	243	244	243	242	240	216
135°	315	317	317	315	314	243
145°	382	383	384	384	382	239
155°	437	437	438	439	437	201
165°	476	475	475	477	475	134
175°	496	494	494	496	494	47
180°	497	497	497	497	497	



TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.4	15.8	14.2	12.7	11.0	10.3	10.6	10.8	11.0	11.3	11.2
90°	0.4	1.3	2.2	3.0	3.9	4.8	5.9	7.1	8.3	9.4	9.7
92.5°	9.5	10.1	10.6	11.2	11.8	12.4	13.1	13.7	14.4	15.0	15.2
95°	23.0	23.6	24.2	24.9	25.5	26.1	26.8	27.5	28.2	28.8	29.2
97.5°	40.9	41.3	41.8	42.3	42.7	43.1	43.7	44.2	44.7	45.2	45.5
100°	53.0	53.6	54.1	54.6	55.1	55.6	56.1	56.5	56.9	57.3	57.6
102.5°	67.1	67.4	67.8	68.0	68.4	68.8	69.4	69.9	70.5	71.1	71.4
105°	87.8	88.0	88.2	88.3	88.5	88.9	89.7	90.5	91.3	92.0	92.0
107.5°	111.8	111.9	112.0	112.1	112.3	112.4	112.8	113.0	113.4	113.7	114.0
110°	126.8	127.0	127.2	127.3	127.5	127.7	127.9	128.0	128.2	128.4	128.7



TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.4	142.5	142.7	142.8	142.8	142.9	142.9	143.0	143.0	143.0	143.4
115°	165.8	166.1	166.3	166.6	166.9	166.9	166.8	166.6	166.4	166.3	166.3
117.5°	189.4	189.6	189.8	189.9	190.1	190.0	189.9	189.6	189.4	189.2	189.2
120°	204.1	204.6	205.1	205.6	206.1	206.2	205.8	205.3	204.9	204.5	204.4
122.5°	219.4	219.7	220.2	220.5	220.8	220.9	220.8	220.5	220.3	220.1	219.8
125°	242.7	243.0	243.2	243.5	243.7	243.7	243.6	243.4	243.2	243.1	242.7
127.5°	264.2	264.8	265.4	265.9	266.5	266.7	266.5	266.2	266.0	265.9	265.4
130°	278.6	279.3	280.0	280.7	281.4	281.5	281.3	281.0	280.8	280.5	280.2
132.5°	292.9	293.6	294.4	295.1	295.8	296.0	295.8	295.6	295.4	295.2	294.8
135°	314.9	315.4	315.9	316.4	316.9	317.2	317.1	317.0	316.9	316.8	316.5
137.5°	335.2	335.6	336.0	336.5	336.9	337.3	337.4	337.7	337.9	338.1	337.8
140°	349.2	349.7	350.1	350.5	350.9	351.2	351.3	351.4	351.5	351.5	351.5
142.5°	362.1	362.5	362.9	363.3	363.8	364.0	364.2	364.4	364.5	364.6	364.5
145°	382.0	382.2	382.4	382.5	382.7	382.9	383.1	383.4	383.7	383.9	383.8
147.5°	399.5	399.8	400.1	400.4	400.7	401.0	401.2	401.5	401.7	402.0	402.0
150°	411.6	411.8	412.0	412.2	412.3	412.5	412.7	412.8	413.0	413.2	413.2
152.5°	421.6	421.9	422.1	422.3	422.6	422.8	422.8	423.0	423.1	423.2	423.4
155°	437.4	437.4	437.4	437.4	437.4	437.5	437.6	437.6	437.7	437.8	438.2
157.5°	450.8	450.7	450.6	450.5	450.4	450.4	450.5	450.6	450.6	450.6	451.0
160°	459.3	459.1	458.9	458.7	458.6	458.5	458.5	458.5	458.5	458.5	458.9
162.5°	466.7	466.5	466.2	466.0	465.8	465.7	465.7	465.8	465.9	466.0	466.4
165°	476.4	476.1	475.9	475.6	475.4	475.3	475.3	475.3	475.3	475.3	475.8
167.5°	484.1	483.8	483.5	483.1	482.8	482.6	482.7	482.8	482.8	482.8	483.5
170°	488.5	488.2	487.8	487.5	487.2	487.0	487.0	487.0	487.0	487.0	487.6
172.5°	492.0	491.6	491.3	490.9	490.5	490.3	490.3	490.3	490.3	490.3	490.9
175°	495.5	495.2	494.8	494.5	494.1	494.0	494.0	494.0	494.0	494.0	494.5
177.5°	497.1	496.7	496.5	496.2	495.9	495.8	495.8	495.8	495.8	495.8	496.2
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7



TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	11.1	10.9	10.8	10.8	10.7	10.5	10.4	10.2
90°	10.1	10.4	10.8	11.0	11.2	11.4	11.5	11.7
92.5°	15.5	15.8	16.1	16.2	16.1	15.9	15.8	15.8
95°	29.5	29.9	30.2	30.4	30.4	30.4	30.4	30.4
97.5°	46.0	46.4	46.8	46.9	46.9	46.9	46.8	46.8
100°	57.9	58.1	58.4	58.6	58.8	59.0	59.2	59.3
102.5°	71.6	71.9	72.2	72.2	72.2	72.2	72.2	72.1
105°	92.0	92.0	92.0	92.1	92.4	92.6	92.7	92.9
107.5°	114.3	114.5	114.8	114.9	114.8	114.7	114.6	114.5
110°	129.1	129.4	129.8	129.8	129.7	129.5	129.3	129.2





TEST NUMBER: P332433-935

CATALOG NUMBER: S123RDIW-S775D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	143.9	144.3	144.7	144.9	144.8	144.8	144.8	144.7
115°	166.4	166.5	166.6	166.6	166.5	166.4	166.3	166.3
117.5°	189.2	189.1	189.1	189.0	188.7	188.5	188.2	188.0
120°	204.3	204.2	204.1	204.0	203.8	203.6	203.5	203.3
122.5°	219.6	219.4	219.1	219.0	218.7	218.4	218.2	217.9
125°	242.4	242.0	241.7	241.3	241.0	240.6	240.3	240.0
127.5°	264.9	264.4	263.9	263.5	263.1	262.7	262.3	261.9
130°	279.8	279.5	279.1	278.7	278.1	277.5	276.9	276.2
132.5°	294.4	293.9	293.5	293.1	292.7	292.1	291.7	291.2
135°	316.2	315.8	315.5	315.2	315.0	314.9	314.7	314.5
137.5°	337.4	337.1	336.7	336.3	336.0	335.7	335.4	335.0
140°	351.4	351.3	351.2	350.9	350.3	349.7	349.0	348.4
142.5°	364.5	364.4	364.3	364.0	363.6	363.1	362.7	362.1
145°	383.7	383.7	383.6	383.4	383.1	382.7	382.4	382.0
147.5°	402.0	402.0	402.0	401.7	401.2	400.6	400.1	399.6
150°	413.2	413.2	413.2	412.9	412.4	411.9	411.4	410.9
152.5°	423.4	423.6	423.8	423.6	423.2	422.7	422.2	421.8
155°	438.5	438.9	439.2	439.0	438.4	437.8	437.2	436.6
157.5°	451.4	451.8	452.1	452.0	451.6	451.1	450.6	450.1
160°	459.3	459.8	460.2	460.2	459.9	459.5	459.2	458.8
162.5°	466.8	467.3	467.7	467.6	467.1	466.5	466.0	465.4
165°	476.3	476.8	477.3	477.3	476.6	476.0	475.4	474.8
167.5°	484.0	484.5	485.0	485.0	484.5	484.0	483.5	482.8
170°	488.2	488.8	489.4	489.4	488.8	488.2	487.6	487.0
172.5°	491.5	492.0	492.5	492.5	491.9	491.3	490.7	490.1
175°	495.0	495.5	496.0	496.0	495.4	494.8	494.2	493.6
177.5°	496.6	497.1	497.4	497.4	496.9	496.5	495.9	495.4
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7

(END OF REPORT)