

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332810-927

Luminaire Tested: **S124DIW-S1020D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332810-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D470U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4796.8 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	2.7
10°-20°	362.7	7.6
20°-30°	533.8	11.1
30°-40°	620.6	12.9
40°-50°	620.6	12.9
50°-60°	542.9	11.3
60°-70°	403.2	8.4
70°-80°	229.1	4.8
80°-90°	67.5	1.4
90°-100°	30.6	0.6
100°-110°	90.7	1.9
110°-120°	153.9	3.2
120°-130°	203.0	4.2
130°-140°	227.9	4.8
140°-150°	224.0	4.7
150°-160°	188.4	3.9
160°-170°	125.3	2.6
170°-180°	43.9	0.9
0°-30°	1025.2	21.4
0°-40°	1645.9	34.3
0°-60°	2809.4	58.6
0°-90°	3509.1	73.2
90°-120°	275.2	5.7
90°-150°	930.1	19.4
90°-180°	1288.0	26.9
0°-180°	4796.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	1	5	8	10	11	5
95°	22	25	27	28	28	24
105°	84	84	85	87	88	89
115°	156	156	156	155	155	154
125°	228	228	228	227	226	203
135°	294	296	296	295	294	227
145°	357	359	359	359	358	223
155°	409	409	409	410	409	188
165°	445	444	444	446	444	126
175°	463	462	461	464	461	44
180°	464	464	464	464	464	



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.0	23.0	23.0	23.0	22.9	22.9	22.8	22.7	22.7	22.6	22.7
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	7.7	8.7	9.7	10.7	11.7	12.4	12.9	13.3	13.8	14.2	14.5
95°	21.5	22.3	23.0	23.7	24.4	25.0	25.6	26.1	26.7	27.3	27.5
97.5°	37.6	38.2	38.7	39.4	39.9	40.6	41.2	41.8	42.5	43.2	43.4
100°	50.2	50.5	50.9	51.2	51.6	52.0	52.8	53.5	54.2	54.9	55.1
102.5°	63.5	63.6	63.7	63.8	64.0	64.4	65.0	65.7	66.3	67.0	67.2
105°	83.7	83.7	83.8	83.9	84.0	84.1	84.4	84.8	85.1	85.4	85.6
107.5°	104.8	104.9	105.0	105.1	105.2	105.3	105.4	105.4	105.4	105.4	105.7
110°	119.1	119.3	119.5	119.6	119.8	119.9	119.8	119.7	119.6	119.5	119.4



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.1	134.1	134.2	134.2	134.3	134.2	134.0	133.9	133.7	133.6	133.6
115°	156.5	156.5	156.5	156.5	156.5	156.5	156.3	156.1	156.0	155.8	155.7
117.5°	177.6	177.7	177.8	177.8	177.8	177.8	177.8	177.6	177.5	177.4	177.1
120°	191.7	192.0	192.3	192.7	193.0	193.0	192.7	192.5	192.3	192.0	191.6
122.5°	206.4	206.4	206.6	206.7	206.8	206.8	206.8	206.6	206.5	206.4	206.1
125°	227.9	227.9	227.9	227.9	227.9	227.9	227.8	227.8	227.7	227.6	227.4
127.5°	247.6	247.8	248.0	248.3	248.5	248.6	248.4	248.3	248.2	248.0	247.9
130°	261.3	261.6	261.8	262.1	262.3	262.4	262.4	262.4	262.4	262.4	262.2
132.5°	275.4	275.6	275.8	275.9	276.1	276.2	276.1	276.0	276.0	275.9	275.8
135°	294.0	294.5	294.9	295.4	295.9	296.1	296.1	296.1	296.1	296.1	296.0
137.5°	314.3	314.5	314.7	314.9	315.1	315.3	315.4	315.6	315.7	315.8	315.6
140°	327.7	327.9	328.0	328.2	328.4	328.4	328.4	328.4	328.4	328.4	328.4
142.5°	340.1	340.2	340.4	340.6	340.7	340.8	340.7	340.6	340.6	340.5	340.5
145°	357.2	357.5	357.8	358.1	358.5	358.6	358.7	358.8	358.9	358.9	358.9
147.5°	374.1	374.5	374.9	375.3	375.7	375.8	375.7	375.7	375.7	375.6	375.5
150°	384.4	384.8	385.1	385.4	385.7	385.9	385.9	385.9	385.9	385.9	385.9
152.5°	394.2	394.4	394.6	394.8	395.0	395.1	395.1	395.2	395.3	395.4	395.5
155°	409.2	409.2	409.2	409.2	409.2	409.2	409.1	409.0	408.9	408.8	409.2
157.5°	421.8	421.7	421.6	421.4	421.3	421.2	421.2	421.2	421.1	421.1	421.4
160°	429.4	429.3	429.2	429.1	429.0	429.0	428.9	428.8	428.7	428.6	428.9
162.5°	436.3	436.0	435.8	435.6	435.4	435.2	435.1	435.1	435.0	434.9	435.4
165°	445.4	445.2	445.0	444.7	444.5	444.3	444.2	444.0	443.9	443.7	444.2
167.5°	452.6	452.3	451.9	451.6	451.2	451.1	451.1	451.1	451.1	451.1	451.6
170°	456.6	456.2	455.8	455.4	455.0	454.9	455.0	455.0	455.1	455.2	455.7
172.5°	459.5	459.1	458.8	458.5	458.1	458.0	458.0	458.0	458.0	458.0	458.6
175°	463.4	463.0	462.6	462.2	461.8	461.6	461.5	461.4	461.4	461.3	461.8
177.5°	464.7	464.4	464.1	463.7	463.4	463.3	463.3	463.3	463.3	463.3	463.7
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.2
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	14.8	15.1	15.4	15.5	15.7	15.8	15.8	15.9
95°	27.7	28.0	28.2	28.4	28.4	28.4	28.4	28.4
97.5°	43.7	44.0	44.3	44.4	44.4	44.4	44.4	44.4
100°	55.2	55.4	55.5	55.6	55.6	55.6	55.6	55.6
102.5°	67.4	67.7	67.9	68.0	68.0	68.1	68.2	68.3
105°	86.0	86.2	86.4	86.7	86.9	87.1	87.4	87.6
107.5°	105.9	106.2	106.4	106.5	106.5	106.5	106.4	106.4
110°	119.2	119.1	118.9	118.9	119.1	119.4	119.6	119.9



TEST NUMBER: P332810-927

CATALOG NUMBER: S124DIW-S1020D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.6	133.5	133.5	133.5	133.6	133.6	133.6	133.6
115°	155.7	155.6	155.5	155.4	155.3	155.3	155.2	155.1
117.5°	176.9	176.6	176.3	176.1	175.9	175.8	175.6	175.5
120°	191.2	190.8	190.4	190.4	190.5	190.7	190.8	191.0
122.5°	205.9	205.6	205.3	205.0	204.8	204.5	204.1	203.9
125°	227.3	227.1	227.0	226.8	226.6	226.5	226.3	226.2
127.5°	247.7	247.6	247.4	247.2	247.2	247.0	246.9	246.8
130°	262.1	261.9	261.7	261.5	261.2	260.9	260.5	260.2
132.5°	275.6	275.4	275.3	275.1	275.0	274.9	274.7	274.6
135°	295.8	295.6	295.5	295.3	295.1	294.9	294.6	294.4
137.5°	315.4	315.2	315.0	314.9	315.0	315.0	315.1	315.1
140°	328.3	328.2	328.1	328.0	328.0	327.9	327.8	327.7
142.5°	340.5	340.5	340.5	340.4	340.4	340.4	340.4	340.4
145°	358.8	358.7	358.6	358.5	358.2	358.0	357.7	357.5
147.5°	375.4	375.3	375.3	375.3	375.2	375.1	375.0	374.9
150°	385.9	385.9	385.9	385.9	385.8	385.7	385.6	385.6
152.5°	395.8	395.9	396.2	396.1	395.9	395.7	395.5	395.3
155°	409.5	409.8	410.1	410.1	409.8	409.5	409.2	408.8
157.5°	421.6	421.8	422.1	422.1	421.8	421.5	421.3	421.0
160°	429.1	429.4	429.6	429.5	429.1	428.7	428.3	427.9
162.5°	435.8	436.3	436.7	436.7	436.3	435.9	435.5	435.1
165°	444.7	445.1	445.6	445.7	445.4	445.0	444.7	444.4
167.5°	452.1	452.6	453.0	453.0	452.6	452.1	451.5	451.1
170°	456.1	456.6	457.1	457.0	456.5	455.9	455.3	454.8
172.5°	459.1	459.7	460.2	460.2	459.6	459.1	458.5	458.0
175°	462.4	463.0	463.5	463.5	463.0	462.4	461.8	461.3
177.5°	464.2	464.6	465.1	465.0	464.5	464.1	463.5	463.0
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1

(END OF REPORT)