

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332436-935

Luminaire Tested: **S123RDIW-S775D755U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332436-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5114.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	73	65	60	75	67	61	56	57	52	49	48	44	42	39	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21
7	59	47	39	33	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.0
10°-20°	290.4	5.7
20°-30°	418.2	8.2
30°-40°	471.1	9.2
40°-50°	450.7	8.8
50°-60°	369.0	7.2
60°-70°	249.0	4.9
70°-80°	125.3	2.4
80°-90°	35.5	0.7
90°-100°	31.0	0.6
100°-110°	147.8	2.9
110°-120°	355.0	6.9
120°-130°	452.0	8.8
130°-140°	482.9	9.4
140°-150°	451.6	8.8
150°-160°	364.3	7.1
160°-170°	235.1	4.6
170°-180°	81.0	1.6
0°-30°	813.0	15.9
0°-40°	1284.1	25.1
0°-60°	2103.8	41.1
0°-90°	2513.6	49.1
90°-120°	533.7	10.4
90°-150°	1920.2	37.5
90°-180°	2601.0	50.9
0°-180°	5114.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	7	15	18	19	4
95°	39	14	20	24	24	48
105°	189	192	139	33	28	200
115°	354	358	364	370	373	349
125°	499	504	507	508	509	446
135°	622	625	628	630	628	478
145°	717	722	723	724	724	449
155°	790	789	790	792	789	364
165°	833	831	831	835	831	235
175°	853	850	850	854	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.5	15.9	14.5	13.0	11.5	10.9	11.3	11.7	12.1	12.4	12.4
90°	0.6	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8
92.5°	11.8	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1
95°	38.7	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7
97.5°	77.7	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5
100°	107.1	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0
102.5°	140.5	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2
105°	188.8	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8
107.5°	239.7	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0
110°	273.7	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.2	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8
115°	354.1	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1
117.5°	400.7	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4
120°	429.6	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3
122.5°	459.0	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8
125°	499.3	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1
127.5°	538.3	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8
130°	562.6	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8
132.5°	585.9	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6
135°	621.6	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3
137.5°	651.9	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8
140°	672.2	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5
142.5°	691.0	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2
145°	717.2	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2
147.5°	741.9	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4
150°	757.2	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6
152.5°	770.8	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9
155°	790.1	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1
157.5°	805.0	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1
160°	814.2	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7
162.5°	822.8	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5
165°	833.2	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7
167.5°	841.3	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8
170°	845.8	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4
172.5°	848.9	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5
175°	852.8	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3
177.5°	853.8	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	12.3	12.3	12.2	12.1	12.1	12.0	11.9	11.7
90°	16.4	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.0	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	21.6	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	22.6	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	23.2	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	34.7	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	88.9	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	217.7	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	276.5	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332436-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	317.9	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	366.5	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	410.5	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	439.5	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	467.6	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.4	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.3	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.4	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.2	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	659.5	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.1	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	697.6	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.5	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.7	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	760.9	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	773.4	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	790.8	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.0	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	814.6	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	822.4	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	832.8	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	848.6	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	852.2	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	853.6	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)