

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332437-935

Luminaire Tested: **S123RDIW-S775D755U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332437-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4767.6 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	82	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	45	43	38
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	44	40	37	37	34	32	28
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.2
10°-20°	290.4	6.1
20°-30°	418.2	8.8
30°-40°	471.1	9.9
40°-50°	450.7	9.5
50°-60°	369.0	7.7
60°-70°	249.0	5.2
70°-80°	125.3	2.6
80°-90°	35.5	0.7
90°-100°	53.0	1.1
100°-110°	158.6	3.3
110°-120°	269.8	5.7
120°-130°	354.9	7.4
130°-140°	398.9	8.4
140°-150°	392.1	8.2
150°-160°	330.1	6.9
160°-170°	219.7	4.6
170°-180°	76.9	1.6
0°-30°	813.0	17.1
0°-40°	1284.1	26.9
0°-60°	2103.8	44.1
0°-90°	2513.6	52.7
90°-120°	481.4	10.1
90°-150°	1627.3	34.1
90°-180°	2254.0	47.3
0°-180°	4767.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	7	15	18	19	5
95°	38	42	47	50	50	42
105°	144	145	151	151	152	154
115°	272	273	272	273	272	269
125°	398	399	398	396	393	354
135°	516	519	519	516	515	397
145°	626	627	629	628	626	391
155°	716	716	717	719	715	330
165°	780	778	778	782	778	220
175°	812	809	809	812	808	77
180°	814	814	814	814	814	



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.5	15.9	14.5	13.0	11.5	10.9	11.4	11.7	12.1	12.5	12.4
90°	0.6	2.1	3.4	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.5	16.4	17.4	18.3	19.3	20.3	21.4	22.5	23.5	24.5	25.0
95°	37.7	38.7	39.7	40.7	41.7	42.7	43.9	45.0	46.1	47.3	47.9
97.5°	67.0	67.7	68.4	69.2	69.9	70.7	71.5	72.3	73.2	74.0	74.6
100°	86.9	87.7	88.6	89.5	90.3	91.1	91.8	92.6	93.2	93.9	94.4
102.5°	109.9	110.5	111.0	111.4	111.9	112.7	113.7	114.6	115.5	116.4	116.8
105°	143.8	144.0	144.4	144.6	144.9	145.7	147.0	148.3	149.6	150.8	150.8
107.5°	183.1	183.3	183.5	183.7	183.8	184.2	184.7	185.2	185.7	186.2	186.7
110°	207.7	208.0	208.3	208.5	208.8	209.1	209.4	209.7	210.0	210.3	210.9



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	233.2	233.4	233.6	233.8	233.9	234.0	234.1	234.2	234.2	234.3	235.0
115°	271.6	272.0	272.4	272.9	273.3	273.4	273.1	272.9	272.5	272.2	272.4
117.5°	310.2	310.5	310.7	311.1	311.3	311.3	310.9	310.6	310.2	309.8	309.8
120°	334.2	335.1	336.0	336.8	337.7	337.7	337.0	336.3	335.6	334.8	334.8
122.5°	359.3	359.9	360.5	361.2	361.8	361.9	361.5	361.2	360.8	360.4	360.1
125°	397.5	398.0	398.4	398.8	399.2	399.2	399.0	398.7	398.4	398.1	397.6
127.5°	432.7	433.7	434.6	435.5	436.4	436.7	436.4	436.1	435.8	435.5	434.6
130°	456.3	457.4	458.6	459.7	460.8	461.2	460.8	460.4	459.9	459.5	458.9
132.5°	479.8	481.0	482.1	483.2	484.4	484.7	484.5	484.1	483.8	483.5	482.8
135°	515.7	516.6	517.5	518.3	519.1	519.5	519.4	519.2	519.1	518.9	518.3
137.5°	549.0	549.7	550.4	551.1	551.8	552.3	552.7	553.1	553.5	553.8	553.2
140°	572.0	572.7	573.4	574.1	574.8	575.2	575.4	575.5	575.7	575.8	575.7
142.5°	593.0	593.7	594.3	595.0	595.7	596.2	596.5	596.8	597.0	597.3	597.1
145°	625.7	625.9	626.2	626.5	626.8	627.2	627.6	628.0	628.4	628.9	628.7
147.5°	654.3	654.8	655.3	655.8	656.3	656.8	657.2	657.5	658.0	658.4	658.4
150°	674.2	674.5	674.8	675.1	675.4	675.6	675.9	676.2	676.5	676.7	676.7
152.5°	690.6	691.0	691.4	691.8	692.2	692.4	692.6	692.8	692.9	693.1	693.4
155°	716.4	716.4	716.4	716.4	716.4	716.4	716.6	716.8	716.9	717.0	717.6
157.5°	738.4	738.2	738.0	737.9	737.7	737.7	737.8	737.9	738.0	738.1	738.7
160°	752.2	751.9	751.7	751.3	751.1	750.9	750.9	750.9	750.9	750.9	751.7
162.5°	764.5	764.1	763.6	763.3	762.8	762.8	762.8	762.9	763.1	763.2	763.9
165°	780.3	779.9	779.5	779.0	778.6	778.3	778.3	778.3	778.3	778.3	779.2
167.5°	793.0	792.4	791.9	791.3	790.7	790.5	790.6	790.7	790.8	790.9	791.8
170°	800.1	799.5	799.0	798.4	797.8	797.5	797.5	797.5	797.5	797.5	798.6
172.5°	805.7	805.2	804.6	804.0	803.5	803.1	803.1	803.1	803.1	803.1	804.1
175°	811.6	811.1	810.5	809.9	809.3	809.1	809.1	809.1	809.1	809.1	809.9
177.5°	814.1	813.6	813.1	812.7	812.3	812.0	812.0	812.0	812.0	812.0	812.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	12.3	12.3	12.2	12.1	12.1	12.0	11.9	11.8
90°	16.4	17.0	17.7	18.0	18.3	18.6	18.9	19.2
92.5°	25.5	25.9	26.3	26.5	26.3	26.2	26.0	25.8
95°	48.4	49.0	49.6	49.9	49.9	49.9	49.9	49.9
97.5°	75.3	75.9	76.6	76.9	76.9	76.8	76.7	76.7
100°	94.8	95.2	95.7	96.0	96.3	96.6	96.9	97.1
102.5°	117.3	117.7	118.1	118.3	118.3	118.2	118.1	118.1
105°	150.8	150.8	150.8	150.9	151.3	151.5	151.8	152.1
107.5°	187.1	187.6	188.0	188.2	188.0	187.9	187.7	187.5
110°	211.4	212.0	212.5	212.7	212.4	212.1	211.8	211.5



TEST NUMBER: P332437-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.7	236.3	237.0	237.3	237.3	237.2	237.1	237.1
115°	272.5	272.7	272.9	272.9	272.7	272.5	272.4	272.2
117.5°	309.8	309.7	309.7	309.5	309.1	308.7	308.3	307.9
120°	334.6	334.4	334.3	334.1	333.8	333.6	333.2	332.9
122.5°	359.7	359.3	359.0	358.6	358.2	357.7	357.4	357.0
125°	397.0	396.4	395.9	395.3	394.8	394.2	393.6	393.0
127.5°	433.9	433.1	432.3	431.5	430.9	430.2	429.6	429.0
130°	458.4	457.8	457.2	456.4	455.5	454.4	453.5	452.5
132.5°	482.2	481.5	480.8	480.1	479.3	478.5	477.8	477.0
135°	517.8	517.2	516.7	516.3	515.9	515.7	515.4	515.1
137.5°	552.6	552.0	551.5	550.9	550.4	549.7	549.2	548.7
140°	575.5	575.4	575.2	574.6	573.7	572.7	571.7	570.7
142.5°	597.0	596.8	596.7	596.2	595.5	594.7	593.9	593.1
145°	628.5	628.4	628.3	627.9	627.3	626.8	626.2	625.7
147.5°	658.4	658.4	658.4	658.0	657.1	656.3	655.4	654.5
150°	676.7	676.7	676.7	676.3	675.5	674.7	673.8	673.0
152.5°	693.6	693.8	694.1	693.8	693.0	692.3	691.6	690.9
155°	718.2	718.8	719.3	719.1	718.1	717.1	716.1	715.1
157.5°	739.3	739.9	740.5	740.4	739.6	738.8	738.0	737.2
160°	752.3	753.0	753.7	753.8	753.3	752.7	752.1	751.6
162.5°	764.6	765.3	766.0	765.9	765.0	764.1	763.2	762.2
165°	780.1	780.9	781.8	781.7	780.8	779.7	778.8	777.7
167.5°	792.6	793.6	794.4	794.4	793.6	792.6	791.8	790.9
170°	799.5	800.6	801.5	801.5	800.6	799.5	798.6	797.5
172.5°	804.9	805.8	806.7	806.7	805.6	804.7	803.7	802.7
175°	810.8	811.6	812.4	812.4	811.4	810.4	809.4	808.4
177.5°	813.4	814.1	814.8	814.7	813.9	813.0	812.3	811.5
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6

(END OF REPORT)