

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332815-927

Luminaire Tested: **S124DIW-S1020D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332815-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5941.9 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50																			
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42																			
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35																			
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30																			
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26																			
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23																			
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20																			
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18																			
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16																			
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	2.2
10°-20°	362.7	6.1
20°-30°	533.8	9.0
30°-40°	620.6	10.4
40°-50°	620.6	10.4
50°-60°	542.9	9.1
60°-70°	403.2	6.8
70°-80°	229.1	3.9
80°-90°	68.4	1.2
90°-100°	26.9	0.5
100°-110°	171.5	2.9
110°-120°	328.0	5.5
120°-130°	416.3	7.0
130°-140°	445.5	7.5
140°-150°	416.6	7.0
150°-160°	335.9	5.7
160°-170°	216.7	3.6
170°-180°	74.7	1.3
0°-30°	1025.2	17.3
0°-40°	1645.9	27.7
0°-60°	2809.4	47.3
0°-90°	3510.0	59.1
90°-120°	526.3	8.9
90°-150°	1804.7	30.4
90°-180°	2432.0	40.9
0°-180°	5941.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	2	8	13	16	18	5
95°	32	14	13	16	17	42
105°	177	180	184	187	168	185
115°	330	332	332	333	333	325
125°	464	467	466	467	468	415
135°	576	576	578	579	580	444
145°	664	666	666	667	668	415
155°	729	729	727	729	728	336
165°	769	766	766	770	765	217
175°	786	783	783	788	782	75
180°	786	786	786	786	786	



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.1	23.2	23.3	23.4	23.5	23.5	23.6	23.6	23.6	23.6	23.8
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	7.4	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2
95°	32.3	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7
97.5°	68.7	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6
100°	96.4	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7
102.5°	127.5	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7
105°	177.0	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7
107.5°	223.0	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3
110°	254.1	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.2	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9
115°	330.5	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9
117.5°	372.2	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8
120°	400.4	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5
122.5°	426.8	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2
125°	464.5	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1
127.5°	500.3	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5
130°	523.3	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9
132.5°	544.5	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0
135°	576.2	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3
137.5°	604.4	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4
140°	622.7	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4
142.5°	639.2	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3
145°	664.5	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4
147.5°	684.6	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4
150°	699.2	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9
152.5°	711.4	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4
155°	728.6	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9
157.5°	743.1	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3
160°	751.5	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0
162.5°	759.0	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0
165°	768.6	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7
167.5°	776.1	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8
170°	780.3	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4
172.5°	783.2	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3
175°	786.2	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4
177.5°	787.6	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	23.9	24.1	24.2	24.3	24.4	24.5	24.5	24.6
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.0	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	14.5	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.7	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	21.5	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	76.8	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	185.8	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	229.9	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	259.8	260.1	260.4	260.7	261.1	261.5	261.9	262.3



TEST NUMBER: P332815-927

CATALOG NUMBER: S124DIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.8	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.2	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.4	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.5	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	525.9	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.0	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.5	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	607.8	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	625.8	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.6	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.5	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.5	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.6	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	728.4	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	757.8	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	767.7	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	775.0	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	779.4	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	782.3	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	785.6	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.0	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)