

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332851-927

Luminaire Tested: **S124DIW-S1195D1050U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332851-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1050U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7373.7 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	2.0
10°-20°	418.9	5.7
20°-30°	616.5	8.4
30°-40°	716.7	9.7
40°-50°	716.8	9.7
50°-60°	627.0	8.5
60°-70°	465.6	6.3
70°-80°	264.5	3.6
80°-90°	79.4	1.1
90°-100°	36.7	0.5
100°-110°	234.0	3.2
110°-120°	447.7	6.1
120°-130°	568.3	7.7
130°-140°	608.0	8.2
140°-150°	568.6	7.7
150°-160°	458.5	6.2
160°-170°	295.7	4.0
170°-180°	101.9	1.4
0°-30°	1184.1	16.1
0°-40°	1900.8	25.8
0°-60°	3244.6	44.0
0°-90°	4054.2	55.0
90°-120°	718.4	9.7
90°-150°	2463.3	33.4
90°-180°	3319.0	45.0
0°-180°	7373.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	2	11	18	22	24	6
95°	44	18	18	22	23	57
105°	242	246	250	256	229	253
115°	451	453	453	454	454	444
125°	634	637	636	638	639	566
135°	787	786	789	791	792	606
145°	907	909	909	910	912	567
155°	994	995	993	996	994	458
165°	1049	1045	1045	1051	1044	296
175°	1073	1069	1069	1075	1067	102
180°	1073	1073	1073	1073	1073	



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.8	26.9	27.1	27.3	27.5	27.6	27.6	27.7	27.7	27.8	28.0
90°	2.4	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7
92.5°	10.1	10.2	10.3	10.5	10.5	11.3	12.8	14.2	15.6	17.0	18.1
95°	44.1	38.1	32.0	26.0	19.9	17.0	17.1	17.3	17.5	17.7	18.7
97.5°	93.7	97.5	101.3	105.1	108.8	100.8	80.9	61.0	41.1	21.2	21.3
100°	131.7	134.8	138.1	141.2	144.5	133.8	109.2	84.5	60.0	35.3	32.3
102.5°	174.0	176.3	178.7	181.1	183.4	183.0	179.8	176.6	173.3	170.2	137.4
105°	241.6	242.6	243.8	244.8	245.9	246.8	247.7	248.7	249.5	250.4	252.0
107.5°	304.4	304.9	305.4	305.9	306.5	307.4	308.6	309.8	311.0	312.2	313.0
110°	346.7	347.3	347.8	348.3	348.9	349.7	350.8	351.8	352.9	353.9	354.3



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.9	388.8	389.8	390.7	391.7	392.4	392.9	393.4	393.9	394.4	394.3
115°	451.1	451.6	452.2	452.7	453.2	453.4	453.2	453.0	452.9	452.7	453.0
117.5°	508.0	508.7	509.5	510.2	510.9	511.4	511.8	512.2	512.6	513.0	512.9
120°	546.6	547.3	548.0	548.7	549.5	549.7	549.5	549.4	549.1	549.0	549.4
122.5°	582.6	583.0	583.4	583.8	584.2	584.6	584.9	585.1	585.3	585.6	585.8
125°	634.1	634.8	635.5	636.2	636.9	637.1	636.8	636.4	636.0	635.6	636.2
127.5°	682.9	683.0	683.3	683.4	683.6	684.0	684.9	685.7	686.5	687.4	687.3
130°	714.3	714.5	714.7	714.9	715.0	715.4	716.0	716.4	717.0	717.6	717.7
132.5°	743.2	743.5	743.9	744.2	744.5	745.0	745.7	746.4	747.0	747.7	747.9
135°	786.6	786.4	786.2	786.0	785.8	786.2	786.9	787.6	788.3	789.0	789.3
137.5°	824.9	825.0	825.1	825.1	825.2	825.6	826.4	827.2	828.0	828.8	829.2
140°	850.0	850.3	850.7	851.0	851.4	851.8	852.2	852.5	852.9	853.2	853.7
142.5°	872.4	873.1	873.7	874.4	875.0	875.4	875.7	875.8	876.1	876.3	876.7
145°	907.0	907.5	908.0	908.6	909.1	909.3	909.3	909.3	909.3	909.3	909.6
147.5°	934.4	935.4	936.4	937.4	938.4	938.8	938.7	938.5	938.3	938.1	938.3
150°	954.3	955.1	955.8	956.5	957.2	957.4	957.3	957.1	956.9	956.7	956.7
152.5°	971.0	971.6	972.2	972.7	973.3	973.4	973.1	972.8	972.5	972.2	972.4
155°	994.4	994.7	994.8	995.0	995.1	995.0	994.4	994.0	993.4	992.8	993.6
157.5°	1014.2	1014.1	1014.0	1013.8	1013.8	1013.4	1012.8	1012.2	1011.6	1011.0	1011.9
160°	1025.7	1025.2	1024.7	1024.1	1023.6	1023.3	1023.1	1022.9	1022.7	1022.5	1023.6
162.5°	1036.0	1035.4	1034.7	1034.0	1033.3	1032.8	1032.7	1032.5	1032.4	1032.1	1033.2
165°	1049.0	1048.1	1047.3	1046.3	1045.4	1045.0	1045.0	1045.0	1045.0	1045.0	1046.5
167.5°	1059.3	1058.4	1057.5	1056.5	1055.6	1055.1	1054.9	1054.9	1054.8	1054.6	1056.2
170°	1065.1	1064.0	1063.0	1061.8	1060.8	1060.3	1060.5	1060.7	1060.9	1061.0	1062.5
172.5°	1068.9	1067.9	1066.8	1065.7	1064.6	1064.2	1064.4	1064.5	1064.8	1064.9	1066.4
175°	1073.1	1072.1	1071.0	1069.9	1068.8	1068.4	1068.6	1068.7	1068.9	1069.1	1070.7
177.5°	1075.0	1074.0	1073.0	1072.1	1071.0	1070.7	1071.0	1071.3	1071.5	1071.8	1072.9
180°	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	28.3	28.4	28.7	28.8	28.9	29.0	29.0	29.1
90°	19.8	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	19.2	20.2	21.3	21.9	21.9	22.0	22.1	22.2
95°	19.8	20.8	21.9	22.6	22.7	22.9	23.1	23.3
97.5°	21.4	21.5	21.6	21.8	21.9	22.1	22.3	22.5
100°	29.2	26.2	23.2	21.8	21.9	22.1	22.3	22.5
102.5°	104.7	72.0	39.3	23.0	23.0	23.1	23.1	23.1
105°	253.7	255.2	256.8	254.4	248.0	241.6	235.2	228.8
107.5°	313.8	314.6	315.4	316.1	316.8	317.4	318.1	318.8
110°	354.7	355.1	355.4	355.8	356.4	356.9	357.4	358.0



TEST NUMBER: P332851-927

CATALOG NUMBER: S124DIW-S1195D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	394.3	394.2	394.1	394.4	395.1	395.8	396.5	397.1
115°	453.4	453.8	454.1	454.3	454.3	454.3	454.3	454.3
117.5°	512.9	512.9	512.8	512.7	512.6	512.5	512.5	512.4
120°	549.7	550.1	550.4	550.4	550.1	549.7	549.4	549.0
122.5°	586.1	586.2	586.5	586.4	586.1	585.7	585.3	584.9
125°	636.8	637.3	637.8	638.2	638.3	638.5	638.7	638.9
127.5°	687.1	687.1	686.9	686.8	686.7	686.5	686.3	686.3
130°	717.9	718.1	718.3	718.4	718.4	718.4	718.4	718.4
132.5°	748.1	748.3	748.5	748.5	748.3	748.1	748.1	747.9
135°	789.7	790.0	790.4	790.8	791.2	791.5	791.9	792.2
137.5°	829.6	830.0	830.4	830.5	830.4	830.3	830.2	830.0
140°	854.3	854.8	855.3	855.7	855.9	856.0	856.2	856.4
142.5°	877.1	877.5	877.9	878.1	878.1	878.1	878.2	878.2
145°	909.7	909.9	910.1	910.4	910.7	911.1	911.4	911.8
147.5°	938.4	938.5	938.7	938.8	939.1	939.2	939.4	939.5
150°	956.7	956.7	956.7	956.8	957.0	957.2	957.4	957.5
152.5°	972.7	973.0	973.3	973.4	973.3	973.1	973.0	973.0
155°	994.3	995.0	995.7	995.8	995.2	994.7	994.2	993.6
157.5°	1012.8	1013.8	1014.7	1014.7	1013.8	1012.8	1011.9	1011.0
160°	1024.7	1025.7	1026.8	1026.8	1025.7	1024.7	1023.6	1022.5
162.5°	1034.3	1035.4	1036.4	1036.4	1035.1	1034.0	1032.8	1031.5
165°	1047.9	1049.3	1050.8	1050.6	1049.0	1047.4	1045.8	1044.2
167.5°	1057.8	1059.4	1060.9	1060.8	1059.1	1057.2	1055.5	1053.7
170°	1063.9	1065.3	1066.8	1066.6	1064.8	1063.0	1061.2	1059.5
172.5°	1067.8	1069.2	1070.6	1070.4	1068.4	1066.5	1064.6	1062.6
175°	1072.3	1073.9	1075.5	1075.2	1073.1	1071.0	1068.8	1066.7
177.5°	1074.1	1075.2	1076.4	1076.1	1074.4	1072.7	1071.0	1069.3
180°	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1	1073.1

(END OF REPORT)