

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332191-840

Luminaire Tested: **S123DIW-S1000D755U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332191-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6806.0 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56	51
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	51	49	47	43
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24	21
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	2.2
10°-20°	425.2	6.2
20°-30°	628.0	9.2
30°-40°	733.6	10.8
40°-50°	737.6	10.8
50°-60°	647.9	9.5
60°-70°	482.7	7.1
70°-80°	275.0	4.0
80°-90°	81.8	1.2
90°-100°	62.2	0.9
100°-110°	186.1	2.7
110°-120°	316.4	4.6
120°-130°	416.2	6.1
130°-140°	467.8	6.9
140°-150°	459.9	6.8
150°-160°	387.1	5.7
160°-170°	257.7	3.8
170°-180°	90.2	1.3
0°-30°	1203.8	17.7
0°-40°	1937.4	28.5
0°-60°	3322.8	48.8
0°-90°	4162.3	61.2
90°-120°	564.7	8.3
90°-150°	1908.6	28.0
90°-180°	2644.0	38.8
0°-180°	6806.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	8	18	21	22	7
95°	44	50	55	58	58	50
105°	169	170	177	177	178	181
115°	319	321	319	320	319	315
125°	466	468	467	464	461	416
135°	605	609	609	606	604	466
145°	734	735	738	737	734	458
155°	840	840	841	844	839	387
165°	915	913	913	917	912	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.8	28.4	28.0	27.6	27.2	27.1	27.3	27.4	27.6	27.8	27.7
90°	0.7	2.4	4.0	5.8	7.4	9.3	11.5	13.6	15.9	18.0	18.7
92.5°	18.2	19.3	20.4	21.5	22.6	23.8	25.0	26.4	27.6	28.8	29.3
95°	44.2	45.3	46.6	47.8	48.9	50.1	51.5	52.8	54.1	55.4	56.1
97.5°	78.6	79.4	80.3	81.2	82.0	82.9	83.9	84.8	85.8	86.8	87.6
100°	101.9	102.9	103.9	104.9	105.9	106.8	107.7	108.6	109.4	110.2	110.7
102.5°	129.0	129.6	130.2	130.7	131.3	132.2	133.3	134.4	135.4	136.5	137.0
105°	168.6	169.0	169.4	169.7	170.0	170.9	172.4	173.9	175.4	176.9	176.9
107.5°	214.8	215.0	215.2	215.4	215.6	216.0	216.6	217.2	217.8	218.4	218.9
110°	243.6	244.0	244.3	244.6	244.9	245.3	245.6	245.9	246.3	246.6	247.3



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	273.6	273.8	274.0	274.2	274.4	274.5	274.6	274.7	274.7	274.8	275.6
115°	318.6	319.0	319.5	320.0	320.5	320.6	320.3	320.0	319.6	319.3	319.5
117.5°	363.9	364.2	364.5	364.9	365.2	365.2	364.7	364.3	363.9	363.3	363.3
120°	392.0	393.0	394.0	395.1	396.1	396.1	395.3	394.5	393.6	392.7	392.6
122.5°	421.4	422.1	422.8	423.6	424.3	424.4	424.0	423.6	423.2	422.7	422.3
125°	466.3	466.8	467.3	467.8	468.3	468.3	468.0	467.7	467.3	467.0	466.4
127.5°	507.6	508.7	509.8	510.8	511.9	512.2	511.9	511.5	511.1	510.8	509.8
130°	535.2	536.5	537.9	539.2	540.5	541.0	540.5	540.0	539.5	539.0	538.3
132.5°	562.8	564.1	565.4	566.7	568.2	568.6	568.3	567.8	567.4	567.1	566.3
135°	604.9	605.9	606.9	607.9	608.8	609.4	609.2	608.9	608.8	608.6	607.9
137.5°	643.9	644.7	645.5	646.4	647.2	647.8	648.2	648.7	649.1	649.5	648.8
140°	670.9	671.7	672.6	673.4	674.2	674.7	674.9	675.0	675.2	675.4	675.2
142.5°	695.5	696.3	697.1	697.9	698.7	699.3	699.6	699.9	700.2	700.5	700.3
145°	733.9	734.2	734.5	734.8	735.2	735.6	736.1	736.6	737.1	737.6	737.4
147.5°	767.4	768.0	768.6	769.2	769.8	770.3	770.8	771.2	771.7	772.2	772.2
150°	790.8	791.1	791.4	791.8	792.1	792.4	792.7	793.1	793.5	793.8	793.8
152.5°	810.0	810.4	810.9	811.4	811.8	812.1	812.3	812.5	812.7	812.9	813.2
155°	840.3	840.3	840.3	840.3	840.3	840.3	840.5	840.7	840.8	841.0	841.7
157.5°	866.1	865.9	865.7	865.5	865.3	865.3	865.4	865.5	865.7	865.8	866.5
160°	882.2	881.9	881.6	881.2	880.9	880.7	880.7	880.7	880.7	880.7	881.6
162.5°	896.7	896.2	895.6	895.2	894.7	894.6	894.7	894.8	895.0	895.1	896.0
165°	915.2	914.7	914.2	913.7	913.2	912.9	912.9	912.9	912.9	912.9	913.9
167.5°	930.1	929.4	928.8	928.1	927.4	927.2	927.3	927.4	927.6	927.7	928.7
170°	938.5	937.8	937.2	936.4	935.7	935.4	935.4	935.4	935.4	935.4	936.6
172.5°	945.0	944.4	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.1
175°	951.9	951.3	950.6	950.0	949.3	949.0	949.0	949.0	949.0	949.0	950.0
177.5°	954.8	954.2	953.7	953.2	952.7	952.4	952.4	952.4	952.4	952.4	953.2
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	27.6	27.5	27.4	27.4	27.4	27.5	27.6	27.6
90°	19.3	20.0	20.7	21.1	21.5	21.8	22.1	22.5
92.5°	29.9	30.4	30.9	31.1	30.9	30.7	30.5	30.3
95°	56.8	57.5	58.2	58.5	58.5	58.5	58.5	58.5
97.5°	88.4	89.1	89.9	90.2	90.2	90.1	90.0	90.0
100°	111.2	111.7	112.2	112.6	112.9	113.3	113.6	113.9
102.5°	137.5	138.0	138.6	138.8	138.8	138.7	138.6	138.6
105°	176.9	176.9	176.9	177.0	177.4	177.7	178.0	178.4
107.5°	219.4	220.0	220.6	220.8	220.6	220.4	220.2	219.9
110°	247.9	248.6	249.2	249.4	249.1	248.7	248.4	248.1



TEST NUMBER: P332191-840

CATALOG NUMBER: S123DIW-S1000D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.4	277.2	278.0	278.3	278.3	278.2	278.1	278.1
115°	319.6	319.8	320.0	320.0	319.8	319.6	319.5	319.3
117.5°	363.3	363.2	363.2	363.0	362.5	362.0	361.6	361.1
120°	392.4	392.2	392.1	391.8	391.5	391.2	390.8	390.5
122.5°	421.9	421.4	421.0	420.6	420.1	419.6	419.2	418.7
125°	465.6	464.9	464.3	463.6	463.0	462.3	461.6	461.0
127.5°	508.9	508.0	507.1	506.1	505.4	504.6	503.9	503.1
130°	537.7	536.9	536.2	535.3	534.2	533.0	531.9	530.7
132.5°	565.5	564.7	563.9	563.1	562.2	561.3	560.4	559.5
135°	607.3	606.6	606.0	605.5	605.1	604.8	604.5	604.1
137.5°	648.1	647.4	646.8	646.1	645.5	644.8	644.2	643.6
140°	675.0	674.9	674.7	674.0	672.9	671.7	670.6	669.3
142.5°	700.2	700.0	699.8	699.3	698.4	697.5	696.6	695.7
145°	737.2	737.1	736.9	736.5	735.8	735.2	734.5	733.9
147.5°	772.2	772.2	772.2	771.7	770.7	769.7	768.7	767.7
150°	793.8	793.8	793.8	793.2	792.2	791.3	790.3	789.3
152.5°	813.5	813.7	814.1	813.7	812.8	812.0	811.1	810.3
155°	842.3	843.0	843.6	843.4	842.2	841.1	839.9	838.8
157.5°	867.2	867.9	868.6	868.4	867.5	866.6	865.7	864.6
160°	882.4	883.2	884.0	884.1	883.5	882.8	882.1	881.5
162.5°	896.8	897.7	898.5	898.4	897.3	896.3	895.1	894.0
165°	914.9	915.9	917.0	916.9	915.7	914.5	913.4	912.2
167.5°	929.7	930.8	931.8	931.8	930.8	929.7	928.7	927.7
170°	937.8	939.0	940.1	940.1	939.0	937.8	936.6	935.4
172.5°	944.1	945.1	946.1	946.1	944.9	943.8	942.6	941.5
175°	951.0	951.9	952.9	952.9	951.7	950.5	949.4	948.2
177.5°	954.0	954.8	955.6	955.5	954.6	953.6	952.7	951.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2

(END OF REPORT)