

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332227-840

Luminaire Tested: **S123DIW-S1165D1030U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332227-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1030U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8416.3 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	33	29
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	36	31	38	33	28	33	29	25	29	25	22	20
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20	18
9	51	39	31	26	48	36	30	25	32	26	22	28	24	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.1
10°-20°	491.0	5.8
20°-30°	725.3	8.6
30°-40°	847.3	10.1
40°-50°	851.8	10.1
50°-60°	748.3	8.9
60°-70°	557.5	6.6
70°-80°	317.6	3.8
80°-90°	95.0	1.1
90°-100°	84.9	1.0
100°-110°	254.0	3.0
110°-120°	431.9	5.1
120°-130°	568.1	6.8
130°-140°	638.6	7.6
140°-150°	627.7	7.5
150°-160°	528.4	6.3
160°-170°	351.8	4.2
170°-180°	123.2	1.5
0°-30°	1390.3	16.5
0°-40°	2237.6	26.6
0°-60°	3837.7	45.6
0°-90°	4807.7	57.1
90°-120°	770.8	9.2
90°-150°	2605.2	31.0
90°-180°	3609.0	42.9
0°-180°	8416.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	1	11	24	29	31	8
95°	60	68	76	80	80	68
105°	230	233	242	242	244	247
115°	435	438	436	437	436	430
125°	636	639	637	633	629	567
135°	826	831	831	827	825	636
145°	1002	1004	1007	1006	1002	625
155°	1147	1147	1148	1151	1145	528
165°	1249	1246	1246	1252	1245	352
175°	1299	1296	1295	1301	1294	123
180°	1302	1302	1302	1302	1302	



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.2	32.8	32.4	32.0	31.6	31.6	31.9	32.2	32.5	32.8	32.7
90°	1.0	3.3	5.6	7.9	10.1	12.7	15.7	18.7	21.6	24.5	25.4
92.5°	24.7	26.3	27.9	29.4	30.9	32.5	34.2	36.0	37.6	39.3	40.0
95°	60.4	61.9	63.5	65.1	66.8	68.5	70.3	72.1	73.9	75.7	76.6
97.5°	107.2	108.4	109.6	110.8	112.0	113.2	114.5	115.8	117.1	118.5	119.6
100°	139.2	140.5	141.9	143.2	144.6	145.8	147.0	148.1	149.3	150.4	151.1
102.5°	176.0	176.8	177.6	178.4	179.3	180.4	181.9	183.4	184.9	186.4	187.1
105°	230.2	230.7	231.2	231.6	232.1	233.3	235.3	237.3	239.4	241.5	241.5
107.5°	293.3	293.5	293.8	294.1	294.3	294.9	295.7	296.5	297.3	298.1	298.8
110°	332.5	333.0	333.5	333.9	334.4	334.8	335.3	335.7	336.2	336.6	337.5



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.4	373.8	374.0	374.3	374.6	374.7	374.8	374.9	375.0	375.1	376.2
115°	434.8	435.5	436.2	436.9	437.6	437.7	437.2	436.8	436.3	435.9	436.1
117.5°	496.7	497.1	497.6	498.0	498.5	498.4	497.8	497.2	496.6	496.0	495.9
120°	535.1	536.4	537.9	539.2	540.6	540.7	539.5	538.4	537.2	536.1	535.8
122.5°	575.2	576.2	577.2	578.1	579.2	579.4	578.9	578.2	577.6	577.0	576.4
125°	636.4	637.0	637.7	638.4	639.1	639.2	638.7	638.3	637.8	637.4	636.5
127.5°	692.9	694.3	695.8	697.2	698.6	699.1	698.6	698.1	697.6	697.1	695.9
130°	730.5	732.4	734.2	736.0	737.8	738.3	737.7	737.0	736.3	735.6	734.7
132.5°	768.1	769.9	771.7	773.7	775.5	776.1	775.6	775.1	774.6	774.1	773.0
135°	825.7	827.0	828.4	829.7	831.1	831.6	831.4	831.2	831.0	830.7	829.8
137.5°	878.9	880.0	881.1	882.2	883.4	884.2	884.8	885.4	886.1	886.7	885.7
140°	915.6	916.9	918.0	919.1	920.2	920.9	921.1	921.4	921.6	921.8	921.6
142.5°	949.3	950.4	951.5	952.6	953.8	954.5	954.9	955.3	955.8	956.2	955.9
145°	1001.6	1002.1	1002.5	1003.0	1003.4	1004.0	1004.7	1005.4	1006.0	1006.7	1006.5
147.5°	1047.4	1048.2	1049.0	1050.0	1050.8	1051.5	1052.1	1052.8	1053.4	1054.0	1054.0
150°	1079.3	1079.8	1080.3	1080.8	1081.2	1081.7	1082.1	1082.6	1083.0	1083.5	1083.5
152.5°	1105.6	1106.2	1106.8	1107.5	1108.1	1108.5	1108.8	1109.1	1109.4	1109.6	1110.0
155°	1146.9	1146.9	1146.9	1146.9	1146.9	1147.0	1147.2	1147.5	1147.7	1147.9	1148.8
157.5°	1182.1	1181.8	1181.5	1181.2	1181.0	1180.9	1181.1	1181.3	1181.5	1181.6	1182.7
160°	1204.2	1203.8	1203.3	1202.9	1202.3	1202.1	1202.1	1202.1	1202.1	1202.1	1203.3
162.5°	1223.9	1223.2	1222.5	1221.9	1221.3	1221.0	1221.2	1221.4	1221.6	1221.8	1222.9
165°	1249.2	1248.5	1247.9	1247.2	1246.5	1246.2	1246.2	1246.2	1246.2	1246.2	1247.5
167.5°	1269.5	1268.6	1267.7	1266.8	1265.9	1265.5	1265.7	1265.9	1266.1	1266.2	1267.6
170°	1280.9	1280.0	1279.1	1278.2	1277.3	1276.9	1276.9	1276.9	1276.9	1276.9	1278.4
172.5°	1289.9	1289.0	1288.1	1287.2	1286.3	1285.9	1285.9	1285.9	1285.9	1285.9	1287.3
175°	1299.4	1298.5	1297.6	1296.7	1295.8	1295.3	1295.3	1295.3	1295.3	1295.3	1296.7
177.5°	1303.2	1302.5	1301.8	1301.0	1300.3	1300.0	1300.0	1300.0	1300.0	1300.0	1301.0
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	32.6	32.5	32.4	32.4	32.5	32.6	32.7	32.8
90°	26.4	27.3	28.2	28.9	29.3	29.8	30.2	30.7
92.5°	40.7	41.5	42.2	42.4	42.1	41.9	41.6	41.3
95°	77.6	78.5	79.4	79.8	79.8	79.8	79.8	79.8
97.5°	120.6	121.6	122.7	123.1	123.0	123.0	122.9	122.8
100°	151.8	152.5	153.1	153.7	154.1	154.6	155.0	155.5
102.5°	187.7	188.4	189.1	189.5	189.3	189.2	189.1	189.0
105°	241.5	241.5	241.5	241.7	242.2	242.6	243.1	243.5
107.5°	299.6	300.3	301.0	301.2	301.0	300.7	300.4	300.1
110°	338.4	339.3	340.2	340.4	340.0	339.5	339.1	338.6



TEST NUMBER: P332227-840

CATALOG NUMBER: S123DIW-S1165D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	377.3	378.3	379.4	379.9	379.8	379.7	379.7	379.6
115°	436.3	436.6	436.8	436.8	436.6	436.3	436.1	435.9
117.5°	495.9	495.8	495.8	495.4	494.8	494.2	493.5	492.9
120°	535.6	535.4	535.2	534.8	534.4	533.9	533.5	533.0
122.5°	575.8	575.2	574.7	574.0	573.4	572.8	572.2	571.5
125°	635.6	634.7	633.8	632.9	632.0	631.1	630.2	629.2
127.5°	694.6	693.4	692.1	690.8	689.8	688.8	687.7	686.7
130°	733.8	732.9	732.0	730.7	729.1	727.5	726.0	724.4
132.5°	771.9	770.8	769.7	768.6	767.3	766.1	764.9	763.7
135°	828.9	828.0	827.1	826.5	826.0	825.6	825.1	824.7
137.5°	884.7	883.7	882.8	881.9	881.0	880.2	879.3	878.5
140°	921.4	921.1	920.9	920.0	918.4	916.9	915.2	913.6
142.5°	955.7	955.5	955.3	954.5	953.3	952.1	950.9	949.7
145°	1006.3	1006.0	1005.8	1005.2	1004.3	1003.4	1002.5	1001.6
147.5°	1054.0	1054.0	1054.0	1053.3	1052.0	1050.6	1049.2	1047.8
150°	1083.5	1083.5	1083.5	1082.8	1081.5	1080.1	1078.7	1077.3
152.5°	1110.3	1110.8	1111.2	1110.8	1109.5	1108.3	1107.1	1106.0
155°	1149.7	1150.6	1151.5	1151.2	1149.6	1148.0	1146.5	1144.9
157.5°	1183.6	1184.6	1185.5	1185.4	1184.1	1182.9	1181.5	1180.2
160°	1204.5	1205.6	1206.7	1206.8	1205.9	1205.0	1204.1	1203.2
162.5°	1224.1	1225.2	1226.4	1226.2	1224.8	1223.2	1221.8	1220.3
165°	1248.9	1250.2	1251.6	1251.5	1249.9	1248.3	1246.7	1245.2
167.5°	1269.0	1270.4	1271.8	1271.8	1270.4	1269.0	1267.6	1266.2
170°	1280.0	1281.6	1283.2	1283.2	1281.6	1280.0	1278.4	1276.9
172.5°	1288.7	1290.1	1291.5	1291.4	1289.8	1288.2	1286.6	1285.1
175°	1298.0	1299.4	1300.7	1300.6	1299.0	1297.4	1295.9	1294.2
177.5°	1302.1	1303.2	1304.3	1304.2	1302.9	1301.7	1300.4	1299.2
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4

(END OF REPORT)