

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332859-927

Luminaire Tested: **S124DIW-S1195D1560U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332859-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U927-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9157.9 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	85	82	79	71	69	67	59	57	55	47	46	45	39
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38	33
3	81	72	64	59	74	66	60	55	56	51	47	46	42	40	37	35	33	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12327	12327	12327	12327
5°	14515	12358	10907	12358
10°	17379	12304	9820	12304
15°	20563	12179	9018	12179
20°	22898	12052	8303	12052
25°	23267	11866	7808	11866
30°	19799	11686	7652	11686
35°	15221	11395	7655	11395
40°	11864	11052	7798	11052
45°	9893	10535	7929	10535
50°	8706	9905	8199	9905
55°	7976	9151	8528	9151
60°	7476	8477	8925	8477
65°	6959	7721	9255	7721
70°	6359	6973	9465	6973
75°	5680	6135	9351	6135
80°	4761	5026	9056	5026
85°	3511	3631	8670	3631



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	1.6
10°-20°	458.5	5.0
20°-30°	727.0	7.9
30°-40°	809.1	8.8
40°-50°	736.5	8.0
50°-60°	601.9	6.6
60°-70°	429.7	4.7
70°-80°	236.6	2.6
80°-90°	69.2	0.8
90°-100°	54.6	0.6
100°-110°	348.3	3.8
110°-120°	666.3	7.3
120°-130°	845.9	9.2
130°-140°	905.0	9.9
140°-150°	846.3	9.2
150°-160°	682.5	7.5
160°-170°	440.2	4.8
170°-180°	151.7	1.7
0°-30°	1334.3	14.6
0°-40°	2143.4	23.4
0°-60°	3481.7	38.0
0°-90°	4217.2	46.0
90°-120°	1069.3	11.7
90°-150°	3666.4	40.0
90°-180°	4941.0	54.0
0°-180°	9157.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1527	1527	1527	1527	1527	
5°	1791	1525	1346	1525	1791	182
15°	2460	1457	1079	1457	2460	695
25°	2612	1332	877	1332	2612	1152
35°	1544	1156	777	1156	1544	980
45°	866	923	694	923	866	683
55°	567	650	606	650	567	512
65°	364	404	484	404	364	361
75°	182	197	300	197	182	194
85°	38	39	94	39	38	47
90°	36	4	36	4	36	17
95°	35	66	35	66	35	28
105°	340	360	340	360	340	297
115°	676	671	676	671	676	669
125°	951	944	951	944	951	847
135°	1179	1171	1179	1171	1179	908
145°	1357	1350	1357	1350	1357	848
155°	1479	1480	1479	1480	1479	682
165°	1554	1561	1554	1561	1554	439
175°	1588	1597	1588	1597	1588	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1625.0	1624.4	1619.5	1618.4	1614.9	1610.3	1609.3	1601.2	1585.0	1577.4	1575.4
5°	1791.2	1803.9	1787.4	1784.2	1782.3	1761.5	1750.7	1738.0	1709.0	1691.9	1678.6
7.5°	1989.6	1991.1	1983.9	1978.1	1962.0	1943.8	1916.4	1887.4	1852.7	1816.6	1789.5
10°	2120.1	2125.2	2116.9	2115.7	2083.4	2063.2	2022.7	1988.5	1949.3	1905.7	1865.8
12.5°	2257.7	2250.7	2246.5	2219.4	2213.4	2176.5	2129.5	2094.3	2033.8	1983.6	1930.6
15°	2460.4	2446.5	2437.6	2400.3	2381.9	2330.7	2280.8	2242.2	2163.1	2087.9	2030.9
17.5°	2579.3	2593.2	2572.7	2557.4	2510.0	2474.1	2423.0	2342.0	2280.1	2186.7	2114.8
20°	2665.3	2666.6	2655.2	2639.4	2602.1	2556.5	2500.8	2412.3	2338.3	2245.4	2146.7
22.5°	2688.6	2688.8	2684.0	2669.3	2641.0	2604.1	2547.9	2474.1	2384.4	2283.3	2184.6
25°	2612.1	2609.6	2615.3	2631.8	2621.0	2609.6	2577.4	2522.4	2438.9	2331.9	2225.7
27.5°	2328.3	2345.7	2377.9	2418.4	2457.3	2487.1	2495.5	2484.1	2432.4	2344.5	2233.2
30°	2123.9	2145.4	2169.5	2209.9	2288.4	2333.2	2382.6	2419.9	2399.0	2328.9	2225.1
32.5°	1899.3	1904.6	1940.2	1986.2	2058.1	2144.5	2222.7	2298.4	2323.6	2286.8	2200.3
35°	1544.5	1553.4	1592.0	1637.5	1725.5	1831.1	1948.7	2053.7	2140.3	2175.1	2130.8
37.5°	1260.4	1285.9	1313.0	1362.0	1439.4	1534.5	1656.8	1792.6	1921.8	2008.3	2022.9
40°	1125.8	1141.6	1161.3	1198.6	1264.3	1358.0	1462.9	1618.5	1755.8	1879.8	1920.2
42.5°	1019.5	1028.8	1040.8	1074.6	1124.7	1217.8	1313.7	1450.6	1588.3	1736.5	1804.4
45°	866.5	876.0	896.2	915.8	953.8	1018.3	1107.5	1220.0	1358.6	1501.5	1626.7
47.5°	756.0	762.0	774.0	795.0	827.3	869.8	942.4	1036.4	1164.8	1303.5	1437.0
50°	693.2	698.2	707.7	726.7	751.4	789.3	848.8	936.7	1037.3	1177.0	1308.0
52.5°	643.6	645.6	652.6	665.5	685.1	717.0	765.8	838.5	932.0	1056.6	1187.1
55°	566.7	569.3	575.6	585.0	602.1	622.3	659.7	714.1	795.7	903.8	1017.0
57.5°	503.4	505.3	510.6	514.2	528.2	544.7	573.4	612.3	674.1	765.8	866.9
60°	463.0	461.7	468.0	471.2	480.7	494.6	516.7	554.1	607.8	681.8	774.8
62.5°	423.5	421.8	427.1	431.3	436.7	448.5	466.7	495.9	539.5	606.4	686.7
65°	364.3	361.8	365.0	370.0	375.1	381.4	394.7	420.6	455.4	503.4	564.8
67.5°	304.8	307.5	308.0	310.5	313.5	322.1	331.1	349.5	374.1	412.5	464.5
70°	269.4	270.1	272.6	272.6	274.5	282.1	289.7	300.4	324.5	359.9	402.3
72.5°	234.0	236.7	235.7	237.7	239.1	244.2	249.7	259.9	280.4	306.7	342.5
75°	182.1	184.0	184.0	184.7	186.6	188.5	192.9	200.5	215.1	234.6	259.3
77.5°	132.8	133.1	134.0	136.3	136.3	139.3	142.6	148.6	155.8	169.3	184.3
80°	102.4	103.7	103.1	104.3	104.3	106.9	108.1	115.7	118.9	127.8	139.7
82.5°	75.2	76.4	76.3	78.0	79.1	79.5	81.4	84.4	87.5	95.4	100.3
85°	37.9	39.2	37.9	39.2	41.1	41.7	43.6	44.3	46.8	48.7	53.2
87.5°	18.3	19.7	19.6	20.0	20.9	21.2	21.4	20.6	22.3	22.5	24.1
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5	26.9	25.3	23.2
95°	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5	27.9	26.3	26.0
97.5°	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8	31.7	31.5	61.2
100°	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6	48.1	52.6	89.2
102.5°	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9	204.5	253.3	258.0
105°	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5	375.1	372.7	371.4
107.5°	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1	465.9	464.7	462.9
110°	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9	527.4	526.8	525.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8	586.9	587.1	586.3
115°	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9	674.3	673.8	674.1
117.5°	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4	763.5	763.6	763.0
120°	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1	817.4
122.5°	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3	872.0	871.6	871.2
125°	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8	947.0	946.2	946.7
127.5°	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8	1022.9	1023.1	1021.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6	1068.3	1068.0	1067.2
132.5°	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5	1113.2	1112.9	1111.9
135°	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4	1174.9	1174.3	1173.3
137.5°	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8	1234.1	1233.6	1232.4
140°	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5	1270.7	1269.9	1269.4
142.5°	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5	1304.9	1304.3	1304.0
145°	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1	1353.8	1353.5	1353.5
147.5°	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7	1396.5	1396.3	1396.5
150°	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0	1424.0	1424.0	1424.3
152.5°	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8	1447.4	1446.9	1447.4
155°	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9	1478.8	1477.7	1478.6
157.5°	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8	1505.7
160°	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9	1522.3
162.5°	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5	1537.9	1536.3	1536.6
165°	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6	1557.5	1555.4	1555.4
167.5°	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5	1572.1	1569.8	1569.9
170°	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6	1581.4	1579.3	1579.1
172.5°	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3	1587.1	1585.1	1584.8
175°	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0	1593.6	1591.3	1591.0
177.5°	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7	1597.0	1595.3	1594.9
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1575.9	1568.8	1563.8	1559.7	1548.6	1542.0	1536.9	1529.9	1521.8	1513.1	1502.5
5°	1665.3	1643.9	1628.0	1604.0	1581.2	1562.3	1542.6	1525.0	1503.4	1480.0	1462.9
7.5°	1759.4	1727.4	1686.3	1650.8	1610.8	1576.0	1544.9	1513.1	1479.9	1447.8	1418.3
10°	1819.0	1777.9	1732.3	1678.6	1628.0	1583.1	1541.3	1500.9	1461.7	1422.4	1388.9
12.5°	1883.3	1832.1	1764.7	1701.9	1645.2	1585.2	1534.8	1485.2	1437.9	1396.7	1357.6
15°	1969.6	1895.5	1817.7	1733.6	1659.0	1588.8	1519.9	1457.2	1404.1	1349.7	1311.8
17.5°	2022.6	1931.0	1842.1	1754.1	1663.8	1575.3	1500.9	1428.7	1362.2	1308.1	1260.3
20°	2057.5	1966.4	1855.7	1767.8	1660.3	1569.2	1483.2	1402.9	1333.3	1275.7	1226.4
22.5°	2087.9	1982.6	1871.9	1756.2	1649.2	1552.5	1458.4	1377.5	1306.5	1245.9	1198.6
25°	2104.3	1983.5	1863.3	1748.2	1626.7	1512.3	1426.9	1332.1	1256.1	1192.2	1141.6
27.5°	2106.1	1976.9	1841.0	1713.0	1587.7	1481.1	1373.2	1288.5	1209.7	1142.2	1093.6
30°	2100.5	1965.8	1819.6	1681.2	1555.3	1439.6	1345.9	1253.6	1173.3	1106.2	1055.6
32.5°	2082.8	1942.5	1792.3	1645.8	1515.3	1402.1	1305.4	1217.7	1139.4	1073.3	1020.2
35°	2031.6	1893.0	1733.0	1580.6	1447.2	1332.7	1245.4	1156.2	1077.8	1015.2	963.9
37.5°	1951.5	1826.2	1663.6	1505.9	1374.8	1259.8	1173.3	1092.7	1022.0	958.4	905.9
40°	1881.7	1771.6	1608.4	1454.7	1313.0	1203.6	1122.7	1048.7	978.4	918.4	868.4
42.5°	1801.2	1705.3	1554.8	1391.9	1255.4	1145.4	1066.5	1000.1	933.9	878.4	828.5
45°	1657.7	1594.5	1452.9	1302.3	1160.0	1056.2	981.0	922.8	867.1	812.8	771.0
47.5°	1492.8	1461.4	1342.1	1199.2	1064.1	961.9	896.6	842.9	794.0	748.0	711.1
50°	1382.0	1366.8	1263.7	1125.8	996.8	900.6	834.9	788.7	746.9	706.5	671.7
52.5°	1272.7	1272.2	1179.2	1053.0	933.6	841.0	775.7	732.5	696.4	663.5	632.2
55°	1105.6	1123.3	1050.6	937.9	831.1	747.6	688.8	650.2	624.9	597.7	574.3
57.5°	952.1	981.5	921.5	822.4	733.2	656.2	605.1	576.1	549.1	532.7	515.6
60°	852.0	879.8	833.0	749.5	665.4	599.6	550.9	525.0	501.5	490.2	478.2
62.5°	762.9	787.7	753.0	675.7	602.6	539.4	498.3	473.3	457.6	445.1	437.2
65°	635.6	656.6	626.8	570.5	507.9	457.3	423.7	404.2	389.0	383.9	375.1
67.5°	513.8	532.8	516.7	468.9	418.7	380.4	354.2	335.3	326.4	321.9	315.6
70°	441.5	460.4	443.4	401.6	363.1	330.8	306.1	295.4	285.9	284.0	275.1
72.5°	380.2	393.2	376.0	343.4	310.5	283.2	264.1	252.9	248.0	244.5	239.7
75°	285.3	296.7	285.3	259.9	236.5	217.6	201.1	196.7	191.0	189.1	185.9
77.5°	201.9	211.8	203.0	187.2	169.8	155.1	146.2	140.5	139.3	136.0	137.5
80°	154.3	160.7	152.4	141.6	127.8	117.6	111.3	108.1	104.3	103.1	105.6
82.5°	110.8	113.6	109.4	102.2	91.8	85.2	81.0	77.3	76.5	76.8	76.8
85°	57.6	57.0	56.3	50.0	46.8	42.4	39.8	39.2	38.6	39.8	41.1
87.5°	23.6	23.7	22.8	20.3	18.1	16.1	15.0	13.9	15.0	16.1	17.1
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1	15.2	15.4	15.5
95°	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7	56.6	47.7	38.7
97.5°	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5	145.1	150.8	156.5
100°	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9	200.7	205.5	210.2
102.5°	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0	262.5	266.0	269.5
105°	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6	361.2	362.7	364.4
107.5°	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0	453.8	454.6	455.4
110°	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1	516.9	517.7	518.5



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3	578.7	580.1	581.5
115°	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4	672.2	673.0	673.8
117.5°	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2	757.2	758.4	759.4
120°	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6	814.6	815.7	816.7
122.5°	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0	867.7	868.3	868.9
125°	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8	944.8	945.9	947.0
127.5°	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4	1016.7	1016.9	1017.2
130°	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3	1063.5	1063.7	1064.1
132.5°	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2	1106.7	1107.2	1107.7
135°	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8	1170.4	1170.2	1170.0
137.5°	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9	1228.0	1228.0	1228.2
140°	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1	1265.7	1266.2	1266.7
142.5°	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5	1299.5	1300.5	1301.5
145°	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0	1350.8	1351.5	1352.3
147.5°	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8	1392.3	1393.8	1395.3
150°	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5	1421.5	1422.5	1423.6
152.5°	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3	1446.1	1447.0	1447.8
155°	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2	1480.4	1480.7	1481.0
157.5°	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6	1509.4	1509.3	1509.1
160°	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8	1526.0	1525.2	1524.4
162.5°	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1	1541.0	1540.0	1539.1
165°	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4	1560.0	1558.8	1557.4
167.5°	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7	1575.3	1573.9	1572.6
170°	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3	1583.7	1582.1	1580.5
172.5°	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0	1589.4	1587.9	1586.3
175°	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2	1595.6	1594.0	1592.4
177.5°	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1	1598.6	1597.1	1595.6
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1497.5	1492.9	1486.4	1477.3	1469.7	1461.6	1459.5	1456.5	1462.5	1457.5	1456.0
5°	1448.4	1435.1	1418.0	1398.4	1387.0	1370.6	1367.5	1361.1	1354.8	1354.2	1347.8
7.5°	1396.4	1376.9	1354.6	1334.5	1316.1	1298.1	1286.3	1283.8	1274.5	1269.0	1262.7
10°	1363.0	1338.9	1313.0	1294.1	1272.6	1253.6	1240.3	1232.7	1226.4	1219.4	1213.1
12.5°	1323.6	1298.0	1276.6	1256.1	1230.6	1216.2	1194.3	1181.1	1179.9	1180.0	1163.6
15°	1277.6	1252.4	1219.4	1190.3	1176.4	1148.6	1136.5	1121.4	1111.9	1102.4	1094.9
17.5°	1225.1	1193.7	1167.9	1134.6	1108.0	1085.8	1070.1	1061.0	1046.6	1033.2	1023.5
20°	1192.2	1158.7	1131.6	1096.1	1067.0	1039.8	1026.5	1013.9	1003.1	991.7	981.0
22.5°	1158.8	1123.8	1090.5	1056.1	1029.0	1000.4	987.5	970.3	960.1	953.8	943.0
25°	1106.2	1068.3	1030.3	997.4	969.6	944.3	927.2	913.9	902.5	897.5	890.6
27.5°	1049.0	1011.4	974.7	937.3	905.7	887.4	873.7	863.7	857.1	850.4	847.3
30°	1012.6	973.4	934.2	899.4	870.3	852.0	839.3	832.3	827.3	824.1	820.9
32.5°	975.7	937.0	895.7	864.0	837.9	821.6	812.0	805.0	802.5	801.4	800.3
35°	916.5	877.3	839.3	810.9	786.2	779.8	771.7	767.9	766.6	771.0	772.9
37.5°	859.2	822.8	787.8	760.3	744.1	734.8	732.1	732.1	736.7	740.6	745.2
40°	822.2	786.8	753.9	729.9	714.7	709.0	707.7	710.9	716.0	720.4	725.5
42.5°	786.3	751.4	721.5	699.0	688.4	683.2	684.0	687.1	694.2	699.7	707.3
45°	730.6	701.4	672.3	654.0	645.2	646.4	646.4	652.1	659.0	667.3	675.5
47.5°	678.0	648.7	624.8	609.3	604.8	603.6	607.2	614.7	624.6	634.8	646.3
50°	642.6	614.8	593.9	580.0	575.0	576.9	581.9	588.8	600.9	613.5	625.5
52.5°	606.7	581.4	562.1	549.1	545.6	549.0	554.1	565.1	575.6	589.2	603.8
55°	550.9	529.4	514.2	504.7	503.4	505.3	511.0	523.1	538.2	555.3	569.3
57.5°	495.4	477.4	463.5	456.9	457.6	459.3	468.7	483.0	499.2	517.4	535.4
60°	457.9	441.5	430.1	425.0	425.6	429.4	440.8	454.2	474.4	492.1	511.0
62.5°	422.5	408.1	397.2	392.7	391.7	400.1	411.0	424.8	445.0	464.8	485.2
65°	365.6	354.2	345.3	342.8	344.7	351.0	365.0	383.3	400.4	421.2	442.8
67.5°	309.9	300.6	294.5	295.6	297.9	307.3	318.9	334.7	354.1	375.7	397.0
70°	274.5	265.6	260.5	261.2	265.0	276.4	286.5	302.3	323.2	345.3	363.1
72.5°	238.1	232.3	227.7	230.4	234.2	242.0	254.6	270.5	288.8	309.4	328.1
75°	182.8	182.8	180.2	182.1	187.8	195.4	204.9	221.3	239.7	256.2	271.3
77.5°	135.6	134.2	135.9	138.2	141.4	150.4	161.3	173.0	186.9	203.3	215.8
80°	103.7	104.3	107.5	111.3	112.6	119.5	130.9	141.6	152.4	166.4	178.4
82.5°	78.0	78.6	80.2	85.0	86.3	93.7	101.1	111.9	121.6	130.9	140.9
85°	42.4	42.4	45.6	47.5	50.6	55.7	60.0	66.4	75.3	81.6	91.1
87.5°	19.3	19.7	22.2	23.6	25.6	28.5	29.9	35.7	38.1	41.0	45.7
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5	30.1	31.7	32.6
95°	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5	31.1	32.6	33.6
97.5°	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8	32.0	32.2	32.4
100°	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6	39.1	34.5	32.4
102.5°	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9	107.2	58.5	34.2
105°	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5	379.9	382.3	378.7
107.5°	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1	468.3	469.4	470.5
110°	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9	528.5	528.9	529.7



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8	586.7	586.6	587.1
115°	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9	675.3	675.9	676.2
117.5°	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4	763.3	763.2	763.1
120°	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2	818.7	819.3	819.3
122.5°	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3	872.6	872.9	872.7
125°	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8	948.6	949.4	949.9
127.5°	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8	1022.6	1022.5	1022.2
130°	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6	1068.8	1069.1	1069.2
132.5°	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5	1113.7	1114.0	1114.0
135°	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4	1175.9	1176.5	1177.0
137.5°	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8	1235.3	1236.0	1236.1
140°	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5	1272.3	1273.1	1273.6
142.5°	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5	1306.1	1306.6	1306.9
145°	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1	1354.3	1354.6	1355.0
147.5°	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7	1396.9	1397.2	1397.4
150°	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0	1424.0	1424.0	1424.2
152.5°	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8	1448.2	1448.7	1448.7
155°	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9	1481.0	1482.0	1482.2
157.5°	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3
160°	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4
162.5°	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5	1541.1	1542.7	1542.5
165°	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6	1561.8	1563.9	1563.8
167.5°	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5	1576.8	1579.1	1579.0
170°	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6	1585.7	1587.9	1587.5
172.5°	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3	1591.4	1593.6	1593.2
175°	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0	1598.5	1600.8	1600.4
177.5°	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7	1600.4	1602.1	1601.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1455.0	1454.0	1450.4	1449.9	1450.4	1454.0	1455.0	1456.0	1457.5	1462.5	1456.5
5°	1344.0	1340.8	1338.9	1345.9	1338.9	1340.8	1344.0	1347.8	1354.2	1354.8	1361.1
7.5°	1260.4	1257.9	1252.4	1250.5	1252.4	1257.9	1260.4	1262.7	1269.0	1274.5	1283.8
10°	1206.8	1204.3	1199.2	1197.9	1199.2	1204.3	1206.8	1213.1	1219.4	1226.4	1232.7
12.5°	1155.2	1150.1	1149.1	1150.4	1149.1	1150.1	1155.2	1163.6	1180.0	1179.9	1181.1
15°	1086.6	1084.1	1077.1	1079.0	1077.1	1084.1	1086.6	1094.9	1102.4	1111.9	1121.4
17.5°	1019.1	1016.1	1007.6	1015.0	1007.6	1016.1	1019.1	1023.5	1033.2	1046.6	1061.0
20°	976.5	971.5	967.1	966.5	967.1	971.5	976.5	981.0	991.7	1003.1	1013.9
22.5°	936.0	931.5	931.1	927.0	931.1	931.5	936.0	943.0	953.8	960.1	970.3
25°	885.5	881.1	879.8	876.6	879.8	881.1	885.5	890.6	897.5	902.5	913.9
27.5°	846.7	844.5	842.2	843.2	842.2	844.5	846.7	847.3	850.4	857.1	863.7
30°	822.8	822.2	820.9	820.9	820.9	822.2	822.8	820.9	824.1	827.3	832.3
32.5°	803.1	803.0	803.7	803.7	803.7	803.0	803.1	800.3	801.4	802.5	805.0
35°	775.5	777.3	778.6	776.7	778.6	777.3	775.5	772.9	771.0	766.6	767.9
37.5°	750.4	752.3	754.1	756.2	754.1	752.3	750.4	745.2	740.6	736.7	732.1
40°	731.2	735.6	736.8	740.0	736.8	735.6	731.2	725.5	720.4	716.0	710.9
42.5°	713.0	717.9	721.1	721.8	721.1	717.9	713.0	707.3	699.7	694.2	687.1
45°	685.0	690.1	694.5	694.5	694.5	690.1	685.0	675.5	667.3	659.0	652.1
47.5°	656.0	663.4	667.8	668.9	667.8	663.4	656.0	646.3	634.8	624.6	614.7
50°	636.3	645.2	649.6	652.8	649.6	645.2	636.3	625.5	613.5	600.9	588.8
52.5°	617.0	625.9	631.8	633.5	631.8	625.9	617.0	603.8	589.2	575.6	565.1
55°	583.8	596.4	603.4	605.9	603.4	596.4	583.8	569.3	555.3	538.2	523.1
57.5°	552.4	564.0	572.1	574.0	572.1	564.0	552.4	535.4	517.4	499.2	483.0
60°	528.1	540.7	550.9	552.8	550.9	540.7	528.1	511.0	492.1	474.4	454.2
62.5°	503.4	516.5	525.6	530.5	525.6	516.5	503.4	485.2	464.8	445.0	424.8
65°	460.4	473.7	482.6	484.5	482.6	473.7	460.4	442.8	421.2	400.4	383.3
67.5°	413.7	426.9	432.8	436.4	432.8	426.9	413.7	397.0	375.7	354.1	334.7
70°	380.7	391.5	397.8	401.0	397.8	391.5	380.7	363.1	345.3	323.2	302.3
72.5°	343.3	354.6	361.9	362.5	361.9	354.6	343.3	328.1	309.4	288.8	270.5
75°	285.9	296.0	299.8	299.8	299.8	296.0	285.9	271.3	256.2	239.7	221.3
77.5°	226.3	231.5	236.3	237.3	236.3	231.5	226.3	215.8	203.3	186.9	173.0
80°	187.8	191.0	194.8	194.8	194.8	191.0	187.8	178.4	166.4	152.4	141.6
82.5°	148.4	151.1	154.9	154.3	154.9	151.1	148.4	140.9	130.9	121.6	111.9
85°	89.8	95.5	94.9	93.6	94.9	95.5	89.8	91.1	81.6	75.3	66.4
87.5°	47.3	47.9	49.6	50.7	49.6	47.9	47.3	45.7	41.0	38.1	35.7
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	32.6	32.8	32.9	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5
95°	33.8	34.1	34.4	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5
97.5°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8
100°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6
102.5°	34.2	34.3	34.4	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9
105°	369.2	359.6	350.1	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5
107.5°	471.5	472.5	473.5	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1
110°	530.4	531.2	532.0	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	588.1	589.1	590.1	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8
115°	676.2	676.2	676.2	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9
117.5°	763.0	762.9	762.8	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4
120°	818.7	818.2	817.7	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2
122.5°	872.3	871.7	871.2	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3
125°	950.1	950.4	950.7	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8
127.5°	1022.1	1021.8	1021.6	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6
132.5°	1113.8	1113.6	1113.4	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5
135°	1177.5	1178.1	1178.6	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4
137.5°	1236.0	1235.8	1235.6	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8
140°	1273.9	1274.1	1274.4	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5
142.5°	1307.0	1307.1	1307.1	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5
145°	1355.5	1356.1	1356.6	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1
147.5°	1397.6	1397.9	1398.2	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7
150°	1424.4	1424.7	1425.0	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0
152.5°	1448.6	1448.4	1448.3	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8
155°	1481.4	1480.6	1479.8	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9
157.5°	1508.9	1507.5	1506.2	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5
160°	1526.8	1525.2	1523.6	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2
162.5°	1540.8	1539.0	1537.2	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5
165°	1561.4	1559.0	1556.6	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6
167.5°	1576.3	1573.7	1571.0	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5
170°	1584.9	1582.2	1579.6	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6
172.5°	1590.3	1587.5	1584.6	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3
175°	1597.2	1594.0	1590.9	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0
177.5°	1599.2	1596.6	1594.0	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1459.5	1461.6	1469.7	1477.3	1486.4	1492.9	1497.5	1502.5	1513.1	1521.8	1529.9
5°	1367.5	1370.6	1387.0	1398.4	1418.0	1435.1	1448.4	1462.9	1480.0	1503.4	1525.0
7.5°	1286.3	1298.1	1316.1	1334.5	1354.6	1376.9	1396.4	1418.3	1447.8	1479.9	1513.1
10°	1240.3	1253.6	1272.6	1294.1	1313.0	1338.9	1363.0	1388.9	1422.4	1461.7	1500.9
12.5°	1194.3	1216.2	1230.6	1256.1	1276.6	1298.0	1323.6	1357.6	1396.7	1437.9	1485.2
15°	1136.5	1148.6	1176.4	1190.3	1219.4	1252.4	1277.6	1311.8	1349.7	1404.1	1457.2
17.5°	1070.1	1085.8	1108.0	1134.6	1167.9	1193.7	1225.1	1260.3	1308.1	1362.2	1428.7
20°	1026.5	1039.8	1067.0	1096.1	1131.6	1158.7	1192.2	1226.4	1275.7	1333.3	1402.9
22.5°	987.5	1000.4	1029.0	1056.1	1090.5	1123.8	1158.8	1198.6	1245.9	1306.5	1377.5
25°	927.2	944.3	969.6	997.4	1030.3	1068.3	1106.2	1141.6	1192.2	1256.1	1332.1
27.5°	873.7	887.4	905.7	937.3	974.7	1011.4	1049.0	1093.6	1142.2	1209.7	1288.5
30°	839.3	852.0	870.3	899.4	934.2	973.4	1012.6	1055.6	1106.2	1173.3	1253.6
32.5°	812.0	821.6	837.9	864.0	895.7	937.0	975.7	1020.2	1073.3	1139.4	1217.7
35°	771.7	779.8	786.2	810.9	839.3	877.3	916.5	963.9	1015.2	1077.8	1156.2
37.5°	732.1	734.8	744.1	760.3	787.8	822.8	859.2	905.9	958.4	1022.0	1092.7
40°	707.7	709.0	714.7	729.9	753.9	786.8	822.2	868.4	918.4	978.4	1048.7
42.5°	684.0	683.2	688.4	699.0	721.5	751.4	786.3	828.5	878.4	933.9	1000.1
45°	646.4	646.4	645.2	654.0	672.3	701.4	730.6	771.0	812.8	867.1	922.8
47.5°	607.2	603.6	604.8	609.3	624.8	648.7	678.0	711.1	748.0	794.0	842.9
50°	581.9	576.9	575.0	580.0	593.9	614.8	642.6	671.7	706.5	746.9	788.7
52.5°	554.1	549.0	545.6	549.1	562.1	581.4	606.7	632.2	663.5	696.4	732.5
55°	511.0	505.3	503.4	504.7	514.2	529.4	550.9	574.3	597.7	624.9	650.2
57.5°	468.7	459.3	457.6	456.9	463.5	477.4	495.4	515.6	532.7	549.1	576.1
60°	440.8	429.4	425.6	425.0	430.1	441.5	457.9	478.2	490.2	501.5	525.0
62.5°	411.0	400.1	391.7	392.7	397.2	408.1	422.5	437.2	445.1	457.6	473.3
65°	365.0	351.0	344.7	342.8	345.3	354.2	365.6	375.1	383.9	389.0	404.2
67.5°	318.9	307.3	297.9	295.6	294.5	300.6	309.9	315.6	321.9	326.4	335.3
70°	286.5	276.4	265.0	261.2	260.5	265.6	274.5	275.1	284.0	285.9	295.4
72.5°	254.6	242.0	234.2	230.4	227.7	232.3	238.1	239.7	244.5	248.0	252.9
75°	204.9	195.4	187.8	182.1	180.2	182.8	182.8	185.9	189.1	191.0	196.7
77.5°	161.3	150.4	141.4	138.2	135.9	134.2	135.6	137.5	136.0	139.3	140.5
80°	130.9	119.5	112.6	111.3	107.5	104.3	103.7	105.6	103.1	104.3	108.1
82.5°	101.1	93.7	86.3	85.0	80.2	78.6	78.0	76.8	76.8	76.5	77.3
85°	60.0	55.7	50.6	47.5	45.6	42.4	42.4	41.1	39.8	38.6	39.2
87.5°	29.9	28.5	25.6	23.6	22.2	19.7	19.3	17.1	16.1	15.0	13.9
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	26.9	25.3	23.2	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1
95°	27.9	26.3	26.0	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7
97.5°	31.7	31.5	61.2	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5
100°	48.1	52.6	89.2	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9
102.5°	204.5	253.3	258.0	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0
105°	375.1	372.7	371.4	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6
107.5°	465.9	464.7	462.9	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0
110°	527.4	526.8	525.2	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	586.9	587.1	586.3	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3
115°	674.3	673.8	674.1	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4
117.5°	763.5	763.6	763.0	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2
120°	817.7	817.1	817.4	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6
122.5°	872.0	871.6	871.2	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0
125°	947.0	946.2	946.7	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8
127.5°	1022.9	1023.1	1021.8	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4
130°	1068.3	1068.0	1067.2	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3
132.5°	1113.2	1112.9	1111.9	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2
135°	1174.9	1174.3	1173.3	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8
137.5°	1234.1	1233.6	1232.4	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9
140°	1270.7	1269.9	1269.4	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1
142.5°	1304.9	1304.3	1304.0	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5
145°	1353.8	1353.5	1353.5	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0
147.5°	1396.5	1396.3	1396.5	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8
150°	1424.0	1424.0	1424.3	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5
152.5°	1447.4	1446.9	1447.4	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3
155°	1478.8	1477.7	1478.6	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2
157.5°	1506.2	1504.8	1505.7	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6
160°	1523.6	1521.9	1522.3	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8
162.5°	1537.9	1536.3	1536.6	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1
165°	1557.5	1555.4	1555.4	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4
167.5°	1572.1	1569.8	1569.9	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7
170°	1581.4	1579.3	1579.1	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3
172.5°	1587.1	1585.1	1584.8	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0
175°	1593.6	1591.3	1591.0	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2
177.5°	1597.0	1595.3	1594.9	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1536.9	1542.0	1548.6	1559.7	1563.8	1568.8	1575.9	1575.4	1577.4	1585.0	1601.2
5°	1542.6	1562.3	1581.2	1604.0	1628.0	1643.9	1665.3	1678.6	1691.9	1709.0	1738.0
7.5°	1544.9	1576.0	1610.8	1650.8	1686.3	1727.4	1759.4	1789.5	1816.6	1852.7	1887.4
10°	1541.3	1583.1	1628.0	1678.6	1732.3	1777.9	1819.0	1865.8	1905.7	1949.3	1988.5
12.5°	1534.8	1585.2	1645.2	1701.9	1764.7	1832.1	1883.3	1930.6	1983.6	2033.8	2094.3
15°	1519.9	1588.8	1659.0	1733.6	1817.7	1895.5	1969.6	2030.9	2087.9	2163.1	2242.2
17.5°	1500.9	1575.3	1663.8	1754.1	1842.1	1931.0	2022.6	2114.8	2186.7	2280.1	2342.0
20°	1483.2	1569.2	1660.3	1767.8	1855.7	1966.4	2057.5	2146.7	2245.4	2338.3	2412.3
22.5°	1458.4	1552.5	1649.2	1756.2	1871.9	1982.6	2087.9	2184.6	2283.3	2384.4	2474.1
25°	1426.9	1512.3	1626.7	1748.2	1863.3	1983.5	2104.3	2225.7	2331.9	2438.9	2522.4
27.5°	1373.2	1481.1	1587.7	1713.0	1841.0	1976.9	2106.1	2233.2	2344.5	2432.4	2484.1
30°	1345.9	1439.6	1555.3	1681.2	1819.6	1965.8	2100.5	2225.1	2328.9	2399.0	2419.9
32.5°	1305.4	1402.1	1515.3	1645.8	1792.3	1942.5	2082.8	2200.3	2286.8	2323.6	2298.4
35°	1245.4	1332.7	1447.2	1580.6	1733.0	1893.0	2031.6	2130.8	2175.1	2140.3	2053.7
37.5°	1173.3	1259.8	1374.8	1505.9	1663.6	1826.2	1951.5	2022.9	2008.3	1921.8	1792.6
40°	1122.7	1203.6	1313.0	1454.7	1608.4	1771.6	1881.7	1920.2	1879.8	1755.8	1618.5
42.5°	1066.5	1145.4	1255.4	1391.9	1554.8	1705.3	1801.2	1804.4	1736.5	1588.3	1450.6
45°	981.0	1056.2	1160.0	1302.3	1452.9	1594.5	1657.7	1626.7	1501.5	1358.6	1220.0
47.5°	896.6	961.9	1064.1	1199.2	1342.1	1461.4	1492.8	1437.0	1303.5	1164.8	1036.4
50°	834.9	900.6	996.8	1125.8	1263.7	1366.8	1382.0	1308.0	1177.0	1037.3	936.7
52.5°	775.7	841.0	933.6	1053.0	1179.2	1272.2	1272.7	1187.1	1056.6	932.0	838.5
55°	688.8	747.6	831.1	937.9	1050.6	1123.3	1105.6	1017.0	903.8	795.7	714.1
57.5°	605.1	656.2	733.2	822.4	921.5	981.5	952.1	866.9	765.8	674.1	612.3
60°	550.9	599.6	665.4	749.5	833.0	879.8	852.0	774.8	681.8	607.8	554.1
62.5°	498.3	539.4	602.6	675.7	753.0	787.7	762.9	686.7	606.4	539.5	495.9
65°	423.7	457.3	507.9	570.5	626.8	656.6	635.6	564.8	503.4	455.4	420.6
67.5°	354.2	380.4	418.7	468.9	516.7	532.8	513.8	464.5	412.5	374.1	349.5
70°	306.1	330.8	363.1	401.6	443.4	460.4	441.5	402.3	359.9	324.5	300.4
72.5°	264.1	283.2	310.5	343.4	376.0	393.2	380.2	342.5	306.7	280.4	259.9
75°	201.1	217.6	236.5	259.9	285.3	296.7	285.3	259.3	234.6	215.1	200.5
77.5°	146.2	155.1	169.8	187.2	203.0	211.8	201.9	184.3	169.3	155.8	148.6
80°	111.3	117.6	127.8	141.6	152.4	160.7	154.3	139.7	127.8	118.9	115.7
82.5°	81.0	85.2	91.8	102.2	109.4	113.6	110.8	100.3	95.4	87.5	84.4
85°	39.8	42.4	46.8	50.0	56.3	57.0	57.6	53.2	48.7	46.8	44.3
87.5°	15.0	16.1	18.1	20.3	22.8	23.7	23.6	24.1	22.5	22.3	20.6
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5
95°	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5
97.5°	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8
100°	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6
102.5°	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9
105°	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5
107.5°	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1
110°	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8
115°	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9
117.5°	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4
120°	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2
122.5°	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3
125°	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8
127.5°	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8
130°	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6
132.5°	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5
135°	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4
137.5°	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8
140°	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5
142.5°	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5
145°	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1
147.5°	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7
150°	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0
152.5°	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8
155°	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9
157.5°	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5
160°	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2
162.5°	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5
165°	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6
167.5°	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5
170°	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6
172.5°	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3
175°	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0
177.5°	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9	1526.9
2.5°	1609.3	1610.3	1614.9	1618.4	1619.5	1624.4	1625.0
5°	1750.7	1761.5	1782.3	1784.2	1787.4	1803.9	1791.2
7.5°	1916.4	1943.8	1962.0	1978.1	1983.9	1991.1	1989.6
10°	2022.7	2063.2	2083.4	2115.7	2116.9	2125.2	2120.1
12.5°	2129.5	2176.5	2213.4	2219.4	2246.5	2250.7	2257.7
15°	2280.8	2330.7	2381.9	2400.3	2437.6	2446.5	2460.4
17.5°	2423.0	2474.1	2510.0	2557.4	2572.7	2593.2	2579.3
20°	2500.8	2556.5	2602.1	2639.4	2655.2	2666.6	2665.3
22.5°	2547.9	2604.1	2641.0	2669.3	2684.0	2688.8	2688.6
25°	2577.4	2609.6	2621.0	2631.8	2615.3	2609.6	2612.1
27.5°	2495.5	2487.1	2457.3	2418.4	2377.9	2345.7	2328.3
30°	2382.6	2333.2	2288.4	2209.9	2169.5	2145.4	2123.9
32.5°	2222.7	2144.5	2058.1	1986.2	1940.2	1904.6	1899.3
35°	1948.7	1831.1	1725.5	1637.5	1592.0	1553.4	1544.5
37.5°	1656.8	1534.5	1439.4	1362.0	1313.0	1285.9	1260.4
40°	1462.9	1358.0	1264.3	1198.6	1161.3	1141.6	1125.8
42.5°	1313.7	1217.8	1124.7	1074.6	1040.8	1028.8	1019.5
45°	1107.5	1018.3	953.8	915.8	896.2	876.0	866.5
47.5°	942.4	869.8	827.3	795.0	774.0	762.0	756.0
50°	848.8	789.3	751.4	726.7	707.7	698.2	693.2
52.5°	765.8	717.0	685.1	665.5	652.6	645.6	643.6
55°	659.7	622.3	602.1	585.0	575.6	569.3	566.7
57.5°	573.4	544.7	528.2	514.2	510.6	505.3	503.4
60°	516.7	494.6	480.7	471.2	468.0	461.7	463.0
62.5°	466.7	448.5	436.7	431.3	427.1	421.8	423.5
65°	394.7	381.4	375.1	370.0	365.0	361.8	364.3
67.5°	331.1	322.1	313.5	310.5	308.0	307.5	304.8
70°	289.7	282.1	274.5	272.6	272.6	270.1	269.4
72.5°	249.7	244.2	239.1	237.7	235.7	236.7	234.0
75°	192.9	188.5	186.6	184.7	184.0	184.0	182.1
77.5°	142.6	139.3	136.3	136.3	134.0	133.1	132.8
80°	108.1	106.9	104.3	104.3	103.1	103.7	102.4
82.5°	81.4	79.5	79.1	78.0	76.3	76.4	75.2
85°	43.6	41.7	41.1	39.2	37.9	39.2	37.9
87.5°	21.4	21.2	20.9	20.0	19.6	19.7	18.3
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P332859-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)