

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332864-927

Luminaire Tested: **S124DIW-S1195D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332864-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1560U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8340.7 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	97	93	89	86	90	86	83	79	72	70	68	60	58	57	48	47	46	41				
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34				
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29				
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17				
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.7	1.8
10°-20°	418.9	5.0
20°-30°	616.5	7.4
30°-40°	716.7	8.6
40°-50°	716.8	8.6
50°-60°	627.0	7.5
60°-70°	465.6	5.6
70°-80°	264.5	3.2
80°-90°	81.0	1.0
90°-100°	101.9	1.2
100°-110°	301.8	3.6
110°-120°	512.2	6.1
120°-130°	675.4	8.1
130°-140°	758.5	9.1
140°-150°	745.3	8.9
150°-160°	626.9	7.5
160°-170°	417.1	5.0
170°-180°	146.1	1.8
0°-30°	1184.1	14.2
0°-40°	1900.8	22.8
0°-60°	3244.6	38.9
0°-90°	4055.7	48.6
90°-120°	915.8	11.0
90°-150°	3095.0	37.1
90°-180°	4285.0	51.4
0°-180°	8340.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	4	17	26	33	36	8
95°	72	82	91	94	94	80
105°	278	280	284	288	291	295
115°	521	521	518	517	516	513
125°	758	758	757	755	752	676
135°	978	985	986	983	980	757
145°	1188	1193	1194	1193	1190	743
155°	1362	1362	1360	1365	1360	626
165°	1482	1479	1476	1483	1479	418
175°	1542	1536	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	27.0	27.4	27.7	28.1	28.4	28.8	28.9	29.2	29.3	29.5	29.9
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	25.6	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2
95°	71.7	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6
97.5°	125.2	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5
100°	167.2	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3
102.5°	211.2	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6
105°	278.3	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1
107.5°	348.8	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6
110°	396.6	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2



TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5
115°	520.8	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2
117.5°	591.0	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4
120°	637.9	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7
122.5°	686.6	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0
125°	758.5	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8
127.5°	823.7	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8
130°	869.6	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7
132.5°	916.4	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6
135°	978.3	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9
137.5°	1045.7	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2
140°	1090.6	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7
142.5°	1131.6	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1
145°	1188.5	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1244.9	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4
150°	1279.3	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1311.8	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2
155°	1361.7	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6
157.5°	1403.7	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2
160°	1428.6	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0
162.5°	1451.5	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7
165°	1482.3	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0
167.5°	1506.0	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8
170°	1519.4	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2
172.5°	1528.9	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0
175°	1542.1	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8
177.5°	1546.3	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	30.2	30.5	30.8	31.1	31.1	31.2	31.4	31.4
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	49.2	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	92.4	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	145.5	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	183.8	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	224.3	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	285.9	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	352.4	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.7	396.2	395.6	395.8	396.6	397.4	398.2	398.9





TEST NUMBER: P332864-927

CATALOG NUMBER: S124DIW-S1195D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	444.3	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.8	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	588.5	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	636.4	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	685.0	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	756.2	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	824.3	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	872.1	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	917.0	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	984.4	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1049.6	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.4	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1133.0	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1194.0	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.3	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1316.8	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.0	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1427.8	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1450.1	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1479.6	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1504.4	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1517.8	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1527.8	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1544.6	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)