

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332846-927

Luminaire Tested: **S124DIW-S1195D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332846-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D770U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6162.6 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	86	80	74	69	71	66	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	2.4
10°-20°	418.9	6.8
20°-30°	616.5	10.0
30°-40°	716.7	11.6
40°-50°	716.8	11.6
50°-60°	627.0	10.2
60°-70°	465.6	7.6
70°-80°	264.5	4.3
80°-90°	78.6	1.3
90°-100°	50.1	0.8
100°-110°	148.5	2.4
110°-120°	252.1	4.1
120°-130°	332.4	5.4
130°-140°	373.3	6.1
140°-150°	366.9	6.0
150°-160°	308.6	5.0
160°-170°	205.3	3.3
170°-180°	71.9	1.2
0°-30°	1184.1	19.2
0°-40°	1900.8	30.8
0°-60°	3244.6	52.7
0°-90°	4053.4	65.8
90°-120°	450.8	7.3
90°-150°	1523.4	24.7
90°-180°	2109.0	34.2
0°-180°	6162.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	2	8	13	16	18	6
95°	35	40	45	46	46	39
105°	137	138	140	142	144	145
115°	256	256	255	255	254	253
125°	373	373	373	372	370	333
135°	482	485	485	484	482	372
145°	585	587	588	587	586	366
155°	670	670	670	672	670	308
165°	730	728	727	730	728	206
175°	759	756	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.7	26.7	26.8	26.9	26.9	26.9	26.9	26.9	26.9	26.9	27.0
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	12.6	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8
95°	35.3	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1
97.5°	61.6	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1
100°	82.3	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2
102.5°	103.9	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1
105°	137.0	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3
107.5°	171.7	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1
110°	195.2	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.7	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8
115°	256.4	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0
117.5°	290.9	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1
120°	313.9	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9
122.5°	337.9	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6
125°	373.4	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5
127.5°	405.4	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0
130°	428.0	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5
132.5°	451.1	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6
135°	481.6	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8
137.5°	514.7	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9
140°	536.8	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8
142.5°	557.0	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7
145°	585.0	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	612.8	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0
150°	629.7	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	645.7	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8
155°	670.3	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2
157.5°	690.9	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1
160°	703.2	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4
162.5°	714.5	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0
165°	729.7	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5
167.5°	741.2	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7
170°	747.9	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3
172.5°	752.6	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1
175°	759.1	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5
177.5°	761.1	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	27.2	27.3	27.5	27.6	27.6	27.7	27.7	27.8
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.2	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.5	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	71.6	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.5	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.4	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	140.7	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.5	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.3	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P332846-927

CATALOG NUMBER: S124DIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	218.7	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.9	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.7	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	313.2	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	337.2	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.2	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.8	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.3	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.4	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.5	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.6	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.7	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.7	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.7	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.9	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.5	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	702.8	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	713.8	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	728.3	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.1	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.0	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	760.3	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)