

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332728-927

Luminaire Tested: **S124DIW-S350D1050U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332728-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1050U927-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4130.7 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	93	89	86	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26				
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27	22				
3	78	69	62	56	70	62	56	51	49	45	42	37	35	32	27	25	23	19				
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	16	12				
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1037	1074	2566	1074



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	1.1
10°-20°	135.9	3.3
20°-30°	215.5	5.2
30°-40°	239.8	5.8
40°-50°	218.3	5.3
50°-60°	178.4	4.3
60°-70°	127.4	3.1
70°-80°	70.1	1.7
80°-90°	22.2	0.5
90°-100°	68.4	1.7
100°-110°	202.7	4.9
110°-120°	344.1	8.3
120°-130°	453.7	11.0
130°-140°	509.6	12.3
140°-150°	500.8	12.1
150°-160°	421.2	10.2
160°-170°	280.2	6.8
170°-180°	98.1	2.4
0°-30°	395.5	9.6
0°-40°	635.3	15.4
0°-60°	1032.1	25.0
0°-90°	1251.8	30.3
90°-120°	615.3	14.9
90°-150°	2079.4	50.3
90°-180°	2879.0	69.7
0°-180°	4130.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	14
90°	24	2	24	2	24	13
95°	63	48	63	48	63	66
105°	196	187	196	187	196	206
115°	347	350	347	350	347	343
125°	506	510	506	510	506	451
135°	658	657	658	657	658	508
145°	799	798	799	798	799	500
155°	914	915	914	915	914	421
165°	994	996	994	996	994	280
175°	1031	1036	1031	1036	1031	98
180°	1038	1038	1038	1038	1038	



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	8.1	8.5	8.4	8.5	8.7	8.7	8.6	8.3	8.7	8.6	9.0
90°	24.1	23.7	23.4	23.0	22.7	21.9	20.8	19.8	18.7	17.7	16.2
92.5°	35.6	35.4	35.2	35.0	34.8	34.4	33.7	33.0	32.4	31.8	30.8
95°	63.4	63.4	63.4	63.4	63.4	63.1	62.6	62.0	61.6	61.0	59.7
97.5°	99.3	99.3	99.3	99.3	99.3	99.0	98.4	97.8	97.1	96.5	95.0
100°	124.4	124.4	124.4	124.4	124.4	124.2	123.8	123.5	123.1	122.8	121.2
102.5°	152.7	152.5	152.3	152.2	152.1	151.8	151.2	150.8	150.3	149.7	148.3
105°	195.8	195.3	194.7	194.2	193.7	193.1	192.6	192.1	191.5	191.0	190.3
107.5°	237.9	237.9	238.0	238.0	238.0	237.8	237.3	236.8	236.3	235.8	235.7
110°	268.1	267.5	267.0	266.4	265.9	265.8	266.2	266.5	266.9	267.2	267.4



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	298.7	298.7	298.6	298.4	298.4	298.5	298.6	298.7	298.7	299.0
115°	346.7	346.9	347.1	347.2	347.4	347.6	347.8	347.9	348.1	348.3	348.6
117.5°	392.3	392.6	393.0	393.3	393.7	394.2	394.7	395.4	396.0	396.6	396.9
120°	426.9	426.6	426.2	425.9	425.5	425.8	426.7	427.5	428.5	429.4	429.9
122.5°	455.8	456.5	457.1	457.7	458.4	459.0	459.6	460.3	460.8	461.4	461.7
125°	505.6	506.0	506.3	506.7	507.0	507.4	507.7	508.1	508.4	508.8	509.0
127.5°	551.7	551.9	552.2	552.5	552.8	553.1	553.5	553.8	554.2	554.5	554.8
130°	581.9	582.6	583.3	584.0	584.7	585.2	585.6	585.9	586.3	586.6	586.6
132.5°	613.9	614.2	614.5	614.8	615.1	615.4	615.8	616.1	616.5	616.8	617.0
135°	658.1	658.6	659.1	659.7	660.2	660.7	661.0	661.4	661.7	662.1	662.1
137.5°	704.4	704.3	704.3	704.1	704.0	704.2	704.6	705.1	705.6	706.1	705.8
140°	732.7	732.8	733.1	733.2	733.4	733.6	733.8	734.0	734.1	734.3	734.3
142.5°	761.0	761.0	761.0	761.0	761.0	761.1	761.1	761.2	761.2	761.3	761.4
145°	799.3	799.9	800.3	800.9	801.5	801.8	802.0	802.2	802.3	802.5	802.3
147.5°	838.1	838.3	838.5	838.7	838.8	839.0	839.2	839.3	839.5	839.6	839.7
150°	861.9	862.1	862.3	862.4	862.6	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	883.8	884.2	884.6	885.1	885.6	885.6	885.2	884.7	884.3	883.9	883.8
155°	914.1	914.8	915.5	916.2	917.0	917.0	916.2	915.5	914.8	914.1	914.3
157.5°	941.2	941.8	942.4	943.0	943.6	943.6	943.1	942.6	942.1	941.5	941.5
160°	956.6	957.5	958.4	959.3	960.1	960.4	959.8	959.3	958.7	958.2	958.4
162.5°	972.6	973.5	974.5	975.3	976.2	976.2	975.2	974.2	973.3	972.3	972.5
165°	993.5	994.2	994.9	995.6	996.3	996.2	995.1	994.0	993.0	991.9	992.3
167.5°	1008.4	1009.6	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.6	1008.5
170°	1016.8	1018.0	1019.3	1020.6	1021.8	1021.8	1020.8	1019.7	1018.7	1017.6	1017.4
172.5°	1023.8	1025.1	1026.4	1027.6	1028.8	1028.9	1027.6	1026.4	1025.2	1024.0	1024.0
175°	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3	1031.4
177.5°	1035.1	1036.3	1037.4	1038.5	1039.7	1039.7	1038.7	1037.8	1036.7	1035.7	1035.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	8.6	8.6	8.1	7.1	6.3	5.5	4.9	4.4	4.9	5.5	6.0
90°	14.8	13.4	12.0	10.2	8.3	6.3	4.4	2.4	4.4	6.3	8.3
92.5°	29.8	28.8	27.8	26.1	23.9	21.7	19.4	17.2	19.4	21.7	23.9
95°	58.5	57.3	56.0	54.6	53.0	51.3	49.7	48.2	49.7	51.3	53.0
97.5°	93.6	92.1	90.6	89.3	87.9	86.7	85.4	84.1	85.4	86.7	87.9
100°	119.5	118.0	116.4	115.2	114.5	113.8	113.0	112.3	113.0	113.8	114.5
102.5°	146.8	145.4	143.9	143.0	142.8	142.4	142.2	141.9	142.2	142.4	142.8
105°	189.6	188.9	188.1	187.7	187.5	187.4	187.2	187.0	187.2	187.4	187.5
107.5°	235.6	235.4	235.4	235.2	235.0	234.7	234.6	234.3	234.6	234.7	235.0
110°	267.6	267.8	267.9	267.8	267.5	267.1	266.8	266.4	266.8	267.1	267.5





TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	299.4	299.7	300.0	300.1	300.0	300.0	299.9	299.8	299.9	300.0	300.0
115°	349.0	349.4	349.7	349.9	349.9	349.9	349.9	349.9	349.9	349.9	349.9
117.5°	397.1	397.4	397.6	397.7	397.5	397.4	397.2	397.1	397.2	397.4	397.5
120°	430.4	430.9	431.5	431.4	430.7	430.0	429.3	428.6	429.3	430.0	430.7
122.5°	461.9	462.2	462.5	462.4	462.2	461.8	461.6	461.3	461.6	461.8	462.2
125°	509.1	509.3	509.5	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
127.5°	555.1	555.4	555.7	555.6	555.0	554.4	554.0	553.4	554.0	554.4	555.0
130°	586.6	586.6	586.6	586.4	585.8	585.3	584.8	584.2	584.8	585.3	585.8
132.5°	617.1	617.3	617.3	617.3	616.9	616.5	616.1	615.7	616.1	616.5	616.9
135°	662.1	662.1	662.1	661.6	660.4	659.4	658.3	657.3	658.3	659.4	660.4
137.5°	705.5	705.2	704.9	704.5	704.0	703.5	703.0	702.5	703.0	703.5	704.0
140°	734.3	734.3	734.3	734.1	733.8	733.4	733.1	732.7	733.1	733.4	733.8
142.5°	761.5	761.7	761.8	761.8	761.4	761.0	760.7	760.3	760.7	761.0	761.4
145°	802.2	802.0	801.8	801.4	800.7	799.9	799.2	798.5	799.2	799.9	800.7
147.5°	839.9	840.0	840.2	839.8	838.9	838.1	837.3	836.4	837.3	838.1	838.9
150°	862.7	862.7	862.7	862.4	861.7	860.9	860.2	859.5	860.2	860.9	861.7
152.5°	883.6	883.4	883.3	883.0	882.6	882.2	881.8	881.3	881.8	882.2	882.6
155°	914.4	914.6	914.8	914.9	914.9	914.9	914.9	914.9	914.9	914.9	914.9
157.5°	941.6	941.6	941.7	941.8	942.1	942.5	942.8	943.1	942.8	942.5	942.1
160°	958.5	958.7	958.9	959.1	959.3	959.4	959.6	959.8	959.6	959.4	959.3
162.5°	972.7	972.9	973.0	973.4	973.8	974.3	974.8	975.2	974.8	974.3	973.8
165°	992.6	993.0	993.3	993.8	994.3	994.8	995.4	995.9	995.4	994.8	994.3
167.5°	1008.5	1008.5	1008.4	1008.8	1009.6	1010.3	1011.1	1011.8	1011.1	1010.3	1009.6
170°	1017.2	1017.1	1016.8	1017.2	1018.1	1019.0	1019.9	1020.8	1019.9	1019.0	1018.1
172.5°	1024.0	1023.9	1023.9	1024.2	1025.0	1025.7	1026.4	1027.2	1026.4	1025.7	1025.0
175°	1031.6	1031.7	1032.0	1032.5	1033.4	1034.3	1035.1	1036.0	1035.1	1034.3	1033.4
177.5°	1035.7	1035.7	1035.7	1036.1	1036.8	1037.5	1038.2	1038.9	1038.2	1037.5	1036.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	6.8	7.2	8.1	8.6	9.4	10.5	10.9	12.8	13.6	14.6	16.1
90°	10.2	12.0	13.4	14.8	16.2	17.7	18.7	19.8	20.8	21.9	22.7
92.5°	26.1	27.8	28.8	29.8	30.8	31.8	32.4	33.0	33.7	34.4	34.8
95°	54.6	56.0	57.3	58.5	59.7	61.0	61.6	62.0	62.6	63.1	63.4
97.5°	89.3	90.6	92.1	93.6	95.0	96.5	97.1	97.8	98.4	99.0	99.3
100°	115.2	116.4	118.0	119.5	121.2	122.8	123.1	123.5	123.8	124.2	124.4
102.5°	143.0	143.9	145.4	146.8	148.3	149.7	150.3	150.8	151.2	151.8	152.1
105°	187.7	188.1	188.9	189.6	190.3	191.0	191.5	192.1	192.6	193.1	193.7
107.5°	235.2	235.4	235.4	235.6	235.7	235.8	236.3	236.8	237.3	237.8	238.0
110°	267.8	267.9	267.8	267.6	267.4	267.2	266.9	266.5	266.2	265.8	265.9



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	300.1	300.0	299.7	299.4	299.0	298.7	298.7	298.6	298.5	298.4	298.4
115°	349.9	349.7	349.4	349.0	348.6	348.3	348.1	347.9	347.8	347.6	347.4
117.5°	397.7	397.6	397.4	397.1	396.9	396.6	396.0	395.4	394.7	394.2	393.7
120°	431.4	431.5	430.9	430.4	429.9	429.4	428.5	427.5	426.7	425.8	425.5
122.5°	462.4	462.5	462.2	461.9	461.7	461.4	460.8	460.3	459.6	459.0	458.4
125°	509.6	509.5	509.3	509.1	509.0	508.8	508.4	508.1	507.7	507.4	507.0
127.5°	555.6	555.7	555.4	555.1	554.8	554.5	554.2	553.8	553.5	553.1	552.8
130°	586.4	586.6	586.6	586.6	586.6	586.6	586.3	585.9	585.6	585.2	584.7
132.5°	617.3	617.3	617.3	617.1	617.0	616.8	616.5	616.1	615.8	615.4	615.1
135°	661.6	662.1	662.1	662.1	662.1	662.1	661.7	661.4	661.0	660.7	660.2
137.5°	704.5	704.9	705.2	705.5	705.8	706.1	705.6	705.1	704.6	704.2	704.0
140°	734.1	734.3	734.3	734.3	734.3	734.3	734.1	734.0	733.8	733.6	733.4
142.5°	761.8	761.8	761.7	761.5	761.4	761.3	761.2	761.2	761.1	761.1	761.0
145°	801.4	801.8	802.0	802.2	802.3	802.5	802.3	802.2	802.0	801.8	801.5
147.5°	839.8	840.2	840.0	839.9	839.7	839.6	839.5	839.3	839.2	839.0	838.8
150°	862.4	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.6
152.5°	883.0	883.3	883.4	883.6	883.8	883.9	884.3	884.7	885.2	885.6	885.6
155°	914.9	914.8	914.6	914.4	914.3	914.1	914.8	915.5	916.2	917.0	917.0
157.5°	941.8	941.7	941.6	941.6	941.5	941.5	942.1	942.6	943.1	943.6	943.6
160°	959.1	958.9	958.7	958.5	958.4	958.2	958.7	959.3	959.8	960.4	960.1
162.5°	973.4	973.0	972.9	972.7	972.5	972.3	973.3	974.2	975.2	976.2	976.2
165°	993.8	993.3	993.0	992.6	992.3	991.9	993.0	994.0	995.1	996.2	996.3
167.5°	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6	1010.7	1011.8	1012.9	1012.9
170°	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7	1019.7	1020.8	1021.8	1021.8
172.5°	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2	1026.4	1027.6	1028.9	1028.8
175°	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3
177.5°	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7	1037.8	1038.7	1039.7	1039.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	16.6	16.8	17.3	17.7	17.3	16.8	16.6	16.1	14.6	13.6	12.8
90°	23.0	23.4	23.7	24.1	23.7	23.4	23.0	22.7	21.9	20.8	19.8
92.5°	35.0	35.2	35.4	35.6	35.4	35.2	35.0	34.8	34.4	33.7	33.0
95°	63.4	63.4	63.4	63.4	63.4	63.4	63.4	63.4	63.1	62.6	62.0
97.5°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.0	98.4	97.8
100°	124.4	124.4	124.4	124.4	124.4	124.4	124.4	124.4	124.2	123.8	123.5
102.5°	152.2	152.3	152.5	152.7	152.5	152.3	152.2	152.1	151.8	151.2	150.8
105°	194.2	194.7	195.3	195.8	195.3	194.7	194.2	193.7	193.1	192.6	192.1
107.5°	238.0	238.0	237.9	237.9	237.9	238.0	238.0	238.0	237.8	237.3	236.8
110°	266.4	267.0	267.5	268.1	267.5	267.0	266.4	265.9	265.8	266.2	266.5



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	298.6	298.7	298.7	298.9	298.7	298.7	298.6	298.4	298.4	298.5	298.6
115°	347.2	347.1	346.9	346.7	346.9	347.1	347.2	347.4	347.6	347.8	347.9
117.5°	393.3	393.0	392.6	392.3	392.6	393.0	393.3	393.7	394.2	394.7	395.4
120°	425.9	426.2	426.6	426.9	426.6	426.2	425.9	425.5	425.8	426.7	427.5
122.5°	457.7	457.1	456.5	455.8	456.5	457.1	457.7	458.4	459.0	459.6	460.3
125°	506.7	506.3	506.0	505.6	506.0	506.3	506.7	507.0	507.4	507.7	508.1
127.5°	552.5	552.2	551.9	551.7	551.9	552.2	552.5	552.8	553.1	553.5	553.8
130°	584.0	583.3	582.6	581.9	582.6	583.3	584.0	584.7	585.2	585.6	585.9
132.5°	614.8	614.5	614.2	613.9	614.2	614.5	614.8	615.1	615.4	615.8	616.1
135°	659.7	659.1	658.6	658.1	658.6	659.1	659.7	660.2	660.7	661.0	661.4
137.5°	704.1	704.3	704.3	704.4	704.3	704.3	704.1	704.0	704.2	704.6	705.1
140°	733.2	733.1	732.8	732.7	732.8	733.1	733.2	733.4	733.6	733.8	734.0
142.5°	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.1	761.1	761.2
145°	800.9	800.3	799.9	799.3	799.9	800.3	800.9	801.5	801.8	802.0	802.2
147.5°	838.7	838.5	838.3	838.1	838.3	838.5	838.7	838.8	839.0	839.2	839.3
150°	862.4	862.3	862.1	861.9	862.1	862.3	862.4	862.6	862.7	862.7	862.7
152.5°	885.1	884.6	884.2	883.8	884.2	884.6	885.1	885.6	885.6	885.2	884.7
155°	916.2	915.5	914.8	914.1	914.8	915.5	916.2	917.0	917.0	916.2	915.5
157.5°	943.0	942.4	941.8	941.2	941.8	942.4	943.0	943.6	943.6	943.1	942.6
160°	959.3	958.4	957.5	956.6	957.5	958.4	959.3	960.1	960.4	959.8	959.3
162.5°	975.3	974.5	973.5	972.6	973.5	974.5	975.3	976.2	976.2	975.2	974.2
165°	995.6	994.9	994.2	993.5	994.2	994.9	995.6	996.3	996.2	995.1	994.0
167.5°	1011.8	1010.7	1009.6	1008.4	1009.6	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7
170°	1020.6	1019.3	1018.0	1016.8	1018.0	1019.3	1020.6	1021.8	1021.8	1020.8	1019.7
172.5°	1027.6	1026.4	1025.1	1023.8	1025.1	1026.4	1027.6	1028.8	1028.9	1027.6	1026.4
175°	1035.0	1033.7	1032.5	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7
177.5°	1038.5	1037.4	1036.3	1035.1	1036.3	1037.4	1038.5	1039.7	1039.7	1038.7	1037.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	10.9	10.5	9.4	8.6	8.1	7.2	6.8	6.0	5.5	4.9	4.4
90°	18.7	17.7	16.2	14.8	13.4	12.0	10.2	8.3	6.3	4.4	2.4
92.5°	32.4	31.8	30.8	29.8	28.8	27.8	26.1	23.9	21.7	19.4	17.2
95°	61.6	61.0	59.7	58.5	57.3	56.0	54.6	53.0	51.3	49.7	48.2
97.5°	97.1	96.5	95.0	93.6	92.1	90.6	89.3	87.9	86.7	85.4	84.1
100°	123.1	122.8	121.2	119.5	118.0	116.4	115.2	114.5	113.8	113.0	112.3
102.5°	150.3	149.7	148.3	146.8	145.4	143.9	143.0	142.8	142.4	142.2	141.9
105°	191.5	191.0	190.3	189.6	188.9	188.1	187.7	187.5	187.4	187.2	187.0
107.5°	236.3	235.8	235.7	235.6	235.4	235.4	235.2	235.0	234.7	234.6	234.3
110°	266.9	267.2	267.4	267.6	267.8	267.9	267.8	267.5	267.1	266.8	266.4



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	298.7	298.7	299.0	299.4	299.7	300.0	300.1	300.0	300.0	299.9	299.8
115°	348.1	348.3	348.6	349.0	349.4	349.7	349.9	349.9	349.9	349.9	349.9
117.5°	396.0	396.6	396.9	397.1	397.4	397.6	397.7	397.5	397.4	397.2	397.1
120°	428.5	429.4	429.9	430.4	430.9	431.5	431.4	430.7	430.0	429.3	428.6
122.5°	460.8	461.4	461.7	461.9	462.2	462.5	462.4	462.2	461.8	461.6	461.3
125°	508.4	508.8	509.0	509.1	509.3	509.5	509.6	509.6	509.6	509.6	509.6
127.5°	554.2	554.5	554.8	555.1	555.4	555.7	555.6	555.0	554.4	554.0	553.4
130°	586.3	586.6	586.6	586.6	586.6	586.6	586.4	585.8	585.3	584.8	584.2
132.5°	616.5	616.8	617.0	617.1	617.3	617.3	617.3	616.9	616.5	616.1	615.7
135°	661.7	662.1	662.1	662.1	662.1	662.1	661.6	660.4	659.4	658.3	657.3
137.5°	705.6	706.1	705.8	705.5	705.2	704.9	704.5	704.0	703.5	703.0	702.5
140°	734.1	734.3	734.3	734.3	734.3	734.3	734.1	733.8	733.4	733.1	732.7
142.5°	761.2	761.3	761.4	761.5	761.7	761.8	761.8	761.4	761.0	760.7	760.3
145°	802.3	802.5	802.3	802.2	802.0	801.8	801.4	800.7	799.9	799.2	798.5
147.5°	839.5	839.6	839.7	839.9	840.0	840.2	839.8	838.9	838.1	837.3	836.4
150°	862.7	862.7	862.7	862.7	862.7	862.7	862.4	861.7	860.9	860.2	859.5
152.5°	884.3	883.9	883.8	883.6	883.4	883.3	883.0	882.6	882.2	881.8	881.3
155°	914.8	914.1	914.3	914.4	914.6	914.8	914.9	914.9	914.9	914.9	914.9
157.5°	942.1	941.5	941.5	941.6	941.6	941.7	941.8	942.1	942.5	942.8	943.1
160°	958.7	958.2	958.4	958.5	958.7	958.9	959.1	959.3	959.4	959.6	959.8
162.5°	973.3	972.3	972.5	972.7	972.9	973.0	973.4	973.8	974.3	974.8	975.2
165°	993.0	991.9	992.3	992.6	993.0	993.3	993.8	994.3	994.8	995.4	995.9
167.5°	1009.6	1008.6	1008.5	1008.5	1008.5	1008.4	1008.8	1009.6	1010.3	1011.1	1011.8
170°	1018.7	1017.6	1017.4	1017.2	1017.1	1016.8	1017.2	1018.1	1019.0	1019.9	1020.8
172.5°	1025.2	1024.0	1024.0	1024.0	1023.9	1023.9	1024.2	1025.0	1025.7	1026.4	1027.2
175°	1032.5	1031.3	1031.4	1031.6	1031.7	1032.0	1032.5	1033.4	1034.3	1035.1	1036.0
177.5°	1036.7	1035.7	1035.7	1035.7	1035.7	1035.7	1036.1	1036.8	1037.5	1038.2	1038.9
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	4.9	5.5	6.3	7.1	8.1	8.6	8.6	9.0	8.6	8.7	8.3
90°	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7	19.8
92.5°	19.4	21.7	23.9	26.1	27.8	28.8	29.8	30.8	31.8	32.4	33.0
95°	49.7	51.3	53.0	54.6	56.0	57.3	58.5	59.7	61.0	61.6	62.0
97.5°	85.4	86.7	87.9	89.3	90.6	92.1	93.6	95.0	96.5	97.1	97.8
100°	113.0	113.8	114.5	115.2	116.4	118.0	119.5	121.2	122.8	123.1	123.5
102.5°	142.2	142.4	142.8	143.0	143.9	145.4	146.8	148.3	149.7	150.3	150.8
105°	187.2	187.4	187.5	187.7	188.1	188.9	189.6	190.3	191.0	191.5	192.1
107.5°	234.6	234.7	235.0	235.2	235.4	235.4	235.6	235.7	235.8	236.3	236.8
110°	266.8	267.1	267.5	267.8	267.9	267.8	267.6	267.4	267.2	266.9	266.5





TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	299.9	300.0	300.0	300.1	300.0	299.7	299.4	299.0	298.7	298.7	298.6
115°	349.9	349.9	349.9	349.9	349.7	349.4	349.0	348.6	348.3	348.1	347.9
117.5°	397.2	397.4	397.5	397.7	397.6	397.4	397.1	396.9	396.6	396.0	395.4
120°	429.3	430.0	430.7	431.4	431.5	430.9	430.4	429.9	429.4	428.5	427.5
122.5°	461.6	461.8	462.2	462.4	462.5	462.2	461.9	461.7	461.4	460.8	460.3
125°	509.6	509.6	509.6	509.6	509.5	509.3	509.1	509.0	508.8	508.4	508.1
127.5°	554.0	554.4	555.0	555.6	555.7	555.4	555.1	554.8	554.5	554.2	553.8
130°	584.8	585.3	585.8	586.4	586.6	586.6	586.6	586.6	586.6	586.3	585.9
132.5°	616.1	616.5	616.9	617.3	617.3	617.3	617.1	617.0	616.8	616.5	616.1
135°	658.3	659.4	660.4	661.6	662.1	662.1	662.1	662.1	662.1	661.7	661.4
137.5°	703.0	703.5	704.0	704.5	704.9	705.2	705.5	705.8	706.1	705.6	705.1
140°	733.1	733.4	733.8	734.1	734.3	734.3	734.3	734.3	734.3	734.1	734.0
142.5°	760.7	761.0	761.4	761.8	761.8	761.7	761.5	761.4	761.3	761.2	761.2
145°	799.2	799.9	800.7	801.4	801.8	802.0	802.2	802.3	802.5	802.3	802.2
147.5°	837.3	838.1	838.9	839.8	840.2	840.0	839.9	839.7	839.6	839.5	839.3
150°	860.2	860.9	861.7	862.4	862.7	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	881.8	882.2	882.6	883.0	883.3	883.4	883.6	883.8	883.9	884.3	884.7
155°	914.9	914.9	914.9	914.9	914.8	914.6	914.4	914.3	914.1	914.8	915.5
157.5°	942.8	942.5	942.1	941.8	941.7	941.6	941.6	941.5	941.5	942.1	942.6
160°	959.6	959.4	959.3	959.1	958.9	958.7	958.5	958.4	958.2	958.7	959.3
162.5°	974.8	974.3	973.8	973.4	973.0	972.9	972.7	972.5	972.3	973.3	974.2
165°	995.4	994.8	994.3	993.8	993.3	993.0	992.6	992.3	991.9	993.0	994.0
167.5°	1011.1	1010.3	1009.6	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6	1010.7
170°	1019.9	1019.0	1018.1	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7	1019.7
172.5°	1026.4	1025.7	1025.0	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2	1026.4
175°	1035.1	1034.3	1033.4	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5	1033.7
177.5°	1038.2	1037.5	1036.8	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7	1037.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	8.6	8.7	8.7	8.5	8.4	8.5	8.1
90°	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	33.7	34.4	34.8	35.0	35.2	35.4	35.6
95°	62.6	63.1	63.4	63.4	63.4	63.4	63.4
97.5°	98.4	99.0	99.3	99.3	99.3	99.3	99.3
100°	123.8	124.2	124.4	124.4	124.4	124.4	124.4
102.5°	151.2	151.8	152.1	152.2	152.3	152.5	152.7
105°	192.6	193.1	193.7	194.2	194.7	195.3	195.8
107.5°	237.3	237.8	238.0	238.0	238.0	237.9	237.9
110°	266.2	265.8	265.9	266.4	267.0	267.5	268.1



TEST NUMBER: P332728-927

CATALOG NUMBER: S124DIW-S350D1050U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.5	298.4	298.4	298.6	298.7	298.7	298.9
115°	347.8	347.6	347.4	347.2	347.1	346.9	346.7
117.5°	394.7	394.2	393.7	393.3	393.0	392.6	392.3
120°	426.7	425.8	425.5	425.9	426.2	426.6	426.9
122.5°	459.6	459.0	458.4	457.7	457.1	456.5	455.8
125°	507.7	507.4	507.0	506.7	506.3	506.0	505.6
127.5°	553.5	553.1	552.8	552.5	552.2	551.9	551.7
130°	585.6	585.2	584.7	584.0	583.3	582.6	581.9
132.5°	615.8	615.4	615.1	614.8	614.5	614.2	613.9
135°	661.0	660.7	660.2	659.7	659.1	658.6	658.1
137.5°	704.6	704.2	704.0	704.1	704.3	704.3	704.4
140°	733.8	733.6	733.4	733.2	733.1	732.8	732.7
142.5°	761.1	761.1	761.0	761.0	761.0	761.0	761.0
145°	802.0	801.8	801.5	800.9	800.3	799.9	799.3
147.5°	839.2	839.0	838.8	838.7	838.5	838.3	838.1
150°	862.7	862.7	862.6	862.4	862.3	862.1	861.9
152.5°	885.2	885.6	885.6	885.1	884.6	884.2	883.8
155°	916.2	917.0	917.0	916.2	915.5	914.8	914.1
157.5°	943.1	943.6	943.6	943.0	942.4	941.8	941.2
160°	959.8	960.4	960.1	959.3	958.4	957.5	956.6
162.5°	975.2	976.2	976.2	975.3	974.5	973.5	972.6
165°	995.1	996.2	996.3	995.6	994.9	994.2	993.5
167.5°	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.4
170°	1020.8	1021.8	1021.8	1020.6	1019.3	1018.0	1016.8
172.5°	1027.6	1028.9	1028.8	1027.6	1026.4	1025.1	1023.8
175°	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3
177.5°	1038.7	1039.7	1039.7	1038.5	1037.4	1036.3	1035.1
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7

(END OF REPORT)