

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332238-840

Luminaire Tested: **S123DIW-S1165D1535U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332238-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1535U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11006.5 lumens  
Efficiency: N/A  
Efficacy: 132.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	65		57	55	54		44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39		39	35	32		31	28	26	22
5	67	56	47	41	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18		22	18	16		18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.9	1.6
10°-20°	491.0	4.5
20°-30°	725.3	6.6
30°-40°	847.3	7.7
40°-50°	851.8	7.7
50°-60°	748.3	6.8
60°-70°	557.5	5.1
70°-80°	317.6	2.9
80°-90°	96.8	0.9
90°-100°	73.9	0.7
100°-110°	352.1	3.2
110°-120°	845.8	7.7
120°-130°	1077.0	9.8
130°-140°	1150.8	10.5
140°-150°	1076.1	9.8
150°-160°	868.0	7.9
160°-170°	560.2	5.1
170°-180°	193.1	1.8
0°-30°	1390.3	12.6
0°-40°	2237.6	20.3
0°-60°	3837.7	34.9
0°-90°	4809.6	43.7
90°-120°	1271.8	11.6
90°-150°	4575.6	41.6
90°-180°	6197.0	56.3
0°-180°	11006.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	2	17	36	42	45	9
95°	92	35	47	57	57	114
105°	450	458	331	78	66	477
115°	844	853	867	881	888	833
125°	1190	1201	1208	1211	1214	1062
135°	1481	1490	1496	1500	1496	1140
145°	1709	1719	1723	1726	1726	1069
155°	1883	1880	1881	1888	1880	867
165°	1985	1981	1979	1990	1981	561
175°	2032	2025	2026	2035	2025	193
180°	2032	2032	2032	2032	2032	



TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.3	33.1	32.9	32.8	32.6	32.8	33.4	34.0	34.6	35.1	35.1
90°	1.5	4.8	8.2	11.6	14.9	18.8	23.1	27.5	31.9	36.3	37.6
92.5°	28.1	27.2	26.2	25.2	24.3	25.4	28.8	32.1	35.3	38.7	40.8
95°	92.1	78.4	64.6	50.8	37.1	32.0	35.7	39.4	43.1	46.8	49.2
97.5°	185.1	178.9	172.8	166.5	160.4	145.2	121.1	96.9	72.8	48.6	51.3
100°	255.2	261.9	268.5	275.3	282.0	259.1	206.8	154.5	102.2	49.8	52.5
102.5°	334.9	339.7	344.6	349.3	354.2	328.0	270.8	213.7	156.5	99.4	91.0
105°	449.9	453.6	457.3	461.0	464.6	451.4	421.2	391.0	360.8	330.6	271.2
107.5°	571.3	574.2	577.1	580.2	583.1	586.9	591.7	596.5	601.3	606.0	562.5
110°	652.2	654.9	657.5	660.2	663.0	666.1	669.8	673.5	677.2	680.9	669.8



TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	729.5	732.0	734.4	736.8	739.1	742.3	745.9	749.6	753.3	757.0	757.2
115°	843.9	846.0	848.0	850.0	852.0	854.5	857.6	860.5	863.5	866.6	869.9
117.5°	954.7	957.3	959.7	962.2	964.7	966.7	968.3	969.8	971.3	972.9	975.5
120°	1023.6	1026.6	1029.7	1032.7	1035.7	1037.7	1038.6	1039.7	1040.7	1041.7	1044.4
122.5°	1093.7	1096.1	1098.6	1101.1	1103.6	1105.5	1106.7	1108.0	1109.2	1110.5	1112.5
125°	1189.6	1192.3	1195.1	1197.7	1200.4	1202.4	1203.8	1205.1	1206.5	1207.8	1208.5
127.5°	1282.6	1285.4	1288.1	1290.7	1293.4	1295.6	1297.2	1298.8	1300.4	1302.0	1303.0
130°	1340.6	1343.3	1346.0	1348.7	1351.4	1353.4	1354.7	1356.0	1357.5	1358.8	1360.1
132.5°	1396.2	1398.9	1401.6	1404.2	1406.9	1408.9	1409.9	1411.0	1412.0	1413.1	1414.4
135°	1481.1	1483.1	1485.1	1487.1	1489.1	1490.8	1492.1	1493.5	1494.8	1496.1	1497.1
137.5°	1553.5	1556.1	1558.6	1561.2	1563.7	1565.4	1566.1	1566.8	1567.6	1568.3	1569.9
140°	1601.8	1603.9	1605.9	1607.9	1609.9	1611.3	1612.4	1613.4	1614.4	1615.4	1616.8
142.5°	1646.5	1648.5	1650.5	1652.5	1654.6	1656.1	1657.1	1658.1	1659.1	1660.1	1661.1
145°	1709.0	1711.3	1713.7	1716.1	1718.4	1719.9	1720.6	1721.2	1721.9	1722.6	1723.2
147.5°	1767.9	1769.5	1771.0	1772.5	1774.0	1775.1	1775.8	1776.6	1777.2	1777.9	1778.6
150°	1804.1	1805.1	1806.1	1807.2	1808.2	1809.0	1809.7	1810.4	1811.0	1811.7	1812.3
152.5°	1836.7	1837.2	1837.7	1838.2	1838.7	1839.1	1839.5	1839.9	1840.3	1840.7	1841.9
155°	1882.6	1882.0	1881.3	1880.7	1880.0	1879.8	1880.2	1880.5	1880.8	1881.1	1882.8
157.5°	1918.2	1918.2	1918.1	1918.0	1918.0	1917.8	1917.4	1917.1	1916.8	1916.4	1918.4
160°	1940.1	1939.6	1939.3	1939.0	1938.6	1938.3	1938.0	1937.6	1937.3	1937.0	1939.0
162.5°	1960.6	1959.6	1958.8	1957.9	1957.0	1956.4	1956.1	1955.8	1955.4	1955.1	1957.4
165°	1985.3	1984.3	1983.3	1982.3	1981.3	1980.6	1980.2	1979.9	1979.6	1979.2	1982.0
167.5°	2004.6	2003.3	2002.0	2000.6	1999.2	1998.6	1998.6	1998.6	1998.6	1998.6	2001.2
170°	2015.5	2014.2	2012.8	2011.4	2010.1	2009.4	2009.4	2009.4	2009.4	2009.4	2012.2
172.5°	2022.8	2021.1	2019.5	2017.9	2016.3	2015.6	2015.9	2016.2	2016.4	2016.7	2019.4
175°	2032.1	2030.4	2028.7	2027.1	2025.4	2024.7	2025.1	2025.4	2025.7	2026.1	2028.4
177.5°	2034.5	2033.2	2031.8	2030.5	2029.1	2028.6	2028.9	2029.1	2029.4	2029.7	2031.8
180°	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1



TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	35.1	35.1	35.1	35.1	35.3	35.4	35.5	35.7
90°	38.9	40.3	41.6	42.6	43.3	43.9	44.6	45.2
92.5°	42.9	45.1	47.3	48.5	48.9	49.3	49.7	50.1
95°	51.5	53.8	56.1	57.4	57.4	57.4	57.4	57.4
97.5°	54.0	56.7	59.4	60.9	61.2	61.5	61.9	62.2
100°	55.1	57.9	60.6	62.1	62.4	62.7	63.1	63.4
102.5°	82.7	74.4	66.0	62.2	62.8	63.4	64.0	64.6
105°	211.9	152.5	93.1	63.7	64.4	65.1	65.7	66.4
107.5°	518.9	475.3	431.8	387.7	343.0	298.1	253.4	208.6
110°	658.7	647.6	636.6	607.0	559.1	511.1	463.1	415.2





TEST NUMBER: P332238-840

CATALOG NUMBER: S123DIW-S1165D1535U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	757.4	757.6	757.8	752.9	742.7	732.6	722.5	712.3
115°	873.3	876.7	880.0	882.3	883.7	885.0	886.4	887.8
117.5°	978.3	980.9	983.6	985.1	985.3	985.6	985.9	986.1
120°	1047.1	1049.8	1052.5	1053.8	1053.8	1053.8	1053.8	1053.8
122.5°	1114.3	1116.2	1118.1	1119.1	1119.4	1119.6	1119.9	1120.2
125°	1209.1	1209.8	1210.4	1211.1	1211.8	1212.4	1213.2	1213.9
127.5°	1304.1	1305.3	1306.3	1306.5	1305.9	1305.1	1304.4	1303.8
130°	1361.4	1362.8	1364.1	1364.4	1363.8	1363.1	1362.4	1361.8
132.5°	1415.8	1417.1	1418.5	1418.7	1417.7	1416.8	1415.8	1414.9
135°	1498.1	1499.1	1500.2	1500.2	1499.1	1498.1	1497.1	1496.1
137.5°	1571.6	1573.2	1574.8	1575.2	1574.6	1573.9	1573.2	1572.6
140°	1618.1	1619.4	1620.7	1621.1	1620.4	1619.8	1619.1	1618.4
142.5°	1662.2	1663.3	1664.4	1664.5	1663.6	1662.5	1661.6	1660.7
145°	1723.9	1724.6	1725.3	1725.7	1725.7	1725.7	1725.7	1725.7
147.5°	1779.2	1779.9	1780.6	1780.1	1778.6	1777.1	1775.4	1773.9
150°	1813.0	1813.7	1814.3	1814.2	1813.2	1812.2	1811.2	1810.2
152.5°	1843.1	1844.3	1845.5	1845.3	1843.8	1842.2	1840.7	1839.2
155°	1884.5	1886.1	1887.8	1887.6	1885.6	1883.6	1881.6	1879.7
157.5°	1920.5	1922.5	1924.5	1924.2	1921.6	1918.9	1916.3	1913.7
160°	1941.1	1943.0	1945.0	1944.9	1942.5	1940.2	1937.8	1935.5
162.5°	1959.6	1962.0	1964.2	1964.3	1962.3	1960.1	1958.1	1956.0
165°	1984.6	1987.3	1990.0	1990.1	1987.8	1985.5	1983.1	1980.7
167.5°	2004.0	2006.6	2009.3	2009.3	2006.6	2004.0	2001.2	1998.6
170°	2014.8	2017.5	2020.2	2020.2	2017.5	2014.8	2012.2	2009.4
172.5°	2022.1	2024.8	2027.4	2027.3	2024.4	2021.4	2018.4	2015.5
175°	2030.7	2033.1	2035.5	2035.3	2032.6	2029.9	2027.2	2024.6
177.5°	2034.0	2036.1	2038.3	2038.0	2035.3	2032.7	2029.9	2027.3
180°	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1

(END OF REPORT)