

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332221-840

Luminaire Tested: **S123DIW-S1165D755U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332221-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D755U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7450.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69	69	69	65
1	101	96	92	89	95	91	87	84	80	77	75		70	68	67		61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62		62	58	56		54	51	49	45
3	84	74	66	60	78	70	63	58	62	57	52		55	50	47		48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45		49	44	40		43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	38		44	39	35		38	35	31	29
6	65	53	44	38	61	50	42	37	44	38	34		40	34	31		35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30		36	31	27		32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24		30	25	22		27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.3
10°-20°	491.0	6.6
20°-30°	725.3	9.7
30°-40°	847.3	11.4
40°-50°	851.8	11.4
50°-60°	748.3	10.0
60°-70°	557.5	7.5
70°-80°	317.6	4.3
80°-90°	94.0	1.3
90°-100°	62.2	0.8
100°-110°	186.1	2.5
110°-120°	316.4	4.2
120°-130°	416.2	5.6
130°-140°	467.8	6.3
140°-150°	459.9	6.2
150°-160°	387.1	5.2
160°-170°	257.7	3.5
170°-180°	90.2	1.2
0°-30°	1390.3	18.7
0°-40°	2237.6	30.0
0°-60°	3837.7	51.5
0°-90°	4806.7	64.5
90°-120°	564.7	7.6
90°-150°	1908.6	25.6
90°-180°	2644.0	35.5
0°-180°	7450.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	1	8	18	21	22	7
95°	44	50	55	58	58	50
105°	169	170	177	177	178	181
115°	319	321	319	320	319	315
125°	466	468	467	464	461	416
135°	605	609	609	606	604	466
145°	734	735	738	737	734	458
155°	840	840	841	844	839	387
165°	915	913	913	917	912	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.1	32.6	32.1	31.6	31.1	30.9	31.1	31.2	31.4	31.5	31.4
90°	0.7	2.4	4.0	5.8	7.4	9.3	11.5	13.6	15.9	18.0	18.7
92.5°	18.2	19.3	20.4	21.5	22.6	23.8	25.0	26.4	27.6	28.8	29.3
95°	44.2	45.3	46.6	47.8	48.9	50.1	51.5	52.8	54.1	55.4	56.1
97.5°	78.6	79.4	80.3	81.2	82.0	82.9	83.9	84.8	85.8	86.8	87.6
100°	101.9	102.9	103.9	104.9	105.9	106.8	107.7	108.6	109.4	110.2	110.7
102.5°	129.0	129.6	130.2	130.7	131.3	132.2	133.3	134.4	135.4	136.5	137.0
105°	168.6	169.0	169.4	169.7	170.0	170.9	172.4	173.9	175.4	176.9	176.9
107.5°	214.8	215.0	215.2	215.4	215.6	216.0	216.6	217.2	217.8	218.4	218.9
110°	243.6	244.0	244.3	244.6	244.9	245.3	245.6	245.9	246.3	246.6	247.3



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	273.6	273.8	274.0	274.2	274.4	274.5	274.6	274.7	274.7	274.8	275.6
115°	318.6	319.0	319.5	320.0	320.5	320.6	320.3	320.0	319.6	319.3	319.5
117.5°	363.9	364.2	364.5	364.9	365.2	365.2	364.7	364.3	363.9	363.3	363.3
120°	392.0	393.0	394.0	395.1	396.1	396.1	395.3	394.5	393.6	392.7	392.6
122.5°	421.4	422.1	422.8	423.6	424.3	424.4	424.0	423.6	423.2	422.7	422.3
125°	466.3	466.8	467.3	467.8	468.3	468.3	468.0	467.7	467.3	467.0	466.4
127.5°	507.6	508.7	509.8	510.8	511.9	512.2	511.9	511.5	511.1	510.8	509.8
130°	535.2	536.5	537.9	539.2	540.5	541.0	540.5	540.0	539.5	539.0	538.3
132.5°	562.8	564.1	565.4	566.7	568.2	568.6	568.3	567.8	567.4	567.1	566.3
135°	604.9	605.9	606.9	607.9	608.8	609.4	609.2	608.9	608.8	608.6	607.9
137.5°	643.9	644.7	645.5	646.4	647.2	647.8	648.2	648.7	649.1	649.5	648.8
140°	670.9	671.7	672.6	673.4	674.2	674.7	674.9	675.0	675.2	675.4	675.2
142.5°	695.5	696.3	697.1	697.9	698.7	699.3	699.6	699.9	700.2	700.5	700.3
145°	733.9	734.2	734.5	734.8	735.2	735.6	736.1	736.6	737.1	737.6	737.4
147.5°	767.4	768.0	768.6	769.2	769.8	770.3	770.8	771.2	771.7	772.2	772.2
150°	790.8	791.1	791.4	791.8	792.1	792.4	792.7	793.1	793.5	793.8	793.8
152.5°	810.0	810.4	810.9	811.4	811.8	812.1	812.3	812.5	812.7	812.9	813.2
155°	840.3	840.3	840.3	840.3	840.3	840.3	840.5	840.7	840.8	841.0	841.7
157.5°	866.1	865.9	865.7	865.5	865.3	865.3	865.4	865.5	865.7	865.8	866.5
160°	882.2	881.9	881.6	881.2	880.9	880.7	880.7	880.7	880.7	880.7	881.6
162.5°	896.7	896.2	895.6	895.2	894.7	894.6	894.7	894.8	895.0	895.1	896.0
165°	915.2	914.7	914.2	913.7	913.2	912.9	912.9	912.9	912.9	912.9	913.9
167.5°	930.1	929.4	928.8	928.1	927.4	927.2	927.3	927.4	927.6	927.7	928.7
170°	938.5	937.8	937.2	936.4	935.7	935.4	935.4	935.4	935.4	935.4	936.6
172.5°	945.0	944.4	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.1
175°	951.9	951.3	950.6	950.0	949.3	949.0	949.0	949.0	949.0	949.0	950.0
177.5°	954.8	954.2	953.7	953.2	952.7	952.4	952.4	952.4	952.4	952.4	953.2
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	31.2	31.1	30.9	30.9	31.0	31.0	31.1	31.2
90°	19.3	20.0	20.7	21.1	21.5	21.8	22.1	22.5
92.5°	29.9	30.4	30.9	31.1	30.9	30.7	30.5	30.3
95°	56.8	57.5	58.2	58.5	58.5	58.5	58.5	58.5
97.5°	88.4	89.1	89.9	90.2	90.2	90.1	90.0	90.0
100°	111.2	111.7	112.2	112.6	112.9	113.3	113.6	113.9
102.5°	137.5	138.0	138.6	138.8	138.8	138.7	138.6	138.6
105°	176.9	176.9	176.9	177.0	177.4	177.7	178.0	178.4
107.5°	219.4	220.0	220.6	220.8	220.6	220.4	220.2	219.9
110°	247.9	248.6	249.2	249.4	249.1	248.7	248.4	248.1



TEST NUMBER: P332221-840

CATALOG NUMBER: S123DIW-S1165D755U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.4	277.2	278.0	278.3	278.3	278.2	278.1	278.1
115°	319.6	319.8	320.0	320.0	319.8	319.6	319.5	319.3
117.5°	363.3	363.2	363.2	363.0	362.5	362.0	361.6	361.1
120°	392.4	392.2	392.1	391.8	391.5	391.2	390.8	390.5
122.5°	421.9	421.4	421.0	420.6	420.1	419.6	419.2	418.7
125°	465.6	464.9	464.3	463.6	463.0	462.3	461.6	461.0
127.5°	508.9	508.0	507.1	506.1	505.4	504.6	503.9	503.1
130°	537.7	536.9	536.2	535.3	534.2	533.0	531.9	530.7
132.5°	565.5	564.7	563.9	563.1	562.2	561.3	560.4	559.5
135°	607.3	606.6	606.0	605.5	605.1	604.8	604.5	604.1
137.5°	648.1	647.4	646.8	646.1	645.5	644.8	644.2	643.6
140°	675.0	674.9	674.7	674.0	672.9	671.7	670.6	669.3
142.5°	700.2	700.0	699.8	699.3	698.4	697.5	696.6	695.7
145°	737.2	737.1	736.9	736.5	735.8	735.2	734.5	733.9
147.5°	772.2	772.2	772.2	771.7	770.7	769.7	768.7	767.7
150°	793.8	793.8	793.8	793.2	792.2	791.3	790.3	789.3
152.5°	813.5	813.7	814.1	813.7	812.8	812.0	811.1	810.3
155°	842.3	843.0	843.6	843.4	842.2	841.1	839.9	838.8
157.5°	867.2	867.9	868.6	868.4	867.5	866.6	865.7	864.6
160°	882.4	883.2	884.0	884.1	883.5	882.8	882.1	881.5
162.5°	896.8	897.7	898.5	898.4	897.3	896.3	895.1	894.0
165°	914.9	915.9	917.0	916.9	915.7	914.5	913.4	912.2
167.5°	929.7	930.8	931.8	931.8	930.8	929.7	928.7	927.7
170°	937.8	939.0	940.1	940.1	939.0	937.8	936.6	935.4
172.5°	944.1	945.1	946.1	946.1	944.9	943.8	942.6	941.5
175°	951.0	951.9	952.9	952.9	951.7	950.5	949.4	948.2
177.5°	954.0	954.8	955.6	955.5	954.6	953.6	952.7	951.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2

(END OF REPORT)