

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332737-927

Luminaire Tested: **S124DIW-S350D1340U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332737-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1340U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5454.3 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	26	19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	22	22	16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	0.8
10°-20°	124.2	2.3
20°-30°	182.8	3.4
30°-40°	212.5	3.9
40°-50°	212.5	3.9
50°-60°	185.9	3.4
60°-70°	138.0	2.5
70°-80°	78.4	1.4
80°-90°	26.6	0.5
90°-100°	47.0	0.9
100°-110°	299.6	5.5
110°-120°	573.1	10.5
120°-130°	727.5	13.3
130°-140°	778.4	14.3
140°-150°	727.9	13.3
150°-160°	587.0	10.8
160°-170°	378.6	6.9
170°-180°	130.5	2.4
0°-30°	351.0	6.4
0°-40°	563.5	10.3
0°-60°	961.8	17.6
0°-90°	1204.8	22.1
90°-120°	919.7	16.9
90°-150°	3153.4	57.8
90°-180°	4250.0	77.9
0°-180°	5454.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	3	14	23	29	31	4
95°	56	24	23	28	30	73
105°	309	315	321	327	293	324
115°	577	580	580	581	582	568
125°	812	816	814	817	818	724
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	725
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1345	1337	379
175°	1374	1368	1369	1377	1366	131
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.4	8.9	9.3	9.7	10.1	10.5	10.9	11.1	11.4	11.7	12.0
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	12.9	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1
95°	56.5	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0
97.5°	120.0	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3
100°	168.5	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4
102.5°	222.8	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9
105°	309.3	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7
107.5°	389.6	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7
110°	443.9	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6



TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.5	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9
115°	577.4	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0
117.5°	650.4	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7
120°	699.7	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3
122.5°	745.8	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0
125°	811.7	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4
127.5°	874.2	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8
130°	914.5	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9
132.5°	951.5	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4
135°	1006.9	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5
137.5°	1056.1	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5
140°	1088.1	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9
142.5°	1116.9	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4
145°	1161.1	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4
147.5°	1196.2	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1
150°	1221.7	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8
152.5°	1243.1	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9
155°	1273.1	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9
157.5°	1298.4	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5
160°	1313.1	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4
162.5°	1326.3	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7
165°	1343.0	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7
167.5°	1356.1	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2
170°	1363.5	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2
172.5°	1368.4	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1
175°	1373.8	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7
177.5°	1376.3	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4
90°	25.3	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	24.6	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	25.3	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.4	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	37.5	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	134.1	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	324.7	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	401.7	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.1	454.5	455.0	455.5	456.2	456.9	457.6	458.3





TEST NUMBER: P332737-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	504.7	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.4	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.6	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.2	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.2	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.7	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.0	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.7	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.0	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.0	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1093.6	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1122.8	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.6	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.3	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.2	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1272.9	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1324.1	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1341.5	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1354.2	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1362.0	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1366.9	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1372.8	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1375.1	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)