

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332738-927

Luminaire Tested: **S124DIW-S350D1340U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332738-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1340U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4890.3 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	68	63	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	49	47	43	39	34	31	29	22	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	32	27	30	25	22	22	19	16	15	13	11	9
8	50	38	31	26	45	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	0.9
10°-20°	124.2	2.5
20°-30°	182.8	3.7
30°-40°	212.5	4.3
40°-50°	212.5	4.3
50°-60°	185.9	3.8
60°-70°	138.0	2.8
70°-80°	78.4	1.6
80°-90°	26.6	0.5
90°-100°	87.6	1.8
100°-110°	259.5	5.3
110°-120°	440.5	9.0
120°-130°	580.9	11.9
130°-140°	652.4	13.3
140°-150°	641.1	13.1
150°-160°	539.2	11.0
160°-170°	358.7	7.3
170°-180°	125.6	2.6
0°-30°	351.0	7.2
0°-40°	563.5	11.5
0°-60°	961.8	19.7
0°-90°	1204.8	24.6
90°-120°	787.7	16.1
90°-150°	2662.0	54.4
90°-180°	3686.0	75.4
0°-180°	4890.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	3	14	23	28	31	5
95°	62	71	78	81	81	69
105°	239	241	244	248	251	254
115°	448	448	446	445	444	442
125°	652	652	651	649	647	581
135°	841	847	848	845	842	651
145°	1022	1026	1027	1026	1023	639
155°	1171	1171	1170	1174	1170	539
165°	1275	1272	1270	1275	1272	359
175°	1326	1321	1320	1327	1320	126
180°	1328	1328	1328	1328	1328	



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.4	8.9	9.3	9.7	10.1	10.5	10.9	11.1	11.4	11.7	12.0
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	22.0	24.9	27.7	30.6	33.5	35.6	36.8	38.1	39.4	40.7	41.5
95°	61.6	63.7	65.8	67.8	69.9	71.7	73.3	74.9	76.4	78.1	78.7
97.5°	107.7	109.3	111.0	112.6	114.2	116.0	117.9	119.8	121.6	123.5	124.3
100°	143.9	144.7	145.7	146.6	147.5	148.9	151.0	153.0	155.1	157.2	157.6
102.5°	181.6	182.0	182.4	182.8	183.1	184.2	186.1	188.0	189.8	191.7	192.3
105°	239.4	239.6	239.9	240.0	240.3	240.8	241.8	242.7	243.6	244.5	245.2
107.5°	300.0	300.2	300.6	300.8	301.1	301.3	301.4	301.6	301.7	301.8	302.5
110°	341.1	341.5	342.0	342.5	342.9	343.0	342.8	342.5	342.4	342.1	341.7



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.8	383.9	384.0	384.1	384.2	384.0	383.7	383.2	382.8	382.4	382.3
115°	447.9	447.9	447.9	447.9	447.9	447.7	447.3	446.8	446.3	445.8	445.7
117.5°	508.3	508.5	508.7	508.9	509.1	509.0	508.7	508.3	508.0	507.7	506.9
120°	548.6	549.5	550.4	551.4	552.2	552.4	551.7	551.0	550.3	549.6	548.5
122.5°	590.5	590.9	591.3	591.6	592.0	592.0	591.7	591.4	591.0	590.7	589.9
125°	652.4	652.4	652.4	652.4	652.4	652.3	652.0	651.8	651.6	651.3	650.9
127.5°	708.4	709.2	709.9	710.5	711.2	711.4	711.0	710.7	710.3	709.9	709.5
130°	747.9	748.6	749.3	750.0	750.7	751.0	751.0	751.0	751.0	751.0	750.5
132.5°	788.2	788.7	789.2	789.7	790.2	790.4	790.2	790.0	789.8	789.6	789.2
135°	841.4	842.8	844.1	845.5	846.9	847.6	847.6	847.6	847.6	847.6	847.2
137.5°	899.4	900.0	900.6	901.3	901.9	902.5	902.8	903.2	903.5	903.9	903.2
140°	938.0	938.4	938.9	939.4	939.8	940.0	940.0	940.0	940.0	940.0	939.8
142.5°	973.4	973.8	974.2	974.7	975.2	975.3	975.1	974.9	974.8	974.5	974.5
145°	1022.2	1023.2	1024.1	1025.0	1025.9	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1
147.5°	1070.7	1071.8	1072.9	1074.0	1075.1	1075.5	1075.4	1075.2	1075.0	1074.8	1074.7
150°	1100.3	1101.2	1102.2	1103.0	1104.0	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4
152.5°	1128.2	1128.8	1129.3	1129.9	1130.4	1130.8	1131.0	1131.2	1131.4	1131.6	1132.1
155°	1171.2	1171.2	1171.2	1171.2	1171.2	1171.1	1170.8	1170.6	1170.4	1170.2	1171.1
157.5°	1207.4	1207.0	1206.6	1206.1	1205.7	1205.5	1205.5	1205.4	1205.4	1205.3	1206.0
160°	1228.8	1228.5	1228.3	1228.0	1227.8	1227.6	1227.3	1227.2	1226.9	1226.7	1227.3
162.5°	1248.5	1247.8	1247.3	1246.7	1246.1	1245.7	1245.5	1245.2	1245.0	1244.8	1246.0
165°	1274.9	1274.3	1273.6	1272.9	1272.2	1271.7	1271.2	1270.7	1270.3	1269.8	1271.2
167.5°	1295.3	1294.3	1293.4	1292.4	1291.5	1291.0	1291.1	1291.1	1291.2	1291.2	1292.6
170°	1306.8	1305.7	1304.6	1303.4	1302.3	1301.8	1302.0	1302.3	1302.5	1302.7	1304.1
172.5°	1315.0	1314.1	1313.1	1312.2	1311.2	1310.7	1310.8	1310.8	1310.9	1310.9	1312.5
175°	1326.4	1325.2	1324.1	1322.9	1321.8	1321.0	1320.9	1320.6	1320.4	1320.2	1321.8
177.5°	1330.0	1329.1	1328.2	1327.3	1326.4	1326.0	1326.0	1326.0	1326.0	1326.0	1327.2
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4
90°	25.3	26.7	28.0	29.0	29.5	29.9	30.3	30.8
92.5°	42.3	43.2	44.0	44.5	44.8	45.1	45.3	45.6
95°	79.5	80.2	80.8	81.2	81.2	81.2	81.2	81.2
97.5°	125.2	126.0	126.7	127.2	127.2	127.2	127.2	127.2
100°	158.1	158.6	159.0	159.2	159.2	159.2	159.2	159.2
102.5°	193.0	193.6	194.2	194.6	194.9	195.0	195.2	195.4
105°	245.9	246.6	247.2	248.0	248.6	249.3	250.0	250.6
107.5°	303.1	303.7	304.4	304.7	304.7	304.6	304.6	304.5
110°	341.2	340.7	340.3	340.4	341.1	341.7	342.5	343.2



TEST NUMBER: P332738-927

CATALOG NUMBER: S124DIW-S350D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.2	382.1	382.0	382.1	382.1	382.3	382.5	382.6
115°	445.4	445.2	445.0	444.7	444.5	444.3	444.0	443.9
117.5°	506.2	505.4	504.6	504.0	503.5	503.1	502.6	502.2
120°	547.4	546.2	545.1	544.7	545.2	545.7	546.1	546.5
122.5°	589.1	588.4	587.6	586.8	586.0	585.2	584.4	583.5
125°	650.5	650.0	649.5	649.0	648.6	648.2	647.7	647.2
127.5°	709.0	708.5	708.1	707.7	707.3	706.9	706.5	706.2
130°	750.1	749.6	749.2	748.5	747.6	746.6	745.8	744.8
132.5°	788.7	788.3	787.8	787.4	787.0	786.6	786.3	785.9
135°	846.7	846.2	845.7	845.2	844.5	843.8	843.1	842.4
137.5°	902.7	902.1	901.5	901.3	901.4	901.6	901.7	901.8
140°	939.6	939.4	939.1	938.9	938.7	938.4	938.2	938.0
142.5°	974.5	974.5	974.4	974.3	974.3	974.2	974.2	974.1
145°	1026.9	1026.7	1026.4	1026.0	1025.3	1024.6	1024.0	1023.3
147.5°	1074.4	1074.3	1074.1	1073.9	1073.6	1073.4	1073.2	1073.0
150°	1104.4	1104.4	1104.4	1104.3	1104.1	1103.8	1103.6	1103.4
152.5°	1132.7	1133.2	1133.8	1133.7	1133.1	1132.5	1131.9	1131.3
155°	1172.0	1172.9	1173.9	1173.9	1172.9	1172.0	1171.1	1170.2
157.5°	1206.7	1207.4	1208.1	1208.0	1207.2	1206.4	1205.7	1204.9
160°	1228.0	1228.8	1229.4	1229.2	1228.0	1226.9	1225.7	1224.6
162.5°	1247.2	1248.5	1249.7	1249.7	1248.6	1247.4	1246.3	1245.2
165°	1272.6	1273.9	1275.3	1275.6	1274.6	1273.7	1272.8	1271.8
167.5°	1294.0	1295.3	1296.6	1296.6	1295.2	1293.8	1292.4	1291.0
170°	1305.4	1306.8	1308.2	1308.1	1306.5	1304.9	1303.3	1301.7
172.5°	1314.0	1315.6	1317.2	1317.1	1315.5	1313.9	1312.3	1310.7
175°	1323.3	1324.9	1326.6	1326.6	1324.9	1323.3	1321.8	1320.2
177.5°	1328.5	1329.8	1331.0	1330.9	1329.5	1328.0	1326.6	1325.1
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4

(END OF REPORT)