

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332739-927

Luminaire Tested: **S124DIW-S350D1560U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332739-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1560U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6194.1 lumens  
Efficiency: N/A  
Efficacy: 116.0 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



80% Up  
20% Dn

— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	20				
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17				
2	83	76	70	65	73	67	63	59	51	48	45	36	34	33	23	22	21	15				
3	76	67	60	54	67	59	54	49	45	41	38	32	30	28	20	19	18	12				
4	69	59	52	46	61	53	46	41	40	36	32	29	26	24	18	16	15	11				
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9				
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12	8				
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10	7				
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9	7				
9	46	35	28	23	41	31	25	21	24	20	16	17	14	12	11	10	8	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1037	1074	2566	1074



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	0.7
10°-20°	135.9	2.2
20°-30°	215.5	3.5
30°-40°	239.8	3.9
40°-50°	218.3	3.5
50°-60°	178.4	2.9
60°-70°	127.4	2.1
70°-80°	70.1	1.1
80°-90°	23.8	0.4
90°-100°	54.6	0.9
100°-110°	348.3	5.6
110°-120°	666.3	10.8
120°-130°	845.9	13.7
130°-140°	905.0	14.6
140°-150°	846.3	13.7
150°-160°	682.5	11.0
160°-170°	440.2	7.1
170°-180°	151.7	2.4
0°-30°	395.5	6.4
0°-40°	635.3	10.3
0°-60°	1032.1	16.7
0°-90°	1253.3	20.2
90°-120°	1069.3	17.3
90°-150°	3666.4	59.2
90°-180°	4941.0	79.8
0°-180°	6194.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	15
90°	36	4	36	4	36	16
95°	35	66	35	66	35	28
105°	340	360	340	360	340	297
115°	676	671	676	671	676	669
125°	951	944	951	944	951	847
135°	1179	1171	1179	1171	1179	908
145°	1357	1350	1357	1350	1357	848
155°	1479	1480	1479	1480	1479	682
165°	1554	1561	1554	1561	1554	439
175°	1588	1597	1588	1597	1588	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	10.5	10.8	10.7	10.8	10.9	10.9	10.7	10.2	10.5	10.4	10.5
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5	26.9	25.3	23.2
95°	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5	27.9	26.3	26.0
97.5°	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8	31.7	31.5	61.2
100°	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6	48.1	52.6	89.2
102.5°	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9	204.5	253.3	258.0
105°	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5	375.1	372.7	371.4
107.5°	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1	465.9	464.7	462.9
110°	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9	527.4	526.8	525.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8	586.9	587.1	586.3
115°	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9	674.3	673.8	674.1
117.5°	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4	763.5	763.6	763.0
120°	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1	817.4
122.5°	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3	872.0	871.6	871.2
125°	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8	947.0	946.2	946.7
127.5°	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8	1022.9	1023.1	1021.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6	1068.3	1068.0	1067.2
132.5°	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5	1113.2	1112.9	1111.9
135°	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4	1174.9	1174.3	1173.3
137.5°	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8	1234.1	1233.6	1232.4
140°	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5	1270.7	1269.9	1269.4
142.5°	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5	1304.9	1304.3	1304.0
145°	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1	1353.8	1353.5	1353.5
147.5°	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7	1396.5	1396.3	1396.5
150°	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0	1424.0	1424.0	1424.3
152.5°	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8	1447.4	1446.9	1447.4
155°	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9	1478.8	1477.7	1478.6
157.5°	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8	1505.7
160°	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9	1522.3
162.5°	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5	1537.9	1536.3	1536.6
165°	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6	1557.5	1555.4	1555.4
167.5°	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5	1572.1	1569.8	1569.9
170°	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6	1581.4	1579.3	1579.1
172.5°	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3	1587.1	1585.1	1584.8
175°	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0	1593.6	1591.3	1591.0
177.5°	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7	1597.0	1595.3	1594.9
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	10.1	9.8	9.3	8.2	7.1	6.1	5.4	4.6	5.4	6.1	6.8
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1	15.2	15.4	15.5
95°	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7	56.6	47.7	38.7
97.5°	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5	145.1	150.8	156.5
100°	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9	200.7	205.5	210.2
102.5°	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0	262.5	266.0	269.5
105°	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6	361.2	362.7	364.4
107.5°	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0	453.8	454.6	455.4
110°	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1	516.9	517.7	518.5





TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3	578.7	580.1	581.5
115°	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4	672.2	673.0	673.8
117.5°	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2	757.2	758.4	759.4
120°	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6	814.6	815.7	816.7
122.5°	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0	867.7	868.3	868.9
125°	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8	944.8	945.9	947.0
127.5°	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4	1016.7	1016.9	1017.2
130°	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3	1063.5	1063.7	1064.1
132.5°	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2	1106.7	1107.2	1107.7
135°	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8	1170.4	1170.2	1170.0
137.5°	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9	1228.0	1228.0	1228.2
140°	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1	1265.7	1266.2	1266.7
142.5°	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5	1299.5	1300.5	1301.5
145°	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0	1350.8	1351.5	1352.3
147.5°	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8	1392.3	1393.8	1395.3
150°	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5	1421.5	1422.5	1423.6
152.5°	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3	1446.1	1447.0	1447.8
155°	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2	1480.4	1480.7	1481.0
157.5°	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6	1509.4	1509.3	1509.1
160°	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8	1526.0	1525.2	1524.4
162.5°	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1	1541.0	1540.0	1539.1
165°	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4	1560.0	1558.8	1557.4
167.5°	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7	1575.3	1573.9	1572.6
170°	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3	1583.7	1582.1	1580.5
172.5°	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0	1589.4	1587.9	1586.3
175°	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2	1595.6	1594.0	1592.4
177.5°	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1	1598.6	1597.1	1595.6
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	7.8	8.3	9.3	10.1	11.0	12.1	12.8	14.7	15.7	16.7	18.3
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5	30.1	31.7	32.6
95°	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5	31.1	32.6	33.6
97.5°	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8	32.0	32.2	32.4
100°	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6	39.1	34.5	32.4
102.5°	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9	107.2	58.5	34.2
105°	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5	379.9	382.3	378.7
107.5°	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1	468.3	469.4	470.5
110°	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9	528.5	528.9	529.7



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8	586.7	586.6	587.1
115°	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9	675.3	675.9	676.2
117.5°	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4	763.3	763.2	763.1
120°	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2	818.7	819.3	819.3
122.5°	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3	872.6	872.9	872.7
125°	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8	948.6	949.4	949.9
127.5°	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8	1022.6	1022.5	1022.2
130°	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6	1068.8	1069.1	1069.2
132.5°	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5	1113.7	1114.0	1114.0
135°	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4	1175.9	1176.5	1177.0
137.5°	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8	1235.3	1236.0	1236.1
140°	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5	1272.3	1273.1	1273.6
142.5°	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5	1306.1	1306.6	1306.9
145°	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1	1354.3	1354.6	1355.0
147.5°	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7	1396.9	1397.2	1397.4
150°	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0	1424.0	1424.0	1424.2
152.5°	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8	1448.2	1448.7	1448.7
155°	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9	1481.0	1482.0	1482.2
157.5°	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3
160°	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4
162.5°	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5	1541.1	1542.7	1542.5
165°	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6	1561.8	1563.9	1563.8
167.5°	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5	1576.8	1579.1	1579.0
170°	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6	1585.7	1587.9	1587.5
172.5°	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3	1591.4	1593.6	1593.2
175°	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0	1598.5	1600.8	1600.4
177.5°	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7	1600.4	1602.1	1601.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	18.9	19.1	19.6	20.0	19.6	19.1	18.9	18.3	16.7	15.7	14.7
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	32.6	32.8	32.9	33.0	32.9	32.8	32.6	32.6	31.7	30.1	28.5
95°	33.8	34.1	34.4	34.6	34.4	34.1	33.8	33.6	32.6	31.1	29.5
97.5°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	32.2	32.0	31.8
100°	32.6	33.0	33.2	33.4	33.2	33.0	32.6	32.4	34.5	39.1	43.6
102.5°	34.2	34.3	34.4	34.4	34.4	34.3	34.2	34.2	58.5	107.2	155.9
105°	369.2	359.6	350.1	340.5	350.1	359.6	369.2	378.7	382.3	379.9	377.5
107.5°	471.5	472.5	473.5	474.5	473.5	472.5	471.5	470.5	469.4	468.3	467.1
110°	530.4	531.2	532.0	532.8	532.0	531.2	530.4	529.7	528.9	528.5	527.9



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	588.1	589.1	590.1	591.1	590.1	589.1	588.1	587.1	586.6	586.7	586.8
115°	676.2	676.2	676.2	676.2	676.2	676.2	676.2	676.2	675.9	675.3	674.9
117.5°	763.0	762.9	762.8	762.6	762.8	762.9	763.0	763.1	763.2	763.3	763.4
120°	818.7	818.2	817.7	817.1	817.7	818.2	818.7	819.3	819.3	818.7	818.2
122.5°	872.3	871.7	871.2	870.7	871.2	871.7	872.3	872.7	872.9	872.6	872.3
125°	950.1	950.4	950.7	950.9	950.7	950.4	950.1	949.9	949.4	948.6	947.8
127.5°	1022.1	1021.8	1021.6	1021.4	1021.6	1021.8	1022.1	1022.2	1022.5	1022.6	1022.8
130°	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.2	1069.1	1068.8	1068.6
132.5°	1113.8	1113.6	1113.4	1113.2	1113.4	1113.6	1113.8	1114.0	1114.0	1113.7	1113.5
135°	1177.5	1178.1	1178.6	1179.1	1178.6	1178.1	1177.5	1177.0	1176.5	1175.9	1175.4
137.5°	1236.0	1235.8	1235.6	1235.5	1235.6	1235.8	1236.0	1236.1	1236.0	1235.3	1234.8
140°	1273.9	1274.1	1274.4	1274.7	1274.4	1274.1	1273.9	1273.6	1273.1	1272.3	1271.5
142.5°	1307.0	1307.1	1307.1	1307.2	1307.1	1307.1	1307.0	1306.9	1306.6	1306.1	1305.5
145°	1355.5	1356.1	1356.6	1357.1	1356.6	1356.1	1355.5	1355.0	1354.6	1354.3	1354.1
147.5°	1397.6	1397.9	1398.2	1398.4	1398.2	1397.9	1397.6	1397.4	1397.2	1396.9	1396.7
150°	1424.4	1424.7	1425.0	1425.2	1425.0	1424.7	1424.4	1424.2	1424.0	1424.0	1424.0
152.5°	1448.6	1448.4	1448.3	1448.1	1448.3	1448.4	1448.6	1448.7	1448.7	1448.2	1447.8
155°	1481.4	1480.6	1479.8	1479.0	1479.8	1480.6	1481.4	1482.2	1482.0	1481.0	1479.9
157.5°	1508.9	1507.5	1506.2	1504.8	1506.2	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5
160°	1526.8	1525.2	1523.6	1521.9	1523.6	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2
162.5°	1540.8	1539.0	1537.2	1535.3	1537.2	1539.0	1540.8	1542.5	1542.7	1541.1	1539.5
165°	1561.4	1559.0	1556.6	1554.3	1556.6	1559.0	1561.4	1563.8	1563.9	1561.8	1559.6
167.5°	1576.3	1573.7	1571.0	1568.4	1571.0	1573.7	1576.3	1579.0	1579.1	1576.8	1574.5
170°	1584.9	1582.2	1579.6	1576.9	1579.6	1582.2	1584.9	1587.5	1587.9	1585.7	1583.6
172.5°	1590.3	1587.5	1584.6	1581.7	1584.6	1587.5	1590.3	1593.2	1593.6	1591.4	1589.3
175°	1597.2	1594.0	1590.9	1587.7	1590.9	1594.0	1597.2	1600.4	1600.8	1598.5	1596.0
177.5°	1599.2	1596.6	1594.0	1591.5	1594.0	1596.6	1599.2	1601.7	1602.1	1600.4	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	12.8	12.1	11.0	10.1	9.3	8.3	7.8	6.8	6.1	5.4	4.6
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	26.9	25.3	23.2	21.1	18.9	16.8	15.7	15.5	15.4	15.2	15.1
95°	27.9	26.3	26.0	25.7	25.5	25.2	29.6	38.7	47.7	56.6	65.7
97.5°	31.7	31.5	61.2	90.8	120.4	150.0	162.1	156.5	150.8	145.1	139.5
100°	48.1	52.6	89.2	125.8	162.5	199.1	215.0	210.2	205.5	200.7	195.9
102.5°	204.5	253.3	258.0	262.8	267.6	272.4	273.0	269.5	266.0	262.5	259.0
105°	375.1	372.7	371.4	370.1	368.8	367.4	366.0	364.4	362.7	361.2	359.6
107.5°	465.9	464.7	462.9	461.1	459.3	457.5	456.2	455.4	454.6	453.8	453.0
110°	527.4	526.8	525.2	523.6	522.0	520.5	519.3	518.5	517.7	516.9	516.1



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	586.9	587.1	586.3	585.6	584.8	584.1	583.0	581.5	580.1	578.7	577.3
115°	674.3	673.8	674.1	674.3	674.5	674.9	674.5	673.8	673.0	672.2	671.4
117.5°	763.5	763.6	763.0	762.5	761.8	761.3	760.5	759.4	758.4	757.2	756.2
120°	817.7	817.1	817.4	817.7	817.9	818.2	817.8	816.7	815.7	814.6	813.6
122.5°	872.0	871.6	871.2	870.8	870.5	870.1	869.7	868.9	868.3	867.7	867.0
125°	947.0	946.2	946.7	947.2	947.8	948.2	948.0	947.0	945.9	944.8	943.8
127.5°	1022.9	1023.1	1021.8	1020.6	1019.5	1018.2	1017.5	1017.2	1016.9	1016.7	1016.4
130°	1068.3	1068.0	1067.2	1066.4	1065.6	1064.9	1064.3	1064.1	1063.7	1063.5	1063.3
132.5°	1113.2	1112.9	1111.9	1110.9	1109.9	1108.9	1108.2	1107.7	1107.2	1106.7	1106.2
135°	1174.9	1174.3	1173.3	1172.2	1171.2	1170.1	1169.7	1170.0	1170.2	1170.4	1170.8
137.5°	1234.1	1233.6	1232.4	1231.3	1230.1	1228.9	1228.3	1228.2	1228.0	1228.0	1227.9
140°	1270.7	1269.9	1269.4	1268.8	1268.3	1267.8	1267.3	1266.7	1266.2	1265.7	1265.1
142.5°	1304.9	1304.3	1304.0	1303.7	1303.4	1303.1	1302.4	1301.5	1300.5	1299.5	1298.5
145°	1353.8	1353.5	1353.5	1353.5	1353.5	1353.5	1353.1	1352.3	1351.5	1350.8	1350.0
147.5°	1396.5	1396.3	1396.5	1396.9	1397.1	1397.3	1396.8	1395.3	1393.8	1392.3	1390.8
150°	1424.0	1424.0	1424.3	1424.6	1424.8	1425.1	1424.7	1423.6	1422.5	1421.5	1420.5
152.5°	1447.4	1446.9	1447.4	1447.9	1448.3	1448.9	1448.7	1447.8	1447.0	1446.1	1445.3
155°	1478.8	1477.7	1478.6	1479.4	1480.2	1481.0	1481.2	1481.0	1480.7	1480.4	1480.2
157.5°	1506.2	1504.8	1505.7	1506.6	1507.4	1508.4	1508.9	1509.1	1509.3	1509.4	1509.6
160°	1523.6	1521.9	1522.3	1522.5	1522.7	1523.0	1523.6	1524.4	1525.2	1526.0	1526.8
162.5°	1537.9	1536.3	1536.6	1536.8	1537.1	1537.4	1538.0	1539.1	1540.0	1541.0	1542.1
165°	1557.5	1555.4	1555.4	1555.4	1555.4	1555.4	1556.1	1557.4	1558.8	1560.0	1561.4
167.5°	1572.1	1569.8	1569.9	1570.1	1570.3	1570.4	1571.1	1572.6	1573.9	1575.3	1576.7
170°	1581.4	1579.3	1579.1	1578.8	1578.5	1578.3	1578.9	1580.5	1582.1	1583.7	1585.3
172.5°	1587.1	1585.1	1584.8	1584.5	1584.3	1584.0	1584.7	1586.3	1587.9	1589.4	1591.0
175°	1593.6	1591.3	1591.0	1590.7	1590.5	1590.2	1590.9	1592.4	1594.0	1595.6	1597.2
177.5°	1597.0	1595.3	1594.9	1594.5	1594.0	1593.6	1594.2	1595.6	1597.1	1598.6	1600.1
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	5.4	6.1	7.1	8.2	9.3	9.8	10.1	10.5	10.4	10.5	10.2
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9	28.5
95°	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9	29.5
97.5°	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7	31.8
100°	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1	43.6
102.5°	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5	155.9
105°	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1	377.5
107.5°	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9	467.1
110°	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4	527.9





TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9	586.8
115°	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3	674.9
117.5°	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5	763.4
120°	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7	818.2
122.5°	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0	872.3
125°	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0	947.8
127.5°	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9	1022.8
130°	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3	1068.6
132.5°	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2	1113.5
135°	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9	1175.4
137.5°	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1	1234.8
140°	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7	1271.5
142.5°	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9	1305.5
145°	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8	1354.1
147.5°	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5	1396.7
150°	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0	1424.0
152.5°	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4	1447.8
155°	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8	1479.9
157.5°	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2	1507.5
160°	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6	1525.2
162.5°	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9	1539.5
165°	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5	1559.6
167.5°	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1	1574.5
170°	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4	1583.6
172.5°	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1	1589.3
175°	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6	1596.0
177.5°	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0	1598.7
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	10.7	10.9	10.9	10.8	10.7	10.8	10.5
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P332739-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)