

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332740-927

Luminaire Tested: **S124DIW-S350D1560U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332740-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5538.3 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19				
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16				
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12				
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9				
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	13	11	10	7				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7				
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1037	1074	2566	1074



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	0.8
10°-20°	135.9	2.5
20°-30°	215.5	3.9
30°-40°	239.8	4.3
40°-50°	218.3	3.9
50°-60°	178.4	3.2
60°-70°	127.4	2.3
70°-80°	70.1	1.3
80°-90°	23.8	0.4
90°-100°	101.9	1.8
100°-110°	301.8	5.4
110°-120°	512.2	9.2
120°-130°	675.4	12.2
130°-140°	758.5	13.7
140°-150°	745.3	13.5
150°-160°	626.9	11.3
160°-170°	417.1	7.5
170°-180°	146.1	2.6
0°-30°	395.5	7.1
0°-40°	635.3	11.5
0°-60°	1032.1	18.6
0°-90°	1253.3	22.6
90°-120°	915.8	16.5
90°-150°	3095.0	55.9
90°-180°	4285.0	77.4
0°-180°	5538.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	15
90°	36	4	36	4	36	19
95°	94	72	94	72	94	98
105°	291	278	291	278	291	307
115°	516	521	516	521	516	510
125°	752	758	752	758	752	671
135°	980	978	980	978	980	756
145°	1190	1188	1190	1188	1190	744
155°	1360	1362	1360	1362	1360	626
165°	1479	1482	1479	1482	1479	416
175°	1535	1542	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	10.5	10.8	10.7	10.8	10.9	10.9	10.7	10.2	10.5	10.4	10.5
90°	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5	27.9	26.3	24.2
92.5°	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2	48.2	47.3	45.8
95°	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4	91.6	90.8	89.0
97.5°	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5	144.5	143.5	141.4
100°	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8	183.3	182.8	180.4
102.5°	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3	223.6	222.9	220.7
105°	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9	285.1	284.3	283.2
107.5°	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4	351.6	350.9	350.8
110°	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7	397.2	397.8	398.0



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3	444.5	444.6	445.0
115°	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8	518.2	518.4	519.0
117.5°	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5	589.4	590.3	590.7
120°	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4	637.7	639.1	639.8
122.5°	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0	686.0	686.8	687.2
125°	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2	756.8	757.3	757.6
127.5°	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3	824.8	825.4	825.9
130°	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1	872.7	873.1	873.1
132.5°	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0	917.6	918.1	918.3
135°	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4	984.9	985.5	985.5
137.5°	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6	1050.2	1050.9	1050.5
140°	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4	1092.7	1093.0	1093.0
142.5°	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0	1133.1	1133.1	1133.3
145°	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3	1249.4	1249.7	1249.9
150°	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8	1316.2	1315.6	1315.4
155°	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5	1360.8
157.5°	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0	1402.2	1401.4	1401.4
160°	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8	1427.0	1426.2	1426.5
162.5°	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1	1448.7	1447.2	1447.5
165°	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6	1478.0	1476.4	1476.9
167.5°	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4	1502.8	1501.3	1501.2
170°	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8	1516.2	1514.6	1514.3
172.5°	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8	1526.0	1524.2	1524.1
175°	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9	1535.2
177.5°	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6	1543.1	1541.6	1541.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	10.1	9.8	9.3	8.2	7.1	6.1	5.4	4.6	5.4	6.1	6.8
90°	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6	6.5	9.4	12.4
92.5°	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6	28.9	32.2	35.6
95°	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7	74.1	76.4	78.8
97.5°	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2	127.1	129.0	130.9
100°	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2	168.3	169.4	170.4
102.5°	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2	211.6	212.1	212.5
105°	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3	278.6	278.8	279.1
107.5°	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8	349.1	349.4	349.7
110°	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6	397.1	397.6	398.2



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2	446.4	446.5	446.6
115°	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8	520.8	520.8	520.8
117.5°	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0	591.2	591.4	591.7
120°	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9	638.9	640.0	641.0
122.5°	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6	687.0	687.5	687.9
125°	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5	758.5	758.5	758.5
127.5°	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7	824.5	825.3	826.1
130°	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6	870.4	871.2	872.0
132.5°	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4	917.0	917.6	918.1
135°	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3	979.9	981.4	983.1
137.5°	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7	1046.4	1047.1	1047.9
140°	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6	1091.1	1091.6	1092.2
142.5°	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6	1132.2	1132.7	1133.2
145°	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5	1189.5	1190.6	1191.7
147.5°	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9	1246.2	1247.4	1248.7
150°	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3	1280.3	1281.4	1282.5
152.5°	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8	1312.4	1313.0	1313.7
155°	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7	1403.3	1402.8	1402.3
160°	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6	1428.3	1428.1	1427.8
162.5°	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5	1450.9	1450.2	1449.5
165°	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3	1481.5	1480.7	1480.0
167.5°	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0	1504.9	1503.8	1502.7
170°	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4	1518.1	1516.7	1515.4
172.5°	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9	1527.8	1526.7	1525.6
175°	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1	1540.7	1539.4	1538.1
177.5°	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3	1545.3	1544.3	1543.2
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	7.8	8.3	9.3	10.1	11.0	12.1	12.8	14.7	15.7	16.7	18.3
90°	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5	31.1	32.6	33.7
92.5°	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2	50.1	51.1	51.7
95°	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4	93.2	94.0	94.3
97.5°	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5	146.5	147.4	147.9
100°	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8	184.3	184.9	185.1
102.5°	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3	225.1	225.9	226.3
105°	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9	286.7	287.5	288.3
107.5°	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4	353.2	353.9	354.3
110°	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7	396.2	395.6	395.8



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3	444.3	444.2	444.2
115°	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8	517.6	517.4	517.1
117.5°	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5	587.6	586.7	586.0
120°	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4	635.1	633.7	633.3
122.5°	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0	684.1	683.3	682.3
125°	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2	755.7	755.2	754.6
127.5°	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3	823.8	823.2	822.8
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1	871.6	871.0	870.2
132.5°	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0	916.5	915.9	915.4
135°	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4	983.9	983.3	982.6
137.5°	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6	1048.8	1048.1	1047.9
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4	1092.2	1091.9	1091.6
142.5°	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0	1132.9	1132.9	1132.8
145°	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.9
147.5°	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3	1249.0	1248.8	1248.6
150°	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8	1317.5	1318.1	1318.1
155°	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8
157.5°	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0	1403.7	1404.5	1404.5
160°	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8	1428.6	1429.4	1429.1
162.5°	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1	1451.5	1452.9	1453.0
165°	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6	1481.1	1482.7	1483.0
167.5°	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4	1506.0	1507.6	1507.6
170°	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8	1519.4	1521.0	1520.8
172.5°	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8	1529.5	1531.4	1531.4
175°	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4
177.5°	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6	1546.0	1547.5	1547.4
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	18.9	19.1	19.6	20.0	19.6	19.1	18.9	18.3	16.7	15.7	14.7
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	32.6	31.1	29.5
92.5°	52.0	52.4	52.7	53.0	52.7	52.4	52.0	51.7	51.1	50.1	49.2
95°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.0	93.2	92.4
97.5°	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.9	147.4	146.5	145.5
100°	185.1	185.1	185.1	185.1	185.1	185.1	185.1	185.1	184.9	184.3	183.8
102.5°	226.6	226.8	227.0	227.2	227.0	226.8	226.6	226.3	225.9	225.1	224.3
105°	289.1	289.9	290.7	291.4	290.7	289.9	289.1	288.3	287.5	286.7	285.9
107.5°	354.2	354.2	354.1	354.0	354.1	354.2	354.2	354.3	353.9	353.2	352.4
110°	396.6	397.4	398.2	398.9	398.2	397.4	396.6	395.8	395.6	396.2	396.7



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	444.5	444.7	444.8	444.7	444.5	444.3	444.2	444.2	444.3	444.3
115°	516.8	516.6	516.3	516.0	516.3	516.6	516.8	517.1	517.4	517.6	517.8
117.5°	585.4	584.9	584.4	583.8	584.4	584.9	585.4	586.0	586.7	587.6	588.5
120°	633.9	634.4	634.9	635.5	634.9	634.4	633.9	633.3	633.7	635.1	636.4
122.5°	681.4	680.4	679.5	678.5	679.5	680.4	681.4	682.3	683.3	684.1	685.0
125°	754.1	753.6	753.0	752.5	753.0	753.6	754.1	754.6	755.2	755.7	756.2
127.5°	822.4	822.0	821.5	821.1	821.5	822.0	822.4	822.8	823.2	823.8	824.3
130°	869.2	868.2	867.0	866.0	867.0	868.2	869.2	870.2	871.0	871.6	872.1
132.5°	915.0	914.7	914.2	913.8	914.2	914.7	915.0	915.4	915.9	916.5	917.0
135°	981.8	981.0	980.2	979.5	980.2	981.0	981.8	982.6	983.3	983.9	984.4
137.5°	1048.1	1048.2	1048.4	1048.5	1048.4	1048.2	1048.1	1047.9	1048.1	1048.8	1049.6
140°	1091.4	1091.1	1090.8	1090.6	1090.8	1091.1	1091.4	1091.6	1091.9	1092.2	1092.4
142.5°	1132.7	1132.7	1132.7	1132.6	1132.7	1132.7	1132.7	1132.8	1132.9	1132.9	1133.0
145°	1192.1	1191.3	1190.5	1189.7	1190.5	1191.3	1192.1	1192.9	1193.4	1193.7	1194.0
147.5°	1248.3	1248.1	1247.8	1247.5	1247.8	1248.1	1248.3	1248.6	1248.8	1249.0	1249.3
150°	1283.7	1283.4	1283.2	1282.9	1283.2	1283.4	1283.7	1284.0	1284.0	1284.0	1284.0
152.5°	1317.4	1316.8	1316.1	1315.3	1316.1	1316.8	1317.4	1318.1	1318.1	1317.5	1316.8
155°	1363.7	1362.6	1361.6	1360.5	1361.6	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6
157.5°	1403.6	1402.7	1401.8	1400.9	1401.8	1402.7	1403.6	1404.5	1404.5	1403.7	1403.0
160°	1427.8	1426.5	1425.1	1423.8	1425.1	1426.5	1427.8	1429.1	1429.4	1428.6	1427.8
162.5°	1451.7	1450.4	1449.1	1447.7	1449.1	1450.4	1451.7	1453.0	1452.9	1451.5	1450.1
165°	1481.9	1480.9	1479.8	1478.8	1479.8	1480.9	1481.9	1483.0	1482.7	1481.1	1479.6
167.5°	1505.9	1504.3	1502.6	1500.9	1502.6	1504.3	1505.9	1507.6	1507.6	1506.0	1504.4
170°	1519.0	1517.1	1515.3	1513.4	1515.3	1517.1	1519.0	1520.8	1521.0	1519.4	1517.8
172.5°	1529.5	1527.6	1525.7	1523.9	1525.7	1527.6	1529.5	1531.4	1531.4	1529.5	1527.8
175°	1540.5	1538.7	1536.8	1534.9	1536.8	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7
177.5°	1545.7	1544.0	1542.4	1540.6	1542.4	1544.0	1545.7	1547.4	1547.5	1546.0	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	12.8	12.1	11.0	10.1	9.3	8.3	7.8	6.8	6.1	5.4	4.6
90°	27.9	26.3	24.2	22.0	19.9	17.8	15.3	12.4	9.4	6.5	3.6
92.5°	48.2	47.3	45.8	44.4	42.9	41.4	39.0	35.6	32.2	28.9	25.6
95°	91.6	90.8	89.0	87.1	85.2	83.3	81.2	78.8	76.4	74.1	71.7
97.5°	144.5	143.5	141.4	139.2	137.0	134.9	132.8	130.9	129.0	127.1	125.2
100°	183.3	182.8	180.4	178.0	175.6	173.2	171.5	170.4	169.4	168.3	167.2
102.5°	223.6	222.9	220.7	218.6	216.3	214.2	212.9	212.5	212.1	211.6	211.2
105°	285.1	284.3	283.2	282.2	281.1	280.0	279.4	279.1	278.8	278.6	278.3
107.5°	351.6	350.9	350.8	350.6	350.5	350.3	350.1	349.7	349.4	349.1	348.8
110°	397.2	397.8	398.0	398.3	398.5	398.9	398.7	398.2	397.6	397.1	396.6



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	444.5	444.6	445.0	445.5	446.0	446.5	446.7	446.6	446.5	446.4	446.2
115°	518.2	518.4	519.0	519.4	520.0	520.5	520.8	520.8	520.8	520.8	520.8
117.5°	589.4	590.3	590.7	591.0	591.4	591.8	591.9	591.7	591.4	591.2	591.0
120°	637.7	639.1	639.8	640.6	641.4	642.2	642.1	641.0	640.0	638.9	637.9
122.5°	686.0	686.8	687.2	687.5	687.9	688.3	688.2	687.9	687.5	687.0	686.6
125°	756.8	757.3	757.6	757.8	758.1	758.4	758.5	758.5	758.5	758.5	758.5
127.5°	824.8	825.4	825.9	826.2	826.6	827.1	826.9	826.1	825.3	824.5	823.7
130°	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.0	871.2	870.4	869.6
132.5°	917.6	918.1	918.3	918.5	918.7	918.9	918.8	918.1	917.6	917.0	916.4
135°	984.9	985.5	985.5	985.5	985.5	985.5	984.7	983.1	981.4	979.9	978.3
137.5°	1050.2	1050.9	1050.5	1050.0	1049.6	1049.2	1048.6	1047.9	1047.1	1046.4	1045.7
140°	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.2	1091.6	1091.1	1090.6
142.5°	1133.1	1133.1	1133.3	1133.5	1133.7	1133.9	1133.8	1133.2	1132.7	1132.2	1131.6
145°	1194.2	1194.5	1194.2	1194.0	1193.7	1193.4	1192.8	1191.7	1190.6	1189.5	1188.5
147.5°	1249.4	1249.7	1249.9	1250.1	1250.3	1250.5	1250.0	1248.7	1247.4	1246.2	1244.9
150°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1283.6	1282.5	1281.4	1280.3	1279.3
152.5°	1316.2	1315.6	1315.4	1315.2	1314.9	1314.8	1314.3	1313.7	1313.0	1312.4	1311.8
155°	1361.6	1360.5	1360.8	1361.0	1361.3	1361.6	1361.7	1361.7	1361.7	1361.7	1361.7
157.5°	1402.2	1401.4	1401.4	1401.4	1401.5	1401.6	1401.8	1402.3	1402.8	1403.3	1403.7
160°	1427.0	1426.2	1426.5	1426.7	1427.0	1427.3	1427.5	1427.8	1428.1	1428.3	1428.6
162.5°	1448.7	1447.2	1447.5	1447.8	1448.0	1448.3	1448.7	1449.5	1450.2	1450.9	1451.5
165°	1478.0	1476.4	1476.9	1477.4	1478.0	1478.5	1479.2	1480.0	1480.7	1481.5	1482.3
167.5°	1502.8	1501.3	1501.2	1501.1	1501.1	1501.0	1501.6	1502.7	1503.8	1504.9	1506.0
170°	1516.2	1514.6	1514.3	1514.1	1513.8	1513.5	1514.1	1515.4	1516.7	1518.1	1519.4
172.5°	1526.0	1524.2	1524.1	1524.1	1524.0	1523.9	1524.5	1525.6	1526.7	1527.8	1528.9
175°	1536.8	1534.9	1535.2	1535.4	1535.7	1536.0	1536.8	1538.1	1539.4	1540.7	1542.1
177.5°	1543.1	1541.6	1541.6	1541.6	1541.6	1541.6	1542.1	1543.2	1544.3	1545.3	1546.3
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	5.4	6.1	7.1	8.2	9.3	9.8	10.1	10.5	10.4	10.5	10.2
90°	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9	29.5
92.5°	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2	49.2
95°	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6	92.4
97.5°	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5	145.5
100°	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3	183.8
102.5°	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6	224.3
105°	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1	285.9
107.5°	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6	352.4
110°	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2	396.7



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5	444.3
115°	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2	517.8
117.5°	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4	588.5
120°	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7	636.4
122.5°	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0	685.0
125°	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8	756.2
127.5°	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8	824.3
130°	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7	872.1
132.5°	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6	917.0
135°	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9	984.4
137.5°	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2	1049.6
140°	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7	1092.4
142.5°	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1	1133.0
145°	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2	1194.0
147.5°	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4	1249.3
150°	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2	1316.8
155°	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6	1362.6
157.5°	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2	1403.0
160°	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0	1427.8
162.5°	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7	1450.1
165°	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0	1479.6
167.5°	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8	1504.4
170°	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2	1517.8
172.5°	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0	1527.8
175°	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8	1538.7
177.5°	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1	1544.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	10.7	10.9	10.9	10.8	10.7	10.8	10.5
90°	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.2	395.6	395.8	396.6	397.4	398.2	398.9



TEST NUMBER: P332740-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)