

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332743-927

Luminaire Tested: **S124DIW-S350D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332743-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6146.2 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	46	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	0.7
10°-20°	124.2	2.0
20°-30°	182.8	3.0
30°-40°	212.5	3.5
40°-50°	212.5	3.5
50°-60°	185.9	3.0
60°-70°	138.0	2.2
70°-80°	78.4	1.3
80°-90°	27.2	0.4
90°-100°	54.6	0.9
100°-110°	348.3	5.7
110°-120°	666.3	10.8
120°-130°	845.9	13.8
130°-140°	905.0	14.7
140°-150°	846.3	13.8
150°-160°	682.5	11.1
160°-170°	440.2	7.2
170°-180°	151.7	2.5
0°-30°	351.0	5.7
0°-40°	563.5	9.2
0°-60°	961.8	15.6
0°-90°	1205.5	19.6
90°-120°	1069.3	17.4
90°-150°	3666.4	59.7
90°-180°	4941.0	80.4
0°-180°	6146.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	4	17	26	33	36	4
95°	66	27	26	33	35	84
105°	360	367	373	380	340	376
115°	671	675	674	676	676	660
125°	944	948	946	950	951	842
135°	1171	1170	1174	1177	1179	902
145°	1350	1353	1354	1355	1357	843
155°	1480	1481	1478	1482	1479	682
165°	1561	1556	1555	1564	1554	441
175°	1597	1591	1591	1601	1588	152
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.6	9.0	9.6	10.1	10.6	11.0	11.4	11.7	12.1	12.4	12.8
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	15.1	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9
95°	65.7	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9
97.5°	139.5	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7
100°	195.9	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1
102.5°	259.0	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5
105°	359.6	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1
107.5°	453.0	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9
110°	516.1	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.3	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9
115°	671.4	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3
117.5°	756.2	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5
120°	813.6	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7
122.5°	867.0	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0
125°	943.8	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0
127.5°	1016.4	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9
130°	1063.3	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3
132.5°	1106.2	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2
135°	1170.8	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9
137.5°	1227.9	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1
140°	1265.1	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7
142.5°	1298.5	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9
145°	1350.0	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8
147.5°	1390.8	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5
150°	1420.5	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0
152.5°	1445.3	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4
155°	1480.2	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8
157.5°	1509.6	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2
160°	1526.8	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6
162.5°	1542.1	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9
165°	1561.4	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5
167.5°	1576.7	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1
170°	1585.3	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4
172.5°	1591.0	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1
175°	1597.2	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6
177.5°	1600.1	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	13.1	13.4	13.7	13.9	14.0	14.2	14.3	14.3
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	28.5	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	29.5	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	31.8	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	43.6	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	155.9	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	377.5	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	467.1	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	527.9	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P332743-927

CATALOG NUMBER: S124DIW-S350D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	586.8	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	674.9	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.4	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.3	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	947.8	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.8	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.6	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.5	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.4	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1234.8	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1271.5	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1305.5	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.1	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.7	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1447.8	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1479.9	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1539.5	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1559.6	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1574.5	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1583.6	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1589.3	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1596.0	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1598.7	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)