

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332139-840

Luminaire Tested: **S123DIW-S560D1320U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332139-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7034.0 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51	45	42	40	33	31	30	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	24	21	20	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8593	8593	8593	8593
5°	10247	8630	7648	8630
10°	12826	8587	6908	8587
15°	15731	8517	6430	8517
20°	18741	8409	6123	8409
25°	19899	8278	6055	8278
30°	17056	8182	6087	8182
35°	11862	8046	6150	8046
40°	8934	7886	6131	7886
45°	7419	7648	6052	7648
50°	6646	7164	5998	7164
55°	6212	6641	5923	6641
60°	5828	6097	5862	6097
65°	5476	5555	5675	5555
70°	5136	4941	5404	4941
75°	4600	4325	4957	4325
80°	4023	3552	4271	3552
85°	3149	2581	2865	2581



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	1.1
10°-20°	252.2	3.6
20°-30°	423.2	6.0
30°-40°	479.2	6.8
40°-50°	429.7	6.1
50°-60°	346.8	4.9
60°-70°	241.7	3.4
70°-80°	127.0	1.8
80°-90°	36.0	0.5
90°-100°	108.6	1.5
100°-110°	325.1	4.6
110°-120°	553.0	7.9
120°-130°	727.3	10.3
130°-140°	817.5	11.6
140°-150°	803.6	11.4
150°-160°	676.5	9.6
160°-170°	450.3	6.4
170°-180°	157.7	2.2
0°-30°	754.0	10.7
0°-40°	1233.2	17.5
0°-60°	2009.7	28.6
0°-90°	2414.4	34.3
90°-120°	986.7	14.0
90°-150°	3335.1	47.4
90°-180°	4620.0	65.7
0°-180°	7034.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	948	799	708	799	948	98
15°	1412	764	577	764	1412	408
25°	1676	697	510	697	1676	735
35°	903	612	468	612	903	586
45°	487	502	398	502	487	386
55°	331	354	316	354	331	297
65°	215	218	223	218	215	214
75°	111	104	119	104	111	118
85°	26	21	23	21	26	31
90°	39	1	39	1	39	20
95°	102	77	102	77	102	105
105°	312	295	312	295	312	331
115°	558	557	558	557	558	552
125°	806	815	806	815	806	720
135°	1056	1057	1056	1057	1056	812
145°	1282	1282	1282	1282	1282	800
155°	1466	1468	1466	1468	1466	675
165°	1594	1599	1594	1599	1594	450
175°	1657	1663	1657	1663	1657	157
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	847.2	846.6	845.1	846.3	843.7	840.4	840.1	837.0	828.0	827.4	825.0
5°	948.4	945.2	944.9	944.5	939.1	931.7	917.8	916.7	898.1	888.8	877.6
7.5°	1079.4	1081.1	1075.4	1070.5	1053.9	1043.0	1028.0	1009.0	986.1	963.0	947.6
10°	1173.5	1186.2	1170.3	1159.5	1149.5	1130.5	1108.5	1081.1	1053.6	1021.5	997.1
12.5°	1274.3	1280.6	1277.5	1267.2	1251.6	1222.7	1183.7	1153.5	1128.1	1074.7	1053.1
15°	1411.7	1435.3	1420.3	1385.4	1386.2	1358.8	1307.7	1251.6	1221.8	1175.0	1111.2
17.5°	1558.1	1561.0	1554.6	1525.6	1506.2	1468.5	1421.4	1367.7	1307.3	1250.7	1183.0
20°	1636.1	1633.8	1620.2	1605.1	1571.9	1542.5	1491.0	1431.1	1353.7	1298.0	1224.2
22.5°	1679.4	1675.5	1669.1	1656.5	1628.8	1597.2	1551.1	1485.5	1411.9	1335.1	1249.8
25°	1675.5	1680.5	1681.3	1677.8	1668.2	1649.2	1612.9	1560.6	1487.1	1388.6	1299.6
27.5°	1523.9	1531.0	1551.7	1570.0	1590.5	1611.3	1608.6	1582.7	1528.3	1443.1	1334.3
30°	1372.3	1356.8	1395.1	1443.4	1476.3	1534.3	1566.8	1568.7	1538.2	1465.1	1359.1
32.5°	1161.8	1178.9	1195.8	1255.3	1327.2	1392.3	1456.9	1509.0	1515.0	1466.3	1373.6
35°	902.7	924.0	954.9	985.9	1063.3	1129.7	1243.4	1342.5	1421.4	1431.8	1374.9
37.5°	727.4	738.0	757.5	788.5	839.1	918.1	1006.0	1131.1	1245.5	1330.5	1334.2
40°	635.8	638.9	661.0	684.6	725.6	790.5	869.9	980.5	1117.4	1236.2	1285.7
42.5°	567.1	574.0	583.3	606.0	638.6	687.5	761.2	852.7	978.2	1114.8	1211.6
45°	487.4	495.0	500.9	515.9	539.2	572.0	623.5	707.0	802.5	943.7	1074.1
47.5°	434.5	435.2	439.5	450.9	466.7	491.4	527.8	581.4	669.1	783.6	917.5
50°	396.9	403.0	404.6	413.4	425.9	444.0	474.2	519.8	591.8	692.4	815.4
52.5°	370.2	372.0	376.4	382.8	393.6	407.8	433.9	469.7	526.1	611.9	725.0
55°	331.0	331.0	335.4	340.3	346.6	359.3	376.7	403.0	446.0	512.5	606.1
57.5°	294.9	296.8	299.8	301.3	306.6	315.1	329.6	349.6	381.6	432.8	507.3
60°	270.7	274.2	273.9	276.9	281.6	288.1	300.5	316.8	345.4	386.4	449.1
62.5°	249.7	249.4	249.4	253.1	257.7	264.0	272.1	286.1	310.4	346.8	400.1
65°	215.0	214.3	217.0	219.3	220.9	225.5	231.7	244.1	260.3	287.4	328.7
67.5°	184.3	182.0	183.5	184.3	186.9	190.6	196.3	204.0	216.9	238.6	269.8
70°	163.2	161.3	160.9	161.7	164.0	166.7	171.0	178.3	190.3	207.7	230.6
72.5°	141.6	140.3	140.2	141.9	143.0	144.7	147.7	154.5	164.0	177.0	198.3
75°	110.6	110.6	110.6	111.0	112.2	113.7	116.0	119.5	126.8	136.1	150.5
77.5°	82.9	82.8	82.4	82.3	84.0	84.7	85.2	88.5	92.6	98.9	109.3
80°	64.9	63.0	63.8	64.9	65.7	66.1	67.3	68.1	71.6	75.0	82.4
82.5°	48.3	46.7	46.8	48.6	48.8	49.1	50.3	51.4	52.7	55.8	59.8
85°	25.5	25.5	26.0	26.0	26.3	26.0	27.1	27.5	27.5	29.4	31.7
87.5°	17.2	16.4	16.6	16.8	16.4	16.5	16.6	16.7	16.8	16.8	16.4
90°	39.3	38.7	38.2	37.6	37.0	36.1	34.9	33.7	32.6	31.4	27.7
92.5°	52.9	53.2	53.6	53.9	54.3	54.0	53.1	52.1	51.2	50.3	48.2
95°	102.2	102.2	102.2	102.2	102.2	101.6	100.4	99.3	98.1	96.9	94.6
97.5°	157.1	157.3	157.4	157.5	157.6	157.0	155.7	154.3	153.0	151.7	150.0
100°	199.0	198.5	197.9	197.3	196.7	196.0	195.1	194.3	193.4	192.6	191.1
102.5°	242.1	242.2	242.3	242.4	242.5	242.2	241.3	240.3	239.5	238.6	236.7
105°	311.7	311.1	310.5	310.0	309.4	309.1	309.1	309.1	309.1	309.1	306.5
107.5°	384.3	384.7	385.0	385.4	385.7	385.4	384.5	383.5	382.6	381.6	380.6
110°	433.5	434.1	434.7	435.3	435.9	435.6	434.4	433.2	432.1	430.9	430.3



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.9	486.0	486.1	486.3	486.4	485.7	484.3	482.9	481.6	480.2	480.1
115°	558.0	558.3	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0	558.6
117.5°	631.1	631.9	632.7	633.5	634.3	634.7	634.8	634.9	634.9	635.0	635.7
120°	682.4	683.0	683.6	684.2	684.7	685.2	685.5	685.7	686.0	686.3	687.8
122.5°	731.6	732.5	733.3	734.1	734.9	735.7	736.4	737.2	737.9	738.7	739.4
125°	805.5	806.7	807.8	809.0	810.2	811.3	812.5	813.6	814.9	816.0	816.6
127.5°	879.1	880.5	881.8	883.1	884.4	886.0	887.6	889.2	890.8	892.5	893.1
130°	927.4	929.4	931.4	933.4	935.4	937.1	938.3	939.4	940.6	941.7	942.6
132.5°	977.7	979.2	980.8	982.3	983.9	985.4	986.7	988.2	989.6	991.0	991.6
135°	1055.7	1056.2	1056.8	1057.4	1058.0	1058.8	1060.1	1061.2	1062.4	1063.5	1063.8
137.5°	1124.6	1125.7	1126.8	1127.9	1129.0	1130.1	1131.4	1132.6	1133.8	1135.1	1134.3
140°	1169.6	1171.6	1173.7	1175.8	1177.8	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.8	1217.3	1218.9	1220.4	1222.0	1222.9	1223.2	1223.6	1223.9	1224.2	1223.6
145°	1282.2	1283.4	1284.5	1285.8	1287.0	1287.7	1288.0	1288.2	1288.5	1288.8	1288.0
147.5°	1341.5	1343.2	1344.9	1346.8	1348.5	1349.3	1349.3	1349.3	1349.3	1349.3	1348.5
150°	1379.2	1380.9	1382.7	1384.4	1386.1	1387.0	1387.0	1387.0	1387.0	1387.0	1386.4
152.5°	1415.8	1417.3	1418.9	1420.4	1421.9	1422.4	1422.0	1421.5	1421.1	1420.6	1420.3
155°	1465.6	1467.6	1469.8	1471.8	1473.8	1474.2	1473.1	1471.9	1470.8	1469.6	1469.3
157.5°	1511.0	1512.6	1514.2	1515.8	1517.4	1517.7	1516.4	1515.2	1514.0	1512.8	1512.6
160°	1540.2	1541.5	1542.7	1543.8	1545.0	1544.8	1543.4	1541.9	1540.4	1538.9	1538.9
162.5°	1562.3	1564.2	1566.0	1567.9	1569.7	1569.9	1568.5	1567.0	1565.6	1564.1	1563.9
165°	1594.0	1596.0	1598.1	1600.1	1602.2	1602.3	1600.5	1598.8	1597.0	1595.3	1595.3
167.5°	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9	1620.7
170°	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6	1634.6
172.5°	1645.1	1647.1	1649.1	1651.2	1653.3	1653.4	1651.5	1649.7	1647.9	1646.1	1646.1
175°	1656.9	1658.9	1660.9	1662.9	1665.0	1665.2	1663.4	1661.6	1659.9	1658.2	1658.2
177.5°	1663.1	1664.8	1666.4	1668.0	1669.7	1669.8	1668.4	1667.0	1665.6	1664.2	1664.2
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	823.0	820.6	818.1	813.7	810.0	804.8	803.2	801.4	795.9	790.8	787.2
5°	873.3	864.0	850.5	838.1	828.1	814.6	806.8	798.7	787.1	776.7	768.1
7.5°	925.9	907.7	886.7	863.9	842.7	822.2	805.8	791.1	774.9	759.4	747.5
10°	967.8	941.4	912.0	880.3	853.2	826.9	804.9	785.6	764.7	746.5	731.3
12.5°	1015.3	976.3	935.8	897.3	865.3	828.8	802.1	777.5	753.9	732.0	715.0
15°	1071.8	1022.3	974.3	921.3	872.5	826.9	795.2	764.3	736.8	714.4	692.7
17.5°	1123.1	1067.0	1003.8	939.4	880.6	826.5	782.0	747.1	712.8	685.3	663.7
20°	1152.2	1088.3	1016.8	949.9	884.9	824.6	775.9	734.1	697.0	667.9	643.6
22.5°	1177.3	1102.6	1028.5	957.0	884.6	819.6	764.5	721.4	681.2	652.8	626.9
25°	1203.3	1113.9	1039.7	955.7	874.8	807.6	745.7	697.0	656.7	623.5	596.8
27.5°	1225.6	1113.2	1025.0	934.7	859.6	792.1	726.1	673.8	631.1	594.9	567.8
30°	1240.4	1114.7	1009.9	920.5	844.8	775.1	710.8	658.3	613.4	576.6	551.2
32.5°	1249.7	1113.8	995.9	900.7	821.2	759.6	694.5	640.1	593.9	557.8	533.2
35°	1255.1	1106.9	972.0	859.8	783.3	723.3	668.7	612.3	563.9	530.3	502.4
37.5°	1244.3	1092.7	944.1	820.3	736.5	677.5	631.6	583.5	537.2	500.2	476.2
40°	1227.2	1083.4	922.4	792.5	704.3	647.4	608.4	561.2	515.5	480.4	458.0
42.5°	1194.8	1064.5	898.7	761.5	670.9	614.0	578.0	538.7	495.4	462.4	440.0
45°	1115.5	1023.4	862.9	715.2	621.6	562.8	531.1	502.4	463.3	431.2	411.9
47.5°	1005.4	961.6	811.2	666.2	570.1	513.5	480.5	457.5	428.9	403.0	384.5
50°	929.1	910.9	776.3	632.8	535.6	480.4	448.7	427.8	407.3	381.3	364.4
52.5°	840.8	852.0	735.4	598.1	500.7	446.4	416.5	399.9	381.3	360.0	345.2
55°	716.7	757.3	664.9	540.0	448.7	396.9	368.6	353.9	343.1	327.2	314.5
57.5°	600.5	652.1	588.5	480.0	397.5	352.8	325.8	309.7	302.8	294.5	284.5
60°	531.4	582.5	534.1	439.8	363.1	320.6	296.7	283.2	276.2	270.3	261.9
62.5°	469.9	521.5	480.9	398.9	329.4	290.0	269.1	255.9	250.4	247.4	240.1
65°	385.3	429.7	402.6	335.4	281.1	246.4	227.4	218.1	213.1	212.0	207.3
67.5°	313.6	347.4	327.7	278.1	235.5	205.4	189.3	181.5	177.6	177.2	173.7
70°	266.5	298.2	283.2	238.2	201.5	177.9	164.0	157.0	154.7	154.3	152.4
72.5°	229.9	252.1	240.1	202.7	174.3	152.9	142.6	135.3	132.7	133.3	132.0
75°	170.2	186.8	179.9	153.9	131.1	117.1	108.7	104.0	101.7	102.9	101.3
77.5°	122.5	133.0	126.7	108.8	94.7	84.6	78.4	75.5	73.4	73.3	72.6
80°	92.4	98.7	95.1	84.3	72.7	64.2	59.2	57.3	56.0	55.7	55.3
82.5°	65.8	71.1	67.0	59.6	51.7	46.6	43.7	41.2	40.3	40.5	40.2
85°	33.2	35.2	33.6	29.0	26.0	23.6	22.0	20.9	20.1	20.5	19.7
87.5°	16.3	15.8	14.1	12.2	11.0	9.5	8.9	7.7	7.7	8.3	8.5
90°	23.8	20.1	16.3	12.9	10.0	7.2	4.2	1.3	4.2	7.2	10.0
92.5°	45.9	43.8	41.7	39.6	37.7	35.6	33.6	31.7	33.6	35.6	37.7
95°	92.3	90.0	87.7	85.4	83.4	81.4	79.3	77.3	79.3	81.4	83.4
97.5°	148.2	146.6	144.9	143.3	141.8	140.3	138.8	137.2	138.8	140.3	141.8
100°	189.7	188.1	186.7	185.1	183.4	181.6	179.9	178.1	179.9	181.6	183.4
102.5°	234.8	232.9	231.0	229.4	228.4	227.4	226.3	225.3	226.3	227.4	228.4
105°	303.9	301.2	298.6	297.0	296.4	295.9	295.3	294.7	295.3	295.9	296.4
107.5°	379.6	378.5	377.5	376.8	376.5	376.1	375.8	375.4	375.8	376.1	376.5
110°	429.8	429.2	428.6	428.0	427.4	426.9	426.3	425.7	426.3	426.9	427.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	479.9	479.8	479.7	479.5	479.1	478.8	478.4	478.1	478.4	478.8	479.1
115°	559.2	559.7	560.3	560.2	559.3	558.4	557.5	556.6	557.5	558.4	559.3
117.5°	636.5	637.2	638.0	638.1	637.5	636.9	636.3	635.8	636.3	636.9	637.5
120°	689.2	690.6	692.2	692.0	690.2	688.5	686.7	685.0	686.7	688.5	690.2
122.5°	740.2	740.9	741.7	741.4	740.2	738.9	737.6	736.4	737.6	738.9	740.2
125°	817.2	817.7	818.3	818.2	817.3	816.4	815.6	814.7	815.6	816.4	817.3
127.5°	893.7	894.4	895.0	894.4	892.5	890.7	888.9	887.0	888.9	890.7	892.5
130°	943.5	944.3	945.2	944.5	942.2	939.9	937.5	935.1	937.5	939.9	942.2
132.5°	992.3	992.9	993.5	992.7	990.4	988.1	985.7	983.4	985.7	988.1	990.4
135°	1064.1	1064.4	1064.7	1064.0	1062.2	1060.5	1058.7	1057.0	1058.7	1060.5	1062.2
137.5°	1133.6	1132.8	1132.1	1130.9	1129.4	1128.0	1126.5	1125.1	1126.5	1128.0	1129.4
140°	1179.5	1179.2	1178.9	1178.1	1176.6	1175.2	1173.7	1172.3	1173.7	1175.2	1176.6
142.5°	1223.0	1222.5	1222.0	1221.0	1219.6	1218.1	1216.7	1215.2	1216.7	1218.1	1219.6
145°	1287.1	1286.2	1285.4	1284.5	1284.0	1283.4	1282.8	1282.2	1282.8	1283.4	1284.0
147.5°	1347.7	1346.9	1346.0	1345.1	1344.1	1343.0	1342.0	1340.9	1342.0	1343.0	1344.1
150°	1385.8	1385.3	1384.7	1384.1	1383.5	1383.0	1382.4	1381.8	1382.4	1383.0	1383.5
152.5°	1419.9	1419.6	1419.2	1418.6	1417.7	1416.9	1416.1	1415.3	1416.1	1416.9	1417.7
155°	1468.9	1468.6	1468.4	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2
157.5°	1512.3	1512.1	1511.9	1511.9	1512.3	1512.6	1513.0	1513.3	1513.0	1512.6	1512.3
160°	1538.9	1538.9	1538.9	1539.2	1539.8	1540.4	1541.1	1541.6	1541.1	1540.4	1539.8
162.5°	1563.7	1563.5	1563.2	1563.5	1564.3	1565.1	1565.9	1566.7	1565.9	1565.1	1564.3
165°	1595.3	1595.3	1595.3	1595.8	1596.6	1597.5	1598.3	1599.2	1598.3	1597.5	1596.6
167.5°	1620.5	1620.2	1620.0	1620.5	1621.6	1622.9	1624.0	1625.2	1624.0	1622.9	1621.6
170°	1634.6	1634.6	1634.6	1635.2	1636.4	1637.5	1638.7	1639.8	1638.7	1637.5	1636.4
172.5°	1646.1	1646.1	1646.1	1646.7	1647.9	1649.0	1650.2	1651.3	1650.2	1649.0	1647.9
175°	1658.2	1658.2	1658.2	1658.7	1659.9	1661.1	1662.2	1663.4	1662.2	1661.1	1659.9
177.5°	1664.2	1664.2	1664.2	1664.7	1665.6	1666.5	1667.5	1668.4	1667.5	1666.5	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	785.0	782.8	779.7	775.1	771.3	765.5	765.5	766.4	766.4	766.1	765.5
5°	761.1	755.4	748.4	740.3	731.7	723.3	721.8	718.6	716.3	714.8	712.9
7.5°	736.0	725.8	715.6	704.3	693.9	685.3	679.3	674.4	671.2	667.8	665.3
10°	719.0	706.2	694.3	682.3	669.1	658.6	652.1	647.4	644.0	640.9	639.3
12.5°	698.9	684.3	671.1	659.6	645.3	634.5	628.2	626.1	622.0	615.5	612.1
15°	669.5	656.0	640.2	622.7	615.7	602.6	595.2	591.8	589.5	584.4	582.9
17.5°	644.4	626.6	608.8	595.8	582.9	572.3	568.2	563.8	560.8	556.6	555.4
20°	624.3	608.4	592.2	578.2	564.7	553.1	549.6	546.5	543.4	541.5	540.0
22.5°	603.8	587.9	574.5	561.5	547.0	539.5	535.6	532.3	530.1	528.8	527.3
25°	575.1	561.2	546.1	534.5	522.9	517.9	515.5	513.6	512.1	510.2	509.8
27.5°	549.5	534.3	522.1	511.2	502.9	498.7	496.4	495.5	495.8	496.6	497.0
30°	530.3	516.3	506.2	497.0	489.3	485.4	485.0	485.0	486.6	487.0	487.8
32.5°	512.6	501.2	491.1	482.1	476.3	473.6	475.1	475.1	476.4	477.4	478.8
35°	487.0	476.9	469.2	461.4	456.4	457.6	458.3	459.1	461.0	463.3	464.9
37.5°	462.4	453.7	445.7	439.6	437.3	439.4	441.2	442.8	445.1	446.9	448.4
40°	444.7	438.2	430.5	425.1	425.9	427.0	428.6	430.5	432.4	433.5	435.2
42.5°	428.4	421.5	415.7	411.1	412.2	413.7	414.7	415.7	417.9	420.0	420.9
45°	403.4	398.0	392.5	389.9	390.6	391.4	392.2	393.3	395.3	396.9	397.2
47.5°	375.4	371.5	367.9	365.3	366.5	366.2	367.2	369.7	370.3	371.2	373.3
50°	357.4	353.9	349.6	348.9	348.9	348.9	349.2	352.3	352.3	353.9	355.5
52.5°	337.6	335.4	332.6	331.2	330.6	330.6	332.2	333.8	334.4	336.6	338.1
55°	308.2	305.9	303.7	302.5	301.6	302.5	305.6	306.3	308.2	309.4	310.5
57.5°	277.7	275.9	274.1	273.5	273.3	274.3	276.0	278.3	278.8	282.4	284.1
60°	257.6	254.9	253.4	253.4	252.6	256.0	255.3	259.1	259.9	262.3	265.0
62.5°	236.8	233.2	232.6	232.6	233.7	234.7	235.8	237.5	239.5	242.5	244.5
65°	203.5	201.5	204.2	203.8	203.1	205.4	205.4	207.3	209.6	212.4	216.6
67.5°	171.8	170.8	171.1	171.1	172.2	173.5	174.6	176.3	179.0	182.0	184.7
70°	150.5	151.6	149.7	151.3	152.4	152.8	153.5	155.8	159.0	160.9	164.0
72.5°	129.8	129.7	129.9	130.5	131.7	132.4	133.1	135.7	139.2	140.8	143.3
75°	99.8	99.4	100.6	100.6	102.5	103.3	104.0	105.2	108.3	110.6	112.6
77.5°	72.9	73.3	73.1	74.4	73.9	74.0	76.4	77.6	77.9	82.5	83.5
80°	54.9	55.7	56.0	56.5	56.9	56.0	58.8	60.0	60.0	62.6	64.6
82.5°	39.5	39.9	40.9	41.3	41.4	42.1	42.4	43.2	44.1	45.3	47.9
85°	19.7	20.9	21.3	20.9	21.3	20.5	21.6	22.0	22.4	22.4	22.4
87.5°	8.8	9.8	10.2	11.3	11.7	12.8	13.0	12.6	12.8	14.0	12.9
90°	12.9	16.3	20.1	23.8	27.7	31.4	32.6	33.7	34.9	36.1	37.0
92.5°	39.6	41.7	43.8	45.9	48.2	50.3	51.2	52.1	53.1	54.0	54.3
95°	85.4	87.7	90.0	92.3	94.6	96.9	98.1	99.3	100.4	101.6	102.2
97.5°	143.3	144.9	146.6	148.2	150.0	151.7	153.0	154.3	155.7	157.0	157.6
100°	185.1	186.7	188.1	189.7	191.1	192.6	193.4	194.3	195.1	196.0	196.7
102.5°	229.4	231.0	232.9	234.8	236.7	238.6	239.5	240.3	241.3	242.2	242.5
105°	297.0	298.6	301.2	303.9	306.5	309.1	309.1	309.1	309.1	309.1	309.4
107.5°	376.8	377.5	378.5	379.6	380.6	381.6	382.6	383.5	384.5	385.4	385.7
110°	428.0	428.6	429.2	429.8	430.3	430.9	432.1	433.2	434.4	435.6	435.9



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	479.5	479.7	479.8	479.9	480.1	480.2	481.6	482.9	484.3	485.7	486.4
115°	560.2	560.3	559.7	559.2	558.6	558.0	558.3	558.6	558.9	559.2	559.2
117.5°	638.1	638.0	637.2	636.5	635.7	635.0	634.9	634.9	634.8	634.7	634.3
120°	692.0	692.2	690.6	689.2	687.8	686.3	686.0	685.7	685.5	685.2	684.7
122.5°	741.4	741.7	740.9	740.2	739.4	738.7	737.9	737.2	736.4	735.7	734.9
125°	818.2	818.3	817.7	817.2	816.6	816.0	814.9	813.6	812.5	811.3	810.2
127.5°	894.4	895.0	894.4	893.7	893.1	892.5	890.8	889.2	887.6	886.0	884.4
130°	944.5	945.2	944.3	943.5	942.6	941.7	940.6	939.4	938.3	937.1	935.4
132.5°	992.7	993.5	992.9	992.3	991.6	991.0	989.6	988.2	986.7	985.4	983.9
135°	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4	1061.2	1060.1	1058.8	1058.0
137.5°	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8	1132.6	1131.4	1130.1	1129.0
140°	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8	1179.5	1179.2	1178.9	1177.8
142.5°	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9	1223.6	1223.2	1222.9	1222.0
145°	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5	1288.2	1288.0	1287.7	1287.0
147.5°	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3	1349.3	1349.3	1349.3	1348.5
150°	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0	1387.0	1387.0	1387.0	1386.1
152.5°	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1	1421.5	1422.0	1422.4	1421.9
155°	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8	1471.9	1473.1	1474.2	1473.8
157.5°	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0	1515.2	1516.4	1517.7	1517.4
160°	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4	1541.9	1543.4	1544.8	1545.0
162.5°	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6	1567.0	1568.5	1569.9	1569.7
165°	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0	1598.8	1600.5	1602.3	1602.2
167.5°	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2
170°	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7
172.5°	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9	1649.7	1651.5	1653.4	1653.3
175°	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9	1661.6	1663.4	1665.2	1665.0
177.5°	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6	1667.0	1668.4	1669.8	1669.7
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	763.4	763.1	765.2	763.7	765.2	763.1	763.4	765.5	766.1	766.4	766.4
5°	710.5	711.7	707.8	707.8	707.8	711.7	710.5	712.9	714.8	716.3	718.6
7.5°	663.5	661.8	662.0	659.8	662.0	661.8	663.5	665.3	667.8	671.2	674.4
10°	634.7	632.4	631.6	632.0	631.6	632.4	634.7	639.3	640.9	644.0	647.4
12.5°	610.9	610.4	605.3	605.4	605.3	610.4	610.9	612.1	615.5	622.0	626.1
15°	582.9	575.5	574.7	577.0	574.7	575.5	582.9	582.9	584.4	589.5	591.8
17.5°	554.8	550.9	551.2	550.0	551.2	550.9	554.8	555.4	556.6	560.8	563.8
20°	540.0	537.7	537.2	534.5	537.2	537.7	540.0	540.0	541.5	543.4	546.5
22.5°	526.3	525.5	525.7	522.8	525.7	525.5	526.3	527.3	528.8	530.1	532.3
25°	509.4	511.3	509.8	509.8	509.8	511.3	509.4	509.8	510.2	512.1	513.6
27.5°	498.0	497.9	497.1	497.1	497.1	497.9	498.0	497.0	496.6	495.8	495.5
30°	489.3	488.9	489.7	489.7	489.7	488.9	489.3	487.8	487.0	486.6	485.0
32.5°	480.6	481.1	481.3	481.6	481.3	481.1	480.6	478.8	477.4	476.4	475.1
35°	467.3	467.6	468.8	468.0	468.8	467.6	467.3	464.9	463.3	461.0	459.1
37.5°	449.1	450.9	450.5	451.1	450.5	450.9	449.1	448.4	446.9	445.1	442.8
40°	435.6	436.7	436.3	436.3	436.3	436.7	435.6	435.2	433.5	432.4	430.5
42.5°	421.6	422.4	421.4	420.8	421.4	422.4	421.6	420.9	420.0	417.9	415.7
45°	398.8	398.0	399.2	397.6	399.2	398.0	398.8	397.2	396.9	395.3	393.3
47.5°	373.2	374.1	374.4	375.5	374.4	374.1	373.2	373.3	371.2	370.3	369.7
50°	356.2	358.5	358.5	358.2	358.5	358.5	356.2	355.5	353.9	352.3	352.3
52.5°	339.5	340.6	342.1	342.0	342.1	340.6	339.5	338.1	336.6	334.4	333.8
55°	313.7	314.5	315.2	315.6	315.2	314.5	313.7	310.5	309.4	308.2	306.3
57.5°	286.9	286.6	288.4	289.0	288.4	286.6	286.9	284.1	282.4	278.8	278.3
60°	268.0	268.0	271.1	272.3	271.1	268.0	268.0	265.0	262.3	259.9	259.1
62.5°	247.9	249.1	252.3	250.6	252.3	249.1	247.9	244.5	242.5	239.5	237.5
65°	218.5	221.7	221.3	222.8	221.3	221.7	218.5	216.6	212.4	209.6	207.3
67.5°	187.8	189.8	192.6	192.8	192.6	189.8	187.8	184.7	182.0	179.0	176.3
70°	167.1	169.1	170.6	171.7	170.6	169.1	167.1	164.0	160.9	159.0	155.8
72.5°	146.9	147.9	151.7	150.1	151.7	147.9	146.9	143.3	140.8	139.2	135.7
75°	115.2	118.0	120.3	119.2	120.3	118.0	115.2	112.6	110.6	108.3	105.2
77.5°	85.2	88.0	89.1	88.1	89.1	88.0	85.2	83.5	82.5	77.9	77.6
80°	67.3	67.0	69.3	68.9	69.3	67.0	67.3	64.6	62.6	60.0	60.0
82.5°	49.4	49.0	50.1	50.3	50.1	49.0	49.4	47.9	45.3	44.1	43.2
85°	23.9	25.1	23.6	23.2	23.6	25.1	23.9	22.4	22.4	22.4	22.0
87.5°	13.1	13.2	13.0	12.8	13.0	13.2	13.1	12.9	14.0	12.8	12.6
90°	37.6	38.2	38.7	39.3	38.7	38.2	37.6	37.0	36.1	34.9	33.7
92.5°	53.9	53.6	53.2	52.9	53.2	53.6	53.9	54.3	54.0	53.1	52.1
95°	102.2	102.2	102.2	102.2	102.2	102.2	102.2	102.2	101.6	100.4	99.3
97.5°	157.5	157.4	157.3	157.1	157.3	157.4	157.5	157.6	157.0	155.7	154.3
100°	197.3	197.9	198.5	199.0	198.5	197.9	197.3	196.7	196.0	195.1	194.3
102.5°	242.4	242.3	242.2	242.1	242.2	242.3	242.4	242.5	242.2	241.3	240.3
105°	310.0	310.5	311.1	311.7	311.1	310.5	310.0	309.4	309.1	309.1	309.1
107.5°	385.4	385.0	384.7	384.3	384.7	385.0	385.4	385.7	385.4	384.5	383.5
110°	435.3	434.7	434.1	433.5	434.1	434.7	435.3	435.9	435.6	434.4	433.2



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	486.3	486.1	486.0	485.9	486.0	486.1	486.3	486.4	485.7	484.3	482.9
115°	558.9	558.6	558.3	558.0	558.3	558.6	558.9	559.2	559.2	558.9	558.6
117.5°	633.5	632.7	631.9	631.1	631.9	632.7	633.5	634.3	634.7	634.8	634.9
120°	684.2	683.6	683.0	682.4	683.0	683.6	684.2	684.7	685.2	685.5	685.7
122.5°	734.1	733.3	732.5	731.6	732.5	733.3	734.1	734.9	735.7	736.4	737.2
125°	809.0	807.8	806.7	805.5	806.7	807.8	809.0	810.2	811.3	812.5	813.6
127.5°	883.1	881.8	880.5	879.1	880.5	881.8	883.1	884.4	886.0	887.6	889.2
130°	933.4	931.4	929.4	927.4	929.4	931.4	933.4	935.4	937.1	938.3	939.4
132.5°	982.3	980.8	979.2	977.7	979.2	980.8	982.3	983.9	985.4	986.7	988.2
135°	1057.4	1056.8	1056.2	1055.7	1056.2	1056.8	1057.4	1058.0	1058.8	1060.1	1061.2
137.5°	1127.9	1126.8	1125.7	1124.6	1125.7	1126.8	1127.9	1129.0	1130.1	1131.4	1132.6
140°	1175.8	1173.7	1171.6	1169.6	1171.6	1173.7	1175.8	1177.8	1178.9	1179.2	1179.5
142.5°	1220.4	1218.9	1217.3	1215.8	1217.3	1218.9	1220.4	1222.0	1222.9	1223.2	1223.6
145°	1285.8	1284.5	1283.4	1282.2	1283.4	1284.5	1285.8	1287.0	1287.7	1288.0	1288.2
147.5°	1346.8	1344.9	1343.2	1341.5	1343.2	1344.9	1346.8	1348.5	1349.3	1349.3	1349.3
150°	1384.4	1382.7	1380.9	1379.2	1380.9	1382.7	1384.4	1386.1	1387.0	1387.0	1387.0
152.5°	1420.4	1418.9	1417.3	1415.8	1417.3	1418.9	1420.4	1421.9	1422.4	1422.0	1421.5
155°	1471.8	1469.8	1467.6	1465.6	1467.6	1469.8	1471.8	1473.8	1474.2	1473.1	1471.9
157.5°	1515.8	1514.2	1512.6	1511.0	1512.6	1514.2	1515.8	1517.4	1517.7	1516.4	1515.2
160°	1543.8	1542.7	1541.5	1540.2	1541.5	1542.7	1543.8	1545.0	1544.8	1543.4	1541.9
162.5°	1567.9	1566.0	1564.2	1562.3	1564.2	1566.0	1567.9	1569.7	1569.9	1568.5	1567.0
165°	1600.1	1598.1	1596.0	1594.0	1596.0	1598.1	1600.1	1602.2	1602.3	1600.5	1598.8
167.5°	1626.4	1624.6	1622.8	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6
170°	1640.7	1638.7	1636.6	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7
172.5°	1651.2	1649.1	1647.1	1645.1	1647.1	1649.1	1651.2	1653.3	1653.4	1651.5	1649.7
175°	1662.9	1660.9	1658.9	1656.9	1658.9	1660.9	1662.9	1665.0	1665.2	1663.4	1661.6
177.5°	1668.0	1666.4	1664.8	1663.1	1664.8	1666.4	1668.0	1669.7	1669.8	1668.4	1667.0
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	765.5	765.5	771.3	775.1	779.7	782.8	785.0	787.2	790.8	795.9	801.4
5°	721.8	723.3	731.7	740.3	748.4	755.4	761.1	768.1	776.7	787.1	798.7
7.5°	679.3	685.3	693.9	704.3	715.6	725.8	736.0	747.5	759.4	774.9	791.1
10°	652.1	658.6	669.1	682.3	694.3	706.2	719.0	731.3	746.5	764.7	785.6
12.5°	628.2	634.5	645.3	659.6	671.1	684.3	698.9	715.0	732.0	753.9	777.5
15°	595.2	602.6	615.7	622.7	640.2	656.0	669.5	692.7	714.4	736.8	764.3
17.5°	568.2	572.3	582.9	595.8	608.8	626.6	644.4	663.7	685.3	712.8	747.1
20°	549.6	553.1	564.7	578.2	592.2	608.4	624.3	643.6	667.9	697.0	734.1
22.5°	535.6	539.5	547.0	561.5	574.5	587.9	603.8	626.9	652.8	681.2	721.4
25°	515.5	517.9	522.9	534.5	546.1	561.2	575.1	596.8	623.5	656.7	697.0
27.5°	496.4	498.7	502.9	511.2	522.1	534.3	549.5	567.8	594.9	631.1	673.8
30°	485.0	485.4	489.3	497.0	506.2	516.3	530.3	551.2	576.6	613.4	658.3
32.5°	475.1	473.6	476.3	482.1	491.1	501.2	512.6	533.2	557.8	593.9	640.1
35°	458.3	457.6	456.4	461.4	469.2	476.9	487.0	502.4	530.3	563.9	612.3
37.5°	441.2	439.4	437.3	439.6	445.7	453.7	462.4	476.2	500.2	537.2	583.5
40°	428.6	427.0	425.9	425.1	430.5	438.2	444.7	458.0	480.4	515.5	561.2
42.5°	414.7	413.7	412.2	411.1	415.7	421.5	428.4	440.0	462.4	495.4	538.7
45°	392.2	391.4	390.6	389.9	392.5	398.0	403.4	411.9	431.2	463.3	502.4
47.5°	367.2	366.2	366.5	365.3	367.9	371.5	375.4	384.5	403.0	428.9	457.5
50°	349.2	348.9	348.9	348.9	349.6	353.9	357.4	364.4	381.3	407.3	427.8
52.5°	332.2	330.6	330.6	331.2	332.6	335.4	337.6	345.2	360.0	381.3	399.9
55°	305.6	302.5	301.6	302.5	303.7	305.9	308.2	314.5	327.2	343.1	353.9
57.5°	276.0	274.3	273.3	273.5	274.1	275.9	277.7	284.5	294.5	302.8	309.7
60°	255.3	256.0	252.6	253.4	253.4	254.9	257.6	261.9	270.3	276.2	283.2
62.5°	235.8	234.7	233.7	232.6	232.6	233.2	236.8	240.1	247.4	250.4	255.9
65°	205.4	205.4	203.1	203.8	204.2	201.5	203.5	207.3	212.0	213.1	218.1
67.5°	174.6	173.5	172.2	171.1	171.1	170.8	171.8	173.7	177.2	177.6	181.5
70°	153.5	152.8	152.4	151.3	149.7	151.6	150.5	152.4	154.3	154.7	157.0
72.5°	133.1	132.4	131.7	130.5	129.9	129.7	129.8	132.0	133.3	132.7	135.3
75°	104.0	103.3	102.5	100.6	100.6	99.4	99.8	101.3	102.9	101.7	104.0
77.5°	76.4	74.0	73.9	74.4	73.1	73.3	72.9	72.6	73.3	73.4	75.5
80°	58.8	56.0	56.9	56.5	56.0	55.7	54.9	55.3	55.7	56.0	57.3
82.5°	42.4	42.1	41.4	41.3	40.9	39.9	39.5	40.2	40.5	40.3	41.2
85°	21.6	20.5	21.3	20.9	21.3	20.9	19.7	19.7	20.5	20.1	20.9
87.5°	13.0	12.8	11.7	11.3	10.2	9.8	8.8	8.5	8.3	7.7	7.7
90°	32.6	31.4	27.7	23.8	20.1	16.3	12.9	10.0	7.2	4.2	1.3
92.5°	51.2	50.3	48.2	45.9	43.8	41.7	39.6	37.7	35.6	33.6	31.7
95°	98.1	96.9	94.6	92.3	90.0	87.7	85.4	83.4	81.4	79.3	77.3
97.5°	153.0	151.7	150.0	148.2	146.6	144.9	143.3	141.8	140.3	138.8	137.2
100°	193.4	192.6	191.1	189.7	188.1	186.7	185.1	183.4	181.6	179.9	178.1
102.5°	239.5	238.6	236.7	234.8	232.9	231.0	229.4	228.4	227.4	226.3	225.3
105°	309.1	309.1	306.5	303.9	301.2	298.6	297.0	296.4	295.9	295.3	294.7
107.5°	382.6	381.6	380.6	379.6	378.5	377.5	376.8	376.5	376.1	375.8	375.4
110°	432.1	430.9	430.3	429.8	429.2	428.6	428.0	427.4	426.9	426.3	425.7



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	481.6	480.2	480.1	479.9	479.8	479.7	479.5	479.1	478.8	478.4	478.1
115°	558.3	558.0	558.6	559.2	559.7	560.3	560.2	559.3	558.4	557.5	556.6
117.5°	634.9	635.0	635.7	636.5	637.2	638.0	638.1	637.5	636.9	636.3	635.8
120°	686.0	686.3	687.8	689.2	690.6	692.2	692.0	690.2	688.5	686.7	685.0
122.5°	737.9	738.7	739.4	740.2	740.9	741.7	741.4	740.2	738.9	737.6	736.4
125°	814.9	816.0	816.6	817.2	817.7	818.3	818.2	817.3	816.4	815.6	814.7
127.5°	890.8	892.5	893.1	893.7	894.4	895.0	894.4	892.5	890.7	888.9	887.0
130°	940.6	941.7	942.6	943.5	944.3	945.2	944.5	942.2	939.9	937.5	935.1
132.5°	989.6	991.0	991.6	992.3	992.9	993.5	992.7	990.4	988.1	985.7	983.4
135°	1062.4	1063.5	1063.8	1064.1	1064.4	1064.7	1064.0	1062.2	1060.5	1058.7	1057.0
137.5°	1133.8	1135.1	1134.3	1133.6	1132.8	1132.1	1130.9	1129.4	1128.0	1126.5	1125.1
140°	1179.8	1180.1	1179.8	1179.5	1179.2	1178.9	1178.1	1176.6	1175.2	1173.7	1172.3
142.5°	1223.9	1224.2	1223.6	1223.0	1222.5	1222.0	1221.0	1219.6	1218.1	1216.7	1215.2
145°	1288.5	1288.8	1288.0	1287.1	1286.2	1285.4	1284.5	1284.0	1283.4	1282.8	1282.2
147.5°	1349.3	1349.3	1348.5	1347.7	1346.9	1346.0	1345.1	1344.1	1343.0	1342.0	1340.9
150°	1387.0	1387.0	1386.4	1385.8	1385.3	1384.7	1384.1	1383.5	1383.0	1382.4	1381.8
152.5°	1421.1	1420.6	1420.3	1419.9	1419.6	1419.2	1418.6	1417.7	1416.9	1416.1	1415.3
155°	1470.8	1469.6	1469.3	1468.9	1468.6	1468.4	1468.2	1468.2	1468.2	1468.2	1468.2
157.5°	1514.0	1512.8	1512.6	1512.3	1512.1	1511.9	1511.9	1512.3	1512.6	1513.0	1513.3
160°	1540.4	1538.9	1538.9	1538.9	1538.9	1538.9	1539.2	1539.8	1540.4	1541.1	1541.6
162.5°	1565.6	1564.1	1563.9	1563.7	1563.5	1563.2	1563.5	1564.3	1565.1	1565.9	1566.7
165°	1597.0	1595.3	1595.3	1595.3	1595.3	1595.3	1595.8	1596.6	1597.5	1598.3	1599.2
167.5°	1622.8	1620.9	1620.7	1620.5	1620.2	1620.0	1620.5	1621.6	1622.9	1624.0	1625.2
170°	1636.6	1634.6	1634.6	1634.6	1634.6	1634.6	1635.2	1636.4	1637.5	1638.7	1639.8
172.5°	1647.9	1646.1	1646.1	1646.1	1646.1	1646.1	1646.7	1647.9	1649.0	1650.2	1651.3
175°	1659.9	1658.2	1658.2	1658.2	1658.2	1658.2	1658.7	1659.9	1661.1	1662.2	1663.4
177.5°	1665.6	1664.2	1664.2	1664.2	1664.2	1664.2	1664.7	1665.6	1666.5	1667.5	1668.4
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	803.2	804.8	810.0	813.7	818.1	820.6	823.0	825.0	827.4	828.0	837.0
5°	806.8	814.6	828.1	838.1	850.5	864.0	873.3	877.6	888.8	898.1	916.7
7.5°	805.8	822.2	842.7	863.9	886.7	907.7	925.9	947.6	963.0	986.1	1009.0
10°	804.9	826.9	853.2	880.3	912.0	941.4	967.8	997.1	1021.5	1053.6	1081.1
12.5°	802.1	828.8	865.3	897.3	935.8	976.3	1015.3	1053.1	1074.7	1128.1	1153.5
15°	795.2	826.9	872.5	921.3	974.3	1022.3	1071.8	1111.2	1175.0	1221.8	1251.6
17.5°	782.0	826.5	880.6	939.4	1003.8	1067.0	1123.1	1183.0	1250.7	1307.3	1367.7
20°	775.9	824.6	884.9	949.9	1016.8	1088.3	1152.2	1224.2	1298.0	1353.7	1431.1
22.5°	764.5	819.6	884.6	957.0	1028.5	1102.6	1177.3	1249.8	1335.1	1411.9	1485.5
25°	745.7	807.6	874.8	955.7	1039.7	1113.9	1203.3	1299.6	1388.6	1487.1	1560.6
27.5°	726.1	792.1	859.6	934.7	1025.0	1113.2	1225.6	1334.3	1443.1	1528.3	1582.7
30°	710.8	775.1	844.8	920.5	1009.9	1114.7	1240.4	1359.1	1465.1	1538.2	1568.7
32.5°	694.5	759.6	821.2	900.7	995.9	1113.8	1249.7	1373.6	1466.3	1515.0	1509.0
35°	668.7	723.3	783.3	859.8	972.0	1106.9	1255.1	1374.9	1431.8	1421.4	1342.5
37.5°	631.6	677.5	736.5	820.3	944.1	1092.7	1244.3	1334.2	1330.5	1245.5	1131.1
40°	608.4	647.4	704.3	792.5	922.4	1083.4	1227.2	1285.7	1236.2	1117.4	980.5
42.5°	578.0	614.0	670.9	761.5	898.7	1064.5	1194.8	1211.6	1114.8	978.2	852.7
45°	531.1	562.8	621.6	715.2	862.9	1023.4	1115.5	1074.1	943.7	802.5	707.0
47.5°	480.5	513.5	570.1	666.2	811.2	961.6	1005.4	917.5	783.6	669.1	581.4
50°	448.7	480.4	535.6	632.8	776.3	910.9	929.1	815.4	692.4	591.8	519.8
52.5°	416.5	446.4	500.7	598.1	735.4	852.0	840.8	725.0	611.9	526.1	469.7
55°	368.6	396.9	448.7	540.0	664.9	757.3	716.7	606.1	512.5	446.0	403.0
57.5°	325.8	352.8	397.5	480.0	588.5	652.1	600.5	507.3	432.8	381.6	349.6
60°	296.7	320.6	363.1	439.8	534.1	582.5	531.4	449.1	386.4	345.4	316.8
62.5°	269.1	290.0	329.4	398.9	480.9	521.5	469.9	400.1	346.8	310.4	286.1
65°	227.4	246.4	281.1	335.4	402.6	429.7	385.3	328.7	287.4	260.3	244.1
67.5°	189.3	205.4	235.5	278.1	327.7	347.4	313.6	269.8	238.6	216.9	204.0
70°	164.0	177.9	201.5	238.2	283.2	298.2	266.5	230.6	207.7	190.3	178.3
72.5°	142.6	152.9	174.3	202.7	240.1	252.1	229.9	198.3	177.0	164.0	154.5
75°	108.7	117.1	131.1	153.9	179.9	186.8	170.2	150.5	136.1	126.8	119.5
77.5°	78.4	84.6	94.7	108.8	126.7	133.0	122.5	109.3	98.9	92.6	88.5
80°	59.2	64.2	72.7	84.3	95.1	98.7	92.4	82.4	75.0	71.6	68.1
82.5°	43.7	46.6	51.7	59.6	67.0	71.1	65.8	59.8	55.8	52.7	51.4
85°	22.0	23.6	26.0	29.0	33.6	35.2	33.2	31.7	29.4	27.5	27.5
87.5°	8.9	9.5	11.0	12.2	14.1	15.8	16.3	16.4	16.8	16.8	16.7
90°	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6	33.7
92.5°	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2	52.1
95°	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1	99.3
97.5°	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0	154.3
100°	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4	194.3
102.5°	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5	240.3
105°	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1	309.1
107.5°	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6	383.5
110°	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1	433.2



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6	482.9
115°	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3	558.6
117.5°	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9	634.9
120°	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0	685.7
122.5°	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9	737.2
125°	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9	813.6
127.5°	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8	889.2
130°	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6	939.4
132.5°	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6	988.2
135°	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4	1061.2
137.5°	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8	1132.6
140°	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8	1179.5
142.5°	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9	1223.6
145°	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5	1288.2
147.5°	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3	1349.3
150°	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0	1387.0
152.5°	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1	1421.5
155°	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8	1471.9
157.5°	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0	1515.2
160°	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4	1541.9
162.5°	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6	1567.0
165°	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0	1598.8
167.5°	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8	1624.6
170°	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6	1638.7
172.5°	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9	1649.7
175°	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9	1661.6
177.5°	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6	1667.0
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	840.1	840.4	843.7	846.3	845.1	846.6	847.2
5°	917.8	931.7	939.1	944.5	944.9	945.2	948.4
7.5°	1028.0	1043.0	1053.9	1070.5	1075.4	1081.1	1079.4
10°	1108.5	1130.5	1149.5	1159.5	1170.3	1186.2	1173.5
12.5°	1183.7	1222.7	1251.6	1267.2	1277.5	1280.6	1274.3
15°	1307.7	1358.8	1386.2	1385.4	1420.3	1435.3	1411.7
17.5°	1421.4	1468.5	1506.2	1525.6	1554.6	1561.0	1558.1
20°	1491.0	1542.5	1571.9	1605.1	1620.2	1633.8	1636.1
22.5°	1551.1	1597.2	1628.8	1656.5	1669.1	1675.5	1679.4
25°	1612.9	1649.2	1668.2	1677.8	1681.3	1680.5	1675.5
27.5°	1608.6	1611.3	1590.5	1570.0	1551.7	1531.0	1523.9
30°	1566.8	1534.3	1476.3	1443.4	1395.1	1356.8	1372.3
32.5°	1456.9	1392.3	1327.2	1255.3	1195.8	1178.9	1161.8
35°	1243.4	1129.7	1063.3	985.9	954.9	924.0	902.7
37.5°	1006.0	918.1	839.1	788.5	757.5	738.0	727.4
40°	869.9	790.5	725.6	684.6	661.0	638.9	635.8
42.5°	761.2	687.5	638.6	606.0	583.3	574.0	567.1
45°	623.5	572.0	539.2	515.9	500.9	495.0	487.4
47.5°	527.8	491.4	466.7	450.9	439.5	435.2	434.5
50°	474.2	444.0	425.9	413.4	404.6	403.0	396.9
52.5°	433.9	407.8	393.6	382.8	376.4	372.0	370.2
55°	376.7	359.3	346.6	340.3	335.4	331.0	331.0
57.5°	329.6	315.1	306.6	301.3	299.8	296.8	294.9
60°	300.5	288.1	281.6	276.9	273.9	274.2	270.7
62.5°	272.1	264.0	257.7	253.1	249.4	249.4	249.7
65°	231.7	225.5	220.9	219.3	217.0	214.3	215.0
67.5°	196.3	190.6	186.9	184.3	183.5	182.0	184.3
70°	171.0	166.7	164.0	161.7	160.9	161.3	163.2
72.5°	147.7	144.7	143.0	141.9	140.2	140.3	141.6
75°	116.0	113.7	112.2	111.0	110.6	110.6	110.6
77.5°	85.2	84.7	84.0	82.3	82.4	82.8	82.9
80°	67.3	66.1	65.7	64.9	63.8	63.0	64.9
82.5°	50.3	49.1	48.8	48.6	46.8	46.7	48.3
85°	27.1	26.0	26.3	26.0	26.0	25.5	25.5
87.5°	16.6	16.5	16.4	16.8	16.6	16.4	17.2
90°	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332139-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)