

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332145-840

Luminaire Tested: **S123DIW-S560D1535U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332145-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D1535U840-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7786.2 lumens  
Efficiency: N/A  
Efficacy: 128.5 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	34	34	33	26
2	85	78	72	68	77	71	66	61	56	53	50	43	41	39	30	29	28	22
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8593	8593	8593	8593
5°	10247	8630	7648	8630
10°	12826	8587	6908	8587
15°	15731	8517	6430	8517
20°	18741	8409	6123	8409
25°	19899	8278	6055	8278
30°	17056	8182	6087	8182
35°	11862	8046	6150	8046
40°	8934	7886	6131	7886
45°	7419	7648	6052	7648
50°	6646	7164	5998	7164
55°	6212	6641	5923	6641
60°	5828	6097	5862	6097
65°	5476	5555	5675	5555
70°	5136	4941	5404	4941
75°	4600	4325	4957	4325
80°	4023	3552	4271	3552
85°	3149	2581	2865	2581



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.6	1.0
10°-20°	252.2	3.2
20°-30°	423.2	5.4
30°-40°	479.2	6.2
40°-50°	429.7	5.5
50°-60°	346.8	4.5
60°-70°	241.7	3.1
70°-80°	127.0	1.6
80°-90°	36.8	0.5
90°-100°	126.3	1.6
100°-110°	378.0	4.9
110°-120°	642.9	8.3
120°-130°	845.6	10.9
130°-140°	950.5	12.2
140°-150°	934.3	12.0
150°-160°	786.5	10.1
160°-170°	523.6	6.7
170°-180°	183.3	2.4
0°-30°	754.0	9.7
0°-40°	1233.2	15.8
0°-60°	2009.7	25.8
0°-90°	2415.2	31.0
90°-120°	1147.2	14.7
90°-150°	3877.6	49.8
90°-180°	5371.0	69.0
0°-180°	7786.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	948	799	708	799	948	98
15°	1412	764	577	764	1412	408
25°	1676	697	510	697	1676	735
35°	903	612	468	612	903	586
45°	487	502	398	502	487	386
55°	331	354	316	354	331	297
65°	215	218	223	218	215	214
75°	111	104	119	104	111	118
85°	26	21	23	21	26	31
90°	46	2	46	2	46	23
95°	119	90	119	90	119	122
105°	362	343	362	343	362	385
115°	649	647	649	647	649	642
125°	936	947	936	947	936	837
135°	1227	1229	1227	1229	1227	944
145°	1491	1491	1491	1491	1491	931
155°	1704	1707	1704	1707	1704	785
165°	1853	1859	1853	1859	1853	523
175°	1926	1934	1926	1934	1926	183
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	847.2	846.6	845.1	846.3	843.7	840.4	840.1	837.0	828.0	827.4	825.0
5°	948.4	945.2	944.9	944.5	939.1	931.7	917.8	916.7	898.1	888.8	877.6
7.5°	1079.4	1081.1	1075.4	1070.5	1053.9	1043.0	1028.0	1009.0	986.1	963.0	947.6
10°	1173.5	1186.2	1170.3	1159.5	1149.5	1130.5	1108.5	1081.1	1053.6	1021.5	997.1
12.5°	1274.3	1280.6	1277.5	1267.2	1251.6	1222.7	1183.7	1153.5	1128.1	1074.7	1053.1
15°	1411.7	1435.3	1420.3	1385.4	1386.2	1358.8	1307.7	1251.6	1221.8	1175.0	1111.2
17.5°	1558.1	1561.0	1554.6	1525.6	1506.2	1468.5	1421.4	1367.7	1307.3	1250.7	1183.0
20°	1636.1	1633.8	1620.2	1605.1	1571.9	1542.5	1491.0	1431.1	1353.7	1298.0	1224.2
22.5°	1679.4	1675.5	1669.1	1656.5	1628.8	1597.2	1551.1	1485.5	1411.9	1335.1	1249.8
25°	1675.5	1680.5	1681.3	1677.8	1668.2	1649.2	1612.9	1560.6	1487.1	1388.6	1299.6
27.5°	1523.9	1531.0	1551.7	1570.0	1590.5	1611.3	1608.6	1582.7	1528.3	1443.1	1334.3
30°	1372.3	1356.8	1395.1	1443.4	1476.3	1534.3	1566.8	1568.7	1538.2	1465.1	1359.1
32.5°	1161.8	1178.9	1195.8	1255.3	1327.2	1392.3	1456.9	1509.0	1515.0	1466.3	1373.6
35°	902.7	924.0	954.9	985.9	1063.3	1129.7	1243.4	1342.5	1421.4	1431.8	1374.9
37.5°	727.4	738.0	757.5	788.5	839.1	918.1	1006.0	1131.1	1245.5	1330.5	1334.2
40°	635.8	638.9	661.0	684.6	725.6	790.5	869.9	980.5	1117.4	1236.2	1285.7
42.5°	567.1	574.0	583.3	606.0	638.6	687.5	761.2	852.7	978.2	1114.8	1211.6
45°	487.4	495.0	500.9	515.9	539.2	572.0	623.5	707.0	802.5	943.7	1074.1
47.5°	434.5	435.2	439.5	450.9	466.7	491.4	527.8	581.4	669.1	783.6	917.5
50°	396.9	403.0	404.6	413.4	425.9	444.0	474.2	519.8	591.8	692.4	815.4
52.5°	370.2	372.0	376.4	382.8	393.6	407.8	433.9	469.7	526.1	611.9	725.0
55°	331.0	331.0	335.4	340.3	346.6	359.3	376.7	403.0	446.0	512.5	606.1
57.5°	294.9	296.8	299.8	301.3	306.6	315.1	329.6	349.6	381.6	432.8	507.3
60°	270.7	274.2	273.9	276.9	281.6	288.1	300.5	316.8	345.4	386.4	449.1
62.5°	249.7	249.4	249.4	253.1	257.7	264.0	272.1	286.1	310.4	346.8	400.1
65°	215.0	214.3	217.0	219.3	220.9	225.5	231.7	244.1	260.3	287.4	328.7
67.5°	184.3	182.0	183.5	184.3	186.9	190.6	196.3	204.0	216.9	238.6	269.8
70°	163.2	161.3	160.9	161.7	164.0	166.7	171.0	178.3	190.3	207.7	230.6
72.5°	141.6	140.3	140.2	141.9	143.0	144.7	147.7	154.5	164.0	177.0	198.3
75°	110.6	110.6	110.6	111.0	112.2	113.7	116.0	119.5	126.8	136.1	150.5
77.5°	82.9	82.8	82.4	82.3	84.0	84.7	85.2	88.5	92.6	98.9	109.3
80°	64.9	63.0	63.8	64.9	65.7	66.1	67.3	68.1	71.6	75.0	82.4
82.5°	48.3	46.7	46.8	48.6	48.8	49.1	50.3	51.4	52.7	55.8	59.8
85°	25.5	25.5	26.0	26.0	26.3	26.0	27.1	27.5	27.5	29.4	31.7
87.5°	18.4	17.7	17.9	18.0	17.6	17.7	17.7	17.8	17.8	17.9	17.3
90°	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3	37.9	36.6	32.1
92.5°	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6	59.6	58.5	55.9
95°	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4	114.0	112.7	110.0
97.5°	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5	177.9	176.3	174.4
100°	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9	224.9	223.9	222.2
102.5°	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5	278.5	277.4	275.2
105°	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4	359.4	359.4	356.4
107.5°	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0	444.8	443.7	442.5
110°	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7	502.4	501.0	500.3



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5	559.9	558.3	558.2
115°	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4	649.0	648.7	649.4
117.5°	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1	738.2	738.3	739.1
120°	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3	797.6	798.0	799.6
122.5°	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1	858.0	858.9	859.8
125°	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0	947.4	948.8	949.4
127.5°	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9	1035.7	1037.6	1038.4
130°	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2	1093.6	1094.9	1095.9
132.5°	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9	1150.5	1152.2	1152.9
135°	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9	1235.2	1236.6	1236.9
137.5°	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9	1318.3	1319.7	1318.8
140°	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7
142.5°	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6	1422.9	1423.2	1422.6
145°	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7	1498.1	1498.4	1497.4
147.5°	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7	1612.7	1612.7	1611.9
152.5°	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7	1652.2	1651.6	1651.2
155°	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3	1710.0	1708.6	1708.3
157.5°	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7	1760.3	1758.9	1758.6
160°	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7	1791.0	1789.3	1789.3
162.5°	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9	1820.3	1818.6	1818.3
165°	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9	1856.8	1854.8	1854.8
167.5°	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6	1884.4
170°	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5	1900.5
172.5°	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0	1916.0	1913.9	1913.9
175°	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0	1930.0	1927.9	1927.9
177.5°	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1	1936.5	1934.9	1934.9
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	823.0	820.6	818.1	813.7	810.0	804.8	803.2	801.4	795.9	790.8	787.2
5°	873.3	864.0	850.5	838.1	828.1	814.6	806.8	798.7	787.1	776.7	768.1
7.5°	925.9	907.7	886.7	863.9	842.7	822.2	805.8	791.1	774.9	759.4	747.5
10°	967.8	941.4	912.0	880.3	853.2	826.9	804.9	785.6	764.7	746.5	731.3
12.5°	1015.3	976.3	935.8	897.3	865.3	828.8	802.1	777.5	753.9	732.0	715.0
15°	1071.8	1022.3	974.3	921.3	872.5	826.9	795.2	764.3	736.8	714.4	692.7
17.5°	1123.1	1067.0	1003.8	939.4	880.6	826.5	782.0	747.1	712.8	685.3	663.7
20°	1152.2	1088.3	1016.8	949.9	884.9	824.6	775.9	734.1	697.0	667.9	643.6
22.5°	1177.3	1102.6	1028.5	957.0	884.6	819.6	764.5	721.4	681.2	652.8	626.9
25°	1203.3	1113.9	1039.7	955.7	874.8	807.6	745.7	697.0	656.7	623.5	596.8
27.5°	1225.6	1113.2	1025.0	934.7	859.6	792.1	726.1	673.8	631.1	594.9	567.8
30°	1240.4	1114.7	1009.9	920.5	844.8	775.1	710.8	658.3	613.4	576.6	551.2
32.5°	1249.7	1113.8	995.9	900.7	821.2	759.6	694.5	640.1	593.9	557.8	533.2
35°	1255.1	1106.9	972.0	859.8	783.3	723.3	668.7	612.3	563.9	530.3	502.4
37.5°	1244.3	1092.7	944.1	820.3	736.5	677.5	631.6	583.5	537.2	500.2	476.2
40°	1227.2	1083.4	922.4	792.5	704.3	647.4	608.4	561.2	515.5	480.4	458.0
42.5°	1194.8	1064.5	898.7	761.5	670.9	614.0	578.0	538.7	495.4	462.4	440.0
45°	1115.5	1023.4	862.9	715.2	621.6	562.8	531.1	502.4	463.3	431.2	411.9
47.5°	1005.4	961.6	811.2	666.2	570.1	513.5	480.5	457.5	428.9	403.0	384.5
50°	929.1	910.9	776.3	632.8	535.6	480.4	448.7	427.8	407.3	381.3	364.4
52.5°	840.8	852.0	735.4	598.1	500.7	446.4	416.5	399.9	381.3	360.0	345.2
55°	716.7	757.3	664.9	540.0	448.7	396.9	368.6	353.9	343.1	327.2	314.5
57.5°	600.5	652.1	588.5	480.0	397.5	352.8	325.8	309.7	302.8	294.5	284.5
60°	531.4	582.5	534.1	439.8	363.1	320.6	296.7	283.2	276.2	270.3	261.9
62.5°	469.9	521.5	480.9	398.9	329.4	290.0	269.1	255.9	250.4	247.4	240.1
65°	385.3	429.7	402.6	335.4	281.1	246.4	227.4	218.1	213.1	212.0	207.3
67.5°	313.6	347.4	327.7	278.1	235.5	205.4	189.3	181.5	177.6	177.2	173.7
70°	266.5	298.2	283.2	238.2	201.5	177.9	164.0	157.0	154.7	154.3	152.4
72.5°	229.9	252.1	240.1	202.7	174.3	152.9	142.6	135.3	132.7	133.3	132.0
75°	170.2	186.8	179.9	153.9	131.1	117.1	108.7	104.0	101.7	102.9	101.3
77.5°	122.5	133.0	126.7	108.8	94.7	84.6	78.4	75.5	73.4	73.3	72.6
80°	92.4	98.7	95.1	84.3	72.7	64.2	59.2	57.3	56.0	55.7	55.3
82.5°	65.8	71.1	67.0	59.6	51.7	46.6	43.7	41.2	40.3	40.5	40.2
85°	33.2	35.2	33.6	29.0	26.0	23.6	22.0	20.9	20.1	20.5	19.7
87.5°	17.0	16.5	14.6	12.6	11.3	9.7	9.0	7.8	7.8	8.5	8.8
90°	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5	4.9	8.3	11.7
92.5°	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9	39.2	41.4	43.7
95°	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9	92.2	94.6	96.9
97.5°	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6	161.4	163.1	164.9
100°	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1	209.1	211.2	213.2
102.5°	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0	263.2	264.4	265.6
105°	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6	343.4	344.0	344.7
107.5°	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5	436.9	437.3	437.7
110°	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9	495.6	496.2	497.0





TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8	556.2	556.6	557.0
115°	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2	648.2	649.2	650.3
117.5°	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2	739.8	740.5	741.2
120°	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5	798.5	800.5	802.5
122.5°	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2	857.6	859.1	860.6
125°	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2	948.2	949.3	950.3
127.5°	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3	1033.4	1035.6	1037.7
130°	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3	1090.0	1092.7	1095.4
132.5°	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4	1146.0	1148.7	1151.4
135°	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9	1230.9	1232.9	1235.0
137.5°	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1	1309.8	1311.5	1313.2
140°	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9	1364.6	1366.3	1368.0
142.5°	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9	1414.5	1416.2	1418.0
145°	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9	1491.6	1492.2	1492.9
147.5°	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0	1560.2	1561.5	1562.8
150°	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6	1607.3	1607.9	1608.6
152.5°	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6	1646.5	1647.5	1648.4
155°	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5	1759.1	1758.7	1758.3
160°	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4	1791.7	1791.0	1790.3
162.5°	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6	1820.7	1819.7	1818.8
165°	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4	1858.4	1857.3	1856.3
167.5°	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6	1888.1	1886.8	1885.4
170°	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5	1905.2	1903.9	1902.5
172.5°	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0	1918.6	1917.2	1915.9
175°	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0	1932.7	1931.3	1930.0
177.5°	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7	1938.7	1937.6	1936.5
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	785.0	782.8	779.7	775.1	771.3	765.5	765.5	766.4	766.4	766.1	765.5
5°	761.1	755.4	748.4	740.3	731.7	723.3	721.8	718.6	716.3	714.8	712.9
7.5°	736.0	725.8	715.6	704.3	693.9	685.3	679.3	674.4	671.2	667.8	665.3
10°	719.0	706.2	694.3	682.3	669.1	658.6	652.1	647.4	644.0	640.9	639.3
12.5°	698.9	684.3	671.1	659.6	645.3	634.5	628.2	626.1	622.0	615.5	612.1
15°	669.5	656.0	640.2	622.7	615.7	602.6	595.2	591.8	589.5	584.4	582.9
17.5°	644.4	626.6	608.8	595.8	582.9	572.3	568.2	563.8	560.8	556.6	555.4
20°	624.3	608.4	592.2	578.2	564.7	553.1	549.6	546.5	543.4	541.5	540.0
22.5°	603.8	587.9	574.5	561.5	547.0	539.5	535.6	532.3	530.1	528.8	527.3
25°	575.1	561.2	546.1	534.5	522.9	517.9	515.5	513.6	512.1	510.2	509.8
27.5°	549.5	534.3	522.1	511.2	502.9	498.7	496.4	495.5	495.8	496.6	497.0
30°	530.3	516.3	506.2	497.0	489.3	485.4	485.0	485.0	486.6	487.0	487.8
32.5°	512.6	501.2	491.1	482.1	476.3	473.6	475.1	475.1	476.4	477.4	478.8
35°	487.0	476.9	469.2	461.4	456.4	457.6	458.3	459.1	461.0	463.3	464.9
37.5°	462.4	453.7	445.7	439.6	437.3	439.4	441.2	442.8	445.1	446.9	448.4
40°	444.7	438.2	430.5	425.1	425.9	427.0	428.6	430.5	432.4	433.5	435.2
42.5°	428.4	421.5	415.7	411.1	412.2	413.7	414.7	415.7	417.9	420.0	420.9
45°	403.4	398.0	392.5	389.9	390.6	391.4	392.2	393.3	395.3	396.9	397.2
47.5°	375.4	371.5	367.9	365.3	366.5	366.2	367.2	369.7	370.3	371.2	373.3
50°	357.4	353.9	349.6	348.9	348.9	348.9	349.2	352.3	352.3	353.9	355.5
52.5°	337.6	335.4	332.6	331.2	330.6	330.6	332.2	333.8	334.4	336.6	338.1
55°	308.2	305.9	303.7	302.5	301.6	302.5	305.6	306.3	308.2	309.4	310.5
57.5°	277.7	275.9	274.1	273.5	273.3	274.3	276.0	278.3	278.8	282.4	284.1
60°	257.6	254.9	253.4	253.4	252.6	256.0	255.3	259.1	259.9	262.3	265.0
62.5°	236.8	233.2	232.6	232.6	233.7	234.7	235.8	237.5	239.5	242.5	244.5
65°	203.5	201.5	204.2	203.8	203.1	205.4	205.4	207.3	209.6	212.4	216.6
67.5°	171.8	170.8	171.1	171.1	172.2	173.5	174.6	176.3	179.0	182.0	184.7
70°	150.5	151.6	149.7	151.3	152.4	152.8	153.5	155.8	159.0	160.9	164.0
72.5°	129.8	129.7	129.9	130.5	131.7	132.4	133.1	135.7	139.2	140.8	143.3
75°	99.8	99.4	100.6	100.6	102.5	103.3	104.0	105.2	108.3	110.6	112.6
77.5°	72.9	73.3	73.1	74.4	73.9	74.0	76.4	77.6	77.9	82.5	83.5
80°	54.9	55.7	56.0	56.5	56.9	56.0	58.8	60.0	60.0	62.6	64.6
82.5°	39.5	39.9	40.9	41.3	41.4	42.1	42.4	43.2	44.1	45.3	47.9
85°	19.7	20.9	21.3	20.9	21.3	20.5	21.6	22.0	22.4	22.4	22.4
87.5°	9.2	10.3	10.9	12.0	12.6	13.8	14.0	13.7	14.0	15.2	14.1
90°	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3	40.6	42.0	43.0
92.5°	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6	61.7	62.8	63.1
95°	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4	116.7	118.1	118.8
97.5°	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5	181.0	182.6	183.3
100°	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9	226.9	227.9	228.7
102.5°	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5	280.5	281.6	282.0
105°	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4	359.4	359.4	359.7
107.5°	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0	447.0	448.1	448.4
110°	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7	505.0	506.4	506.8



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5	563.1	564.7	565.5
115°	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4	649.7	650.1	650.1
117.5°	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1	738.1	738.0	737.5
120°	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3	797.0	796.6	796.1
122.5°	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1	856.3	855.4	854.4
125°	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0	944.6	943.3	941.9
127.5°	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9	1032.0	1030.1	1028.3
130°	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2	1090.9	1089.5	1087.6
132.5°	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9	1147.3	1145.7	1144.0
135°	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9	1232.4	1231.1	1230.1
137.5°	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9	1315.5	1314.0	1312.6
140°	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.4
142.5°	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6	1422.2	1421.9	1420.8
145°	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7	1497.4	1497.1	1496.2
147.5°	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7	1612.7	1612.7	1611.6
152.5°	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7	1653.3	1653.9	1653.3
155°	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3	1712.6	1714.0	1713.5
157.5°	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7	1763.1	1764.5	1764.3
160°	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7	1794.4	1796.0	1796.2
162.5°	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9	1823.6	1825.3	1825.1
165°	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9	1860.9	1862.9	1862.8
167.5°	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0
170°	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0
172.5°	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0	1920.2	1922.3	1922.2
175°	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0	1934.0	1936.0	1935.8
177.5°	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1	1939.7	1941.4	1941.3
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	763.4	763.1	765.2	763.7	765.2	763.1	763.4	765.5	766.1	766.4	766.4
5°	710.5	711.7	707.8	707.8	707.8	711.7	710.5	712.9	714.8	716.3	718.6
7.5°	663.5	661.8	662.0	659.8	662.0	661.8	663.5	665.3	667.8	671.2	674.4
10°	634.7	632.4	631.6	632.0	631.6	632.4	634.7	639.3	640.9	644.0	647.4
12.5°	610.9	610.4	605.3	605.4	605.3	610.4	610.9	612.1	615.5	622.0	626.1
15°	582.9	575.5	574.7	577.0	574.7	575.5	582.9	582.9	584.4	589.5	591.8
17.5°	554.8	550.9	551.2	550.0	551.2	550.9	554.8	555.4	556.6	560.8	563.8
20°	540.0	537.7	537.2	534.5	537.2	537.7	540.0	540.0	541.5	543.4	546.5
22.5°	526.3	525.5	525.7	522.8	525.7	525.5	526.3	527.3	528.8	530.1	532.3
25°	509.4	511.3	509.8	509.8	509.8	511.3	509.4	509.8	510.2	512.1	513.6
27.5°	498.0	497.9	497.1	497.1	497.1	497.9	498.0	497.0	496.6	495.8	495.5
30°	489.3	488.9	489.7	489.7	489.7	488.9	489.3	487.8	487.0	486.6	485.0
32.5°	480.6	481.1	481.3	481.6	481.3	481.1	480.6	478.8	477.4	476.4	475.1
35°	467.3	467.6	468.8	468.0	468.8	467.6	467.3	464.9	463.3	461.0	459.1
37.5°	449.1	450.9	450.5	451.1	450.5	450.9	449.1	448.4	446.9	445.1	442.8
40°	435.6	436.7	436.3	436.3	436.3	436.7	435.6	435.2	433.5	432.4	430.5
42.5°	421.6	422.4	421.4	420.8	421.4	422.4	421.6	420.9	420.0	417.9	415.7
45°	398.8	398.0	399.2	397.6	399.2	398.0	398.8	397.2	396.9	395.3	393.3
47.5°	373.2	374.1	374.4	375.5	374.4	374.1	373.2	373.3	371.2	370.3	369.7
50°	356.2	358.5	358.5	358.2	358.5	358.5	356.2	355.5	353.9	352.3	352.3
52.5°	339.5	340.6	342.1	342.0	342.1	340.6	339.5	338.1	336.6	334.4	333.8
55°	313.7	314.5	315.2	315.6	315.2	314.5	313.7	310.5	309.4	308.2	306.3
57.5°	286.9	286.6	288.4	289.0	288.4	286.6	286.9	284.1	282.4	278.8	278.3
60°	268.0	268.0	271.1	272.3	271.1	268.0	268.0	265.0	262.3	259.9	259.1
62.5°	247.9	249.1	252.3	250.6	252.3	249.1	247.9	244.5	242.5	239.5	237.5
65°	218.5	221.7	221.3	222.8	221.3	221.7	218.5	216.6	212.4	209.6	207.3
67.5°	187.8	189.8	192.6	192.8	192.6	189.8	187.8	184.7	182.0	179.0	176.3
70°	167.1	169.1	170.6	171.7	170.6	169.1	167.1	164.0	160.9	159.0	155.8
72.5°	146.9	147.9	151.7	150.1	151.7	147.9	146.9	143.3	140.8	139.2	135.7
75°	115.2	118.0	120.3	119.2	120.3	118.0	115.2	112.6	110.6	108.3	105.2
77.5°	85.2	88.0	89.1	88.1	89.1	88.0	85.2	83.5	82.5	77.9	77.6
80°	67.3	67.0	69.3	68.9	69.3	67.0	67.3	64.6	62.6	60.0	60.0
82.5°	49.4	49.0	50.1	50.3	50.1	49.0	49.4	47.9	45.3	44.1	43.2
85°	23.9	25.1	23.6	23.2	23.6	25.1	23.9	22.4	22.4	22.4	22.0
87.5°	14.3	14.4	14.2	14.1	14.2	14.4	14.3	14.1	15.2	14.0	13.7
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3
92.5°	62.7	62.3	61.9	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6
95°	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4
97.5°	183.2	183.0	182.9	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5
100°	229.4	230.1	230.8	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9
102.5°	281.9	281.7	281.6	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5
105°	360.4	361.1	361.7	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4
107.5°	448.0	447.6	447.2	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0
110°	506.0	505.4	504.7	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	565.4	565.2	565.1	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5
115°	649.7	649.4	649.0	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4
117.5°	736.5	735.6	734.7	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1
120°	795.5	794.8	794.1	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3
122.5°	853.5	852.5	851.6	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1
125°	940.6	939.3	937.9	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0
127.5°	1026.8	1025.2	1023.7	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9
130°	1085.3	1082.9	1080.6	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2
132.5°	1142.2	1140.3	1138.4	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9
135°	1229.4	1228.7	1228.1	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9
137.5°	1311.3	1310.1	1308.8	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9
140°	1367.0	1364.6	1362.2	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4
142.5°	1419.0	1417.1	1415.3	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6
145°	1494.9	1493.6	1492.2	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7
147.5°	1565.8	1563.8	1561.7	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8
150°	1609.6	1607.6	1605.6	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7
152.5°	1651.4	1649.7	1647.9	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7
155°	1711.1	1708.8	1706.4	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3
157.5°	1762.4	1760.5	1758.6	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7
160°	1794.9	1793.5	1792.2	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7
162.5°	1822.9	1820.8	1818.6	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9
165°	1860.4	1858.1	1855.6	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9
167.5°	1891.0	1888.9	1886.7	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9
170°	1907.6	1905.2	1902.9	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2
172.5°	1919.8	1917.4	1915.0	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0
175°	1933.5	1931.1	1928.7	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0
177.5°	1939.3	1937.4	1935.6	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	765.5	765.5	771.3	775.1	779.7	782.8	785.0	787.2	790.8	795.9	801.4
5°	721.8	723.3	731.7	740.3	748.4	755.4	761.1	768.1	776.7	787.1	798.7
7.5°	679.3	685.3	693.9	704.3	715.6	725.8	736.0	747.5	759.4	774.9	791.1
10°	652.1	658.6	669.1	682.3	694.3	706.2	719.0	731.3	746.5	764.7	785.6
12.5°	628.2	634.5	645.3	659.6	671.1	684.3	698.9	715.0	732.0	753.9	777.5
15°	595.2	602.6	615.7	622.7	640.2	656.0	669.5	692.7	714.4	736.8	764.3
17.5°	568.2	572.3	582.9	595.8	608.8	626.6	644.4	663.7	685.3	712.8	747.1
20°	549.6	553.1	564.7	578.2	592.2	608.4	624.3	643.6	667.9	697.0	734.1
22.5°	535.6	539.5	547.0	561.5	574.5	587.9	603.8	626.9	652.8	681.2	721.4
25°	515.5	517.9	522.9	534.5	546.1	561.2	575.1	596.8	623.5	656.7	697.0
27.5°	496.4	498.7	502.9	511.2	522.1	534.3	549.5	567.8	594.9	631.1	673.8
30°	485.0	485.4	489.3	497.0	506.2	516.3	530.3	551.2	576.6	613.4	658.3
32.5°	475.1	473.6	476.3	482.1	491.1	501.2	512.6	533.2	557.8	593.9	640.1
35°	458.3	457.6	456.4	461.4	469.2	476.9	487.0	502.4	530.3	563.9	612.3
37.5°	441.2	439.4	437.3	439.6	445.7	453.7	462.4	476.2	500.2	537.2	583.5
40°	428.6	427.0	425.9	425.1	430.5	438.2	444.7	458.0	480.4	515.5	561.2
42.5°	414.7	413.7	412.2	411.1	415.7	421.5	428.4	440.0	462.4	495.4	538.7
45°	392.2	391.4	390.6	389.9	392.5	398.0	403.4	411.9	431.2	463.3	502.4
47.5°	367.2	366.2	366.5	365.3	367.9	371.5	375.4	384.5	403.0	428.9	457.5
50°	349.2	348.9	348.9	348.9	349.6	353.9	357.4	364.4	381.3	407.3	427.8
52.5°	332.2	330.6	330.6	331.2	332.6	335.4	337.6	345.2	360.0	381.3	399.9
55°	305.6	302.5	301.6	302.5	303.7	305.9	308.2	314.5	327.2	343.1	353.9
57.5°	276.0	274.3	273.3	273.5	274.1	275.9	277.7	284.5	294.5	302.8	309.7
60°	255.3	256.0	252.6	253.4	253.4	254.9	257.6	261.9	270.3	276.2	283.2
62.5°	235.8	234.7	233.7	232.6	232.6	233.2	236.8	240.1	247.4	250.4	255.9
65°	205.4	205.4	203.1	203.8	204.2	201.5	203.5	207.3	212.0	213.1	218.1
67.5°	174.6	173.5	172.2	171.1	171.1	170.8	171.8	173.7	177.2	177.6	181.5
70°	153.5	152.8	152.4	151.3	149.7	151.6	150.5	152.4	154.3	154.7	157.0
72.5°	133.1	132.4	131.7	130.5	129.9	129.7	129.8	132.0	133.3	132.7	135.3
75°	104.0	103.3	102.5	100.6	100.6	99.4	99.8	101.3	102.9	101.7	104.0
77.5°	76.4	74.0	73.9	74.4	73.1	73.3	72.9	72.6	73.3	73.4	75.5
80°	58.8	56.0	56.9	56.5	56.0	55.7	54.9	55.3	55.7	56.0	57.3
82.5°	42.4	42.1	41.4	41.3	40.9	39.9	39.5	40.2	40.5	40.3	41.2
85°	21.6	20.5	21.3	20.9	21.3	20.9	19.7	19.7	20.5	20.1	20.9
87.5°	14.0	13.8	12.6	12.0	10.9	10.3	9.2	8.8	8.5	7.8	7.8
90°	37.9	36.6	32.1	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5
92.5°	59.6	58.5	55.9	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9
95°	114.0	112.7	110.0	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9
97.5°	177.9	176.3	174.4	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6
100°	224.9	223.9	222.2	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1
102.5°	278.5	277.4	275.2	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0
105°	359.4	359.4	356.4	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6
107.5°	444.8	443.7	442.5	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5
110°	502.4	501.0	500.3	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	559.9	558.3	558.2	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8
115°	649.0	648.7	649.4	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2
117.5°	738.2	738.3	739.1	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2
120°	797.6	798.0	799.6	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5
122.5°	858.0	858.9	859.8	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2
125°	947.4	948.8	949.4	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2
127.5°	1035.7	1037.6	1038.4	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3
130°	1093.6	1094.9	1095.9	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3
132.5°	1150.5	1152.2	1152.9	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4
135°	1235.2	1236.6	1236.9	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9
137.5°	1318.3	1319.7	1318.8	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1
140°	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9
142.5°	1422.9	1423.2	1422.6	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9
145°	1498.1	1498.4	1497.4	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9
147.5°	1568.8	1568.8	1567.8	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0
150°	1612.7	1612.7	1611.9	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6
152.5°	1652.2	1651.6	1651.2	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6
155°	1710.0	1708.6	1708.3	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1760.3	1758.9	1758.6	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5
160°	1791.0	1789.3	1789.3	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4
162.5°	1820.3	1818.6	1818.3	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6
165°	1856.8	1854.8	1854.8	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4
167.5°	1886.7	1884.6	1884.4	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6
170°	1902.9	1900.5	1900.5	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5
172.5°	1916.0	1913.9	1913.9	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0
175°	1930.0	1927.9	1927.9	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0
177.5°	1936.5	1934.9	1934.9	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	803.2	804.8	810.0	813.7	818.1	820.6	823.0	825.0	827.4	828.0	837.0
5°	806.8	814.6	828.1	838.1	850.5	864.0	873.3	877.6	888.8	898.1	916.7
7.5°	805.8	822.2	842.7	863.9	886.7	907.7	925.9	947.6	963.0	986.1	1009.0
10°	804.9	826.9	853.2	880.3	912.0	941.4	967.8	997.1	1021.5	1053.6	1081.1
12.5°	802.1	828.8	865.3	897.3	935.8	976.3	1015.3	1053.1	1074.7	1128.1	1153.5
15°	795.2	826.9	872.5	921.3	974.3	1022.3	1071.8	1111.2	1175.0	1221.8	1251.6
17.5°	782.0	826.5	880.6	939.4	1003.8	1067.0	1123.1	1183.0	1250.7	1307.3	1367.7
20°	775.9	824.6	884.9	949.9	1016.8	1088.3	1152.2	1224.2	1298.0	1353.7	1431.1
22.5°	764.5	819.6	884.6	957.0	1028.5	1102.6	1177.3	1249.8	1335.1	1411.9	1485.5
25°	745.7	807.6	874.8	955.7	1039.7	1113.9	1203.3	1299.6	1388.6	1487.1	1560.6
27.5°	726.1	792.1	859.6	934.7	1025.0	1113.2	1225.6	1334.3	1443.1	1528.3	1582.7
30°	710.8	775.1	844.8	920.5	1009.9	1114.7	1240.4	1359.1	1465.1	1538.2	1568.7
32.5°	694.5	759.6	821.2	900.7	995.9	1113.8	1249.7	1373.6	1466.3	1515.0	1509.0
35°	668.7	723.3	783.3	859.8	972.0	1106.9	1255.1	1374.9	1431.8	1421.4	1342.5
37.5°	631.6	677.5	736.5	820.3	944.1	1092.7	1244.3	1334.2	1330.5	1245.5	1131.1
40°	608.4	647.4	704.3	792.5	922.4	1083.4	1227.2	1285.7	1236.2	1117.4	980.5
42.5°	578.0	614.0	670.9	761.5	898.7	1064.5	1194.8	1211.6	1114.8	978.2	852.7
45°	531.1	562.8	621.6	715.2	862.9	1023.4	1115.5	1074.1	943.7	802.5	707.0
47.5°	480.5	513.5	570.1	666.2	811.2	961.6	1005.4	917.5	783.6	669.1	581.4
50°	448.7	480.4	535.6	632.8	776.3	910.9	929.1	815.4	692.4	591.8	519.8
52.5°	416.5	446.4	500.7	598.1	735.4	852.0	840.8	725.0	611.9	526.1	469.7
55°	368.6	396.9	448.7	540.0	664.9	757.3	716.7	606.1	512.5	446.0	403.0
57.5°	325.8	352.8	397.5	480.0	588.5	652.1	600.5	507.3	432.8	381.6	349.6
60°	296.7	320.6	363.1	439.8	534.1	582.5	531.4	449.1	386.4	345.4	316.8
62.5°	269.1	290.0	329.4	398.9	480.9	521.5	469.9	400.1	346.8	310.4	286.1
65°	227.4	246.4	281.1	335.4	402.6	429.7	385.3	328.7	287.4	260.3	244.1
67.5°	189.3	205.4	235.5	278.1	327.7	347.4	313.6	269.8	238.6	216.9	204.0
70°	164.0	177.9	201.5	238.2	283.2	298.2	266.5	230.6	207.7	190.3	178.3
72.5°	142.6	152.9	174.3	202.7	240.1	252.1	229.9	198.3	177.0	164.0	154.5
75°	108.7	117.1	131.1	153.9	179.9	186.8	170.2	150.5	136.1	126.8	119.5
77.5°	78.4	84.6	94.7	108.8	126.7	133.0	122.5	109.3	98.9	92.6	88.5
80°	59.2	64.2	72.7	84.3	95.1	98.7	92.4	82.4	75.0	71.6	68.1
82.5°	43.7	46.6	51.7	59.6	67.0	71.1	65.8	59.8	55.8	52.7	51.4
85°	22.0	23.6	26.0	29.0	33.6	35.2	33.2	31.7	29.4	27.5	27.5
87.5°	9.0	9.7	11.3	12.6	14.6	16.5	17.0	17.3	17.9	17.8	17.8
90°	4.9	8.3	11.7	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3
92.5°	39.2	41.4	43.7	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6
95°	92.2	94.6	96.9	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4
97.5°	161.4	163.1	164.9	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5
100°	209.1	211.2	213.2	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9
102.5°	263.2	264.4	265.6	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5
105°	343.4	344.0	344.7	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4
107.5°	436.9	437.3	437.7	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0
110°	495.6	496.2	497.0	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7





TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	556.2	556.6	557.0	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5
115°	648.2	649.2	650.3	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4
117.5°	739.8	740.5	741.2	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1
120°	798.5	800.5	802.5	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3
122.5°	857.6	859.1	860.6	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1
125°	948.2	949.3	950.3	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0
127.5°	1033.4	1035.6	1037.7	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9
130°	1090.0	1092.7	1095.4	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2
132.5°	1146.0	1148.7	1151.4	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9
135°	1230.9	1232.9	1235.0	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9
137.5°	1309.8	1311.5	1313.2	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9
140°	1364.6	1366.3	1368.0	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4
142.5°	1414.5	1416.2	1418.0	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6
145°	1491.6	1492.2	1492.9	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7
147.5°	1560.2	1561.5	1562.8	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8
150°	1607.3	1607.9	1608.6	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7
152.5°	1646.5	1647.5	1648.4	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7
155°	1707.1	1707.1	1707.1	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3
157.5°	1759.1	1758.7	1758.3	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7
160°	1791.7	1791.0	1790.3	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7
162.5°	1820.7	1819.7	1818.8	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9
165°	1858.4	1857.3	1856.3	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9
167.5°	1888.1	1886.8	1885.4	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9
170°	1905.2	1903.9	1902.5	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2
172.5°	1918.6	1917.2	1915.9	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0
175°	1932.7	1931.3	1930.0	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0
177.5°	1938.7	1937.6	1936.5	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	840.1	840.4	843.7	846.3	845.1	846.6	847.2
5°	917.8	931.7	939.1	944.5	944.9	945.2	948.4
7.5°	1028.0	1043.0	1053.9	1070.5	1075.4	1081.1	1079.4
10°	1108.5	1130.5	1149.5	1159.5	1170.3	1186.2	1173.5
12.5°	1183.7	1222.7	1251.6	1267.2	1277.5	1280.6	1274.3
15°	1307.7	1358.8	1386.2	1385.4	1420.3	1435.3	1411.7
17.5°	1421.4	1468.5	1506.2	1525.6	1554.6	1561.0	1558.1
20°	1491.0	1542.5	1571.9	1605.1	1620.2	1633.8	1636.1
22.5°	1551.1	1597.2	1628.8	1656.5	1669.1	1675.5	1679.4
25°	1612.9	1649.2	1668.2	1677.8	1681.3	1680.5	1675.5
27.5°	1608.6	1611.3	1590.5	1570.0	1551.7	1531.0	1523.9
30°	1566.8	1534.3	1476.3	1443.4	1395.1	1356.8	1372.3
32.5°	1456.9	1392.3	1327.2	1255.3	1195.8	1178.9	1161.8
35°	1243.4	1129.7	1063.3	985.9	954.9	924.0	902.7
37.5°	1006.0	918.1	839.1	788.5	757.5	738.0	727.4
40°	869.9	790.5	725.6	684.6	661.0	638.9	635.8
42.5°	761.2	687.5	638.6	606.0	583.3	574.0	567.1
45°	623.5	572.0	539.2	515.9	500.9	495.0	487.4
47.5°	527.8	491.4	466.7	450.9	439.5	435.2	434.5
50°	474.2	444.0	425.9	413.4	404.6	403.0	396.9
52.5°	433.9	407.8	393.6	382.8	376.4	372.0	370.2
55°	376.7	359.3	346.6	340.3	335.4	331.0	331.0
57.5°	329.6	315.1	306.6	301.3	299.8	296.8	294.9
60°	300.5	288.1	281.6	276.9	273.9	274.2	270.7
62.5°	272.1	264.0	257.7	253.1	249.4	249.4	249.7
65°	231.7	225.5	220.9	219.3	217.0	214.3	215.0
67.5°	196.3	190.6	186.9	184.3	183.5	182.0	184.3
70°	171.0	166.7	164.0	161.7	160.9	161.3	163.2
72.5°	147.7	144.7	143.0	141.9	140.2	140.3	141.6
75°	116.0	113.7	112.2	111.0	110.6	110.6	110.6
77.5°	85.2	84.7	84.0	82.3	82.4	82.8	82.9
80°	67.3	66.1	65.7	64.9	63.8	63.0	64.9
82.5°	50.3	49.1	48.8	48.6	46.8	46.7	48.3
85°	27.1	26.0	26.3	26.0	26.0	25.5	25.5
87.5°	17.7	17.7	17.6	18.0	17.9	17.7	18.4
90°	40.6	42.0	43.0	43.6	44.3	45.0	45.6
92.5°	61.7	62.8	63.1	62.7	62.3	61.9	61.5
95°	116.7	118.1	118.8	118.8	118.8	118.8	118.8
97.5°	181.0	182.6	183.3	183.2	183.0	182.9	182.8
100°	226.9	227.9	228.7	229.4	230.1	230.8	231.5
102.5°	280.5	281.6	282.0	281.9	281.7	281.6	281.4
105°	359.4	359.4	359.7	360.4	361.1	361.7	362.4
107.5°	447.0	448.1	448.4	448.0	447.6	447.2	446.8
110°	505.0	506.4	506.8	506.0	505.4	504.7	504.0



TEST NUMBER: P332145-840

CATALOG NUMBER: S123DIW-S560D1535U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	563.1	564.7	565.5	565.4	565.2	565.1	564.9
115°	649.7	650.1	650.1	649.7	649.4	649.0	648.7
117.5°	738.1	738.0	737.5	736.5	735.6	734.7	733.7
120°	797.0	796.6	796.1	795.5	794.8	794.1	793.3
122.5°	856.3	855.4	854.4	853.5	852.5	851.6	850.6
125°	944.6	943.3	941.9	940.6	939.3	937.9	936.5
127.5°	1032.0	1030.1	1028.3	1026.8	1025.2	1023.7	1022.1
130°	1090.9	1089.5	1087.6	1085.3	1082.9	1080.6	1078.1
132.5°	1147.3	1145.7	1144.0	1142.2	1140.3	1138.4	1136.6
135°	1232.4	1231.1	1230.1	1229.4	1228.7	1228.1	1227.4
137.5°	1315.5	1314.0	1312.6	1311.3	1310.1	1308.8	1307.5
140°	1371.1	1370.7	1369.4	1367.0	1364.6	1362.2	1359.9
142.5°	1422.2	1421.9	1420.8	1419.0	1417.1	1415.3	1413.5
145°	1497.4	1497.1	1496.2	1494.9	1493.6	1492.2	1490.9
147.5°	1568.8	1568.8	1567.8	1565.8	1563.8	1561.7	1559.6
150°	1612.7	1612.7	1611.6	1609.6	1607.6	1605.6	1603.6
152.5°	1653.3	1653.9	1653.3	1651.4	1649.7	1647.9	1646.2
155°	1712.6	1714.0	1713.5	1711.1	1708.8	1706.4	1704.0
157.5°	1763.1	1764.5	1764.3	1762.4	1760.5	1758.6	1756.8
160°	1794.4	1796.0	1796.2	1794.9	1793.5	1792.2	1790.8
162.5°	1823.6	1825.3	1825.1	1822.9	1820.8	1818.6	1816.4
165°	1860.9	1862.9	1862.8	1860.4	1858.1	1855.6	1853.3
167.5°	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6
170°	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5
172.5°	1920.2	1922.3	1922.2	1919.8	1917.4	1915.0	1912.7
175°	1934.0	1936.0	1935.8	1933.5	1931.1	1928.7	1926.4
177.5°	1939.7	1941.4	1941.3	1939.3	1937.4	1935.6	1933.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5

(END OF REPORT)