

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332725-927

Luminaire Tested: **S124DIW-S350D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332725-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D770U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3635.1 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	19	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.2
10°-20°	124.2	3.4
20°-30°	182.8	5.0
30°-40°	212.5	5.8
40°-50°	212.5	5.8
50°-60°	185.9	5.1
60°-70°	138.0	3.8
70°-80°	78.4	2.2
80°-90°	24.9	0.7
90°-100°	26.9	0.7
100°-110°	171.5	4.7
110°-120°	328.0	9.0
120°-130°	416.3	11.5
130°-140°	445.5	12.3
140°-150°	416.6	11.5
150°-160°	335.9	9.2
160°-170°	216.7	6.0
170°-180°	74.7	2.1
0°-30°	351.0	9.7
0°-40°	563.5	15.5
0°-60°	961.8	26.5
0°-90°	1203.1	33.1
90°-120°	526.3	14.5
90°-150°	1804.7	49.6
90°-180°	2432.0	66.9
0°-180°	3635.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	2	8	13	16	18	3
95°	32	14	13	16	17	42
105°	177	180	184	187	168	185
115°	330	332	332	333	333	325
125°	464	467	466	467	468	415
135°	576	576	578	579	580	444
145°	664	666	666	667	668	415
155°	729	729	727	729	728	336
165°	769	766	766	770	765	217
175°	786	783	783	788	782	75
180°	786	786	786	786	786	



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.2	8.4	8.6	8.8	9.0	9.2	9.3	9.5	9.7	9.8	10.0
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	7.4	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2
95°	32.3	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7
97.5°	68.7	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6
100°	96.4	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7
102.5°	127.5	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7
105°	177.0	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7
107.5°	223.0	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3
110°	254.1	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.2	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9
115°	330.5	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9
117.5°	372.2	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8
120°	400.4	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5
122.5°	426.8	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2
125°	464.5	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1
127.5°	500.3	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5
130°	523.3	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9
132.5°	544.5	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0
135°	576.2	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3
137.5°	604.4	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4
140°	622.7	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4
142.5°	639.2	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3
145°	664.5	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4
147.5°	684.6	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4
150°	699.2	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9
152.5°	711.4	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4
155°	728.6	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9
157.5°	743.1	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3
160°	751.5	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0
162.5°	759.0	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0
165°	768.6	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7
167.5°	776.1	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8
170°	780.3	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4
172.5°	783.2	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3
175°	786.2	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4
177.5°	787.6	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	10.1	10.2	10.4	10.5	10.5	10.6	10.7	10.7
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.0	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	14.5	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.7	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	21.5	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	76.8	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	185.8	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	229.9	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	259.8	260.1	260.4	260.7	261.1	261.5	261.9	262.3



TEST NUMBER: P332725-927

CATALOG NUMBER: S124DIW-S350D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.8	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.2	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.4	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.5	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	525.9	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.0	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.5	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	607.8	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	625.8	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.6	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.5	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.5	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.6	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	728.4	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	757.8	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	767.7	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	775.0	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	779.4	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	782.3	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	785.6	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.0	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)