

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332126-840

Luminaire Tested: **S123DIW-S560D755U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332126-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5462.5 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8593	8593	8593	8593
5°	10247	8630	7648	8630
10°	12826	8587	6908	8587
15°	15731	8517	6430	8517
20°	18741	8409	6123	8409
25°	19899	8278	6055	8278
30°	17056	8182	6087	8182
35°	11862	8046	6150	8046
40°	8934	7886	6131	7886
45°	7419	7648	6052	7648
50°	6646	7164	5998	7164
55°	6212	6641	5923	6641
60°	5828	6097	5862	6097
65°	5476	5555	5675	5555
70°	5136	4941	5404	4941
75°	4600	4325	4957	4325
80°	4023	3552	4271	3552
85°	3149	2581	2865	2581



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	1.4
10°-20°	252.2	4.6
20°-30°	423.2	7.7
30°-40°	479.2	8.8
40°-50°	429.7	7.9
50°-60°	346.8	6.3
60°-70°	241.7	4.4
70°-80°	127.0	2.3
80°-90°	33.9	0.6
90°-100°	36.4	0.7
100°-110°	173.3	3.2
110°-120°	416.3	7.6
120°-130°	530.1	9.7
130°-140°	566.4	10.4
140°-150°	529.7	9.7
150°-160°	427.3	7.8
160°-170°	275.7	5.0
170°-180°	95.0	1.7
0°-30°	754.0	13.8
0°-40°	1233.2	22.6
0°-60°	2009.7	36.8
0°-90°	2412.2	44.2
90°-120°	626.0	11.5
90°-150°	2252.2	41.2
90°-180°	3050.0	55.8
0°-180°	5462.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	948	799	708	799	948	98
15°	1412	764	577	764	1412	408
25°	1676	697	510	697	1676	735
35°	903	612	468	612	903	586
45°	487	502	398	502	487	386
55°	331	354	316	354	331	297
65°	215	218	223	218	215	214
75°	111	104	119	104	111	118
85°	26	21	23	21	26	31
90°	22	1	22	1	22	11
95°	28	45	28	45	28	24
105°	33	222	33	222	33	75
115°	437	415	437	415	437	404
125°	597	586	597	586	597	534
135°	736	729	736	729	736	568
145°	849	841	849	841	849	530
155°	925	927	925	927	925	427
165°	975	977	975	977	975	275
175°	996	1000	996	1000	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	847.2	846.6	845.1	846.3	843.7	840.4	840.1	837.0	828.0	827.4	825.0
5°	948.4	945.2	944.9	944.5	939.1	931.7	917.8	916.7	898.1	888.8	877.6
7.5°	1079.4	1081.1	1075.4	1070.5	1053.9	1043.0	1028.0	1009.0	986.1	963.0	947.6
10°	1173.5	1186.2	1170.3	1159.5	1149.5	1130.5	1108.5	1081.1	1053.6	1021.5	997.1
12.5°	1274.3	1280.6	1277.5	1267.2	1251.6	1222.7	1183.7	1153.5	1128.1	1074.7	1053.1
15°	1411.7	1435.3	1420.3	1385.4	1386.2	1358.8	1307.7	1251.6	1221.8	1175.0	1111.2
17.5°	1558.1	1561.0	1554.6	1525.6	1506.2	1468.5	1421.4	1367.7	1307.3	1250.7	1183.0
20°	1636.1	1633.8	1620.2	1605.1	1571.9	1542.5	1491.0	1431.1	1353.7	1298.0	1224.2
22.5°	1679.4	1675.5	1669.1	1656.5	1628.8	1597.2	1551.1	1485.5	1411.9	1335.1	1249.8
25°	1675.5	1680.5	1681.3	1677.8	1668.2	1649.2	1612.9	1560.6	1487.1	1388.6	1299.6
27.5°	1523.9	1531.0	1551.7	1570.0	1590.5	1611.3	1608.6	1582.7	1528.3	1443.1	1334.3
30°	1372.3	1356.8	1395.1	1443.4	1476.3	1534.3	1566.8	1568.7	1538.2	1465.1	1359.1
32.5°	1161.8	1178.9	1195.8	1255.3	1327.2	1392.3	1456.9	1509.0	1515.0	1466.3	1373.6
35°	902.7	924.0	954.9	985.9	1063.3	1129.7	1243.4	1342.5	1421.4	1431.8	1374.9
37.5°	727.4	738.0	757.5	788.5	839.1	918.1	1006.0	1131.1	1245.5	1330.5	1334.2
40°	635.8	638.9	661.0	684.6	725.6	790.5	869.9	980.5	1117.4	1236.2	1285.7
42.5°	567.1	574.0	583.3	606.0	638.6	687.5	761.2	852.7	978.2	1114.8	1211.6
45°	487.4	495.0	500.9	515.9	539.2	572.0	623.5	707.0	802.5	943.7	1074.1
47.5°	434.5	435.2	439.5	450.9	466.7	491.4	527.8	581.4	669.1	783.6	917.5
50°	396.9	403.0	404.6	413.4	425.9	444.0	474.2	519.8	591.8	692.4	815.4
52.5°	370.2	372.0	376.4	382.8	393.6	407.8	433.9	469.7	526.1	611.9	725.0
55°	331.0	331.0	335.4	340.3	346.6	359.3	376.7	403.0	446.0	512.5	606.1
57.5°	294.9	296.8	299.8	301.3	306.6	315.1	329.6	349.6	381.6	432.8	507.3
60°	270.7	274.2	273.9	276.9	281.6	288.1	300.5	316.8	345.4	386.4	449.1
62.5°	249.7	249.4	249.4	253.1	257.7	264.0	272.1	286.1	310.4	346.8	400.1
65°	215.0	214.3	217.0	219.3	220.9	225.5	231.7	244.1	260.3	287.4	328.7
67.5°	184.3	182.0	183.5	184.3	186.9	190.6	196.3	204.0	216.9	238.6	269.8
70°	163.2	161.3	160.9	161.7	164.0	166.7	171.0	178.3	190.3	207.7	230.6
72.5°	141.6	140.3	140.2	141.9	143.0	144.7	147.7	154.5	164.0	177.0	198.3
75°	110.6	110.6	110.6	111.0	112.2	113.7	116.0	119.5	126.8	136.1	150.5
77.5°	82.9	82.8	82.4	82.3	84.0	84.7	85.2	88.5	92.6	98.9	109.3
80°	64.9	63.0	63.8	64.9	65.7	66.1	67.3	68.1	71.6	75.0	82.4
82.5°	48.3	46.7	46.8	48.6	48.8	49.1	50.3	51.4	52.7	55.8	59.8
85°	25.5	25.5	26.0	26.0	26.3	26.0	27.1	27.5	27.5	29.4	31.7
87.5°	13.7	13.0	13.3	13.5	13.1	13.3	13.5	13.7	13.9	14.0	13.9
90°	22.3	21.9	21.6	21.3	21.0	20.5	19.8	19.2	18.5	17.9	15.7
92.5°	24.6	24.4	24.2	24.0	23.8	23.2	22.2	21.1	20.1	19.0	17.4
95°	28.3	28.3	28.3	28.3	28.3	27.7	26.5	25.3	24.2	23.0	21.2
97.5°	30.6	30.5	30.3	30.1	30.0	29.2	27.9	26.6	25.2	23.9	35.9
100°	31.2	31.0	30.9	30.7	30.6	29.8	28.5	27.2	25.9	24.5	50.3
102.5°	31.8	31.5	31.2	30.9	30.6	32.5	36.7	40.7	44.8	48.9	77.1
105°	32.7	32.4	32.0	31.7	31.4	45.8	75.0	104.3	133.5	162.8	177.6
107.5°	102.7	124.7	146.7	168.7	190.9	212.6	234.0	255.4	276.8	298.3	296.0
110°	204.4	227.9	251.6	275.2	298.8	313.4	318.8	324.3	329.7	335.2	333.4



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.6	355.6	360.6	365.6	370.5	373.0	372.9	372.8	372.7	372.6	370.8
115°	437.0	436.3	435.7	434.9	434.3	433.1	431.5	429.9	428.2	426.6	425.1
117.5°	485.4	485.2	485.1	485.0	484.8	484.1	482.8	481.5	480.2	478.9	478.1
120°	518.7	518.7	518.7	518.7	518.7	518.1	516.7	515.4	514.1	512.7	512.3
122.5°	551.4	551.3	551.1	551.0	550.9	550.4	549.4	548.5	547.5	546.6	546.0
125°	597.4	597.1	596.8	596.5	596.1	595.8	595.5	595.1	594.8	594.5	593.8
127.5°	641.8	642.1	642.4	642.8	643.1	643.0	642.5	642.0	641.4	640.9	640.1
130°	670.2	670.7	671.0	671.3	671.7	671.5	670.8	670.1	669.4	668.8	668.1
132.5°	696.4	696.9	697.4	697.8	698.3	698.2	697.5	696.9	696.2	695.6	695.0
135°	736.4	736.9	737.4	737.9	738.4	738.4	737.9	737.4	736.9	736.4	735.8
137.5°	774.1	774.4	774.7	775.1	775.4	775.2	774.4	773.6	772.7	771.9	771.6
140°	796.6	797.0	797.3	797.6	798.0	797.8	797.1	796.5	795.8	795.2	794.7
142.5°	817.4	817.9	818.4	818.8	819.3	819.2	818.7	818.2	817.7	817.2	816.7
145°	849.4	849.4	849.4	849.4	849.4	849.2	848.9	848.6	848.2	847.9	847.6
147.5°	873.1	873.9	874.6	875.5	876.2	876.5	876.1	875.8	875.5	875.0	874.7
150°	891.0	891.5	892.0	892.5	893.0	893.0	892.7	892.4	892.1	891.7	891.4
152.5°	905.2	906.1	906.8	907.6	908.3	908.4	907.8	907.2	906.6	906.1	905.8
155°	925.1	926.1	927.2	928.2	929.2	929.3	928.4	927.6	926.8	925.9	925.7
157.5°	942.0	943.3	944.5	945.8	947.2	947.3	946.2	945.3	944.3	943.3	943.5
160°	952.7	953.8	955.0	956.1	957.4	957.4	956.4	955.4	954.4	953.4	953.6
162.5°	962.8	963.8	964.8	965.8	966.8	966.8	965.7	964.6	963.5	962.3	962.5
165°	974.9	976.1	977.2	978.5	979.6	979.5	978.2	976.8	975.5	974.2	974.4
167.5°	983.7	985.0	986.3	987.7	989.1	989.1	987.7	986.3	985.0	983.7	983.7
170°	989.1	990.4	991.7	993.1	994.4	994.4	993.1	991.7	990.4	989.1	989.1
172.5°	992.1	993.5	995.0	996.4	997.8	997.9	996.6	995.3	994.0	992.7	992.5
175°	996.5	997.8	999.2	1000.5	1001.8	1001.9	1000.8	999.6	998.5	997.2	997.1
177.5°	997.8	999.2	1000.5	1001.8	1003.1	1003.3	1002.2	1001.2	1000.1	999.1	999.0
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	823.0	820.6	818.1	813.7	810.0	804.8	803.2	801.4	795.9	790.8	787.2
5°	873.3	864.0	850.5	838.1	828.1	814.6	806.8	798.7	787.1	776.7	768.1
7.5°	925.9	907.7	886.7	863.9	842.7	822.2	805.8	791.1	774.9	759.4	747.5
10°	967.8	941.4	912.0	880.3	853.2	826.9	804.9	785.6	764.7	746.5	731.3
12.5°	1015.3	976.3	935.8	897.3	865.3	828.8	802.1	777.5	753.9	732.0	715.0
15°	1071.8	1022.3	974.3	921.3	872.5	826.9	795.2	764.3	736.8	714.4	692.7
17.5°	1123.1	1067.0	1003.8	939.4	880.6	826.5	782.0	747.1	712.8	685.3	663.7
20°	1152.2	1088.3	1016.8	949.9	884.9	824.6	775.9	734.1	697.0	667.9	643.6
22.5°	1177.3	1102.6	1028.5	957.0	884.6	819.6	764.5	721.4	681.2	652.8	626.9
25°	1203.3	1113.9	1039.7	955.7	874.8	807.6	745.7	697.0	656.7	623.5	596.8
27.5°	1225.6	1113.2	1025.0	934.7	859.6	792.1	726.1	673.8	631.1	594.9	567.8
30°	1240.4	1114.7	1009.9	920.5	844.8	775.1	710.8	658.3	613.4	576.6	551.2
32.5°	1249.7	1113.8	995.9	900.7	821.2	759.6	694.5	640.1	593.9	557.8	533.2
35°	1255.1	1106.9	972.0	859.8	783.3	723.3	668.7	612.3	563.9	530.3	502.4
37.5°	1244.3	1092.7	944.1	820.3	736.5	677.5	631.6	583.5	537.2	500.2	476.2
40°	1227.2	1083.4	922.4	792.5	704.3	647.4	608.4	561.2	515.5	480.4	458.0
42.5°	1194.8	1064.5	898.7	761.5	670.9	614.0	578.0	538.7	495.4	462.4	440.0
45°	1115.5	1023.4	862.9	715.2	621.6	562.8	531.1	502.4	463.3	431.2	411.9
47.5°	1005.4	961.6	811.2	666.2	570.1	513.5	480.5	457.5	428.9	403.0	384.5
50°	929.1	910.9	776.3	632.8	535.6	480.4	448.7	427.8	407.3	381.3	364.4
52.5°	840.8	852.0	735.4	598.1	500.7	446.4	416.5	399.9	381.3	360.0	345.2
55°	716.7	757.3	664.9	540.0	448.7	396.9	368.6	353.9	343.1	327.2	314.5
57.5°	600.5	652.1	588.5	480.0	397.5	352.8	325.8	309.7	302.8	294.5	284.5
60°	531.4	582.5	534.1	439.8	363.1	320.6	296.7	283.2	276.2	270.3	261.9
62.5°	469.9	521.5	480.9	398.9	329.4	290.0	269.1	255.9	250.4	247.4	240.1
65°	385.3	429.7	402.6	335.4	281.1	246.4	227.4	218.1	213.1	212.0	207.3
67.5°	313.6	347.4	327.7	278.1	235.5	205.4	189.3	181.5	177.6	177.2	173.7
70°	266.5	298.2	283.2	238.2	201.5	177.9	164.0	157.0	154.7	154.3	152.4
72.5°	229.9	252.1	240.1	202.7	174.3	152.9	142.6	135.3	132.7	133.3	132.0
75°	170.2	186.8	179.9	153.9	131.1	117.1	108.7	104.0	101.7	102.9	101.3
77.5°	122.5	133.0	126.7	108.8	94.7	84.6	78.4	75.5	73.4	73.3	72.6
80°	92.4	98.7	95.1	84.3	72.7	64.2	59.2	57.3	56.0	55.7	55.3
82.5°	65.8	71.1	67.0	59.6	51.7	46.6	43.7	41.2	40.3	40.5	40.2
85°	33.2	35.2	33.6	29.0	26.0	23.6	22.0	20.9	20.1	20.5	19.7
87.5°	14.1	14.0	12.7	11.1	10.1	8.9	8.5	7.6	7.3	7.6	7.7
90°	13.5	11.4	9.3	7.4	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	15.8	14.1	12.5	12.0	12.4	12.9	13.3	13.8	13.3	12.9	12.4
95°	19.4	17.6	15.8	18.3	25.0	31.8	38.6	45.3	38.6	31.8	25.0
97.5°	47.7	59.6	71.5	79.0	82.0	85.0	88.1	91.1	88.1	85.0	82.0
100°	76.0	101.8	127.5	138.8	135.5	132.2	128.9	125.6	128.9	132.2	135.5
102.5°	105.1	133.3	161.5	174.3	172.0	169.6	167.2	164.8	167.2	169.6	172.0
105°	192.5	207.3	222.2	228.7	226.9	225.1	223.3	221.5	223.3	225.1	226.9
107.5°	293.6	291.2	288.9	287.0	285.6	284.1	282.7	281.1	282.7	284.1	285.6
110°	331.5	329.7	327.9	326.3	325.0	323.7	322.3	321.0	322.3	323.7	325.0



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.0	367.2	365.4	363.9	362.6	361.4	360.2	359.1	360.2	361.4	362.6
115°	423.5	422.1	420.6	419.4	418.4	417.4	416.4	415.4	416.4	417.4	418.4
117.5°	477.4	476.6	475.8	474.8	473.6	472.4	471.2	470.0	471.2	472.4	473.6
120°	511.8	511.3	510.8	509.8	508.3	506.9	505.3	503.8	505.3	506.9	508.3
122.5°	545.4	544.7	544.1	543.2	542.0	540.8	539.6	538.4	539.6	540.8	542.0
125°	593.2	592.5	591.9	590.9	589.6	588.2	586.9	585.6	586.9	588.2	589.6
127.5°	639.2	638.5	637.7	636.6	635.3	634.0	632.7	631.4	632.7	634.0	635.3
130°	667.5	666.8	666.2	665.2	663.9	662.6	661.3	659.8	661.3	662.6	663.9
132.5°	694.5	694.0	693.5	692.6	691.2	689.8	688.5	687.2	688.5	689.8	691.2
135°	735.1	734.5	733.8	733.0	732.0	730.9	730.0	729.0	730.0	730.9	732.0
137.5°	771.2	770.8	770.5	769.7	768.4	767.2	765.9	764.7	765.9	767.2	768.4
140°	794.2	793.7	793.1	792.4	791.4	790.4	789.4	788.4	789.4	790.4	791.4
142.5°	816.2	815.7	815.2	814.5	813.4	812.4	811.4	810.4	811.4	812.4	813.4
145°	847.3	846.9	846.6	845.9	844.7	843.5	842.3	841.2	842.3	843.5	844.7
147.5°	874.4	874.1	873.7	873.2	872.4	871.7	870.9	870.2	870.9	871.7	872.4
150°	891.1	890.8	890.4	890.0	889.5	889.0	888.5	888.1	888.5	889.0	889.5
152.5°	905.6	905.4	905.2	905.0	904.7	904.5	904.3	904.0	904.3	904.5	904.7
155°	925.6	925.4	925.2	925.3	925.6	926.0	926.3	926.7	926.3	926.0	925.6
157.5°	943.6	943.8	944.0	944.1	944.1	944.1	944.2	944.2	944.2	944.1	944.1
160°	953.7	953.9	954.1	954.2	954.4	954.6	954.7	954.9	954.7	954.6	954.4
162.5°	962.7	962.8	963.0	963.3	963.7	964.1	964.6	965.0	964.6	964.1	963.7
165°	974.5	974.7	974.9	975.2	975.7	976.2	976.7	977.2	976.7	976.2	975.7
167.5°	983.7	983.7	983.7	984.1	984.7	985.4	986.0	986.7	986.0	985.4	984.7
170°	989.1	989.1	989.1	989.5	990.1	990.8	991.4	992.1	991.4	990.8	990.1
172.5°	992.4	992.3	992.1	992.5	993.3	994.0	994.8	995.6	994.8	994.0	993.3
175°	996.9	996.7	996.6	996.9	997.7	998.6	999.4	1000.3	999.4	998.6	997.7
177.5°	998.8	998.7	998.6	998.8	999.5	1000.1	1000.8	1001.4	1000.8	1000.1	999.5
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	785.0	782.8	779.7	775.1	771.3	765.5	765.5	766.4	766.4	766.1	765.5
5°	761.1	755.4	748.4	740.3	731.7	723.3	721.8	718.6	716.3	714.8	712.9
7.5°	736.0	725.8	715.6	704.3	693.9	685.3	679.3	674.4	671.2	667.8	665.3
10°	719.0	706.2	694.3	682.3	669.1	658.6	652.1	647.4	644.0	640.9	639.3
12.5°	698.9	684.3	671.1	659.6	645.3	634.5	628.2	626.1	622.0	615.5	612.1
15°	669.5	656.0	640.2	622.7	615.7	602.6	595.2	591.8	589.5	584.4	582.9
17.5°	644.4	626.6	608.8	595.8	582.9	572.3	568.2	563.8	560.8	556.6	555.4
20°	624.3	608.4	592.2	578.2	564.7	553.1	549.6	546.5	543.4	541.5	540.0
22.5°	603.8	587.9	574.5	561.5	547.0	539.5	535.6	532.3	530.1	528.8	527.3
25°	575.1	561.2	546.1	534.5	522.9	517.9	515.5	513.6	512.1	510.2	509.8
27.5°	549.5	534.3	522.1	511.2	502.9	498.7	496.4	495.5	495.8	496.6	497.0
30°	530.3	516.3	506.2	497.0	489.3	485.4	485.0	485.0	486.6	487.0	487.8
32.5°	512.6	501.2	491.1	482.1	476.3	473.6	475.1	475.1	476.4	477.4	478.8
35°	487.0	476.9	469.2	461.4	456.4	457.6	458.3	459.1	461.0	463.3	464.9
37.5°	462.4	453.7	445.7	439.6	437.3	439.4	441.2	442.8	445.1	446.9	448.4
40°	444.7	438.2	430.5	425.1	425.9	427.0	428.6	430.5	432.4	433.5	435.2
42.5°	428.4	421.5	415.7	411.1	412.2	413.7	414.7	415.7	417.9	420.0	420.9
45°	403.4	398.0	392.5	389.9	390.6	391.4	392.2	393.3	395.3	396.9	397.2
47.5°	375.4	371.5	367.9	365.3	366.5	366.2	367.2	369.7	370.3	371.2	373.3
50°	357.4	353.9	349.6	348.9	348.9	348.9	349.2	352.3	352.3	353.9	355.5
52.5°	337.6	335.4	332.6	331.2	330.6	330.6	332.2	333.8	334.4	336.6	338.1
55°	308.2	305.9	303.7	302.5	301.6	302.5	305.6	306.3	308.2	309.4	310.5
57.5°	277.7	275.9	274.1	273.5	273.3	274.3	276.0	278.3	278.8	282.4	284.1
60°	257.6	254.9	253.4	253.4	252.6	256.0	255.3	259.1	259.9	262.3	265.0
62.5°	236.8	233.2	232.6	232.6	233.7	234.7	235.8	237.5	239.5	242.5	244.5
65°	203.5	201.5	204.2	203.8	203.1	205.4	205.4	207.3	209.6	212.4	216.6
67.5°	171.8	170.8	171.1	171.1	172.2	173.5	174.6	176.3	179.0	182.0	184.7
70°	150.5	151.6	149.7	151.3	152.4	152.8	153.5	155.8	159.0	160.9	164.0
72.5°	129.8	129.7	129.9	130.5	131.7	132.4	133.1	135.7	139.2	140.8	143.3
75°	99.8	99.4	100.6	100.6	102.5	103.3	104.0	105.2	108.3	110.6	112.6
77.5°	72.9	73.3	73.1	74.4	73.9	74.0	76.4	77.6	77.9	82.5	83.5
80°	54.9	55.7	56.0	56.5	56.9	56.0	58.8	60.0	60.0	62.6	64.6
82.5°	39.5	39.9	40.9	41.3	41.4	42.1	42.4	43.2	44.1	45.3	47.9
85°	19.7	20.9	21.3	20.9	21.3	20.5	21.6	22.0	22.4	22.4	22.4
87.5°	7.7	8.4	8.5	9.2	9.3	10.1	10.2	9.7	9.8	10.9	9.8
90°	7.4	9.3	11.4	13.5	15.7	17.9	18.5	19.2	19.8	20.5	21.0
92.5°	12.0	12.5	14.1	15.8	17.4	19.0	20.1	21.1	22.2	23.2	23.8
95°	18.3	15.8	17.6	19.4	21.2	23.0	24.2	25.3	26.5	27.7	28.3
97.5°	79.0	71.5	59.6	47.7	35.9	23.9	25.2	26.6	27.9	29.2	30.0
100°	138.8	127.5	101.8	76.0	50.3	24.5	25.9	27.2	28.5	29.8	30.6
102.5°	174.3	161.5	133.3	105.1	77.1	48.9	44.8	40.7	36.7	32.5	30.6
105°	228.7	222.2	207.3	192.5	177.6	162.8	133.5	104.3	75.0	45.8	31.4
107.5°	287.0	288.9	291.2	293.6	296.0	298.3	276.8	255.4	234.0	212.6	190.9
110°	326.3	327.9	329.7	331.5	333.4	335.2	329.7	324.3	318.8	313.4	298.8



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	363.9	365.4	367.2	369.0	370.8	372.6	372.7	372.8	372.9	373.0	370.5
115°	419.4	420.6	422.1	423.5	425.1	426.6	428.2	429.9	431.5	433.1	434.3
117.5°	474.8	475.8	476.6	477.4	478.1	478.9	480.2	481.5	482.8	484.1	484.8
120°	509.8	510.8	511.3	511.8	512.3	512.7	514.1	515.4	516.7	518.1	518.7
122.5°	543.2	544.1	544.7	545.4	546.0	546.6	547.5	548.5	549.4	550.4	550.9
125°	590.9	591.9	592.5	593.2	593.8	594.5	594.8	595.1	595.5	595.8	596.1
127.5°	636.6	637.7	638.5	639.2	640.1	640.9	641.4	642.0	642.5	643.0	643.1
130°	665.2	666.2	666.8	667.5	668.1	668.8	669.4	670.1	670.8	671.5	671.7
132.5°	692.6	693.5	694.0	694.5	695.0	695.6	696.2	696.9	697.5	698.2	698.3
135°	733.0	733.8	734.5	735.1	735.8	736.4	736.9	737.4	737.9	738.4	738.4
137.5°	769.7	770.5	770.8	771.2	771.6	771.9	772.7	773.6	774.4	775.2	775.4
140°	792.4	793.1	793.7	794.2	794.7	795.2	795.8	796.5	797.1	797.8	798.0
142.5°	814.5	815.2	815.7	816.2	816.7	817.2	817.7	818.2	818.7	819.2	819.3
145°	845.9	846.6	846.9	847.3	847.6	847.9	848.2	848.6	848.9	849.2	849.4
147.5°	873.2	873.7	874.1	874.4	874.7	875.0	875.5	875.8	876.1	876.5	876.2
150°	890.0	890.4	890.8	891.1	891.4	891.7	892.1	892.4	892.7	893.0	893.0
152.5°	905.0	905.2	905.4	905.6	905.8	906.1	906.6	907.2	907.8	908.4	908.3
155°	925.3	925.2	925.4	925.6	925.7	925.9	926.8	927.6	928.4	929.3	929.2
157.5°	944.1	944.0	943.8	943.6	943.5	943.3	944.3	945.3	946.2	947.3	947.2
160°	954.2	954.1	953.9	953.7	953.6	953.4	954.4	955.4	956.4	957.4	957.4
162.5°	963.3	963.0	962.8	962.7	962.5	962.3	963.5	964.6	965.7	966.8	966.8
165°	975.2	974.9	974.7	974.5	974.4	974.2	975.5	976.8	978.2	979.5	979.6
167.5°	984.1	983.7	983.7	983.7	983.7	983.7	985.0	986.3	987.7	989.1	989.1
170°	989.5	989.1	989.1	989.1	989.1	989.1	990.4	991.7	993.1	994.4	994.4
172.5°	992.5	992.1	992.3	992.4	992.5	992.7	994.0	995.3	996.6	997.9	997.8
175°	996.9	996.6	996.7	996.9	997.1	997.2	998.5	999.6	1000.8	1001.9	1001.8
177.5°	998.8	998.6	998.7	998.8	999.0	999.1	1000.1	1001.2	1002.2	1003.3	1003.1
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	763.4	763.1	765.2	763.7	765.2	763.1	763.4	765.5	766.1	766.4	766.4
5°	710.5	711.7	707.8	707.8	707.8	711.7	710.5	712.9	714.8	716.3	718.6
7.5°	663.5	661.8	662.0	659.8	662.0	661.8	663.5	665.3	667.8	671.2	674.4
10°	634.7	632.4	631.6	632.0	631.6	632.4	634.7	639.3	640.9	644.0	647.4
12.5°	610.9	610.4	605.3	605.4	605.3	610.4	610.9	612.1	615.5	622.0	626.1
15°	582.9	575.5	574.7	577.0	574.7	575.5	582.9	582.9	584.4	589.5	591.8
17.5°	554.8	550.9	551.2	550.0	551.2	550.9	554.8	555.4	556.6	560.8	563.8
20°	540.0	537.7	537.2	534.5	537.2	537.7	540.0	540.0	541.5	543.4	546.5
22.5°	526.3	525.5	525.7	522.8	525.7	525.5	526.3	527.3	528.8	530.1	532.3
25°	509.4	511.3	509.8	509.8	509.8	511.3	509.4	509.8	510.2	512.1	513.6
27.5°	498.0	497.9	497.1	497.1	497.1	497.9	498.0	497.0	496.6	495.8	495.5
30°	489.3	488.9	489.7	489.7	489.7	488.9	489.3	487.8	487.0	486.6	485.0
32.5°	480.6	481.1	481.3	481.6	481.3	481.1	480.6	478.8	477.4	476.4	475.1
35°	467.3	467.6	468.8	468.0	468.8	467.6	467.3	464.9	463.3	461.0	459.1
37.5°	449.1	450.9	450.5	451.1	450.5	450.9	449.1	448.4	446.9	445.1	442.8
40°	435.6	436.7	436.3	436.3	436.3	436.7	435.6	435.2	433.5	432.4	430.5
42.5°	421.6	422.4	421.4	420.8	421.4	422.4	421.6	420.9	420.0	417.9	415.7
45°	398.8	398.0	399.2	397.6	399.2	398.0	398.8	397.2	396.9	395.3	393.3
47.5°	373.2	374.1	374.4	375.5	374.4	374.1	373.2	373.3	371.2	370.3	369.7
50°	356.2	358.5	358.5	358.2	358.5	358.5	356.2	355.5	353.9	352.3	352.3
52.5°	339.5	340.6	342.1	342.0	342.1	340.6	339.5	338.1	336.6	334.4	333.8
55°	313.7	314.5	315.2	315.6	315.2	314.5	313.7	310.5	309.4	308.2	306.3
57.5°	286.9	286.6	288.4	289.0	288.4	286.6	286.9	284.1	282.4	278.8	278.3
60°	268.0	268.0	271.1	272.3	271.1	268.0	268.0	265.0	262.3	259.9	259.1
62.5°	247.9	249.1	252.3	250.6	252.3	249.1	247.9	244.5	242.5	239.5	237.5
65°	218.5	221.7	221.3	222.8	221.3	221.7	218.5	216.6	212.4	209.6	207.3
67.5°	187.8	189.8	192.6	192.8	192.6	189.8	187.8	184.7	182.0	179.0	176.3
70°	167.1	169.1	170.6	171.7	170.6	169.1	167.1	164.0	160.9	159.0	155.8
72.5°	146.9	147.9	151.7	150.1	151.7	147.9	146.9	143.3	140.8	139.2	135.7
75°	115.2	118.0	120.3	119.2	120.3	118.0	115.2	112.6	110.6	108.3	105.2
77.5°	85.2	88.0	89.1	88.1	89.1	88.0	85.2	83.5	82.5	77.9	77.6
80°	67.3	67.0	69.3	68.9	69.3	67.0	67.3	64.6	62.6	60.0	60.0
82.5°	49.4	49.0	50.1	50.3	50.1	49.0	49.4	47.9	45.3	44.1	43.2
85°	23.9	25.1	23.6	23.2	23.6	25.1	23.9	22.4	22.4	22.4	22.0
87.5°	9.8	9.9	9.7	9.4	9.7	9.9	9.8	9.8	10.9	9.8	9.7
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	21.0	20.5	19.8	19.2
92.5°	24.0	24.2	24.4	24.6	24.4	24.2	24.0	23.8	23.2	22.2	21.1
95°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.7	26.5	25.3
97.5°	30.1	30.3	30.5	30.6	30.5	30.3	30.1	30.0	29.2	27.9	26.6
100°	30.7	30.9	31.0	31.2	31.0	30.9	30.7	30.6	29.8	28.5	27.2
102.5°	30.9	31.2	31.5	31.8	31.5	31.2	30.9	30.6	32.5	36.7	40.7
105°	31.7	32.0	32.4	32.7	32.4	32.0	31.7	31.4	45.8	75.0	104.3
107.5°	168.7	146.7	124.7	102.7	124.7	146.7	168.7	190.9	212.6	234.0	255.4
110°	275.2	251.6	227.9	204.4	227.9	251.6	275.2	298.8	313.4	318.8	324.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	365.6	360.6	355.6	350.6	355.6	360.6	365.6	370.5	373.0	372.9	372.8
115°	434.9	435.7	436.3	437.0	436.3	435.7	434.9	434.3	433.1	431.5	429.9
117.5°	485.0	485.1	485.2	485.4	485.2	485.1	485.0	484.8	484.1	482.8	481.5
120°	518.7	518.7	518.7	518.7	518.7	518.7	518.7	518.7	518.1	516.7	515.4
122.5°	551.0	551.1	551.3	551.4	551.3	551.1	551.0	550.9	550.4	549.4	548.5
125°	596.5	596.8	597.1	597.4	597.1	596.8	596.5	596.1	595.8	595.5	595.1
127.5°	642.8	642.4	642.1	641.8	642.1	642.4	642.8	643.1	643.0	642.5	642.0
130°	671.3	671.0	670.7	670.2	670.7	671.0	671.3	671.7	671.5	670.8	670.1
132.5°	697.8	697.4	696.9	696.4	696.9	697.4	697.8	698.3	698.2	697.5	696.9
135°	737.9	737.4	736.9	736.4	736.9	737.4	737.9	738.4	738.4	737.9	737.4
137.5°	775.1	774.7	774.4	774.1	774.4	774.7	775.1	775.4	775.2	774.4	773.6
140°	797.6	797.3	797.0	796.6	797.0	797.3	797.6	798.0	797.8	797.1	796.5
142.5°	818.8	818.4	817.9	817.4	817.9	818.4	818.8	819.3	819.2	818.7	818.2
145°	849.4	849.4	849.4	849.4	849.4	849.4	849.4	849.4	849.2	848.9	848.6
147.5°	875.5	874.6	873.9	873.1	873.9	874.6	875.5	876.2	876.5	876.1	875.8
150°	892.5	892.0	891.5	891.0	891.5	892.0	892.5	893.0	893.0	892.7	892.4
152.5°	907.6	906.8	906.1	905.2	906.1	906.8	907.6	908.3	908.4	907.8	907.2
155°	928.2	927.2	926.1	925.1	926.1	927.2	928.2	929.2	929.3	928.4	927.6
157.5°	945.8	944.5	943.3	942.0	943.3	944.5	945.8	947.2	947.3	946.2	945.3
160°	956.1	955.0	953.8	952.7	953.8	955.0	956.1	957.4	957.4	956.4	955.4
162.5°	965.8	964.8	963.8	962.8	963.8	964.8	965.8	966.8	966.8	965.7	964.6
165°	978.5	977.2	976.1	974.9	976.1	977.2	978.5	979.6	979.5	978.2	976.8
167.5°	987.7	986.3	985.0	983.7	985.0	986.3	987.7	989.1	989.1	987.7	986.3
170°	993.1	991.7	990.4	989.1	990.4	991.7	993.1	994.4	994.4	993.1	991.7
172.5°	996.4	995.0	993.5	992.1	993.5	995.0	996.4	997.8	997.9	996.6	995.3
175°	1000.5	999.2	997.8	996.5	997.8	999.2	1000.5	1001.8	1001.9	1000.8	999.6
177.5°	1001.8	1000.5	999.2	997.8	999.2	1000.5	1001.8	1003.1	1003.3	1002.2	1001.2
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	765.5	765.5	771.3	775.1	779.7	782.8	785.0	787.2	790.8	795.9	801.4
5°	721.8	723.3	731.7	740.3	748.4	755.4	761.1	768.1	776.7	787.1	798.7
7.5°	679.3	685.3	693.9	704.3	715.6	725.8	736.0	747.5	759.4	774.9	791.1
10°	652.1	658.6	669.1	682.3	694.3	706.2	719.0	731.3	746.5	764.7	785.6
12.5°	628.2	634.5	645.3	659.6	671.1	684.3	698.9	715.0	732.0	753.9	777.5
15°	595.2	602.6	615.7	622.7	640.2	656.0	669.5	692.7	714.4	736.8	764.3
17.5°	568.2	572.3	582.9	595.8	608.8	626.6	644.4	663.7	685.3	712.8	747.1
20°	549.6	553.1	564.7	578.2	592.2	608.4	624.3	643.6	667.9	697.0	734.1
22.5°	535.6	539.5	547.0	561.5	574.5	587.9	603.8	626.9	652.8	681.2	721.4
25°	515.5	517.9	522.9	534.5	546.1	561.2	575.1	596.8	623.5	656.7	697.0
27.5°	496.4	498.7	502.9	511.2	522.1	534.3	549.5	567.8	594.9	631.1	673.8
30°	485.0	485.4	489.3	497.0	506.2	516.3	530.3	551.2	576.6	613.4	658.3
32.5°	475.1	473.6	476.3	482.1	491.1	501.2	512.6	533.2	557.8	593.9	640.1
35°	458.3	457.6	456.4	461.4	469.2	476.9	487.0	502.4	530.3	563.9	612.3
37.5°	441.2	439.4	437.3	439.6	445.7	453.7	462.4	476.2	500.2	537.2	583.5
40°	428.6	427.0	425.9	425.1	430.5	438.2	444.7	458.0	480.4	515.5	561.2
42.5°	414.7	413.7	412.2	411.1	415.7	421.5	428.4	440.0	462.4	495.4	538.7
45°	392.2	391.4	390.6	389.9	392.5	398.0	403.4	411.9	431.2	463.3	502.4
47.5°	367.2	366.2	366.5	365.3	367.9	371.5	375.4	384.5	403.0	428.9	457.5
50°	349.2	348.9	348.9	348.9	349.6	353.9	357.4	364.4	381.3	407.3	427.8
52.5°	332.2	330.6	330.6	331.2	332.6	335.4	337.6	345.2	360.0	381.3	399.9
55°	305.6	302.5	301.6	302.5	303.7	305.9	308.2	314.5	327.2	343.1	353.9
57.5°	276.0	274.3	273.3	273.5	274.1	275.9	277.7	284.5	294.5	302.8	309.7
60°	255.3	256.0	252.6	253.4	253.4	254.9	257.6	261.9	270.3	276.2	283.2
62.5°	235.8	234.7	233.7	232.6	232.6	233.2	236.8	240.1	247.4	250.4	255.9
65°	205.4	205.4	203.1	203.8	204.2	201.5	203.5	207.3	212.0	213.1	218.1
67.5°	174.6	173.5	172.2	171.1	171.1	170.8	171.8	173.7	177.2	177.6	181.5
70°	153.5	152.8	152.4	151.3	149.7	151.6	150.5	152.4	154.3	154.7	157.0
72.5°	133.1	132.4	131.7	130.5	129.9	129.7	129.8	132.0	133.3	132.7	135.3
75°	104.0	103.3	102.5	100.6	100.6	99.4	99.8	101.3	102.9	101.7	104.0
77.5°	76.4	74.0	73.9	74.4	73.1	73.3	72.9	72.6	73.3	73.4	75.5
80°	58.8	56.0	56.9	56.5	56.0	55.7	54.9	55.3	55.7	56.0	57.3
82.5°	42.4	42.1	41.4	41.3	40.9	39.9	39.5	40.2	40.5	40.3	41.2
85°	21.6	20.5	21.3	20.9	21.3	20.9	19.7	19.7	20.5	20.1	20.9
87.5°	10.2	10.1	9.3	9.2	8.5	8.4	7.7	7.7	7.6	7.3	7.6
90°	18.5	17.9	15.7	13.5	11.4	9.3	7.4	5.7	4.0	2.4	0.7
92.5°	20.1	19.0	17.4	15.8	14.1	12.5	12.0	12.4	12.9	13.3	13.8
95°	24.2	23.0	21.2	19.4	17.6	15.8	18.3	25.0	31.8	38.6	45.3
97.5°	25.2	23.9	35.9	47.7	59.6	71.5	79.0	82.0	85.0	88.1	91.1
100°	25.9	24.5	50.3	76.0	101.8	127.5	138.8	135.5	132.2	128.9	125.6
102.5°	44.8	48.9	77.1	105.1	133.3	161.5	174.3	172.0	169.6	167.2	164.8
105°	133.5	162.8	177.6	192.5	207.3	222.2	228.7	226.9	225.1	223.3	221.5
107.5°	276.8	298.3	296.0	293.6	291.2	288.9	287.0	285.6	284.1	282.7	281.1
110°	329.7	335.2	333.4	331.5	329.7	327.9	326.3	325.0	323.7	322.3	321.0



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	372.7	372.6	370.8	369.0	367.2	365.4	363.9	362.6	361.4	360.2	359.1
115°	428.2	426.6	425.1	423.5	422.1	420.6	419.4	418.4	417.4	416.4	415.4
117.5°	480.2	478.9	478.1	477.4	476.6	475.8	474.8	473.6	472.4	471.2	470.0
120°	514.1	512.7	512.3	511.8	511.3	510.8	509.8	508.3	506.9	505.3	503.8
122.5°	547.5	546.6	546.0	545.4	544.7	544.1	543.2	542.0	540.8	539.6	538.4
125°	594.8	594.5	593.8	593.2	592.5	591.9	590.9	589.6	588.2	586.9	585.6
127.5°	641.4	640.9	640.1	639.2	638.5	637.7	636.6	635.3	634.0	632.7	631.4
130°	669.4	668.8	668.1	667.5	666.8	666.2	665.2	663.9	662.6	661.3	659.8
132.5°	696.2	695.6	695.0	694.5	694.0	693.5	692.6	691.2	689.8	688.5	687.2
135°	736.9	736.4	735.8	735.1	734.5	733.8	733.0	732.0	730.9	730.0	729.0
137.5°	772.7	771.9	771.6	771.2	770.8	770.5	769.7	768.4	767.2	765.9	764.7
140°	795.8	795.2	794.7	794.2	793.7	793.1	792.4	791.4	790.4	789.4	788.4
142.5°	817.7	817.2	816.7	816.2	815.7	815.2	814.5	813.4	812.4	811.4	810.4
145°	848.2	847.9	847.6	847.3	846.9	846.6	845.9	844.7	843.5	842.3	841.2
147.5°	875.5	875.0	874.7	874.4	874.1	873.7	873.2	872.4	871.7	870.9	870.2
150°	892.1	891.7	891.4	891.1	890.8	890.4	890.0	889.5	889.0	888.5	888.1
152.5°	906.6	906.1	905.8	905.6	905.4	905.2	905.0	904.7	904.5	904.3	904.0
155°	926.8	925.9	925.7	925.6	925.4	925.2	925.3	925.6	926.0	926.3	926.7
157.5°	944.3	943.3	943.5	943.6	943.8	944.0	944.1	944.1	944.1	944.2	944.2
160°	954.4	953.4	953.6	953.7	953.9	954.1	954.2	954.4	954.6	954.7	954.9
162.5°	963.5	962.3	962.5	962.7	962.8	963.0	963.3	963.7	964.1	964.6	965.0
165°	975.5	974.2	974.4	974.5	974.7	974.9	975.2	975.7	976.2	976.7	977.2
167.5°	985.0	983.7	983.7	983.7	983.7	983.7	984.1	984.7	985.4	986.0	986.7
170°	990.4	989.1	989.1	989.1	989.1	989.1	989.5	990.1	990.8	991.4	992.1
172.5°	994.0	992.7	992.5	992.4	992.3	992.1	992.5	993.3	994.0	994.8	995.6
175°	998.5	997.2	997.1	996.9	996.7	996.6	996.9	997.7	998.6	999.4	1000.3
177.5°	1000.1	999.1	999.0	998.8	998.7	998.6	998.8	999.5	1000.1	1000.8	1001.4
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	803.2	804.8	810.0	813.7	818.1	820.6	823.0	825.0	827.4	828.0	837.0
5°	806.8	814.6	828.1	838.1	850.5	864.0	873.3	877.6	888.8	898.1	916.7
7.5°	805.8	822.2	842.7	863.9	886.7	907.7	925.9	947.6	963.0	986.1	1009.0
10°	804.9	826.9	853.2	880.3	912.0	941.4	967.8	997.1	1021.5	1053.6	1081.1
12.5°	802.1	828.8	865.3	897.3	935.8	976.3	1015.3	1053.1	1074.7	1128.1	1153.5
15°	795.2	826.9	872.5	921.3	974.3	1022.3	1071.8	1111.2	1175.0	1221.8	1251.6
17.5°	782.0	826.5	880.6	939.4	1003.8	1067.0	1123.1	1183.0	1250.7	1307.3	1367.7
20°	775.9	824.6	884.9	949.9	1016.8	1088.3	1152.2	1224.2	1298.0	1353.7	1431.1
22.5°	764.5	819.6	884.6	957.0	1028.5	1102.6	1177.3	1249.8	1335.1	1411.9	1485.5
25°	745.7	807.6	874.8	955.7	1039.7	1113.9	1203.3	1299.6	1388.6	1487.1	1560.6
27.5°	726.1	792.1	859.6	934.7	1025.0	1113.2	1225.6	1334.3	1443.1	1528.3	1582.7
30°	710.8	775.1	844.8	920.5	1009.9	1114.7	1240.4	1359.1	1465.1	1538.2	1568.7
32.5°	694.5	759.6	821.2	900.7	995.9	1113.8	1249.7	1373.6	1466.3	1515.0	1509.0
35°	668.7	723.3	783.3	859.8	972.0	1106.9	1255.1	1374.9	1431.8	1421.4	1342.5
37.5°	631.6	677.5	736.5	820.3	944.1	1092.7	1244.3	1334.2	1330.5	1245.5	1131.1
40°	608.4	647.4	704.3	792.5	922.4	1083.4	1227.2	1285.7	1236.2	1117.4	980.5
42.5°	578.0	614.0	670.9	761.5	898.7	1064.5	1194.8	1211.6	1114.8	978.2	852.7
45°	531.1	562.8	621.6	715.2	862.9	1023.4	1115.5	1074.1	943.7	802.5	707.0
47.5°	480.5	513.5	570.1	666.2	811.2	961.6	1005.4	917.5	783.6	669.1	581.4
50°	448.7	480.4	535.6	632.8	776.3	910.9	929.1	815.4	692.4	591.8	519.8
52.5°	416.5	446.4	500.7	598.1	735.4	852.0	840.8	725.0	611.9	526.1	469.7
55°	368.6	396.9	448.7	540.0	664.9	757.3	716.7	606.1	512.5	446.0	403.0
57.5°	325.8	352.8	397.5	480.0	588.5	652.1	600.5	507.3	432.8	381.6	349.6
60°	296.7	320.6	363.1	439.8	534.1	582.5	531.4	449.1	386.4	345.4	316.8
62.5°	269.1	290.0	329.4	398.9	480.9	521.5	469.9	400.1	346.8	310.4	286.1
65°	227.4	246.4	281.1	335.4	402.6	429.7	385.3	328.7	287.4	260.3	244.1
67.5°	189.3	205.4	235.5	278.1	327.7	347.4	313.6	269.8	238.6	216.9	204.0
70°	164.0	177.9	201.5	238.2	283.2	298.2	266.5	230.6	207.7	190.3	178.3
72.5°	142.6	152.9	174.3	202.7	240.1	252.1	229.9	198.3	177.0	164.0	154.5
75°	108.7	117.1	131.1	153.9	179.9	186.8	170.2	150.5	136.1	126.8	119.5
77.5°	78.4	84.6	94.7	108.8	126.7	133.0	122.5	109.3	98.9	92.6	88.5
80°	59.2	64.2	72.7	84.3	95.1	98.7	92.4	82.4	75.0	71.6	68.1
82.5°	43.7	46.6	51.7	59.6	67.0	71.1	65.8	59.8	55.8	52.7	51.4
85°	22.0	23.6	26.0	29.0	33.6	35.2	33.2	31.7	29.4	27.5	27.5
87.5°	8.5	8.9	10.1	11.1	12.7	14.0	14.1	13.9	14.0	13.9	13.7
90°	2.4	4.0	5.7	7.4	9.3	11.4	13.5	15.7	17.9	18.5	19.2
92.5°	13.3	12.9	12.4	12.0	12.5	14.1	15.8	17.4	19.0	20.1	21.1
95°	38.6	31.8	25.0	18.3	15.8	17.6	19.4	21.2	23.0	24.2	25.3
97.5°	88.1	85.0	82.0	79.0	71.5	59.6	47.7	35.9	23.9	25.2	26.6
100°	128.9	132.2	135.5	138.8	127.5	101.8	76.0	50.3	24.5	25.9	27.2
102.5°	167.2	169.6	172.0	174.3	161.5	133.3	105.1	77.1	48.9	44.8	40.7
105°	223.3	225.1	226.9	228.7	222.2	207.3	192.5	177.6	162.8	133.5	104.3
107.5°	282.7	284.1	285.6	287.0	288.9	291.2	293.6	296.0	298.3	276.8	255.4
110°	322.3	323.7	325.0	326.3	327.9	329.7	331.5	333.4	335.2	329.7	324.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.2	361.4	362.6	363.9	365.4	367.2	369.0	370.8	372.6	372.7	372.8
115°	416.4	417.4	418.4	419.4	420.6	422.1	423.5	425.1	426.6	428.2	429.9
117.5°	471.2	472.4	473.6	474.8	475.8	476.6	477.4	478.1	478.9	480.2	481.5
120°	505.3	506.9	508.3	509.8	510.8	511.3	511.8	512.3	512.7	514.1	515.4
122.5°	539.6	540.8	542.0	543.2	544.1	544.7	545.4	546.0	546.6	547.5	548.5
125°	586.9	588.2	589.6	590.9	591.9	592.5	593.2	593.8	594.5	594.8	595.1
127.5°	632.7	634.0	635.3	636.6	637.7	638.5	639.2	640.1	640.9	641.4	642.0
130°	661.3	662.6	663.9	665.2	666.2	666.8	667.5	668.1	668.8	669.4	670.1
132.5°	688.5	689.8	691.2	692.6	693.5	694.0	694.5	695.0	695.6	696.2	696.9
135°	730.0	730.9	732.0	733.0	733.8	734.5	735.1	735.8	736.4	736.9	737.4
137.5°	765.9	767.2	768.4	769.7	770.5	770.8	771.2	771.6	771.9	772.7	773.6
140°	789.4	790.4	791.4	792.4	793.1	793.7	794.2	794.7	795.2	795.8	796.5
142.5°	811.4	812.4	813.4	814.5	815.2	815.7	816.2	816.7	817.2	817.7	818.2
145°	842.3	843.5	844.7	845.9	846.6	846.9	847.3	847.6	847.9	848.2	848.6
147.5°	870.9	871.7	872.4	873.2	873.7	874.1	874.4	874.7	875.0	875.5	875.8
150°	888.5	889.0	889.5	890.0	890.4	890.8	891.1	891.4	891.7	892.1	892.4
152.5°	904.3	904.5	904.7	905.0	905.2	905.4	905.6	905.8	906.1	906.6	907.2
155°	926.3	926.0	925.6	925.3	925.2	925.4	925.6	925.7	925.9	926.8	927.6
157.5°	944.2	944.1	944.1	944.1	944.0	943.8	943.6	943.5	943.3	944.3	945.3
160°	954.7	954.6	954.4	954.2	954.1	953.9	953.7	953.6	953.4	954.4	955.4
162.5°	964.6	964.1	963.7	963.3	963.0	962.8	962.7	962.5	962.3	963.5	964.6
165°	976.7	976.2	975.7	975.2	974.9	974.7	974.5	974.4	974.2	975.5	976.8
167.5°	986.0	985.4	984.7	984.1	983.7	983.7	983.7	983.7	983.7	985.0	986.3
170°	991.4	990.8	990.1	989.5	989.1	989.1	989.1	989.1	989.1	990.4	991.7
172.5°	994.8	994.0	993.3	992.5	992.1	992.3	992.4	992.5	992.7	994.0	995.3
175°	999.4	998.6	997.7	996.9	996.6	996.7	996.9	997.1	997.2	998.5	999.6
177.5°	1000.8	1000.1	999.5	998.8	998.6	998.7	998.8	999.0	999.1	1000.1	1001.2
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	840.1	840.4	843.7	846.3	845.1	846.6	847.2
5°	917.8	931.7	939.1	944.5	944.9	945.2	948.4
7.5°	1028.0	1043.0	1053.9	1070.5	1075.4	1081.1	1079.4
10°	1108.5	1130.5	1149.5	1159.5	1170.3	1186.2	1173.5
12.5°	1183.7	1222.7	1251.6	1267.2	1277.5	1280.6	1274.3
15°	1307.7	1358.8	1386.2	1385.4	1420.3	1435.3	1411.7
17.5°	1421.4	1468.5	1506.2	1525.6	1554.6	1561.0	1558.1
20°	1491.0	1542.5	1571.9	1605.1	1620.2	1633.8	1636.1
22.5°	1551.1	1597.2	1628.8	1656.5	1669.1	1675.5	1679.4
25°	1612.9	1649.2	1668.2	1677.8	1681.3	1680.5	1675.5
27.5°	1608.6	1611.3	1590.5	1570.0	1551.7	1531.0	1523.9
30°	1566.8	1534.3	1476.3	1443.4	1395.1	1356.8	1372.3
32.5°	1456.9	1392.3	1327.2	1255.3	1195.8	1178.9	1161.8
35°	1243.4	1129.7	1063.3	985.9	954.9	924.0	902.7
37.5°	1006.0	918.1	839.1	788.5	757.5	738.0	727.4
40°	869.9	790.5	725.6	684.6	661.0	638.9	635.8
42.5°	761.2	687.5	638.6	606.0	583.3	574.0	567.1
45°	623.5	572.0	539.2	515.9	500.9	495.0	487.4
47.5°	527.8	491.4	466.7	450.9	439.5	435.2	434.5
50°	474.2	444.0	425.9	413.4	404.6	403.0	396.9
52.5°	433.9	407.8	393.6	382.8	376.4	372.0	370.2
55°	376.7	359.3	346.6	340.3	335.4	331.0	331.0
57.5°	329.6	315.1	306.6	301.3	299.8	296.8	294.9
60°	300.5	288.1	281.6	276.9	273.9	274.2	270.7
62.5°	272.1	264.0	257.7	253.1	249.4	249.4	249.7
65°	231.7	225.5	220.9	219.3	217.0	214.3	215.0
67.5°	196.3	190.6	186.9	184.3	183.5	182.0	184.3
70°	171.0	166.7	164.0	161.7	160.9	161.3	163.2
72.5°	147.7	144.7	143.0	141.9	140.2	140.3	141.6
75°	116.0	113.7	112.2	111.0	110.6	110.6	110.6
77.5°	85.2	84.7	84.0	82.3	82.4	82.8	82.9
80°	67.3	66.1	65.7	64.9	63.8	63.0	64.9
82.5°	50.3	49.1	48.8	48.6	46.8	46.7	48.3
85°	27.1	26.0	26.3	26.0	26.0	25.5	25.5
87.5°	13.5	13.3	13.1	13.5	13.3	13.0	13.7
90°	19.8	20.5	21.0	21.3	21.6	21.9	22.3
92.5°	22.2	23.2	23.8	24.0	24.2	24.4	24.6
95°	26.5	27.7	28.3	28.3	28.3	28.3	28.3
97.5°	27.9	29.2	30.0	30.1	30.3	30.5	30.6
100°	28.5	29.8	30.6	30.7	30.9	31.0	31.2
102.5°	36.7	32.5	30.6	30.9	31.2	31.5	31.8
105°	75.0	45.8	31.4	31.7	32.0	32.4	32.7
107.5°	234.0	212.6	190.9	168.7	146.7	124.7	102.7
110°	318.8	313.4	298.8	275.2	251.6	227.9	204.4



TEST NUMBER: P332126-840

CATALOG NUMBER: S123DIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.9	373.0	370.5	365.6	360.6	355.6	350.6
115°	431.5	433.1	434.3	434.9	435.7	436.3	437.0
117.5°	482.8	484.1	484.8	485.0	485.1	485.2	485.4
120°	516.7	518.1	518.7	518.7	518.7	518.7	518.7
122.5°	549.4	550.4	550.9	551.0	551.1	551.3	551.4
125°	595.5	595.8	596.1	596.5	596.8	597.1	597.4
127.5°	642.5	643.0	643.1	642.8	642.4	642.1	641.8
130°	670.8	671.5	671.7	671.3	671.0	670.7	670.2
132.5°	697.5	698.2	698.3	697.8	697.4	696.9	696.4
135°	737.9	738.4	738.4	737.9	737.4	736.9	736.4
137.5°	774.4	775.2	775.4	775.1	774.7	774.4	774.1
140°	797.1	797.8	798.0	797.6	797.3	797.0	796.6
142.5°	818.7	819.2	819.3	818.8	818.4	817.9	817.4
145°	848.9	849.2	849.4	849.4	849.4	849.4	849.4
147.5°	876.1	876.5	876.2	875.5	874.6	873.9	873.1
150°	892.7	893.0	893.0	892.5	892.0	891.5	891.0
152.5°	907.8	908.4	908.3	907.6	906.8	906.1	905.2
155°	928.4	929.3	929.2	928.2	927.2	926.1	925.1
157.5°	946.2	947.3	947.2	945.8	944.5	943.3	942.0
160°	956.4	957.4	957.4	956.1	955.0	953.8	952.7
162.5°	965.7	966.8	966.8	965.8	964.8	963.8	962.8
165°	978.2	979.5	979.6	978.5	977.2	976.1	974.9
167.5°	987.7	989.1	989.1	987.7	986.3	985.0	983.7
170°	993.1	994.4	994.4	993.1	991.7	990.4	989.1
172.5°	996.6	997.9	997.8	996.4	995.0	993.5	992.1
175°	1000.8	1001.9	1001.8	1000.5	999.2	997.8	996.5
177.5°	1002.2	1003.3	1003.1	1001.8	1000.5	999.2	997.8
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3

(END OF REPORT)