

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332166-840

Luminaire Tested: **S123DIW-S775D1030U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332166-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1030U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7367.2 lumens  
Efficiency: N/A  
Efficacy: 140.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	54	48	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.8	1.6
10°-20°	327.1	4.4
20°-30°	483.2	6.6
30°-40°	564.4	7.7
40°-50°	567.4	7.7
50°-60°	498.4	6.8
60°-70°	371.3	5.0
70°-80°	211.6	2.9
80°-90°	64.5	0.9
90°-100°	49.6	0.7
100°-110°	236.6	3.2
110°-120°	568.2	7.7
120°-130°	723.6	9.8
130°-140°	773.1	10.5
140°-150°	723.0	9.8
150°-160°	583.2	7.9
160°-170°	376.4	5.1
170°-180°	129.7	1.8
0°-30°	926.1	12.6
0°-40°	1490.5	20.2
0°-60°	2556.3	34.7
0°-90°	3203.8	43.5
90°-120°	854.5	11.6
90°-150°	3074.2	41.7
90°-180°	4163.0	56.5
0°-180°	7367.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	11	24	28	30	6
95°	62	23	31	38	39	76
105°	302	308	222	53	45	320
115°	567	573	582	592	596	560
125°	799	807	811	813	816	714
135°	995	1001	1005	1008	1005	766
145°	1148	1155	1157	1159	1159	718
155°	1265	1263	1264	1268	1263	583
165°	1334	1331	1330	1337	1331	377
175°	1365	1361	1361	1368	1360	130
180°	1365	1365	1365	1365	1365	



TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.2	22.1	22.0	21.8	21.7	21.9	22.3	22.7	23.1	23.4	23.4
90°	1.0	3.2	5.6	7.8	10.0	12.6	15.6	18.5	21.4	24.3	25.2
92.5°	18.9	18.3	17.6	17.0	16.4	17.2	19.4	21.5	23.7	26.0	27.4
95°	61.9	52.6	43.4	34.1	24.9	21.5	24.0	26.5	29.0	31.4	33.0
97.5°	124.3	120.2	116.0	111.9	107.8	97.6	81.4	65.1	48.9	32.6	34.4
100°	171.4	175.9	180.5	184.9	189.5	174.1	139.0	103.8	68.7	33.4	35.2
102.5°	225.0	228.2	231.5	234.7	237.9	220.4	182.0	143.6	105.1	66.8	61.2
105°	302.3	304.8	307.2	309.7	312.1	303.3	283.0	262.7	242.5	222.2	182.3
107.5°	383.8	385.8	387.8	389.8	391.7	394.4	397.6	400.7	403.9	407.2	377.9
110°	438.2	440.0	441.8	443.6	445.4	447.6	450.0	452.5	454.9	457.5	450.0



TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.1	491.7	493.3	495.0	496.7	498.7	501.1	503.6	506.1	508.6	508.7
115°	567.0	568.4	569.7	571.1	572.4	574.1	576.1	578.1	580.2	582.2	584.5
117.5°	641.5	643.1	644.8	646.4	648.1	649.4	650.6	651.6	652.6	653.6	655.4
120°	687.7	689.7	691.8	693.8	695.8	697.2	697.8	698.5	699.2	699.8	701.7
122.5°	734.8	736.4	738.1	739.7	741.4	742.7	743.6	744.4	745.3	746.1	747.4
125°	799.3	801.1	802.8	804.7	806.5	807.9	808.7	809.6	810.5	811.4	811.9
127.5°	861.7	863.5	865.4	867.2	869.0	870.4	871.5	872.6	873.6	874.7	875.5
130°	900.7	902.5	904.3	906.2	908.0	909.3	910.2	911.1	912.0	912.9	913.8
132.5°	938.1	939.9	941.6	943.4	945.2	946.5	947.3	948.0	948.7	949.4	950.3
135°	995.0	996.4	997.7	999.1	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8
137.5°	1043.7	1045.4	1047.1	1048.8	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7
140°	1076.2	1077.5	1078.9	1080.3	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2
142.5°	1106.2	1107.5	1108.9	1110.2	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1
145°	1148.2	1149.7	1151.3	1153.0	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8
147.5°	1187.8	1188.8	1189.8	1190.8	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9
150°	1212.1	1212.7	1213.5	1214.2	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6
152.5°	1234.1	1234.4	1234.7	1235.0	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5
155°	1264.9	1264.4	1263.9	1263.5	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0
157.5°	1288.8	1288.8	1288.7	1288.7	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9
160°	1303.4	1303.1	1302.9	1302.7	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7
162.5°	1317.2	1316.6	1316.1	1315.5	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0
165°	1333.8	1333.1	1332.5	1331.8	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6
167.5°	1346.8	1345.9	1345.0	1344.1	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5
170°	1354.1	1353.2	1352.3	1351.4	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8
172.5°	1359.0	1357.9	1356.9	1355.7	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8
175°	1365.2	1364.1	1363.0	1361.9	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8
177.5°	1366.9	1365.9	1365.1	1364.2	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	23.4	23.4	23.4	23.5	23.5	23.6	23.7	23.8
90°	26.2	27.1	28.0	28.6	29.1	29.5	30.0	30.4
92.5°	28.9	30.3	31.7	32.6	32.8	33.1	33.4	33.6
95°	34.6	36.2	37.8	38.6	38.6	38.6	38.6	38.6
97.5°	36.3	38.1	39.9	40.9	41.1	41.3	41.6	41.8
100°	37.1	38.9	40.7	41.7	41.9	42.1	42.4	42.6
102.5°	55.5	50.0	44.3	41.8	42.2	42.6	43.0	43.4
105°	142.4	102.4	62.5	42.8	43.3	43.7	44.1	44.6
107.5°	348.6	319.4	290.1	260.4	230.4	200.4	170.3	140.2
110°	442.6	435.2	427.7	407.9	375.7	343.4	311.1	278.9





TEST NUMBER: P332166-840

CATALOG NUMBER: S123DIW-S775D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	508.9	509.0	509.1	505.7	499.0	492.2	485.3	478.6
115°	586.7	589.0	591.3	592.8	593.7	594.6	595.5	596.4
117.5°	657.2	659.0	660.9	661.9	662.0	662.2	662.4	662.6
120°	703.5	705.3	707.1	708.0	708.0	708.0	708.0	708.0
122.5°	748.6	749.9	751.1	751.9	752.0	752.2	752.5	752.7
125°	812.3	812.8	813.2	813.7	814.2	814.6	815.1	815.5
127.5°	876.2	876.9	877.7	877.8	877.3	876.9	876.5	876.0
130°	914.7	915.5	916.5	916.8	916.3	915.8	915.3	914.9
132.5°	951.2	952.1	953.0	953.1	952.5	951.9	951.3	950.6
135°	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2
137.5°	1055.8	1056.9	1058.0	1058.3	1057.8	1057.4	1056.9	1056.5
140°	1087.1	1088.0	1088.9	1089.1	1088.7	1088.2	1087.8	1087.3
142.5°	1116.8	1117.5	1118.2	1118.2	1117.6	1117.0	1116.4	1115.7
145°	1158.2	1158.7	1159.1	1159.3	1159.3	1159.3	1159.3	1159.3
147.5°	1195.4	1195.8	1196.3	1196.0	1195.0	1193.9	1192.9	1191.8
150°	1218.1	1218.5	1219.0	1218.9	1218.2	1217.5	1216.9	1216.2
152.5°	1238.3	1239.1	1239.9	1239.8	1238.7	1237.7	1236.7	1235.7
155°	1266.1	1267.2	1268.4	1268.2	1266.9	1265.6	1264.1	1262.8
157.5°	1290.3	1291.6	1292.9	1292.7	1291.0	1289.3	1287.5	1285.8
160°	1304.0	1305.5	1306.8	1306.7	1305.0	1303.5	1301.9	1300.3
162.5°	1316.6	1318.2	1319.7	1319.7	1318.4	1317.0	1315.6	1314.1
165°	1333.3	1335.1	1337.0	1337.1	1335.5	1333.9	1332.3	1330.8
167.5°	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7
170°	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1
172.5°	1358.6	1360.3	1362.1	1362.0	1360.1	1358.1	1356.0	1354.1
175°	1364.3	1365.9	1367.6	1367.5	1365.6	1363.8	1362.0	1360.2
177.5°	1366.5	1368.0	1369.4	1369.3	1367.5	1365.6	1363.8	1362.0
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2

(END OF REPORT)