

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332774-927

Luminaire Tested: **S124DIW-S575D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332774-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1560U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6263.8 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	1.2
10°-20°	204.1	3.3
20°-30°	300.5	4.8
30°-40°	349.3	5.6
40°-50°	349.3	5.6
50°-60°	305.5	4.9
60°-70°	226.9	3.6
70°-80°	128.9	2.1
80°-90°	41.8	0.7
90°-100°	101.9	1.6
100°-110°	301.8	4.8
110°-120°	512.2	8.2
120°-130°	675.4	10.8
130°-140°	758.5	12.1
140°-150°	745.3	11.9
150°-160°	626.9	10.0
160°-170°	417.1	6.7
170°-180°	146.1	2.3
0°-30°	577.0	9.2
0°-40°	926.3	14.8
0°-60°	1581.2	25.2
0°-90°	1978.8	31.6
90°-120°	915.8	14.6
90°-150°	3095.0	49.4
90°-180°	4285.0	68.4
0°-180°	6263.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	4	17	26	33	36	6
95°	72	82	91	94	94	80
105°	278	280	284	288	291	295
115°	521	521	518	517	516	513
125°	758	758	757	755	752	676
135°	978	985	986	983	980	757
145°	1188	1193	1194	1193	1190	743
155°	1362	1362	1360	1365	1360	626
165°	1482	1479	1476	1483	1479	418
175°	1542	1536	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.5	14.0	14.5	15.0	15.4	15.8	16.2	16.5	16.8	17.1	17.4
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	25.6	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2
95°	71.7	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6
97.5°	125.2	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5
100°	167.2	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3
102.5°	211.2	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6
105°	278.3	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1
107.5°	348.8	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6
110°	396.6	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2



TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5
115°	520.8	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2
117.5°	591.0	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4
120°	637.9	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7
122.5°	686.6	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0
125°	758.5	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8
127.5°	823.7	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8
130°	869.6	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7
132.5°	916.4	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6
135°	978.3	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9
137.5°	1045.7	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2
140°	1090.6	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7
142.5°	1131.6	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1
145°	1188.5	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1244.9	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4
150°	1279.3	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1311.8	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2
155°	1361.7	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6
157.5°	1403.7	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2
160°	1428.6	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0
162.5°	1451.5	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7
165°	1482.3	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0
167.5°	1506.0	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8
170°	1519.4	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2
172.5°	1528.9	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0
175°	1542.1	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8
177.5°	1546.3	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	17.7	18.1	18.4	18.6	18.7	18.8	18.9	19.0
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	49.2	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	92.4	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	145.5	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	183.8	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	224.3	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	285.9	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	352.4	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.7	396.2	395.6	395.8	396.6	397.4	398.2	398.9





TEST NUMBER: P332774-927

CATALOG NUMBER: S124DIW-S575D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	444.3	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.8	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	588.5	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	636.4	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	685.0	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	756.2	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	824.3	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	872.1	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	917.0	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	984.4	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1049.6	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.4	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1133.0	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1194.0	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.3	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1316.8	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.0	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1427.8	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1450.1	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1479.6	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1504.4	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1517.8	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1527.8	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1544.6	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)