

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332155-840

Luminaire Tested: **S123DIW-S775D460U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332155-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D460U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4815.8 lumens  
Efficiency: N/A  
Efficacy: 127.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	69	71	67	63	63	59	57	55	53	51	47
3	84	74	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40
4	77	66	58	51	72	62	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.8	2.4
10°-20°	327.1	6.8
20°-30°	483.2	10.0
30°-40°	564.4	11.7
40°-50°	567.4	11.8
50°-60°	498.4	10.3
60°-70°	371.3	7.7
70°-80°	211.6	4.4
80°-90°	62.5	1.3
90°-100°	37.9	0.8
100°-110°	113.6	2.4
110°-120°	193.2	4.0
120°-130°	254.1	5.3
130°-140°	285.6	5.9
140°-150°	280.8	5.8
150°-160°	236.4	4.9
160°-170°	157.3	3.3
170°-180°	55.1	1.1
0°-30°	926.1	19.2
0°-40°	1490.5	30.9
0°-60°	2556.3	53.1
0°-90°	3201.7	66.5
90°-120°	344.8	7.2
90°-150°	1165.3	24.2
90°-180°	1614.0	33.5
0°-180°	4815.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	0	5	11	13	14	5
95°	27	30	34	36	36	30
105°	103	104	108	108	109	110
115°	194	196	195	195	195	192
125°	285	286	285	283	281	254
135°	369	372	372	370	369	284
145°	448	449	450	450	448	280
155°	513	513	514	515	512	236
165°	559	557	557	560	557	157
175°	581	580	579	582	579	55
180°	583	583	583	583	583	



TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.1	21.7	21.4	21.0	20.6	20.5	20.6	20.7	20.7	20.8	20.7
90°	0.5	1.5	2.5	3.5	4.5	5.7	7.0	8.4	9.7	11.0	11.4
92.5°	11.1	11.8	12.4	13.1	13.8	14.5	15.3	16.1	16.9	17.6	17.9
95°	27.0	27.7	28.4	29.2	29.9	30.6	31.4	32.2	33.0	33.8	34.2
97.5°	48.0	48.5	49.0	49.6	50.1	50.6	51.2	51.8	52.4	53.0	53.4
100°	62.2	62.8	63.4	64.0	64.6	65.2	65.7	66.2	66.8	67.3	67.6
102.5°	78.7	79.1	79.5	79.8	80.2	80.7	81.4	82.0	82.7	83.4	83.7
105°	103.0	103.2	103.4	103.6	103.8	104.3	105.2	106.1	107.0	108.0	108.0
107.5°	131.2	131.3	131.4	131.5	131.7	131.9	132.3	132.6	133.0	133.4	133.7
110°	148.8	149.0	149.2	149.4	149.6	149.8	150.0	150.2	150.4	150.6	151.0



TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.1	167.3	167.4	167.5	167.6	167.6	167.7	167.7	167.7	168.2
115°	194.5	194.8	195.1	195.4	195.7	195.8	195.6	195.4	195.2	195.0	195.1
117.5°	222.2	222.4	222.6	222.8	223.0	222.9	222.7	222.4	222.2	221.9	221.9
120°	239.3	239.9	240.5	241.2	241.8	241.9	241.4	240.9	240.3	239.8	239.7
122.5°	257.3	257.7	258.2	258.6	259.0	259.1	258.9	258.6	258.4	258.1	257.8
125°	284.7	285.0	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.1	284.7
127.5°	309.9	310.5	311.2	311.8	312.6	312.8	312.6	312.3	312.0	311.8	311.2
130°	326.8	327.6	328.4	329.2	330.0	330.2	329.9	329.6	329.3	329.0	328.6
132.5°	343.6	344.4	345.3	346.1	346.9	347.2	346.9	346.7	346.5	346.3	345.8
135°	369.3	369.9	370.5	371.1	371.7	372.0	371.9	371.8	371.7	371.6	371.2
137.5°	393.1	393.6	394.2	394.7	395.2	395.6	395.8	396.1	396.4	396.6	396.2
140°	409.6	410.1	410.6	411.1	411.6	411.9	412.0	412.1	412.2	412.3	412.2
142.5°	424.6	425.2	425.7	426.2	426.7	427.0	427.2	427.4	427.6	427.7	427.6
145°	448.1	448.3	448.5	448.7	448.9	449.1	449.4	449.7	450.0	450.3	450.2
147.5°	468.6	468.9	469.3	469.6	470.0	470.3	470.6	470.9	471.2	471.5	471.5
150°	482.8	483.0	483.2	483.4	483.6	483.8	484.0	484.2	484.4	484.6	484.6
152.5°	494.5	494.8	495.1	495.3	495.6	495.8	495.9	496.1	496.2	496.3	496.6
155°	513.0	513.0	513.0	513.0	513.0	513.1	513.2	513.3	513.4	513.5	513.9
157.5°	528.8	528.7	528.6	528.4	528.3	528.3	528.4	528.5	528.5	528.6	529.0
160°	538.7	538.5	538.3	538.1	537.9	537.8	537.8	537.8	537.8	537.8	538.3
162.5°	547.4	547.1	546.8	546.5	546.3	546.2	546.2	546.3	546.4	546.5	547.0
165°	558.8	558.5	558.2	557.8	557.5	557.4	557.4	557.4	557.4	557.4	558.1
167.5°	567.8	567.4	567.0	566.6	566.2	566.0	566.1	566.2	566.3	566.3	567.0
170°	573.0	572.6	572.2	571.8	571.4	571.2	571.2	571.2	571.2	571.2	571.9
172.5°	577.0	576.6	576.2	575.8	575.3	575.1	575.1	575.1	575.1	575.1	575.8
175°	581.2	580.8	580.4	580.0	579.6	579.4	579.4	579.4	579.4	579.4	580.0
177.5°	583.0	582.6	582.3	582.0	581.7	581.5	581.5	581.5	581.5	581.5	582.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	20.6	20.5	20.4	20.3	20.4	20.4	20.5	20.5
90°	11.8	12.2	12.6	12.9	13.1	13.3	13.5	13.7
92.5°	18.2	18.6	18.9	19.0	18.9	18.7	18.6	18.5
95°	34.6	35.0	35.4	35.6	35.6	35.6	35.6	35.6
97.5°	53.9	54.4	54.8	55.0	55.0	55.0	54.9	54.9
100°	67.9	68.2	68.5	68.8	69.0	69.2	69.4	69.6
102.5°	84.0	84.3	84.6	84.7	84.7	84.6	84.6	84.5
105°	108.0	108.0	108.0	108.1	108.4	108.6	108.8	109.0
107.5°	134.0	134.3	134.6	134.7	134.6	134.5	134.4	134.3
110°	151.4	151.8	152.2	152.3	152.1	151.9	151.7	151.5





TEST NUMBER: P332155-840

CATALOG NUMBER: S123DIW-S775D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.7	169.3	169.8	170.0	169.9	169.9	169.9	169.8
115°	195.2	195.3	195.4	195.4	195.3	195.2	195.1	195.0
117.5°	221.9	221.8	221.8	221.7	221.4	221.1	220.8	220.5
120°	239.6	239.5	239.4	239.2	239.0	238.8	238.6	238.4
122.5°	257.6	257.3	257.0	256.8	256.5	256.2	255.9	255.6
125°	284.3	283.9	283.5	283.1	282.7	282.3	281.9	281.4
127.5°	310.7	310.1	309.5	309.0	308.6	308.1	307.6	307.2
130°	328.2	327.8	327.4	326.9	326.2	325.5	324.8	324.0
132.5°	345.3	344.8	344.3	343.8	343.3	342.6	342.1	341.5
135°	370.8	370.4	370.0	369.7	369.5	369.3	369.1	368.9
137.5°	395.8	395.4	394.9	394.5	394.0	393.7	393.3	392.9
140°	412.1	412.0	411.9	411.5	410.8	410.1	409.4	408.7
142.5°	427.5	427.4	427.3	427.0	426.5	425.9	425.4	424.7
145°	450.1	450.0	449.9	449.7	449.3	448.9	448.5	448.1
147.5°	471.5	471.5	471.5	471.2	470.6	469.9	469.3	468.7
150°	484.6	484.6	484.6	484.3	483.7	483.1	482.5	481.9
152.5°	496.7	496.9	497.1	496.9	496.3	495.7	495.2	494.7
155°	514.3	514.7	515.1	514.9	514.2	513.5	512.8	512.1
157.5°	529.5	529.9	530.3	530.2	529.7	529.1	528.5	528.0
160°	538.8	539.3	539.8	539.8	539.4	539.0	538.6	538.2
162.5°	547.5	548.1	548.6	548.5	547.9	547.1	546.5	545.8
165°	558.7	559.3	559.9	559.8	559.1	558.4	557.6	556.9
167.5°	567.6	568.3	568.9	568.9	568.3	567.6	567.0	566.3
170°	572.6	573.3	574.0	574.0	573.3	572.6	571.9	571.2
172.5°	576.4	577.0	577.6	577.6	576.9	576.2	575.5	574.8
175°	580.6	581.2	581.8	581.8	581.1	580.4	579.7	579.0
177.5°	582.5	583.0	583.4	583.4	582.8	582.3	581.7	581.1
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6

(END OF REPORT)