

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332750-927

Luminaire Tested: **S124DIW-S575D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332750-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D470U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3263.3 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	84	77	72	85	78	73	68	69	64	61	59	56	54	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	2.2
10°-20°	204.1	6.3
20°-30°	300.5	9.2
30°-40°	349.3	10.7
40°-50°	349.3	10.7
50°-60°	305.5	9.4
60°-70°	226.9	7.0
70°-80°	128.9	4.0
80°-90°	38.6	1.2
90°-100°	30.6	0.9
100°-110°	90.7	2.8
110°-120°	153.9	4.7
120°-130°	203.0	6.2
130°-140°	227.9	7.0
140°-150°	224.0	6.9
150°-160°	188.4	5.8
160°-170°	125.3	3.8
170°-180°	43.9	1.3
0°-30°	577.0	17.7
0°-40°	926.3	28.4
0°-60°	1581.2	48.5
0°-90°	1975.6	60.5
90°-120°	275.2	8.4
90°-150°	930.1	28.5
90°-180°	1288.0	39.5
0°-180°	3263.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	1	5	8	10	11	3
95°	22	25	27	28	28	24
105°	84	84	85	87	88	89
115°	156	156	156	155	155	154
125°	228	228	228	227	226	203
135°	294	296	296	295	294	227
145°	357	359	359	359	358	223
155°	409	409	409	410	409	188
165°	445	444	444	446	444	126
175°	463	462	461	464	461	44
180°	464	464	464	464	464	



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.1	13.1	13.2	13.2	13.3	13.3	13.4	13.4	13.4	13.4	13.5
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	7.7	8.7	9.7	10.7	11.7	12.4	12.9	13.3	13.8	14.2	14.5
95°	21.5	22.3	23.0	23.7	24.4	25.0	25.6	26.1	26.7	27.3	27.5
97.5°	37.6	38.2	38.7	39.4	39.9	40.6	41.2	41.8	42.5	43.2	43.4
100°	50.2	50.5	50.9	51.2	51.6	52.0	52.8	53.5	54.2	54.9	55.1
102.5°	63.5	63.6	63.7	63.8	64.0	64.4	65.0	65.7	66.3	67.0	67.2
105°	83.7	83.7	83.8	83.9	84.0	84.1	84.4	84.8	85.1	85.4	85.6
107.5°	104.8	104.9	105.0	105.1	105.2	105.3	105.4	105.4	105.4	105.4	105.7
110°	119.1	119.3	119.5	119.6	119.8	119.9	119.8	119.7	119.6	119.5	119.4



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.1	134.1	134.2	134.2	134.3	134.2	134.0	133.9	133.7	133.6	133.6
115°	156.5	156.5	156.5	156.5	156.5	156.5	156.3	156.1	156.0	155.8	155.7
117.5°	177.6	177.7	177.8	177.8	177.8	177.8	177.8	177.6	177.5	177.4	177.1
120°	191.7	192.0	192.3	192.7	193.0	193.0	192.7	192.5	192.3	192.0	191.6
122.5°	206.4	206.4	206.6	206.7	206.8	206.8	206.8	206.6	206.5	206.4	206.1
125°	227.9	227.9	227.9	227.9	227.9	227.9	227.8	227.8	227.7	227.6	227.4
127.5°	247.6	247.8	248.0	248.3	248.5	248.6	248.4	248.3	248.2	248.0	247.9
130°	261.3	261.6	261.8	262.1	262.3	262.4	262.4	262.4	262.4	262.4	262.2
132.5°	275.4	275.6	275.8	275.9	276.1	276.2	276.1	276.0	276.0	275.9	275.8
135°	294.0	294.5	294.9	295.4	295.9	296.1	296.1	296.1	296.1	296.1	296.0
137.5°	314.3	314.5	314.7	314.9	315.1	315.3	315.4	315.6	315.7	315.8	315.6
140°	327.7	327.9	328.0	328.2	328.4	328.4	328.4	328.4	328.4	328.4	328.4
142.5°	340.1	340.2	340.4	340.6	340.7	340.8	340.7	340.6	340.6	340.5	340.5
145°	357.2	357.5	357.8	358.1	358.5	358.6	358.7	358.8	358.9	358.9	358.9
147.5°	374.1	374.5	374.9	375.3	375.7	375.8	375.7	375.7	375.7	375.6	375.5
150°	384.4	384.8	385.1	385.4	385.7	385.9	385.9	385.9	385.9	385.9	385.9
152.5°	394.2	394.4	394.6	394.8	395.0	395.1	395.1	395.2	395.3	395.4	395.5
155°	409.2	409.2	409.2	409.2	409.2	409.2	409.1	409.0	408.9	408.8	409.2
157.5°	421.8	421.7	421.6	421.4	421.3	421.2	421.2	421.2	421.1	421.1	421.4
160°	429.4	429.3	429.2	429.1	429.0	429.0	428.9	428.8	428.7	428.6	428.9
162.5°	436.3	436.0	435.8	435.6	435.4	435.2	435.1	435.1	435.0	434.9	435.4
165°	445.4	445.2	445.0	444.7	444.5	444.3	444.2	444.0	443.9	443.7	444.2
167.5°	452.6	452.3	451.9	451.6	451.2	451.1	451.1	451.1	451.1	451.1	451.6
170°	456.6	456.2	455.8	455.4	455.0	454.9	455.0	455.0	455.1	455.2	455.7
172.5°	459.5	459.1	458.8	458.5	458.1	458.0	458.0	458.0	458.0	458.0	458.6
175°	463.4	463.0	462.6	462.2	461.8	461.6	461.5	461.4	461.4	461.3	461.8
177.5°	464.7	464.4	464.1	463.7	463.4	463.3	463.3	463.3	463.3	463.3	463.7
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	13.6	13.7	13.8	13.9	13.9	13.9	13.9	14.0
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	14.8	15.1	15.4	15.5	15.7	15.8	15.8	15.9
95°	27.7	28.0	28.2	28.4	28.4	28.4	28.4	28.4
97.5°	43.7	44.0	44.3	44.4	44.4	44.4	44.4	44.4
100°	55.2	55.4	55.5	55.6	55.6	55.6	55.6	55.6
102.5°	67.4	67.7	67.9	68.0	68.0	68.1	68.2	68.3
105°	86.0	86.2	86.4	86.7	86.9	87.1	87.4	87.6
107.5°	105.9	106.2	106.4	106.5	106.5	106.5	106.4	106.4
110°	119.2	119.1	118.9	118.9	119.1	119.4	119.6	119.9



TEST NUMBER: P332750-927

CATALOG NUMBER: S124DIW-S575D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.6	133.5	133.5	133.5	133.6	133.6	133.6	133.6
115°	155.7	155.6	155.5	155.4	155.3	155.3	155.2	155.1
117.5°	176.9	176.6	176.3	176.1	175.9	175.8	175.6	175.5
120°	191.2	190.8	190.4	190.4	190.5	190.7	190.8	191.0
122.5°	205.9	205.6	205.3	205.0	204.8	204.5	204.1	203.9
125°	227.3	227.1	227.0	226.8	226.6	226.5	226.3	226.2
127.5°	247.7	247.6	247.4	247.2	247.2	247.0	246.9	246.8
130°	262.1	261.9	261.7	261.5	261.2	260.9	260.5	260.2
132.5°	275.6	275.4	275.3	275.1	275.0	274.9	274.7	274.6
135°	295.8	295.6	295.5	295.3	295.1	294.9	294.6	294.4
137.5°	315.4	315.2	315.0	314.9	315.0	315.0	315.1	315.1
140°	328.3	328.2	328.1	328.0	328.0	327.9	327.8	327.7
142.5°	340.5	340.5	340.5	340.4	340.4	340.4	340.4	340.4
145°	358.8	358.7	358.6	358.5	358.2	358.0	357.7	357.5
147.5°	375.4	375.3	375.3	375.3	375.2	375.1	375.0	374.9
150°	385.9	385.9	385.9	385.9	385.8	385.7	385.6	385.6
152.5°	395.8	395.9	396.2	396.1	395.9	395.7	395.5	395.3
155°	409.5	409.8	410.1	410.1	409.8	409.5	409.2	408.8
157.5°	421.6	421.8	422.1	422.1	421.8	421.5	421.3	421.0
160°	429.1	429.4	429.6	429.5	429.1	428.7	428.3	427.9
162.5°	435.8	436.3	436.7	436.7	436.3	435.9	435.5	435.1
165°	444.7	445.1	445.6	445.7	445.4	445.0	444.7	444.4
167.5°	452.1	452.6	453.0	453.0	452.6	452.1	451.5	451.1
170°	456.1	456.6	457.1	457.0	456.5	455.9	455.3	454.8
172.5°	459.1	459.7	460.2	460.2	459.6	459.1	458.5	458.0
175°	462.4	463.0	463.5	463.5	463.0	462.4	461.8	461.3
177.5°	464.2	464.6	465.1	465.0	464.5	464.1	463.5	463.0
180°	464.1	464.1	464.1	464.1	464.1	464.1	464.1	464.1

(END OF REPORT)