

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332467-840

Luminaire Tested: **S123RDIW-S1000D1535U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332467-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9374.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	44	43	37
2	88	81	76	71	81	75	70	65	62	59	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	18	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17280	17280	17280	17280
5°	20599	17354	15282	17354
10°	25719	17254	13806	17254
15°	30190	17079	12590	17079
20°	33693	16814	11557	16814
25°	33155	16537	10922	16537
30°	23832	16281	10268	16281
35°	15912	15948	9843	15948
40°	11724	15548	9405	15548
45°	9834	14845	8977	14845
50°	8678	13924	8378	13924
55°	7610	12872	7557	12872
60°	6777	11866	6923	11866
65°	5952	10781	6441	10781
70°	4674	9819	5882	9819
75°	4117	8576	5373	8576
80°	3583	7283	5281	7283
85°	2878	5866	5595	5866



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.7
10°-20°	493.2	5.3
20°-30°	774.9	8.3
30°-40°	808.4	8.6
40°-50°	691.8	7.4
50°-60°	527.3	5.6
60°-70°	338.0	3.6
70°-80°	162.6	1.7
80°-90°	48.8	0.5
90°-100°	126.3	1.3
100°-110°	378.0	4.0
110°-120°	642.9	6.9
120°-130°	845.6	9.0
130°-140°	950.5	10.1
140°-150°	934.3	10.0
150°-160°	786.5	8.4
160°-170°	523.6	5.6
170°-180°	183.3	2.0
0°-30°	1426.0	15.2
0°-40°	2234.4	23.8
0°-60°	3453.6	36.8
0°-90°	4002.9	42.7
90°-120°	1147.2	12.2
90°-150°	3877.6	41.4
90°-180°	5371.0	57.3
0°-180°	9374.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1605	1605	1605	1605	1605	
5°	1906	1606	1414	1606	1906	197
15°	2709	1533	1130	1533	2709	768
25°	2792	1392	920	1392	2792	1200
35°	1211	1214	749	1214	1211	794
45°	646	975	590	975	646	508
55°	406	686	403	686	406	367
65°	234	423	253	423	234	230
75°	99	206	129	206	99	106
85°	23	48	45	48	23	28
90°	46	2	46	2	46	23
95°	119	90	119	90	119	122
105°	362	343	362	343	362	385
115°	649	647	649	647	649	642
125°	936	947	936	947	936	837
135°	1227	1229	1227	1229	1227	944
145°	1491	1491	1491	1491	1491	931
155°	1704	1707	1704	1707	1704	785
165°	1853	1859	1853	1859	1853	523
175°	1926	1934	1926	1934	1926	183
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1709.9	1712.0	1705.0	1703.8	1695.6	1693.3	1693.3	1681.8	1674.7	1665.4	1659.8
5°	1906.4	1917.4	1911.9	1899.6	1879.0	1874.1	1861.1	1840.5	1817.1	1788.2	1774.4
7.5°	2151.9	2166.9	2161.1	2142.0	2120.4	2102.9	2066.2	2031.9	1984.0	1941.9	1905.9
10°	2353.1	2337.3	2324.9	2306.4	2286.4	2254.1	2215.6	2162.7	2101.6	2053.5	1999.9
12.5°	2503.8	2501.1	2485.5	2466.4	2438.2	2407.5	2360.3	2295.8	2224.7	2155.3	2093.9
15°	2709.2	2713.2	2702.9	2683.0	2643.1	2588.9	2517.4	2490.6	2388.8	2313.3	2237.7
17.5°	2851.3	2850.4	2849.0	2821.5	2780.8	2742.1	2675.8	2605.4	2513.3	2406.7	2304.9
20°	2941.4	2934.6	2935.9	2905.0	2874.8	2830.0	2765.5	2663.1	2587.5	2464.5	2359.3
22.5°	2939.2	2937.8	2943.0	2932.4	2910.5	2876.3	2825.4	2739.0	2642.4	2518.3	2400.0
25°	2791.6	2786.1	2818.4	2827.3	2862.4	2868.5	2853.5	2806.0	2714.6	2586.8	2440.4
27.5°	2336.3	2333.3	2393.3	2468.3	2563.4	2637.4	2708.9	2743.4	2714.6	2623.1	2476.4
30°	1917.4	1982.1	2012.3	2120.8	2241.8	2386.1	2512.5	2632.8	2662.4	2622.5	2502.2
32.5°	1592.0	1648.3	1673.5	1766.8	1879.5	2048.5	2238.3	2408.5	2528.8	2559.3	2486.9
35°	1210.9	1211.6	1269.3	1310.6	1415.0	1588.9	1773.1	2001.2	2228.1	2399.8	2417.7
37.5°	966.2	969.7	1004.6	1045.7	1124.1	1216.0	1378.2	1567.9	1829.9	2093.7	2248.3
40°	834.4	840.5	866.7	907.2	963.5	1032.9	1159.4	1338.1	1556.6	1850.1	2089.9
42.5°	749.6	759.7	773.2	804.4	839.3	904.2	1006.5	1144.6	1343.3	1620.8	1897.5
45°	646.0	651.5	661.9	676.2	707.8	753.3	821.9	914.7	1079.6	1303.0	1579.9
47.5°	569.9	566.9	577.8	589.6	610.6	641.5	687.5	763.3	880.9	1060.2	1295.1
50°	518.2	517.5	525.0	534.0	553.9	576.6	614.4	671.5	764.9	913.3	1128.4
52.5°	469.8	472.4	477.8	488.9	503.3	521.6	555.5	596.6	676.9	805.1	984.4
55°	405.5	407.6	415.1	421.3	431.6	450.1	471.4	505.8	560.8	650.2	797.9
57.5°	351.0	350.1	357.4	358.9	370.5	385.7	402.1	428.9	468.7	535.1	634.6
60°	314.8	312.7	318.9	323.7	329.9	342.2	356.0	382.1	413.7	462.5	547.8
62.5°	281.8	280.8	285.4	290.1	295.3	306.5	318.1	338.1	363.1	404.2	471.9
65°	233.7	235.7	237.8	239.8	242.6	249.4	260.4	274.2	291.3	320.2	369.0
67.5°	183.6	185.7	186.4	190.7	196.5	200.9	207.5	219.7	231.8	256.1	283.9
70°	148.5	147.7	148.5	150.5	158.0	165.6	174.6	183.5	191.1	208.2	231.6
72.5°	127.5	126.3	128.2	128.6	132.2	134.3	140.0	148.3	158.0	169.8	186.5
75°	99.0	99.0	99.0	99.0	101.7	103.1	105.1	107.2	110.7	116.1	128.6
77.5°	73.1	73.2	74.2	74.9	75.4	76.2	77.6	79.6	80.8	83.7	89.1
80°	57.8	58.4	57.8	58.4	58.4	59.8	60.5	62.5	63.2	66.7	68.8
82.5°	43.4	43.0	43.4	44.1	44.1	45.5	45.6	47.2	47.3	49.1	51.1
85°	23.3	22.0	23.3	22.7	24.0	22.7	23.3	24.7	24.7	25.4	28.2
87.5°	14.6	15.6	14.3	14.7	14.6	14.9	14.7	14.4	15.2	14.4	14.1
90°	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3	37.9	36.6	32.1
92.5°	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6	59.6	58.5	55.9
95°	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4	114.0	112.7	110.0
97.5°	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5	177.9	176.3	174.4
100°	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9	224.9	223.9	222.2
102.5°	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5	278.5	277.4	275.2
105°	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4	359.4	359.4	356.4
107.5°	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0	444.8	443.7	442.5
110°	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7	502.4	501.0	500.3



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5	559.9	558.3	558.2
115°	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4	649.0	648.7	649.4
117.5°	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1	738.2	738.3	739.1
120°	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3	797.6	798.0	799.6
122.5°	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1	858.0	858.9	859.8
125°	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0	947.4	948.8	949.4
127.5°	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9	1035.7	1037.6	1038.4
130°	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2	1093.6	1094.9	1095.9
132.5°	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9	1150.5	1152.2	1152.9
135°	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9	1235.2	1236.6	1236.9
137.5°	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9	1318.3	1319.7	1318.8
140°	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7
142.5°	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6	1422.9	1423.2	1422.6
145°	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7	1498.1	1498.4	1497.4
147.5°	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7	1612.7	1612.7	1611.9
152.5°	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7	1652.2	1651.6	1651.2
155°	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3	1710.0	1708.6	1708.3
157.5°	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7	1760.3	1758.9	1758.6
160°	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7	1791.0	1789.3	1789.3
162.5°	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9	1820.3	1818.6	1818.3
165°	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9	1856.8	1854.8	1854.8
167.5°	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6	1884.4
170°	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5	1900.5
172.5°	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0	1916.0	1913.9	1913.9
175°	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0	1930.0	1927.9	1927.9
177.5°	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1	1936.5	1934.9	1934.9
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1657.6	1656.0	1648.3	1639.5	1627.9	1620.2	1614.2	1610.9	1601.0	1588.9	1580.6
5°	1760.0	1739.4	1717.5	1690.6	1665.9	1640.4	1624.7	1606.1	1583.4	1558.0	1540.1
7.5°	1869.8	1829.3	1785.7	1740.8	1696.4	1656.6	1621.3	1591.2	1555.1	1518.6	1493.1
10°	1953.9	1894.7	1833.6	1771.0	1713.9	1660.4	1619.1	1578.6	1535.3	1493.4	1461.8
12.5°	2030.2	1952.5	1882.0	1805.1	1732.1	1668.1	1608.7	1561.0	1508.9	1464.2	1428.3
15°	2127.0	2047.3	1962.1	1845.2	1748.4	1667.3	1595.1	1532.6	1469.4	1414.3	1379.3
17.5°	2217.5	2097.5	1983.0	1885.5	1759.6	1658.3	1570.2	1495.4	1426.0	1367.8	1324.6
20°	2254.8	2138.7	2014.3	1890.0	1766.3	1652.8	1550.4	1467.9	1395.8	1329.8	1290.0
22.5°	2277.3	2145.9	2014.9	1881.2	1749.7	1631.9	1530.7	1440.0	1361.7	1299.0	1249.8
25°	2303.6	2147.0	2002.7	1870.7	1736.7	1608.8	1488.5	1392.4	1307.9	1241.1	1188.9
27.5°	2321.0	2136.7	1966.1	1819.4	1683.4	1556.2	1445.9	1343.9	1258.2	1187.7	1131.7
30°	2324.3	2128.4	1938.0	1779.3	1641.1	1524.3	1407.4	1309.9	1219.2	1144.3	1092.1
32.5°	2328.6	2108.1	1900.1	1731.4	1590.0	1474.3	1368.5	1275.3	1182.3	1108.5	1055.2
35°	2310.6	2096.8	1842.5	1648.7	1507.1	1395.1	1299.6	1213.7	1122.3	1050.8	996.5
37.5°	2232.4	2052.1	1782.8	1555.5	1407.4	1303.7	1225.9	1151.0	1067.1	990.1	938.9
40°	2153.8	2008.1	1736.7	1498.8	1344.2	1237.7	1167.6	1106.5	1025.4	953.2	898.3
42.5°	2036.7	1948.2	1692.7	1439.5	1272.7	1170.1	1111.0	1053.7	982.5	909.2	857.6
45°	1821.9	1833.6	1602.7	1344.9	1173.8	1070.8	1015.0	975.2	912.0	851.5	798.6
47.5°	1552.5	1661.7	1496.9	1244.2	1069.4	972.7	924.0	889.3	846.7	787.3	739.0
50°	1376.5	1532.6	1412.3	1176.6	1004.1	907.9	859.7	831.5	794.5	747.7	701.7
52.5°	1214.4	1381.9	1310.0	1101.3	933.1	845.2	798.2	775.0	745.5	701.6	659.8
55°	990.3	1160.0	1143.6	987.5	826.8	747.7	712.0	685.9	665.9	633.0	600.0
57.5°	801.0	962.0	970.5	861.1	733.1	654.9	624.2	604.5	591.5	566.5	536.0
60°	681.8	829.5	858.4	775.9	665.9	597.2	566.9	551.2	540.9	520.9	497.6
62.5°	582.8	708.5	741.2	681.9	601.6	537.2	513.6	498.4	491.4	474.2	453.6
65°	446.1	550.5	582.1	549.1	507.2	455.7	436.4	423.3	417.2	407.6	392.4
67.5°	335.4	411.5	446.2	422.9	407.8	375.3	363.0	356.0	350.5	343.9	331.2
70°	269.4	325.8	361.5	355.3	343.0	325.8	316.8	312.0	306.5	301.0	290.0
72.5°	216.6	255.4	288.9	292.1	282.0	278.5	270.6	268.6	265.3	258.7	252.7
75°	143.6	170.5	193.8	202.8	206.8	210.3	206.8	206.2	205.5	200.0	196.5
77.5°	94.1	108.6	123.3	138.6	145.0	149.7	150.8	153.3	151.5	148.6	146.9
80°	72.2	75.6	85.9	99.0	109.3	113.4	116.1	117.5	116.8	116.1	113.4
82.5°	52.4	55.2	60.1	69.3	78.0	84.8	86.4	86.1	87.7	88.1	85.9
85°	28.2	28.9	30.2	31.6	36.5	44.0	46.0	47.5	48.8	48.8	44.6
87.5°	14.3	12.9	13.1	12.3	13.3	13.2	15.9	17.9	19.1	17.6	18.3
90°	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5	4.9	8.3	11.7
92.5°	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9	39.2	41.4	43.7
95°	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9	92.2	94.6	96.9
97.5°	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6	161.4	163.1	164.9
100°	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1	209.1	211.2	213.2
102.5°	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0	263.2	264.4	265.6
105°	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6	343.4	344.0	344.7
107.5°	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5	436.9	437.3	437.7
110°	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9	495.6	496.2	497.0



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8	556.2	556.6	557.0
115°	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2	648.2	649.2	650.3
117.5°	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2	739.8	740.5	741.2
120°	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5	798.5	800.5	802.5
122.5°	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2	857.6	859.1	860.6
125°	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2	948.2	949.3	950.3
127.5°	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3	1033.4	1035.6	1037.7
130°	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3	1090.0	1092.7	1095.4
132.5°	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4	1146.0	1148.7	1151.4
135°	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9	1230.9	1232.9	1235.0
137.5°	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1	1309.8	1311.5	1313.2
140°	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9	1364.6	1366.3	1368.0
142.5°	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9	1414.5	1416.2	1418.0
145°	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9	1491.6	1492.2	1492.9
147.5°	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0	1560.2	1561.5	1562.8
150°	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6	1607.3	1607.9	1608.6
152.5°	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6	1646.5	1647.5	1648.4
155°	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5	1759.1	1758.7	1758.3
160°	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4	1791.7	1791.0	1790.3
162.5°	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6	1820.7	1819.7	1818.8
165°	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4	1858.4	1857.3	1856.3
167.5°	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6	1888.1	1886.8	1885.4
170°	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5	1905.2	1903.9	1902.5
172.5°	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0	1918.6	1917.2	1915.9
175°	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0	1932.7	1931.3	1930.0
177.5°	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7	1938.7	1937.6	1936.5
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1577.9	1570.7	1565.8	1554.8	1547.7	1539.9	1532.3	1537.2	1536.7	1536.1	1536.1
5°	1525.0	1509.1	1494.8	1476.2	1464.5	1450.1	1439.1	1437.7	1440.5	1430.9	1425.3
7.5°	1472.5	1450.9	1430.5	1410.0	1388.3	1370.9	1360.1	1354.9	1348.0	1342.0	1335.8
10°	1435.6	1410.3	1390.3	1364.8	1341.5	1320.9	1307.9	1298.9	1294.0	1289.3	1280.3
12.5°	1397.8	1372.8	1347.5	1318.7	1296.5	1272.5	1262.7	1252.7	1243.5	1238.1	1225.9
15°	1342.2	1309.9	1283.1	1252.8	1228.1	1204.8	1191.0	1171.0	1168.3	1161.4	1149.1
17.5°	1286.6	1251.4	1214.5	1192.1	1164.2	1139.8	1118.9	1112.3	1092.6	1085.2	1074.4
20°	1242.5	1210.2	1182.0	1152.6	1112.0	1089.2	1072.8	1063.9	1048.0	1038.4	1031.6
22.5°	1204.6	1171.7	1139.2	1104.7	1071.3	1045.8	1033.8	1019.9	1011.2	997.7	990.3
25°	1150.4	1114.7	1075.5	1038.4	1014.4	995.1	975.9	963.5	951.2	944.9	931.2
27.5°	1087.5	1050.2	1013.5	985.3	955.8	936.9	919.4	908.4	893.5	883.1	875.6
30°	1052.9	1008.9	977.2	951.8	914.0	896.2	883.1	869.4	858.4	847.4	839.8
32.5°	1012.7	972.6	942.6	911.2	882.1	862.6	845.8	833.6	824.3	813.9	806.3
35°	949.8	916.1	885.1	853.5	832.2	812.3	792.4	782.0	773.2	763.6	756.7
37.5°	892.8	861.4	832.0	802.0	775.6	759.4	743.4	735.5	723.4	716.9	709.9
40°	857.7	826.8	795.2	766.3	738.8	726.4	712.0	700.3	689.3	684.5	676.9
42.5°	819.2	788.3	761.6	730.5	708.0	691.3	677.9	665.1	656.9	649.8	645.6
45°	762.1	734.7	708.5	677.6	656.3	641.9	626.7	615.1	607.5	602.7	595.1
47.5°	706.8	679.2	652.8	625.8	605.2	588.7	573.6	565.4	555.4	549.6	544.4
50°	666.6	641.9	613.7	589.0	568.4	551.9	539.5	529.2	520.3	512.7	509.3
52.5°	629.8	603.4	579.1	556.0	534.2	515.5	504.3	493.4	486.8	478.1	474.0
55°	569.1	543.6	523.0	500.3	479.0	463.2	449.5	439.8	432.9	423.3	417.9
57.5°	512.0	489.2	464.5	444.9	422.9	409.6	398.2	385.2	376.8	369.2	363.9
60°	473.5	447.4	426.1	407.6	388.3	371.1	360.8	350.5	341.5	334.0	329.2
62.5°	433.3	410.6	390.3	370.1	352.5	337.6	325.6	317.0	309.1	304.3	299.5
65°	371.8	354.0	333.4	316.8	300.3	289.3	279.7	272.2	266.6	263.2	259.1
67.5°	315.2	297.8	279.8	263.7	252.7	244.3	237.9	231.5	228.7	224.3	221.6
70°	278.3	260.4	244.7	232.3	221.3	215.1	211.0	206.2	203.4	197.9	195.2
72.5°	238.2	225.3	213.9	203.7	194.9	189.2	184.0	178.1	173.7	167.6	164.9
75°	187.6	175.9	167.0	160.2	154.6	147.0	139.5	133.3	131.3	129.2	128.6
77.5°	139.0	131.6	125.1	119.3	112.4	106.9	105.3	103.9	103.5	102.4	102.4
80°	109.3	102.4	97.6	90.7	86.5	86.5	86.5	85.2	85.9	85.9	85.9
82.5°	81.2	74.9	72.3	69.8	69.0	69.6	69.6	69.8	69.4	70.5	70.0
85°	41.9	42.6	44.0	43.3	44.0	44.0	45.3	44.6	45.3	44.0	45.3
87.5°	18.4	20.8	22.2	23.7	25.1	25.4	26.3	26.6	27.4	27.7	27.9
90°	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3	40.6	42.0	43.0
92.5°	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6	61.7	62.8	63.1
95°	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4	116.7	118.1	118.8
97.5°	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5	181.0	182.6	183.3
100°	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9	226.9	227.9	228.7
102.5°	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5	280.5	281.6	282.0
105°	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4	359.4	359.4	359.7
107.5°	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0	447.0	448.1	448.4
110°	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7	505.0	506.4	506.8



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5	563.1	564.7	565.5
115°	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4	649.7	650.1	650.1
117.5°	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1	738.1	738.0	737.5
120°	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3	797.0	796.6	796.1
122.5°	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1	856.3	855.4	854.4
125°	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0	944.6	943.3	941.9
127.5°	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9	1032.0	1030.1	1028.3
130°	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2	1090.9	1089.5	1087.6
132.5°	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9	1147.3	1145.7	1144.0
135°	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9	1232.4	1231.1	1230.1
137.5°	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9	1315.5	1314.0	1312.6
140°	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.4
142.5°	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6	1422.2	1421.9	1420.8
145°	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7	1497.4	1497.1	1496.2
147.5°	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7	1612.7	1612.7	1611.6
152.5°	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7	1653.3	1653.9	1653.3
155°	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3	1712.6	1714.0	1713.5
157.5°	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7	1763.1	1764.5	1764.3
160°	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7	1794.4	1796.0	1796.2
162.5°	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9	1823.6	1825.3	1825.1
165°	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9	1860.9	1862.9	1862.8
167.5°	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0
170°	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0
172.5°	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0	1920.2	1922.3	1922.2
175°	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0	1934.0	1936.0	1935.8
177.5°	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1	1939.7	1941.4	1941.3
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1529.5	1528.9	1529.5	1527.3	1529.5	1528.9	1529.5	1536.1	1536.1	1536.7	1537.2
5°	1423.3	1422.6	1420.6	1414.3	1420.6	1422.6	1423.3	1425.3	1430.9	1440.5	1437.7
7.5°	1330.5	1329.6	1323.5	1323.6	1323.5	1329.6	1330.5	1335.8	1342.0	1348.0	1354.9
10°	1275.6	1276.2	1268.0	1263.1	1268.0	1276.2	1275.6	1280.3	1289.3	1294.0	1298.9
12.5°	1222.2	1219.0	1212.4	1207.1	1212.4	1219.0	1222.2	1225.9	1238.1	1243.5	1252.7
15°	1151.9	1145.0	1128.4	1129.8	1128.4	1145.0	1151.9	1149.1	1161.4	1168.3	1171.0
17.5°	1068.9	1063.9	1063.6	1054.0	1063.6	1063.9	1068.9	1074.4	1085.2	1092.6	1112.3
20°	1020.6	1017.1	1018.4	1008.9	1018.4	1017.1	1020.6	1031.6	1038.4	1048.0	1063.9
22.5°	982.6	979.2	973.4	970.4	973.4	979.2	982.6	990.3	997.7	1011.2	1019.9
25°	927.1	921.6	916.1	919.6	916.1	921.6	927.1	931.2	944.9	951.2	963.5
27.5°	871.6	867.5	861.9	861.2	861.9	867.5	871.6	875.6	883.1	893.5	908.4
30°	836.4	832.2	829.5	826.1	829.5	832.2	836.4	839.8	847.4	858.4	869.4
32.5°	800.6	799.8	794.9	794.2	794.9	799.8	800.6	806.3	813.9	824.3	833.6
35°	753.9	749.8	748.4	749.1	748.4	749.8	753.9	756.7	763.6	773.2	782.0
37.5°	709.5	704.0	701.6	699.0	701.6	704.0	709.5	709.9	716.9	723.4	735.5
40°	677.6	672.2	670.8	669.3	670.8	672.2	677.6	676.9	684.5	689.3	700.3
42.5°	641.9	639.6	638.8	636.4	638.8	639.6	641.9	645.6	649.8	656.9	665.1
45°	593.1	592.4	588.2	589.7	588.2	592.4	593.1	595.1	602.7	607.5	615.1
47.5°	541.7	538.7	535.7	537.7	535.7	538.7	541.7	544.4	549.6	555.4	565.4
50°	506.5	505.1	499.0	500.3	499.0	505.1	506.5	509.3	512.7	520.3	529.2
52.5°	471.3	466.1	463.7	462.9	463.7	466.1	471.3	474.0	478.1	486.8	493.4
55°	413.0	406.9	404.1	402.7	404.1	406.9	413.0	417.9	423.3	432.9	439.8
57.5°	355.9	354.2	352.0	353.6	352.0	354.2	355.9	363.9	369.2	376.8	385.2
60°	322.3	322.3	322.3	321.6	322.3	322.3	322.3	329.2	334.0	341.5	350.5
62.5°	296.5	294.8	294.3	295.3	294.3	294.8	296.5	299.5	304.3	309.1	317.0
65°	257.0	256.3	253.6	252.9	253.6	256.3	257.0	259.1	263.2	266.6	272.2
67.5°	219.7	217.3	216.5	215.5	216.5	217.3	219.7	221.6	224.3	228.7	231.5
70°	191.8	190.4	186.2	186.9	186.2	190.4	191.8	195.2	197.9	203.4	206.2
72.5°	161.5	160.2	159.3	158.3	159.3	160.2	161.5	164.9	167.6	173.7	178.1
75°	127.8	127.1	126.4	129.2	126.4	127.1	127.8	128.6	129.2	131.3	133.3
77.5°	102.4	102.4	102.8	101.7	102.8	102.4	102.4	102.4	102.4	103.5	103.9
80°	85.9	85.9	85.2	85.2	85.2	85.9	85.9	85.9	85.9	85.9	85.2
82.5°	68.9	69.4	69.8	68.8	69.8	69.4	68.9	70.0	70.5	69.4	69.8
85°	45.3	44.6	46.0	45.3	46.0	44.6	45.3	45.3	44.0	45.3	44.6
87.5°	29.1	28.1	28.3	28.9	28.3	28.1	29.1	27.9	27.7	27.4	26.6
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3
92.5°	62.7	62.3	61.9	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6
95°	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4
97.5°	183.2	183.0	182.9	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5
100°	229.4	230.1	230.8	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9
102.5°	281.9	281.7	281.6	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5
105°	360.4	361.1	361.7	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4
107.5°	448.0	447.6	447.2	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0
110°	506.0	505.4	504.7	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	565.4	565.2	565.1	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5
115°	649.7	649.4	649.0	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4
117.5°	736.5	735.6	734.7	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1
120°	795.5	794.8	794.1	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3
122.5°	853.5	852.5	851.6	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1
125°	940.6	939.3	937.9	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0
127.5°	1026.8	1025.2	1023.7	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9
130°	1085.3	1082.9	1080.6	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2
132.5°	1142.2	1140.3	1138.4	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9
135°	1229.4	1228.7	1228.1	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9
137.5°	1311.3	1310.1	1308.8	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9
140°	1367.0	1364.6	1362.2	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4
142.5°	1419.0	1417.1	1415.3	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6
145°	1494.9	1493.6	1492.2	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7
147.5°	1565.8	1563.8	1561.7	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8
150°	1609.6	1607.6	1605.6	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7
152.5°	1651.4	1649.7	1647.9	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7
155°	1711.1	1708.8	1706.4	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3
157.5°	1762.4	1760.5	1758.6	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7
160°	1794.9	1793.5	1792.2	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7
162.5°	1822.9	1820.8	1818.6	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9
165°	1860.4	1858.1	1855.6	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9
167.5°	1891.0	1888.9	1886.7	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9
170°	1907.6	1905.2	1902.9	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2
172.5°	1919.8	1917.4	1915.0	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0
175°	1933.5	1931.1	1928.7	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0
177.5°	1939.3	1937.4	1935.6	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1532.3	1539.9	1547.7	1554.8	1565.8	1570.7	1577.9	1580.6	1588.9	1601.0	1610.9
5°	1439.1	1450.1	1464.5	1476.2	1494.8	1509.1	1525.0	1540.1	1558.0	1583.4	1606.1
7.5°	1360.1	1370.9	1388.3	1410.0	1430.5	1450.9	1472.5	1493.1	1518.6	1555.1	1591.2
10°	1307.9	1320.9	1341.5	1364.8	1390.3	1410.3	1435.6	1461.8	1493.4	1535.3	1578.6
12.5°	1262.7	1272.5	1296.5	1318.7	1347.5	1372.8	1397.8	1428.3	1464.2	1508.9	1561.0
15°	1191.0	1204.8	1228.1	1252.8	1283.1	1309.9	1342.2	1379.3	1414.3	1469.4	1532.6
17.5°	1118.9	1139.8	1164.2	1192.1	1214.5	1251.4	1286.6	1324.6	1367.8	1426.0	1495.4
20°	1072.8	1089.2	1112.0	1152.6	1182.0	1210.2	1242.5	1290.0	1329.8	1395.8	1467.9
22.5°	1033.8	1045.8	1071.3	1104.7	1139.2	1171.7	1204.6	1249.8	1299.0	1361.7	1440.0
25°	975.9	995.1	1014.4	1038.4	1075.5	1114.7	1150.4	1188.9	1241.1	1307.9	1392.4
27.5°	919.4	936.9	955.8	985.3	1013.5	1050.2	1087.5	1131.7	1187.7	1258.2	1343.9
30°	883.1	896.2	914.0	951.8	977.2	1008.9	1052.9	1092.1	1144.3	1219.2	1309.9
32.5°	845.8	862.6	882.1	911.2	942.6	972.6	1012.7	1055.2	1108.5	1182.3	1275.3
35°	792.4	812.3	832.2	853.5	885.1	916.1	949.8	996.5	1050.8	1122.3	1213.7
37.5°	743.4	759.4	775.6	802.0	832.0	861.4	892.8	938.9	990.1	1067.1	1151.0
40°	712.0	726.4	738.8	766.3	795.2	826.8	857.7	898.3	953.2	1025.4	1106.5
42.5°	677.9	691.3	708.0	730.5	761.6	788.3	819.2	857.6	909.2	982.5	1053.7
45°	626.7	641.9	656.3	677.6	708.5	734.7	762.1	798.6	851.5	912.0	975.2
47.5°	573.6	588.7	605.2	625.8	652.8	679.2	706.8	739.0	787.3	846.7	889.3
50°	539.5	551.9	568.4	589.0	613.7	641.9	666.6	701.7	747.7	794.5	831.5
52.5°	504.3	515.5	534.2	556.0	579.1	603.4	629.8	659.8	701.6	745.5	775.0
55°	449.5	463.2	479.0	500.3	523.0	543.6	569.1	600.0	633.0	665.9	685.9
57.5°	398.2	409.6	422.9	444.9	464.5	489.2	512.0	536.0	566.5	591.5	604.5
60°	360.8	371.1	388.3	407.6	426.1	447.4	473.5	497.6	520.9	540.9	551.2
62.5°	325.6	337.6	352.5	370.1	390.3	410.6	433.3	453.6	474.2	491.4	498.4
65°	279.7	289.3	300.3	316.8	333.4	354.0	371.8	392.4	407.6	417.2	423.3
67.5°	237.9	244.3	252.7	263.7	279.8	297.8	315.2	331.2	343.9	350.5	356.0
70°	211.0	215.1	221.3	232.3	244.7	260.4	278.3	290.0	301.0	306.5	312.0
72.5°	184.0	189.2	194.9	203.7	213.9	225.3	238.2	252.7	258.7	265.3	268.6
75°	139.5	147.0	154.6	160.2	167.0	175.9	187.6	196.5	200.0	205.5	206.2
77.5°	105.3	106.9	112.4	119.3	125.1	131.6	139.0	146.9	148.6	151.5	153.3
80°	86.5	86.5	86.5	90.7	97.6	102.4	109.3	113.4	116.1	116.8	117.5
82.5°	69.6	69.6	69.0	69.8	72.3	74.9	81.2	85.9	88.1	87.7	86.1
85°	45.3	44.0	44.0	43.3	44.0	42.6	41.9	44.6	48.8	48.8	47.5
87.5°	26.3	25.4	25.1	23.7	22.2	20.8	18.4	18.3	17.6	19.1	17.9
90°	37.9	36.6	32.1	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5
92.5°	59.6	58.5	55.9	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9
95°	114.0	112.7	110.0	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9
97.5°	177.9	176.3	174.4	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6
100°	224.9	223.9	222.2	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1
102.5°	278.5	277.4	275.2	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0
105°	359.4	359.4	356.4	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6
107.5°	444.8	443.7	442.5	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5
110°	502.4	501.0	500.3	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	559.9	558.3	558.2	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8
115°	649.0	648.7	649.4	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2
117.5°	738.2	738.3	739.1	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2
120°	797.6	798.0	799.6	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5
122.5°	858.0	858.9	859.8	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2
125°	947.4	948.8	949.4	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2
127.5°	1035.7	1037.6	1038.4	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3
130°	1093.6	1094.9	1095.9	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3
132.5°	1150.5	1152.2	1152.9	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4
135°	1235.2	1236.6	1236.9	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9
137.5°	1318.3	1319.7	1318.8	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1
140°	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9
142.5°	1422.9	1423.2	1422.6	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9
145°	1498.1	1498.4	1497.4	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9
147.5°	1568.8	1568.8	1567.8	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0
150°	1612.7	1612.7	1611.9	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6
152.5°	1652.2	1651.6	1651.2	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6
155°	1710.0	1708.6	1708.3	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1760.3	1758.9	1758.6	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5
160°	1791.0	1789.3	1789.3	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4
162.5°	1820.3	1818.6	1818.3	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6
165°	1856.8	1854.8	1854.8	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4
167.5°	1886.7	1884.6	1884.4	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6
170°	1902.9	1900.5	1900.5	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5
172.5°	1916.0	1913.9	1913.9	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0
175°	1930.0	1927.9	1927.9	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0
177.5°	1936.5	1934.9	1934.9	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1614.2	1620.2	1627.9	1639.5	1648.3	1656.0	1657.6	1659.8	1665.4	1674.7	1681.8
5°	1624.7	1640.4	1665.9	1690.6	1717.5	1739.4	1760.0	1774.4	1788.2	1817.1	1840.5
7.5°	1621.3	1656.6	1696.4	1740.8	1785.7	1829.3	1869.8	1905.9	1941.9	1984.0	2031.9
10°	1619.1	1660.4	1713.9	1771.0	1833.6	1894.7	1953.9	1999.9	2053.5	2101.6	2162.7
12.5°	1608.7	1668.1	1732.1	1805.1	1882.0	1952.5	2030.2	2093.9	2155.3	2224.7	2295.8
15°	1595.1	1667.3	1748.4	1845.2	1962.1	2047.3	2127.0	2237.7	2313.3	2388.8	2490.6
17.5°	1570.2	1658.3	1759.6	1885.5	1983.0	2097.5	2217.5	2304.9	2406.7	2513.3	2605.4
20°	1550.4	1652.8	1766.3	1890.0	2014.3	2138.7	2254.8	2359.3	2464.5	2587.5	2663.1
22.5°	1530.7	1631.9	1749.7	1881.2	2014.9	2145.9	2277.3	2400.0	2518.3	2642.4	2739.0
25°	1488.5	1608.8	1736.7	1870.7	2002.7	2147.0	2303.6	2440.4	2586.8	2714.6	2806.0
27.5°	1445.9	1556.2	1683.4	1819.4	1966.1	2136.7	2321.0	2476.4	2623.1	2714.6	2743.4
30°	1407.4	1524.3	1641.1	1779.3	1938.0	2128.4	2324.3	2502.2	2622.5	2662.4	2632.8
32.5°	1368.5	1474.3	1590.0	1731.4	1900.1	2108.1	2328.6	2486.9	2559.3	2528.8	2408.5
35°	1299.6	1395.1	1507.1	1648.7	1842.5	2096.8	2310.6	2417.7	2399.8	2228.1	2001.2
37.5°	1225.9	1303.7	1407.4	1555.5	1782.8	2052.1	2232.4	2248.3	2093.7	1829.9	1567.9
40°	1167.6	1237.7	1344.2	1498.8	1736.7	2008.1	2153.8	2089.9	1850.1	1556.6	1338.1
42.5°	1111.0	1170.1	1272.7	1439.5	1692.7	1948.2	2036.7	1897.5	1620.8	1343.3	1144.6
45°	1015.0	1070.8	1173.8	1344.9	1602.7	1833.6	1821.9	1579.9	1303.0	1079.6	914.7
47.5°	924.0	972.7	1069.4	1244.2	1496.9	1661.7	1552.5	1295.1	1060.2	880.9	763.3
50°	859.7	907.9	1004.1	1176.6	1412.3	1532.6	1376.5	1128.4	913.3	764.9	671.5
52.5°	798.2	845.2	933.1	1101.3	1310.0	1381.9	1214.4	984.4	805.1	676.9	596.6
55°	712.0	747.7	826.8	987.5	1143.6	1160.0	990.3	797.9	650.2	560.8	505.8
57.5°	624.2	654.9	733.1	861.1	970.5	962.0	801.0	634.6	535.1	468.7	428.9
60°	566.9	597.2	665.9	775.9	858.4	829.5	681.8	547.8	462.5	413.7	382.1
62.5°	513.6	537.2	601.6	681.9	741.2	708.5	582.8	471.9	404.2	363.1	338.1
65°	436.4	455.7	507.2	549.1	582.1	550.5	446.1	369.0	320.2	291.3	274.2
67.5°	363.0	375.3	407.8	422.9	446.2	411.5	335.4	283.9	256.1	231.8	219.7
70°	316.8	325.8	343.0	355.3	361.5	325.8	269.4	231.6	208.2	191.1	183.5
72.5°	270.6	278.5	282.0	292.1	288.9	255.4	216.6	186.5	169.8	158.0	148.3
75°	206.8	210.3	206.8	202.8	193.8	170.5	143.6	128.6	116.1	110.7	107.2
77.5°	150.8	149.7	145.0	138.6	123.3	108.6	94.1	89.1	83.7	80.8	79.6
80°	116.1	113.4	109.3	99.0	85.9	75.6	72.2	68.8	66.7	63.2	62.5
82.5°	86.4	84.8	78.0	69.3	60.1	55.2	52.4	51.1	49.1	47.3	47.2
85°	46.0	44.0	36.5	31.6	30.2	28.9	28.2	28.2	25.4	24.7	24.7
87.5°	15.9	13.2	13.3	12.3	13.1	12.9	14.3	14.1	14.4	15.2	14.4
90°	4.9	8.3	11.7	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3
92.5°	39.2	41.4	43.7	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6
95°	92.2	94.6	96.9	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4
97.5°	161.4	163.1	164.9	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5
100°	209.1	211.2	213.2	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9
102.5°	263.2	264.4	265.6	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5
105°	343.4	344.0	344.7	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4
107.5°	436.9	437.3	437.7	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0
110°	495.6	496.2	497.0	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	556.2	556.6	557.0	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5
115°	648.2	649.2	650.3	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4
117.5°	739.8	740.5	741.2	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1
120°	798.5	800.5	802.5	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3
122.5°	857.6	859.1	860.6	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1
125°	948.2	949.3	950.3	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0
127.5°	1033.4	1035.6	1037.7	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9
130°	1090.0	1092.7	1095.4	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2
132.5°	1146.0	1148.7	1151.4	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9
135°	1230.9	1232.9	1235.0	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9
137.5°	1309.8	1311.5	1313.2	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9
140°	1364.6	1366.3	1368.0	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4
142.5°	1414.5	1416.2	1418.0	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6
145°	1491.6	1492.2	1492.9	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7
147.5°	1560.2	1561.5	1562.8	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8
150°	1607.3	1607.9	1608.6	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7
152.5°	1646.5	1647.5	1648.4	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7
155°	1707.1	1707.1	1707.1	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3
157.5°	1759.1	1758.7	1758.3	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7
160°	1791.7	1791.0	1790.3	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7
162.5°	1820.7	1819.7	1818.8	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9
165°	1858.4	1857.3	1856.3	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9
167.5°	1888.1	1886.8	1885.4	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9
170°	1905.2	1903.9	1902.5	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2
172.5°	1918.6	1917.2	1915.9	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0
175°	1932.7	1931.3	1930.0	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0
177.5°	1938.7	1937.6	1936.5	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1693.3	1693.3	1695.6	1703.8	1705.0	1712.0	1709.9
5°	1861.1	1874.1	1879.0	1899.6	1911.9	1917.4	1906.4
7.5°	2066.2	2102.9	2120.4	2142.0	2161.1	2166.9	2151.9
10°	2215.6	2254.1	2286.4	2306.4	2324.9	2337.3	2353.1
12.5°	2360.3	2407.5	2438.2	2466.4	2485.5	2501.1	2503.8
15°	2517.4	2588.9	2643.1	2683.0	2702.9	2713.2	2709.2
17.5°	2675.8	2742.1	2780.8	2821.5	2849.0	2850.4	2851.3
20°	2765.5	2830.0	2874.8	2905.0	2935.9	2934.6	2941.4
22.5°	2825.4	2876.3	2910.5	2932.4	2943.0	2937.8	2939.2
25°	2853.5	2868.5	2862.4	2827.3	2818.4	2786.1	2791.6
27.5°	2708.9	2637.4	2563.4	2468.3	2393.3	2333.3	2336.3
30°	2512.5	2386.1	2241.8	2120.8	2012.3	1982.1	1917.4
32.5°	2238.3	2048.5	1879.5	1766.8	1673.5	1648.3	1592.0
35°	1773.1	1588.9	1415.0	1310.6	1269.3	1211.6	1210.9
37.5°	1378.2	1216.0	1124.1	1045.7	1004.6	969.7	966.2
40°	1159.4	1032.9	963.5	907.2	866.7	840.5	834.4
42.5°	1006.5	904.2	839.3	804.4	773.2	759.7	749.6
45°	821.9	753.3	707.8	676.2	661.9	651.5	646.0
47.5°	687.5	641.5	610.6	589.6	577.8	566.9	569.9
50°	614.4	576.6	553.9	534.0	525.0	517.5	518.2
52.5°	555.5	521.6	503.3	488.9	477.8	472.4	469.8
55°	471.4	450.1	431.6	421.3	415.1	407.6	405.5
57.5°	402.1	385.7	370.5	358.9	357.4	350.1	351.0
60°	356.0	342.2	329.9	323.7	318.9	312.7	314.8
62.5°	318.1	306.5	295.3	290.1	285.4	280.8	281.8
65°	260.4	249.4	242.6	239.8	237.8	235.7	233.7
67.5°	207.5	200.9	196.5	190.7	186.4	185.7	183.6
70°	174.6	165.6	158.0	150.5	148.5	147.7	148.5
72.5°	140.0	134.3	132.2	128.6	128.2	126.3	127.5
75°	105.1	103.1	101.7	99.0	99.0	99.0	99.0
77.5°	77.6	76.2	75.4	74.9	74.2	73.2	73.1
80°	60.5	59.8	58.4	58.4	57.8	58.4	57.8
82.5°	45.6	45.5	44.1	44.1	43.4	43.0	43.4
85°	23.3	22.7	24.0	22.7	23.3	22.0	23.3
87.5°	14.7	14.9	14.6	14.7	14.3	15.6	14.6
90°	40.6	42.0	43.0	43.6	44.3	45.0	45.6
92.5°	61.7	62.8	63.1	62.7	62.3	61.9	61.5
95°	116.7	118.1	118.8	118.8	118.8	118.8	118.8
97.5°	181.0	182.6	183.3	183.2	183.0	182.9	182.8
100°	226.9	227.9	228.7	229.4	230.1	230.8	231.5
102.5°	280.5	281.6	282.0	281.9	281.7	281.6	281.4
105°	359.4	359.4	359.7	360.4	361.1	361.7	362.4
107.5°	447.0	448.1	448.4	448.0	447.6	447.2	446.8
110°	505.0	506.4	506.8	506.0	505.4	504.7	504.0



TEST NUMBER: P332467-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	563.1	564.7	565.5	565.4	565.2	565.1	564.9
115°	649.7	650.1	650.1	649.7	649.4	649.0	648.7
117.5°	738.1	738.0	737.5	736.5	735.6	734.7	733.7
120°	797.0	796.6	796.1	795.5	794.8	794.1	793.3
122.5°	856.3	855.4	854.4	853.5	852.5	851.6	850.6
125°	944.6	943.3	941.9	940.6	939.3	937.9	936.5
127.5°	1032.0	1030.1	1028.3	1026.8	1025.2	1023.7	1022.1
130°	1090.9	1089.5	1087.6	1085.3	1082.9	1080.6	1078.1
132.5°	1147.3	1145.7	1144.0	1142.2	1140.3	1138.4	1136.6
135°	1232.4	1231.1	1230.1	1229.4	1228.7	1228.1	1227.4
137.5°	1315.5	1314.0	1312.6	1311.3	1310.1	1308.8	1307.5
140°	1371.1	1370.7	1369.4	1367.0	1364.6	1362.2	1359.9
142.5°	1422.2	1421.9	1420.8	1419.0	1417.1	1415.3	1413.5
145°	1497.4	1497.1	1496.2	1494.9	1493.6	1492.2	1490.9
147.5°	1568.8	1568.8	1567.8	1565.8	1563.8	1561.7	1559.6
150°	1612.7	1612.7	1611.6	1609.6	1607.6	1605.6	1603.6
152.5°	1653.3	1653.9	1653.3	1651.4	1649.7	1647.9	1646.2
155°	1712.6	1714.0	1713.5	1711.1	1708.8	1706.4	1704.0
157.5°	1763.1	1764.5	1764.3	1762.4	1760.5	1758.6	1756.8
160°	1794.4	1796.0	1796.2	1794.9	1793.5	1792.2	1790.8
162.5°	1823.6	1825.3	1825.1	1822.9	1820.8	1818.6	1816.4
165°	1860.9	1862.9	1862.8	1860.4	1858.1	1855.6	1853.3
167.5°	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6
170°	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5
172.5°	1920.2	1922.3	1922.2	1919.8	1917.4	1915.0	1912.7
175°	1934.0	1936.0	1935.8	1933.5	1931.1	1928.7	1926.4
177.5°	1939.7	1941.4	1941.3	1939.3	1937.4	1935.6	1933.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5

(END OF REPORT)