

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332755-927

Luminaire Tested: **S124DIW-S575D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332755-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D770U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4408.4 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	1.6
10°-20°	204.1	4.6
20°-30°	300.5	6.8
30°-40°	349.3	7.9
40°-50°	349.3	7.9
50°-60°	305.5	6.9
60°-70°	226.9	5.1
70°-80°	128.9	2.9
80°-90°	39.5	0.9
90°-100°	26.9	0.6
100°-110°	171.5	3.9
110°-120°	328.0	7.4
120°-130°	416.3	9.4
130°-140°	445.5	10.1
140°-150°	416.6	9.4
150°-160°	335.9	7.6
160°-170°	216.7	4.9
170°-180°	74.7	1.7
0°-30°	577.0	13.1
0°-40°	926.3	21.0
0°-60°	1581.2	35.9
0°-90°	1976.5	44.8
90°-120°	526.3	11.9
90°-150°	1804.7	40.9
90°-180°	2432.0	55.2
0°-180°	4408.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	2	8	13	16	18	3
95°	32	14	13	16	17	42
105°	177	180	184	187	168	185
115°	330	332	332	333	333	325
125°	464	467	466	467	468	415
135°	576	576	578	579	580	444
145°	664	666	666	667	668	415
155°	729	729	727	729	728	336
165°	769	766	766	770	765	217
175°	786	783	783	788	782	75
180°	786	786	786	786	786	



TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.2	13.4	13.5	13.7	13.9	14.0	14.1	14.3	14.3	14.4	14.6
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	7.4	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2
95°	32.3	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7
97.5°	68.7	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6
100°	96.4	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7
102.5°	127.5	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7
105°	177.0	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7
107.5°	223.0	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3
110°	254.1	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6



TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.2	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9
115°	330.5	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9
117.5°	372.2	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8
120°	400.4	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5
122.5°	426.8	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2
125°	464.5	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1
127.5°	500.3	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5
130°	523.3	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9
132.5°	544.5	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0
135°	576.2	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3
137.5°	604.4	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4
140°	622.7	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4
142.5°	639.2	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3
145°	664.5	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4
147.5°	684.6	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4
150°	699.2	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9
152.5°	711.4	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4
155°	728.6	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9
157.5°	743.1	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3
160°	751.5	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0
162.5°	759.0	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0
165°	768.6	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7
167.5°	776.1	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8
170°	780.3	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4
172.5°	783.2	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3
175°	786.2	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4
177.5°	787.6	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	14.7	14.9	15.1	15.1	15.2	15.3	15.3	15.4
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.0	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	14.5	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.7	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	21.5	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	76.8	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	185.8	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	229.9	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	259.8	260.1	260.4	260.7	261.1	261.5	261.9	262.3





TEST NUMBER: P332755-927

CATALOG NUMBER: S124DIW-S575D770U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.8	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.2	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.4	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.5	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	525.9	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.0	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.5	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	607.8	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	625.8	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.6	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.5	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.5	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.6	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	728.4	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	757.8	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	767.7	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	775.0	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	779.4	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	782.3	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	785.6	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.0	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)