

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332453-840

Luminaire Tested: **S123RDIW-S1000D460U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332453-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5444.4 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70					70			
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60					60			
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51					51			
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44					44			
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38					38			
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33					33			
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29					29			
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26					26			
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24					24			
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21					21			
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19					19			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.9
10°-20°	442.8	8.1
20°-30°	637.6	11.7
30°-40°	718.2	13.2
40°-50°	687.1	12.6
50°-60°	562.6	10.3
60°-70°	379.6	7.0
70°-80°	191.0	3.5
80°-90°	52.2	1.0
90°-100°	37.9	0.7
100°-110°	113.6	2.1
110°-120°	193.2	3.5
120°-130°	254.1	4.7
130°-140°	285.6	5.2
140°-150°	280.8	5.2
150°-160°	236.4	4.3
160°-170°	157.3	2.9
170°-180°	55.1	1.0
0°-30°	1239.5	22.8
0°-40°	1957.7	36.0
0°-60°	3207.4	58.9
0°-90°	3830.3	70.4
90°-120°	344.8	6.3
90°-150°	1165.3	21.4
90°-180°	1614.0	29.6
0°-180°	5444.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	0	5	11	13	14	5
95°	27	30	34	36	36	30
105°	103	104	108	108	109	110
115°	194	196	195	195	195	192
125°	285	286	285	283	281	254
135°	369	372	372	370	369	284
145°	448	449	450	450	448	280
155°	513	513	514	515	512	236
165°	559	557	557	560	557	157
175°	581	580	579	582	579	55
180°	583	583	583	583	583	



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.5	24.0	21.5	19.0	16.6	15.5	15.7	16.0	16.3	16.5	16.4
90°	0.5	1.5	2.5	3.5	4.5	5.7	7.0	8.4	9.7	11.0	11.4
92.5°	11.1	11.8	12.4	13.1	13.8	14.5	15.3	16.1	16.9	17.6	17.9
95°	27.0	27.7	28.4	29.2	29.9	30.6	31.4	32.2	33.0	33.8	34.2
97.5°	48.0	48.5	49.0	49.6	50.1	50.6	51.2	51.8	52.4	53.0	53.4
100°	62.2	62.8	63.4	64.0	64.6	65.2	65.7	66.2	66.8	67.3	67.6
102.5°	78.7	79.1	79.5	79.8	80.2	80.7	81.4	82.0	82.7	83.4	83.7
105°	103.0	103.2	103.4	103.6	103.8	104.3	105.2	106.1	107.0	108.0	108.0
107.5°	131.2	131.3	131.4	131.5	131.7	131.9	132.3	132.6	133.0	133.4	133.7
110°	148.8	149.0	149.2	149.4	149.6	149.8	150.0	150.2	150.4	150.6	151.0



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.1	167.3	167.4	167.5	167.6	167.6	167.7	167.7	167.7	168.2
115°	194.5	194.8	195.1	195.4	195.7	195.8	195.6	195.4	195.2	195.0	195.1
117.5°	222.2	222.4	222.6	222.8	223.0	222.9	222.7	222.4	222.2	221.9	221.9
120°	239.3	239.9	240.5	241.2	241.8	241.9	241.4	240.9	240.3	239.8	239.7
122.5°	257.3	257.7	258.2	258.6	259.0	259.1	258.9	258.6	258.4	258.1	257.8
125°	284.7	285.0	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.1	284.7
127.5°	309.9	310.5	311.2	311.8	312.6	312.8	312.6	312.3	312.0	311.8	311.2
130°	326.8	327.6	328.4	329.2	330.0	330.2	329.9	329.6	329.3	329.0	328.6
132.5°	343.6	344.4	345.3	346.1	346.9	347.2	346.9	346.7	346.5	346.3	345.8
135°	369.3	369.9	370.5	371.1	371.7	372.0	371.9	371.8	371.7	371.6	371.2
137.5°	393.1	393.6	394.2	394.7	395.2	395.6	395.8	396.1	396.4	396.6	396.2
140°	409.6	410.1	410.6	411.1	411.6	411.9	412.0	412.1	412.2	412.3	412.2
142.5°	424.6	425.2	425.7	426.2	426.7	427.0	427.2	427.4	427.6	427.7	427.6
145°	448.1	448.3	448.5	448.7	448.9	449.1	449.4	449.7	450.0	450.3	450.2
147.5°	468.6	468.9	469.3	469.6	470.0	470.3	470.6	470.9	471.2	471.5	471.5
150°	482.8	483.0	483.2	483.4	483.6	483.8	484.0	484.2	484.4	484.6	484.6
152.5°	494.5	494.8	495.1	495.3	495.6	495.8	495.9	496.1	496.2	496.3	496.6
155°	513.0	513.0	513.0	513.0	513.0	513.1	513.2	513.3	513.4	513.5	513.9
157.5°	528.8	528.7	528.6	528.4	528.3	528.3	528.4	528.5	528.5	528.6	529.0
160°	538.7	538.5	538.3	538.1	537.9	537.8	537.8	537.8	537.8	537.8	538.3
162.5°	547.4	547.1	546.8	546.5	546.3	546.2	546.2	546.3	546.4	546.5	547.0
165°	558.8	558.5	558.2	557.8	557.5	557.4	557.4	557.4	557.4	557.4	558.1
167.5°	567.8	567.4	567.0	566.6	566.2	566.0	566.1	566.2	566.3	566.3	567.0
170°	573.0	572.6	572.2	571.8	571.4	571.2	571.2	571.2	571.2	571.2	571.9
172.5°	577.0	576.6	576.2	575.8	575.3	575.1	575.1	575.1	575.1	575.1	575.8
175°	581.2	580.8	580.4	580.0	579.6	579.4	579.4	579.4	579.4	579.4	580.0
177.5°	583.0	582.6	582.3	582.0	581.7	581.5	581.5	581.5	581.5	581.5	582.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	16.2	16.0	15.9	15.7	15.5	15.2	15.0	14.8
90°	11.8	12.2	12.6	12.9	13.1	13.3	13.5	13.7
92.5°	18.2	18.6	18.9	19.0	18.9	18.7	18.6	18.5
95°	34.6	35.0	35.4	35.6	35.6	35.6	35.6	35.6
97.5°	53.9	54.4	54.8	55.0	55.0	55.0	54.9	54.9
100°	67.9	68.2	68.5	68.8	69.0	69.2	69.4	69.6
102.5°	84.0	84.3	84.6	84.7	84.7	84.6	84.6	84.5
105°	108.0	108.0	108.0	108.1	108.4	108.6	108.8	109.0
107.5°	134.0	134.3	134.6	134.7	134.6	134.5	134.4	134.3
110°	151.4	151.8	152.2	152.3	152.1	151.9	151.7	151.5



TEST NUMBER: P332453-840

CATALOG NUMBER: S123RDIW-S1000D460U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.7	169.3	169.8	170.0	169.9	169.9	169.9	169.8
115°	195.2	195.3	195.4	195.4	195.3	195.2	195.1	195.0
117.5°	221.9	221.8	221.8	221.7	221.4	221.1	220.8	220.5
120°	239.6	239.5	239.4	239.2	239.0	238.8	238.6	238.4
122.5°	257.6	257.3	257.0	256.8	256.5	256.2	255.9	255.6
125°	284.3	283.9	283.5	283.1	282.7	282.3	281.9	281.4
127.5°	310.7	310.1	309.5	309.0	308.6	308.1	307.6	307.2
130°	328.2	327.8	327.4	326.9	326.2	325.5	324.8	324.0
132.5°	345.3	344.8	344.3	343.8	343.3	342.6	342.1	341.5
135°	370.8	370.4	370.0	369.7	369.5	369.3	369.1	368.9
137.5°	395.8	395.4	394.9	394.5	394.0	393.7	393.3	392.9
140°	412.1	412.0	411.9	411.5	410.8	410.1	409.4	408.7
142.5°	427.5	427.4	427.3	427.0	426.5	425.9	425.4	424.7
145°	450.1	450.0	449.9	449.7	449.3	448.9	448.5	448.1
147.5°	471.5	471.5	471.5	471.2	470.6	469.9	469.3	468.7
150°	484.6	484.6	484.6	484.3	483.7	483.1	482.5	481.9
152.5°	496.7	496.9	497.1	496.9	496.3	495.7	495.2	494.7
155°	514.3	514.7	515.1	514.9	514.2	513.5	512.8	512.1
157.5°	529.5	529.9	530.3	530.2	529.7	529.1	528.5	528.0
160°	538.8	539.3	539.8	539.8	539.4	539.0	538.6	538.2
162.5°	547.5	548.1	548.6	548.5	547.9	547.1	546.5	545.8
165°	558.7	559.3	559.9	559.8	559.1	558.4	557.6	556.9
167.5°	567.6	568.3	568.9	568.9	568.3	567.6	567.0	566.3
170°	572.6	573.3	574.0	574.0	573.3	572.6	571.9	571.2
172.5°	576.4	577.0	577.6	577.6	576.9	576.2	575.5	574.8
175°	580.6	581.2	581.8	581.8	581.1	580.4	579.7	579.0
177.5°	582.5	583.0	583.4	583.4	582.8	582.3	581.7	581.1
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6

(END OF REPORT)