

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333086-927

Luminaire Tested: **S124RDIW-S1020D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333086-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6186.9 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	2.2
10°-20°	374.7	6.1
20°-30°	541.1	8.7
30°-40°	613.3	9.9
40°-50°	592.3	9.6
50°-60°	492.5	8.0
60°-70°	340.1	5.5
70°-80°	172.4	2.8
80°-90°	47.3	0.8
90°-100°	68.4	1.1
100°-110°	202.7	3.3
110°-120°	344.1	5.6
120°-130°	453.7	7.3
130°-140°	509.6	8.2
140°-150°	500.8	8.1
150°-160°	421.2	6.8
160°-170°	280.2	4.5
170°-180°	98.1	1.6
0°-30°	1050.1	17.0
0°-40°	1663.5	26.9
0°-60°	2748.2	44.4
0°-90°	3308.0	53.5
90°-120°	615.3	9.9
90°-150°	2079.4	33.6
90°-180°	2879.0	46.5
0°-180°	6186.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	2	11	18	22	24	6
95°	48	55	61	63	63	54
105°	187	188	191	193	196	198
115°	350	350	348	348	347	345
125°	510	510	509	507	506	454
135°	657	662	662	660	658	508
145°	798	802	802	802	799	500
155°	915	915	914	917	914	421
165°	996	994	992	996	994	281
175°	1036	1032	1031	1036	1031	98
180°	1038	1038	1038	1038	1038	



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.6	19.5	18.3	17.1	16.0	15.4	15.5	15.6	15.7	15.8	15.8
90°	2.4	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7
92.5°	17.2	19.4	21.7	23.9	26.1	27.8	28.8	29.8	30.8	31.8	32.4
95°	48.2	49.7	51.3	53.0	54.6	56.0	57.3	58.5	59.7	61.0	61.6
97.5°	84.1	85.4	86.7	87.9	89.3	90.6	92.1	93.6	95.0	96.5	97.1
100°	112.3	113.0	113.8	114.5	115.2	116.4	118.0	119.5	121.2	122.8	123.1
102.5°	141.9	142.2	142.4	142.8	143.0	143.9	145.4	146.8	148.3	149.7	150.3
105°	187.0	187.2	187.4	187.5	187.7	188.1	188.9	189.6	190.3	191.0	191.5
107.5°	234.3	234.6	234.7	235.0	235.2	235.4	235.4	235.6	235.7	235.8	236.3
110°	266.4	266.8	267.1	267.5	267.8	267.9	267.8	267.6	267.4	267.2	266.9



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.8	299.9	300.0	300.0	300.1	300.0	299.7	299.4	299.0	298.7	298.7
115°	349.9	349.9	349.9	349.9	349.9	349.7	349.4	349.0	348.6	348.3	348.1
117.5°	397.1	397.2	397.4	397.5	397.7	397.6	397.4	397.1	396.9	396.6	396.0
120°	428.6	429.3	430.0	430.7	431.4	431.5	430.9	430.4	429.9	429.4	428.5
122.5°	461.3	461.6	461.8	462.2	462.4	462.5	462.2	461.9	461.7	461.4	460.8
125°	509.6	509.6	509.6	509.6	509.6	509.5	509.3	509.1	509.0	508.8	508.4
127.5°	553.4	554.0	554.4	555.0	555.6	555.7	555.4	555.1	554.8	554.5	554.2
130°	584.2	584.8	585.3	585.8	586.4	586.6	586.6	586.6	586.6	586.6	586.3
132.5°	615.7	616.1	616.5	616.9	617.3	617.3	617.3	617.1	617.0	616.8	616.5
135°	657.3	658.3	659.4	660.4	661.6	662.1	662.1	662.1	662.1	662.1	661.7
137.5°	702.5	703.0	703.5	704.0	704.5	704.9	705.2	705.5	705.8	706.1	705.6
140°	732.7	733.1	733.4	733.8	734.1	734.3	734.3	734.3	734.3	734.3	734.1
142.5°	760.3	760.7	761.0	761.4	761.8	761.8	761.7	761.5	761.4	761.3	761.2
145°	798.5	799.2	799.9	800.7	801.4	801.8	802.0	802.2	802.3	802.5	802.3
147.5°	836.4	837.3	838.1	838.9	839.8	840.2	840.0	839.9	839.7	839.6	839.5
150°	859.5	860.2	860.9	861.7	862.4	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	881.3	881.8	882.2	882.6	883.0	883.3	883.4	883.6	883.8	883.9	884.3
155°	914.9	914.9	914.9	914.9	914.9	914.8	914.6	914.4	914.3	914.1	914.8
157.5°	943.1	942.8	942.5	942.1	941.8	941.7	941.6	941.6	941.5	941.5	942.1
160°	959.8	959.6	959.4	959.3	959.1	958.9	958.7	958.5	958.4	958.2	958.7
162.5°	975.2	974.8	974.3	973.8	973.4	973.0	972.9	972.7	972.5	972.3	973.3
165°	995.9	995.4	994.8	994.3	993.8	993.3	993.0	992.6	992.3	991.9	993.0
167.5°	1011.8	1011.1	1010.3	1009.6	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6
170°	1020.8	1019.9	1019.0	1018.1	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7
172.5°	1027.2	1026.4	1025.7	1025.0	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2
175°	1036.0	1035.1	1034.3	1033.4	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5
177.5°	1038.9	1038.2	1037.5	1036.8	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	15.8	15.8	15.8	16.0	16.3	16.6	16.8	17.1
90°	19.8	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	33.0	33.7	34.4	34.8	35.0	35.2	35.4	35.6
95°	62.0	62.6	63.1	63.4	63.4	63.4	63.4	63.4
97.5°	97.8	98.4	99.0	99.3	99.3	99.3	99.3	99.3
100°	123.5	123.8	124.2	124.4	124.4	124.4	124.4	124.4
102.5°	150.8	151.2	151.8	152.1	152.2	152.3	152.5	152.7
105°	192.1	192.6	193.1	193.7	194.2	194.7	195.3	195.8
107.5°	236.8	237.3	237.8	238.0	238.0	238.0	237.9	237.9
110°	266.5	266.2	265.8	265.9	266.4	267.0	267.5	268.1



TEST NUMBER: P333086-927

CATALOG NUMBER: S124RDIW-S1020D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	298.6	298.5	298.4	298.4	298.6	298.7	298.7	298.9
115°	347.9	347.8	347.6	347.4	347.2	347.1	346.9	346.7
117.5°	395.4	394.7	394.2	393.7	393.3	393.0	392.6	392.3
120°	427.5	426.7	425.8	425.5	425.9	426.2	426.6	426.9
122.5°	460.3	459.6	459.0	458.4	457.7	457.1	456.5	455.8
125°	508.1	507.7	507.4	507.0	506.7	506.3	506.0	505.6
127.5°	553.8	553.5	553.1	552.8	552.5	552.2	551.9	551.7
130°	585.9	585.6	585.2	584.7	584.0	583.3	582.6	581.9
132.5°	616.1	615.8	615.4	615.1	614.8	614.5	614.2	613.9
135°	661.4	661.0	660.7	660.2	659.7	659.1	658.6	658.1
137.5°	705.1	704.6	704.2	704.0	704.1	704.3	704.3	704.4
140°	734.0	733.8	733.6	733.4	733.2	733.1	732.8	732.7
142.5°	761.2	761.1	761.1	761.0	761.0	761.0	761.0	761.0
145°	802.2	802.0	801.8	801.5	800.9	800.3	799.9	799.3
147.5°	839.3	839.2	839.0	838.8	838.7	838.5	838.3	838.1
150°	862.7	862.7	862.7	862.6	862.4	862.3	862.1	861.9
152.5°	884.7	885.2	885.6	885.6	885.1	884.6	884.2	883.8
155°	915.5	916.2	917.0	917.0	916.2	915.5	914.8	914.1
157.5°	942.6	943.1	943.6	943.6	943.0	942.4	941.8	941.2
160°	959.3	959.8	960.4	960.1	959.3	958.4	957.5	956.6
162.5°	974.2	975.2	976.2	976.2	975.3	974.5	973.5	972.6
165°	994.0	995.1	996.2	996.3	995.6	994.9	994.2	993.5
167.5°	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.4
170°	1019.7	1020.8	1021.8	1021.8	1020.6	1019.3	1018.0	1016.8
172.5°	1026.4	1027.6	1028.9	1028.8	1027.6	1026.4	1025.1	1023.8
175°	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3
177.5°	1037.8	1038.7	1039.7	1039.7	1038.5	1037.4	1036.3	1035.1
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7

(END OF REPORT)