

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332481-840

Luminaire Tested: **S123RDIW-S1165D1030U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332481-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8034.1 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	66	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23	20
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	2.3
10°-20°	511.4	6.4
20°-30°	736.4	9.2
30°-40°	829.4	10.3
40°-50°	793.5	9.9
50°-60°	649.8	8.1
60°-70°	438.4	5.5
70°-80°	220.6	2.7
80°-90°	62.2	0.8
90°-100°	84.9	1.1
100°-110°	254.0	3.2
110°-120°	431.9	5.4
120°-130°	568.1	7.1
130°-140°	638.6	7.9
140°-150°	627.7	7.8
150°-160°	528.4	6.6
160°-170°	351.8	4.4
170°-180°	123.2	1.5
0°-30°	1431.6	17.8
0°-40°	2261.0	28.1
0°-60°	3704.3	46.1
0°-90°	4425.5	55.1
90°-120°	770.8	9.6
90°-150°	2605.2	32.4
90°-180°	3609.0	44.9
0°-180°	8034.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	11	24	29	31	8
95°	60	68	76	80	80	68
105°	230	233	242	242	244	247
115°	435	438	436	437	436	430
125°	636	639	637	633	629	567
135°	826	831	831	827	825	636
145°	1002	1004	1007	1006	1002	625
155°	1147	1147	1148	1151	1145	528
165°	1249	1246	1246	1252	1245	352
175°	1299	1296	1295	1301	1294	123
180°	1302	1302	1302	1302	1302	



TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.7	28.1	25.3	22.7	20.1	19.1	19.7	20.2	20.8	21.4	21.3
90°	1.0	3.3	5.6	7.9	10.1	12.7	15.7	18.7	21.6	24.5	25.4
92.5°	24.7	26.3	27.9	29.4	30.9	32.5	34.2	36.0	37.6	39.3	40.0
95°	60.4	61.9	63.5	65.1	66.8	68.5	70.3	72.1	73.9	75.7	76.6
97.5°	107.2	108.4	109.6	110.8	112.0	113.2	114.5	115.8	117.1	118.5	119.6
100°	139.2	140.5	141.9	143.2	144.6	145.8	147.0	148.1	149.3	150.4	151.1
102.5°	176.0	176.8	177.6	178.4	179.3	180.4	181.9	183.4	184.9	186.4	187.1
105°	230.2	230.7	231.2	231.6	232.1	233.3	235.3	237.3	239.4	241.5	241.5
107.5°	293.3	293.5	293.8	294.1	294.3	294.9	295.7	296.5	297.3	298.1	298.8
110°	332.5	333.0	333.5	333.9	334.4	334.8	335.3	335.7	336.2	336.6	337.5



TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.4	373.8	374.0	374.3	374.6	374.7	374.8	374.9	375.0	375.1	376.2
115°	434.8	435.5	436.2	436.9	437.6	437.7	437.2	436.8	436.3	435.9	436.1
117.5°	496.7	497.1	497.6	498.0	498.5	498.4	497.8	497.2	496.6	496.0	495.9
120°	535.1	536.4	537.9	539.2	540.6	540.7	539.5	538.4	537.2	536.1	535.8
122.5°	575.2	576.2	577.2	578.1	579.2	579.4	578.9	578.2	577.6	577.0	576.4
125°	636.4	637.0	637.7	638.4	639.1	639.2	638.7	638.3	637.8	637.4	636.5
127.5°	692.9	694.3	695.8	697.2	698.6	699.1	698.6	698.1	697.6	697.1	695.9
130°	730.5	732.4	734.2	736.0	737.8	738.3	737.7	737.0	736.3	735.6	734.7
132.5°	768.1	769.9	771.7	773.7	775.5	776.1	775.6	775.1	774.6	774.1	773.0
135°	825.7	827.0	828.4	829.7	831.1	831.6	831.4	831.2	831.0	830.7	829.8
137.5°	878.9	880.0	881.1	882.2	883.4	884.2	884.8	885.4	886.1	886.7	885.7
140°	915.6	916.9	918.0	919.1	920.2	920.9	921.1	921.4	921.6	921.8	921.6
142.5°	949.3	950.4	951.5	952.6	953.8	954.5	954.9	955.3	955.8	956.2	955.9
145°	1001.6	1002.1	1002.5	1003.0	1003.4	1004.0	1004.7	1005.4	1006.0	1006.7	1006.5
147.5°	1047.4	1048.2	1049.0	1050.0	1050.8	1051.5	1052.1	1052.8	1053.4	1054.0	1054.0
150°	1079.3	1079.8	1080.3	1080.8	1081.2	1081.7	1082.1	1082.6	1083.0	1083.5	1083.5
152.5°	1105.6	1106.2	1106.8	1107.5	1108.1	1108.5	1108.8	1109.1	1109.4	1109.6	1110.0
155°	1146.9	1146.9	1146.9	1146.9	1146.9	1147.0	1147.2	1147.5	1147.7	1147.9	1148.8
157.5°	1182.1	1181.8	1181.5	1181.2	1181.0	1180.9	1181.1	1181.3	1181.5	1181.6	1182.7
160°	1204.2	1203.8	1203.3	1202.9	1202.3	1202.1	1202.1	1202.1	1202.1	1202.1	1203.3
162.5°	1223.9	1223.2	1222.5	1221.9	1221.3	1221.0	1221.2	1221.4	1221.6	1221.8	1222.9
165°	1249.2	1248.5	1247.9	1247.2	1246.5	1246.2	1246.2	1246.2	1246.2	1246.2	1247.5
167.5°	1269.5	1268.6	1267.7	1266.8	1265.9	1265.5	1265.7	1265.9	1266.1	1266.2	1267.6
170°	1280.9	1280.0	1279.1	1278.2	1277.3	1276.9	1276.9	1276.9	1276.9	1276.9	1278.4
172.5°	1289.9	1289.0	1288.1	1287.2	1286.3	1285.9	1285.9	1285.9	1285.9	1285.9	1287.3
175°	1299.4	1298.5	1297.6	1296.7	1295.8	1295.3	1295.3	1295.3	1295.3	1295.3	1296.7
177.5°	1303.2	1302.5	1301.8	1301.0	1300.3	1300.0	1300.0	1300.0	1300.0	1300.0	1301.0
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4



TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	21.2	21.1	21.0	20.9	20.7	20.5	20.3	20.1
90°	26.4	27.3	28.2	28.9	29.3	29.8	30.2	30.7
92.5°	40.7	41.5	42.2	42.4	42.1	41.9	41.6	41.3
95°	77.6	78.5	79.4	79.8	79.8	79.8	79.8	79.8
97.5°	120.6	121.6	122.7	123.1	123.0	123.0	122.9	122.8
100°	151.8	152.5	153.1	153.7	154.1	154.6	155.0	155.5
102.5°	187.7	188.4	189.1	189.5	189.3	189.2	189.1	189.0
105°	241.5	241.5	241.5	241.7	242.2	242.6	243.1	243.5
107.5°	299.6	300.3	301.0	301.2	301.0	300.7	300.4	300.1
110°	338.4	339.3	340.2	340.4	340.0	339.5	339.1	338.6





TEST NUMBER: P332481-840

CATALOG NUMBER: S123RDIW-S1165D1030U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	377.3	378.3	379.4	379.9	379.8	379.7	379.7	379.6
115°	436.3	436.6	436.8	436.8	436.6	436.3	436.1	435.9
117.5°	495.9	495.8	495.8	495.4	494.8	494.2	493.5	492.9
120°	535.6	535.4	535.2	534.8	534.4	533.9	533.5	533.0
122.5°	575.8	575.2	574.7	574.0	573.4	572.8	572.2	571.5
125°	635.6	634.7	633.8	632.9	632.0	631.1	630.2	629.2
127.5°	694.6	693.4	692.1	690.8	689.8	688.8	687.7	686.7
130°	733.8	732.9	732.0	730.7	729.1	727.5	726.0	724.4
132.5°	771.9	770.8	769.7	768.6	767.3	766.1	764.9	763.7
135°	828.9	828.0	827.1	826.5	826.0	825.6	825.1	824.7
137.5°	884.7	883.7	882.8	881.9	881.0	880.2	879.3	878.5
140°	921.4	921.1	920.9	920.0	918.4	916.9	915.2	913.6
142.5°	955.7	955.5	955.3	954.5	953.3	952.1	950.9	949.7
145°	1006.3	1006.0	1005.8	1005.2	1004.3	1003.4	1002.5	1001.6
147.5°	1054.0	1054.0	1054.0	1053.3	1052.0	1050.6	1049.2	1047.8
150°	1083.5	1083.5	1083.5	1082.8	1081.5	1080.1	1078.7	1077.3
152.5°	1110.3	1110.8	1111.2	1110.8	1109.5	1108.3	1107.1	1106.0
155°	1149.7	1150.6	1151.5	1151.2	1149.6	1148.0	1146.5	1144.9
157.5°	1183.6	1184.6	1185.5	1185.4	1184.1	1182.9	1181.5	1180.2
160°	1204.5	1205.6	1206.7	1206.8	1205.9	1205.0	1204.1	1203.2
162.5°	1224.1	1225.2	1226.4	1226.2	1224.8	1223.2	1221.8	1220.3
165°	1248.9	1250.2	1251.6	1251.5	1249.9	1248.3	1246.7	1245.2
167.5°	1269.0	1270.4	1271.8	1271.8	1270.4	1269.0	1267.6	1266.2
170°	1280.0	1281.6	1283.2	1283.2	1281.6	1280.0	1278.4	1276.9
172.5°	1288.7	1290.1	1291.5	1291.4	1289.8	1288.2	1286.6	1285.1
175°	1298.0	1299.4	1300.7	1300.6	1299.0	1297.4	1295.9	1294.2
177.5°	1302.1	1303.2	1304.3	1304.2	1302.9	1301.7	1300.4	1299.2
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4

(END OF REPORT)