

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333094-927

Luminaire Tested: **S124RDIW-S1020D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333094-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7594.5 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66		57	55	54		45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55		50	48	45		40	38	36	31
3	80	71	64	58	73	66	59	54	55	50	46		45	41	39		35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40		40	36	33		32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34		36	32	29		29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30		32	28	25		26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26		30	26	23		24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24		27	23	20		22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21		25	21	18		20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19		23	19	16		19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	1.8
10°-20°	374.7	4.9
20°-30°	541.1	7.1
30°-40°	613.3	8.1
40°-50°	592.3	7.8
50°-60°	492.5	6.5
60°-70°	340.1	4.5
70°-80°	172.4	2.3
80°-90°	48.8	0.6
90°-100°	101.9	1.3
100°-110°	301.8	4.0
110°-120°	512.2	6.7
120°-130°	675.4	8.9
130°-140°	758.5	10.0
140°-150°	745.3	9.8
150°-160°	626.9	8.3
160°-170°	417.1	5.5
170°-180°	146.1	1.9
0°-30°	1050.1	13.8
0°-40°	1663.5	21.9
0°-60°	2748.2	36.2
0°-90°	3309.5	43.6
90°-120°	915.8	12.1
90°-150°	3095.0	40.8
90°-180°	4285.0	56.4
0°-180°	7594.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	4	17	26	33	36	7
95°	72	82	91	94	94	80
105°	278	280	284	288	291	295
115°	521	521	518	517	516	513
125°	758	758	757	755	752	676
135°	978	985	986	983	980	757
145°	1188	1193	1194	1193	1190	743
155°	1362	1362	1360	1365	1360	626
165°	1482	1479	1476	1483	1479	418
175°	1542	1536	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.8	19.9	18.9	18.0	17.0	16.6	16.8	17.0	17.3	17.5	17.7
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	25.6	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2
95°	71.7	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6
97.5°	125.2	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5
100°	167.2	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3
102.5°	211.2	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6
105°	278.3	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1
107.5°	348.8	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6
110°	396.6	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2



TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5
115°	520.8	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2
117.5°	591.0	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4
120°	637.9	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7
122.5°	686.6	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0
125°	758.5	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8
127.5°	823.7	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8
130°	869.6	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7
132.5°	916.4	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6
135°	978.3	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9
137.5°	1045.7	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2
140°	1090.6	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7
142.5°	1131.6	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1
145°	1188.5	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1244.9	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4
150°	1279.3	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1311.8	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2
155°	1361.7	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6
157.5°	1403.7	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2
160°	1428.6	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0
162.5°	1451.5	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7
165°	1482.3	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0
167.5°	1506.0	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8
170°	1519.4	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2
172.5°	1528.9	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0
175°	1542.1	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8
177.5°	1546.3	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	17.7	17.9	18.0	18.2	18.5	18.9	19.2	19.4
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	49.2	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	92.4	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	145.5	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	183.8	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	224.3	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	285.9	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	352.4	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.7	396.2	395.6	395.8	396.6	397.4	398.2	398.9





TEST NUMBER: P333094-927

CATALOG NUMBER: S124RDIW-S1020D1560U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	444.3	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.8	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	588.5	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	636.4	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	685.0	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	756.2	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	824.3	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	872.1	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	917.0	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	984.4	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1049.6	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.4	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1133.0	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1194.0	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.3	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1316.8	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.0	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1427.8	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1450.1	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1479.6	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1504.4	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1517.8	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1527.8	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1544.6	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)