

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333081-927

Luminaire Tested: **S124RDIW-S1020D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333081-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5739.1 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	88	88	88		75	75	75		63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73		66	65	63		56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61		59	56	53		50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51		52	48	45		44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44		47	42	39		40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38		42	38	34		36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33		38	33	30		33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30		35	30	27		30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26		32	27	24		28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24		29	25	22		26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22		27	23	20		24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	2.3
10°-20°	374.7	6.5
20°-30°	541.1	9.4
30°-40°	613.3	10.7
40°-50°	592.3	10.3
50°-60°	492.5	8.6
60°-70°	340.1	5.9
70°-80°	172.4	3.0
80°-90°	46.5	0.8
90°-100°	26.9	0.5
100°-110°	171.5	3.0
110°-120°	328.0	5.7
120°-130°	416.3	7.3
130°-140°	445.5	7.8
140°-150°	416.6	7.3
150°-160°	335.9	5.9
160°-170°	216.7	3.8
170°-180°	74.7	1.3
0°-30°	1050.1	18.3
0°-40°	1663.5	29.0
0°-60°	2748.2	47.9
0°-90°	3307.2	57.6
90°-120°	526.3	9.2
90°-150°	1804.7	31.4
90°-180°	2432.0	42.4
0°-180°	5739.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	2	8	13	16	18	4
95°	32	14	13	16	17	42
105°	177	180	184	187	168	185
115°	330	332	332	333	333	325
125°	464	467	466	467	468	415
135°	576	576	578	579	580	444
145°	664	666	666	667	668	415
155°	729	729	727	729	728	336
165°	769	766	766	770	765	217
175°	786	783	783	788	782	75
180°	786	786	786	786	786	



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.5	19.3	18.0	16.7	15.4	14.8	14.8	14.8	14.8	14.9	14.8
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	7.4	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2
95°	32.3	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7
97.5°	68.7	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6
100°	96.4	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7
102.5°	127.5	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7
105°	177.0	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7
107.5°	223.0	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3
110°	254.1	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.2	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9
115°	330.5	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9
117.5°	372.2	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8
120°	400.4	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5
122.5°	426.8	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2
125°	464.5	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1
127.5°	500.3	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5
130°	523.3	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9
132.5°	544.5	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0
135°	576.2	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3
137.5°	604.4	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4
140°	622.7	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4
142.5°	639.2	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3
145°	664.5	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4
147.5°	684.6	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4
150°	699.2	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9
152.5°	711.4	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4
155°	728.6	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9
157.5°	743.1	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3
160°	751.5	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0
162.5°	759.0	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0
165°	768.6	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7
167.5°	776.1	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8
170°	780.3	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4
172.5°	783.2	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3
175°	786.2	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4
177.5°	787.6	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	14.8	14.7	14.7	14.8	15.1	15.3	15.5	15.8
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.0	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	14.5	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.7	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	21.5	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	76.8	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	185.8	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	229.9	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	259.8	260.1	260.4	260.7	261.1	261.5	261.9	262.3



TEST NUMBER: P333081-927

CATALOG NUMBER: S124RDIW-S1020D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.8	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.2	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.4	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.5	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	525.9	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.0	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.5	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	607.8	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	625.8	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.6	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.5	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.5	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.6	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	728.4	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	757.8	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	767.7	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	775.0	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	779.4	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	782.3	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	785.6	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.0	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)