

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332484-840

Luminaire Tested: **S123RDIW-S1165D1320U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332484-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9756.5 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28				
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	1.9
10°-20°	511.4	5.2
20°-30°	736.4	7.5
30°-40°	829.4	8.5
40°-50°	793.5	8.1
50°-60°	649.8	6.7
60°-70°	438.4	4.5
70°-80°	220.6	2.3
80°-90°	63.2	0.6
90°-100°	63.5	0.7
100°-110°	302.9	3.1
110°-120°	727.5	7.5
120°-130°	926.3	9.5
130°-140°	989.8	10.1
140°-150°	925.5	9.5
150°-160°	746.6	7.7
160°-170°	481.8	4.9
170°-180°	166.1	1.7
0°-30°	1431.6	14.7
0°-40°	2261.0	23.2
0°-60°	3704.3	38.0
0°-90°	4426.6	45.4
90°-120°	1093.9	11.2
90°-150°	3935.5	40.3
90°-180°	5330.0	54.6
0°-180°	9756.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	14	31	36	39	8
95°	79	30	40	49	49	98
105°	387	394	284	67	57	410
115°	726	734	745	758	764	716
125°	1023	1033	1039	1041	1044	913
135°	1274	1282	1287	1290	1287	980
145°	1470	1479	1482	1484	1484	920
155°	1619	1617	1618	1624	1617	746
165°	1708	1704	1702	1712	1704	482
175°	1748	1742	1743	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.7	28.2	25.7	23.1	20.6	19.7	20.5	21.2	22.0	22.7	22.7
90°	1.3	4.1	7.1	10.0	12.8	16.2	19.9	23.6	27.4	31.2	32.3
92.5°	24.1	23.3	22.5	21.7	20.9	21.9	24.7	27.6	30.4	33.2	35.0
95°	79.2	67.4	55.5	43.7	31.9	27.6	30.7	33.9	37.1	40.3	42.3
97.5°	159.2	153.9	148.6	143.3	137.9	124.9	104.1	83.4	62.6	41.8	44.1
100°	219.4	225.2	231.0	236.7	242.6	222.9	177.9	132.9	87.9	42.8	45.1
102.5°	288.0	292.2	296.3	300.4	304.7	282.2	233.0	183.8	134.6	85.4	78.3
105°	387.0	390.1	393.3	396.5	399.6	388.3	362.2	336.3	310.3	284.4	233.3
107.5°	491.4	493.9	496.4	499.0	501.5	504.8	509.0	513.0	517.2	521.2	483.7
110°	561.0	563.3	565.5	567.8	570.2	572.9	576.1	579.3	582.5	585.6	576.1



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.5	631.6	633.7	635.7	638.3	641.6	644.7	647.9	651.1	651.3
115°	725.9	727.6	729.3	731.0	732.8	735.0	737.5	740.1	742.8	745.4	748.2
117.5°	821.2	823.3	825.5	827.6	829.7	831.4	832.7	834.1	835.5	836.8	839.1
120°	880.4	883.0	885.6	888.2	890.8	892.5	893.3	894.2	895.1	896.0	898.3
122.5°	940.7	942.8	944.9	947.1	949.2	950.8	951.9	953.0	954.1	955.2	956.8
125°	1023.2	1025.5	1027.8	1030.2	1032.5	1034.2	1035.3	1036.5	1037.6	1038.8	1039.4
127.5°	1103.2	1105.5	1107.8	1110.1	1112.5	1114.3	1115.7	1117.1	1118.4	1119.8	1120.7
130°	1153.1	1155.4	1157.7	1160.0	1162.4	1164.1	1165.2	1166.4	1167.5	1168.6	1169.8
132.5°	1200.8	1203.2	1205.5	1207.8	1210.1	1211.7	1212.6	1213.6	1214.5	1215.4	1216.6
135°	1273.8	1275.6	1277.3	1279.0	1280.8	1282.2	1283.3	1284.5	1285.7	1286.9	1287.7
137.5°	1336.2	1338.4	1340.6	1342.7	1344.9	1346.4	1347.0	1347.7	1348.3	1348.9	1350.3
140°	1377.8	1379.5	1381.2	1382.9	1384.6	1385.9	1386.8	1387.7	1388.6	1389.4	1390.6
142.5°	1416.1	1417.9	1419.7	1421.4	1423.1	1424.4	1425.2	1426.1	1426.9	1427.8	1428.8
145°	1470.0	1472.0	1474.0	1476.0	1478.0	1479.3	1479.9	1480.5	1481.1	1481.6	1482.2
147.5°	1520.6	1521.9	1523.2	1524.5	1525.9	1526.8	1527.4	1527.9	1528.5	1529.1	1529.7
150°	1551.8	1552.6	1553.5	1554.3	1555.2	1555.9	1556.5	1557.0	1557.6	1558.2	1558.8
152.5°	1579.7	1580.1	1580.5	1580.9	1581.3	1581.8	1582.2	1582.5	1582.8	1583.2	1584.2
155°	1619.2	1618.7	1618.1	1617.5	1616.9	1616.8	1617.1	1617.4	1617.7	1617.9	1619.4
157.5°	1649.9	1649.8	1649.8	1649.7	1649.6	1649.5	1649.2	1648.9	1648.6	1648.3	1650.0
160°	1668.6	1668.3	1668.0	1667.7	1667.4	1667.2	1666.9	1666.6	1666.3	1666.0	1667.7
162.5°	1686.3	1685.5	1684.8	1683.9	1683.2	1682.7	1682.4	1682.1	1681.8	1681.5	1683.5
165°	1707.6	1706.7	1705.8	1705.0	1704.0	1703.5	1703.2	1702.9	1702.6	1702.3	1704.7
167.5°	1724.1	1723.0	1721.8	1720.7	1719.5	1719.0	1719.0	1719.0	1719.0	1719.0	1721.3
170°	1733.5	1732.3	1731.2	1730.1	1728.9	1728.3	1728.3	1728.3	1728.3	1728.3	1730.6
172.5°	1739.8	1738.4	1737.0	1735.6	1734.2	1733.6	1733.8	1734.1	1734.3	1734.5	1736.9
175°	1747.8	1746.4	1744.9	1743.4	1742.0	1741.4	1741.7	1742.0	1742.3	1742.6	1744.6
177.5°	1749.9	1748.7	1747.6	1746.5	1745.2	1744.8	1745.0	1745.2	1745.5	1745.8	1747.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	22.6	22.6	22.5	22.4	22.2	22.1	21.9	21.7
90°	33.4	34.6	35.7	36.7	37.3	37.8	38.4	39.0
92.5°	37.0	38.8	40.6	41.7	42.1	42.4	42.7	43.1
95°	44.3	46.4	48.4	49.4	49.4	49.4	49.4	49.4
97.5°	46.5	48.8	51.0	52.3	52.6	52.9	53.2	53.5
100°	47.5	49.8	52.1	53.4	53.6	53.9	54.2	54.5
102.5°	71.1	63.9	56.9	53.5	54.0	54.5	55.0	55.5
105°	182.2	131.2	80.1	54.8	55.4	55.9	56.6	57.2
107.5°	446.4	408.9	371.4	333.5	295.0	256.4	217.9	179.5
110°	566.5	557.0	547.5	522.1	480.9	439.6	398.4	357.1



TEST NUMBER: P332484-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	651.5	651.6	651.8	647.5	638.7	630.1	621.4	612.7
115°	751.1	754.0	756.9	758.9	760.0	761.2	762.3	763.6
117.5°	841.4	843.6	846.0	847.3	847.5	847.7	848.0	848.2
120°	900.6	902.9	905.2	906.4	906.4	906.4	906.4	906.4
122.5°	958.5	960.1	961.7	962.6	962.8	963.0	963.3	963.5
125°	1040.0	1040.6	1041.1	1041.7	1042.3	1042.9	1043.4	1044.0
127.5°	1121.7	1122.6	1123.6	1123.7	1123.2	1122.6	1122.0	1121.4
130°	1170.9	1172.2	1173.3	1173.6	1173.0	1172.5	1171.8	1171.2
132.5°	1217.7	1218.9	1220.0	1220.2	1219.4	1218.6	1217.8	1217.0
135°	1288.6	1289.4	1290.3	1290.3	1289.4	1288.6	1287.7	1286.9
137.5°	1351.7	1353.0	1354.4	1354.8	1354.2	1353.7	1353.1	1352.5
140°	1391.7	1392.9	1394.0	1394.3	1393.7	1393.1	1392.6	1392.0
142.5°	1429.7	1430.6	1431.6	1431.6	1430.8	1430.0	1429.2	1428.4
145°	1482.8	1483.3	1483.9	1484.2	1484.2	1484.2	1484.2	1484.2
147.5°	1530.2	1530.9	1531.5	1531.1	1529.7	1528.4	1527.1	1525.7
150°	1559.3	1559.9	1560.5	1560.3	1559.5	1558.6	1557.8	1556.9
152.5°	1585.2	1586.3	1587.3	1587.2	1585.8	1584.5	1583.2	1581.9
155°	1620.8	1622.2	1623.8	1623.6	1621.8	1620.1	1618.4	1616.7
157.5°	1651.8	1653.6	1655.3	1655.0	1652.7	1650.5	1648.2	1646.0
160°	1669.4	1671.2	1672.9	1672.7	1670.7	1668.7	1666.7	1664.7
162.5°	1685.5	1687.5	1689.4	1689.5	1687.7	1686.0	1684.2	1682.3
165°	1707.0	1709.3	1711.6	1711.7	1709.7	1707.7	1705.7	1703.6
167.5°	1723.6	1725.9	1728.2	1728.2	1725.9	1723.6	1721.3	1719.0
170°	1732.9	1735.3	1737.6	1737.6	1735.3	1732.9	1730.6	1728.3
172.5°	1739.2	1741.5	1743.8	1743.6	1741.1	1738.6	1736.1	1733.5
175°	1746.7	1748.7	1750.7	1750.5	1748.3	1746.0	1743.6	1741.3
177.5°	1749.4	1751.3	1753.1	1752.9	1750.6	1748.3	1746.0	1743.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8

(END OF REPORT)